



Installation Guide

Priority Valve

Type OLS 40 and OLS 80



11080596



P301 262

11080596

M	Max. tilspændingsmoment Max. tightening torque Max Anzugsmoment Couple de serrage max.								
	Tilslutning Connection Anschluß Raccordement			Tilslutning Connection Anschluß Raccordement			Tilslutning Connection Anschluß Raccordement		
	P/EF			CF			PP/LS		
Forskrning Screwed connection Verschraubung Raccord	1/2 RG 1/2 BSP.F R 1/2 G 1/2	7/8-14 UNF	M22 × 1.5	1/2 RG 1/2 BSP.F R 1/2 G 1/2	3/4-16 UNF	M18 × 1.5	1/4 RG 1/4 BSP.F R 1/4 G 1/4	7/16-20 UNF	M12 × 1.5
med kobberskive with copper washer mit Kupferscheibe avec rondelle en cuivre	55 Nm [490 lbf·in]		65 Nm [575 lbf·in]	55 Nm [490 lbf·in]		55 Nm [490 lbf·in]	35 Nm [310 lbf·in]		20 Nm [180 lbf·in]
med aluminiumsskive with aluminium washer mit Aluminiumscheibe avec rondelle en aluminium	80 Nm [710 lbf·in]		80 Nm [710 lbf·in]	80 Nm [710 lbf·in]		70 Nm [620 lbf·in]	35 Nm [310 lbf·in]		30 Nm [265 lbf·in]
med skærekant with cutting edge mit Dichtkanta tranchant	100 Nm [885 lbf·in]		100 Nm [885 lbf·in]	100 Nm [885 lbf·in]		80 Nm [710 lbf·in]	35 Nm [310 lbf·in]		30 Nm [265 lbf·in]
med O-ring with O-ring mit O-ring avec joint torique	55 Nm [490 lbf·in]	90 Nm [800 lbf·in]	60 Nm [530 lbf·in]	55 Nm [490 lbf·in]	60 Nm [530 lbf·in]	50 Nm [440 lbf·in]	35 Nm [310 lbf·in]	20 Nm [180 lbf·in]	25 Nm [220 lbf·in]