

Data Sheet

ACCPBT temperature sensors



The ACCPBT sensors can be used for surface mounting or insertable temperature monitoring in conjunction with Danfoss controllers in the following applications:

- Residential HVAC
- Commercial HVAC
- Commercial refrigeration
- Food retail refrigeration
- Transport refrigeration
- HACCP applications
- Industrial refrigeration

The ACCPBT sensors comes adjusted and complies with tolerance requirements according to EN 60751, class B for the Pt1000 elements and the NTC elements has 1% Beta value tolerance.

Features

Table 1: Product features

ACCPBT code	Sensor element	Temperature range	Cable length	Cable type	IP - class
080G0202	NTC 10K 1% BETA 3435	-50 to +110°C	3.0 m	Black thermoplastic elastomer	68
080G0205			1.5 m		
080G0206			3.0 m		
080G0207			6.0 m		
080G0209	PT1000, class B	-50 to +110°C	1.5 m	Blue thermoplastic elastomer	68
080G0210			6.0 m		
080G0212	NTC 100 k 1% BETA 4240	-50 to +200°C	1.5 m	Blue silicone rubber	67

Table 2: Sensor cap diameter Ø6 mm

Type	Cable	Sensor cap length	Code no.	Packing Qty.
ACCPBT NTC 10K Black elastomer cable	3.0 m	20 mm	080G0202	10
	1.5 m	40 mm	080G0205	
	3.0 m		080G0206	
	6.0 m		080G0207	
ACCPBT Pt1000 Blue elastomer cable	1.5 m	40 mm	080G0209	10
	3.5 m		080G0210	
ACCPBT NTC 100K Blue silicone rubber cable	1.5 m	40 mm	080G0212	10

Product specification


Technical Data

Table 3: Technical data

ACCPBT code number	080G0209 & 080G2010	080G02-02, 05, 06, 07	080G0212
Nominal resistance	1000 ohm at 0 °C	10K ohm at 25 °C	100K ohm at 25 °C
Measuring accuracy	Class B, EN 60751	BETA 3435, 1%	BETA 4240, 1%
Temperature range	-50 – 110 °C	-50 – 110 °C	-50 – 200 °C
Cable material	TPE: 2 x 0.25 mm ² , Ø3.3 mm	TPE: 2 x 0.25 mm ² , Ø3.3 mm	Silicone: 2 x 0.25 mm ² , Ø4,6 mm
Sensor cap Ø6	AISI 304	AISI 304	AISI 304
Enclosure	IP68	IP68	IP67

Dimensions

Figure 1: Dimensions



Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.