

ENGINEERING
TOMORROW



Danfoss | Semi-welded plate heat exchanger


More than a heat exchanger

The SONDEX® series of semi-welded plate heat exchangers is optimized for industrial applications and is the prime choice for challenging applications that involve aggressive media and high pressure.

With Danfoss, you get much more than just a high-quality heat exchanger. You also get all the benefits from partnering with a world-leading supplier in a wide range of industries. All to help professionals achieve and maintain a safer and more energy efficient operation.


Safe

operation with
challenging and
aggressive media,
high temperatures,
and pressure



heatexchangers.danfoss.com

SONDEX®



Handle demanding media with peace of mind

The semi-welded plate heat exchangers are very versatile which means that they can easily be configured for use in different industries and applications that involve challenging media, such as chemical processing.

We customize each heat exchanger according to your specifications and offer durable solutions designed to withstand extreme conditions and minimize the risks of operation.

You can safely operate with hazardous or aggressive media, high pressure, or extreme temperatures that are unsuitable for regular fully gasketed heat exchangers. We design to give you peace of mind.

Suitable media and processes



Clean liquids



Challenging/
aggressive media



Liquid-liquid




Steam/vapor/
gas-liquid




Condensation
of vapors


Typical/common industries




Beverage




Chemical




Mining




Oil & gas



Petrochemical



Pulp & Paper



Sugar


Semi-welded. Full efficiency.

Our range of semi-welded plate heat exchangers has been carefully designed and upgraded to ensure optimal performance, maximum safety and easy maintenance, including a new and highly efficient plate design, a reinforced and double-barrier gasket system, and an improved frame design.

The range of semi-welded plate heat exchangers comes with several upgrades that not only add more value to your application but also to your business.


New plate design delivers excellent heat transfer capabilities

- Improves plate strength and stability thanks to the optimized plate geometry across the entire plate
- Improves thermal performance due to optimized plate geometry supporting high turbulent flow
- Repositioned welding track for improved quality



New gasket system improves plate pack stability

- Ensures high gasket stability and optimal plate alignment due to new gasket and gasket groove design
- Improves sealing effect and prevents gasket-blow out
- Reduces the risk of contamination due to the double gasket barrier that will drain potential leakages outside the plate pack
- Gasket system designed for easy maintenance



Solid frame design eases service and maintenance

- Improves accessibility to the plate pack with the non-corrosive nylon roller that makes it easy to slide the follower along the carrying bar
- Makes the assembly of the heat exchanger fast and safe thanks to fixed bolt heads and lock bushes which prevent the nut and bolt head from rotating when opening and closing the unit




You get **much more** than a **heat exchanger**

Our new range of semi-welded plate heat exchangers is supported by extensive application knowledge. Because finding the right plate heat exchanger to match your application needs requires a lot of expertise.

At Danfoss, we offer you comprehensive knowledge on your applications which, in combination with our high product quality and diversified product range, offers you the optimum conditions to find the best possible solution to match your needs.

And that is why, we are proud to say that you get more than just a plate heat exchanger when working with Danfoss – you get all the benefits from partnering with a world-leading supplier.



Application knowledge

- Turn to Danfoss for application knowledge and product insights for best-fit solution to match your specific application and overall system design requirements
- Optimize safety during design phase by solid layout and correct material selections
- Solutions designed for long-life and sound service and maintenance plan



Diversified product range

- Streamline supplier management by combining high quality valves, controls and heat exchangers from Danfoss
- Increase application efficiency with high quality products and proven designs



Excellent heat transfer capabilities

- High heat transfer coefficient and efficient flow distribution due to optimized plate design/geometry
- High shear-stress capabilities to help prevent fouling and ensure good cleanability of your plate heat exchanger



Reliable design - operational safety

- Re-enforced gasket system provides improved sealing effect and prevents gasket blow-out
- Reduced risk of contamination due to double gasket barrier draining potential leak outside of the plate pack
- Proven and verified design through mechanical and life-time testing

Technical data

Semi-welded plate heat exchangers SW19 – SW202 Range

Product data	Metric	Imperial
Media	Liquids e.g. water, glycol, chemicals, oils, juice.	
Min./Max. working pressure	16/25 barg	150/300 psig
Min./Max. temperature	-20°C/180°C	-4°F/356°F
Frame material	Painted carbon steel (Blue, RAL5010)	
Connection size	DN65 (2½") up to DN500 (20")	
Connection classification	EN1092-1-PN16/25	ANSI B16.5 – Class 150/300
Connections material	Stainless steel and titanium	
Plate material	AISI 304, AISI 316, titanium. Other materials available upon request.	
Plate thickness	0.5 mm Stainless Steel for 16 barg (150 psig) 0.6 and 0.7 mm Stainless steel and titanium for 25 barg (300 psig)	
Gasket	Various grades of NBR HT and EPDM HT, and Viton. Other materials available upon request.	
Ring gasket	Various grades of NBR, EPDM, Chloroprene, Viton, PTFE. Other materials available upon request.	
Design code	EN13445	ASME VIII, Sec. 1

Size	SW19B	SW26A	SW40A	SW54	SW59	SW102	SW122	SW189	SW202
Port, DN (in)	65 (2½)	100 (4)	100 (4)	150 (6)	200 (8)	200 (8)	300 (12)	300 (12)	500 (20)
Height, mm (in)	820 (32)	800 (31)	1208 (48)	1242 (49)	1208 (48)	1746 (69)	1878 (74)	2508 (99)	2400 (94)
Width, mm (in)	304 (12)	378 (15)	378 (15)	502 (20)	664 (26)	664 (26)	868 (34)	868 (34)	1248 (49)

Danfoss genuine spare parts for reliable operation

The availability of reliable spare parts is essential for heat exchanger solutions handling critical processes and utility applications. By using original spare parts, you minimize the risk of unscheduled stoppages due to premature failure of non-original components and parts.

Critical spare parts to service the Danfoss portfolio of semi-welded plate heat exchangers are always at hand when you need them. They include:

- Spare ring and flow gaskets to service or adjust your plate heat exchanger to maintain its performance.
- Spare plate cassettes are available if you need to replace or adjust the number of cassettes for your plate heat exchanger to meet extended or new application requirements.

Accessories:

A range of accessories is available to further complement the safe and efficient operation and functionalities of the Danfoss semi-welded plate heat exchangers.

Insulation jacket:

To prevent outside temperature impact, mounting an insulation jacket around plate heat exchanger can prevent energy loss and increase the efficiency considerably. The Insulation jacket is made from non-flammable mineral wool encased by aluminium plate. Snap locks fittings make assembly and disassembly simple and ensure easy maintenance access.

A wide range of standard sizes are available which are customized to fit the actual size of the plate heat exchanger. There is no bottom cover in the design of the insulation jackets. Custom-made solutions are available upon request.

Drip tray:

Drip trays are used to collect condensed water during defrost or stand-still situations and prevent liquid to flow to the floor. They are available as insulated or drainable versions and made from either stainless or galvanized steel. Standard sizes are fitted to the actual size of the plate heat exchanger.

Spray screen:

For additional operational safety spray screens may be mounted on the plate heat exchanger to improve the protection of personnel and surroundings in the event of a leakage. Spray screens are available in stainless steel AISI 304 and are customized to fit the size of the actual plate heat exchanger.

In-line filter:

In-line filters prevent foreign objects and particles from entering and clogging the plate heat exchanger (e.g. from seawater, sea wheat, sea shells, etc.). It is used to filter the brine and help to prevent particles disrupting the performance of your system. The in-line filter is made from stainless steel (AISI 304) and titanium.

Ratchet spanner:

To ease the opening and closing of the plate heat exchanger Danfoss offers ratchet spanners which are designed to fit the nut size of the plate heat exchangers.

Semi-welded. Fully tested.

All semi-welded plate heat exchangers are fully tested before they leave the Danfoss factory. Because, as dedicated engineers, we are not satisfied until we offer you products that match application needs and meet your highest expectations.

Thermal performance testing

The Danfoss semi-welded plate heat exchangers have a solid and reliable design which has been documented through thermal performance testing and mechanical and life-time tests.

- The thermal performance of the complete semi-welded plate range has been proven and verified on our own full-scale testing facility
- The thermal performance tests have been performed across the entire semi-welded portfolio (i.e. plate sizes and plate patterns), for various plate-pack sizes at various capacities

Mechanical testing

The entire Danfoss semi-welded portfolio including plate and frame designs across various plate and gasket materials has been mechanically tested to document its solid design and durability. The mechanical tests include:

- Strength test according to PED and ASME requirements to document pressure ratings
- Fatigue test running 35.000 pressure-change cycles (from 5-25 bar) to test life-time durability

Cassette testing




To ensure high and consistent product quality every semi-welded plate cassette is helium leak tested to detect holes after pressing the materials and welded cassette tightness.

- Following laser welding, each plate cassette is helium (He) leak tested
- The helium leak testing is a calibrated system meeting Danfoss QA and performance procedures
- This ensures a high level of product quality and helps minimize potential product failure later in the in assembly process

Final product testing

Once assembled, we perform the final product test to ensure that the semi-welded plate heat exchanger lives up to our high Danfoss standards.

- Hydraulic strength test is performed according to specified design codes (PED or ASME)



A partnership based on extensive application knowledge

Working with Danfoss means more. It means that you do not only get highly reliable, efficient, and innovative solutions – you also get a partner that is a world-leading supplier in a wide range of applications.

Our partnership gives you access to a wide range of benefits. From extensive application knowledge to a wide range of solutions and tools.

Do you want to discover more?

Visit heatexchangers.danfoss.com to learn more about our heat exchanger solutions.

Gasketed HEX

Standard plate HEX
Semi-welded plate HEX
Free Flow plate HEX
Sanitary plate HEX
Evaporators
Condensers

Welded HEX


Plate and shell HEX
Spiral HEX

Brazed HEX

Fishbone brazed HEX
Micro Plate™ brazed HEX

Micro channel

Flat condenser
Formed condenser
Slab evaporator
Folded evaporator
Interlaced MCHE
V-coil



Danfoss A/S

Climate Solutions • danfoss.com • heatexchangers.danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.