



**SERIES ARC300**

**ESBE®**  
NO.1 IN HYDRONIC SYSTEM CONTROL


Mtrl.nr: 9814 09 55 • Ritn.nr 8466 vers. A • Rev 1512






Series ARC300

CE

LVD 2006/95/EC valid until April 19th 2016  
LVD 2014/35/EU valid from April 20th 2016  
EMC 2004/108/EC valid until April 19th 2016  
EMC 2014/30/EU valid from April 20th 2016  
RoHS 2011/65/EU




Series ARC300



# Actuator Settings **D**amper Assembly

**D  
1A**





Max working range  
0° – 90°

**D  
1B**

Limiting working range • Clockwise working direction (R/CW)

Example R/CW working range 20°- 70°



ARC368/  
ARC369  
Dip Switch 4





**E  
3**

**D  
1C**

Limiting working range • Counter clockwise working direction (L/CCW)

Min working range  
45° – 45°



Exampel L/CCW working range 35°- 60°





ARC368/  
ARC369  
Dip Switch 4




**E  
3**

**i**



9 – 18 mm







9 – 26 mm

**i****D2****D3**


R/CW =  
Closed (0%) position





L/CCW =  
Open (100%) position

**D4**


D  
5



D  
6



D  
7



D  
8



i

**ARC300**  
Electrical  
Settings

