




**SERIES ARD100/ARD200**



Series ARD100  
Series ARD200

CE  
LVD 2006/95/EC valid until April 19th 2016  
LVD 2014/35/EU valid from April 20th 2016  
EMC 2004/108/EC valid until April 19th 2016  
EMC 2014/30/EU valid from April 20th 2016  
RoHS 2011/65/EU



Series ARD100










Series ARD200

Mtrl.nr: 9814 09 41 • Ritn.nr 8456 vers. A • Rev 1512




**i**  
ARD100/  
ARD200  
Valve  
Assembly  
ARD100/  
ARD200  
Damper  
Assembly



# ARD155/ARD157/ ARD255/ARD257

**E  
2A**

2-point




ARD155/ARD255 = 85...265V AC/DC

ARD157/ARD257 = 19...29V AC/DC




# ARD169/ARD269

**E  
2B**



AC 19...29 V  
DC 19...29 V


**i**



R/CW=Clockwise working direction  
L/CCW=Counter clockwise working direction


# ARD169/ARD269

**E 3a**



=

Y=0 - 10 V DC/0-20mA  
U = 0-10 V DC




=




Y = 2 - 10 V DC/4-20mA  
U = 2 -10 V DC

**E 3b**



=

Current (mA)




=





Voltage (V DC)


**E 3c**



=



=



**E 3d**

Adaption working range

