

Data sheet

Micro Plate Heat Exchanger (MPHE): XB25

Description



Micro Plate Heat Exchangers - a revolutionary technology from Danfoss. Characterized by their unique plate pattern, MPHEs enable heat to be transferred more efficient than any previous model of heat exchangers.

Benefits:

- Energy and cost savings
- Better heat transfer
- Lower pressure loss
- More flexible design
- Longer life time

more on:

MPHE.danfoss.com


XB25 is copper brazed heat exchanger, designed and configured for District Heating, District Cooling and other Heating applications.

Approval:




Pressure Equipment Directive (PED).

Ordering

1-pass heat exchanger **XB25**

Picture	No. of plates, n	Connection	Code No.
	8	Thread G 3/4	004H4324
	10		004H4325
	16		004H4326
	20		004H4327
	26		004H4328
	30		004H4329
	36		004H4330
	40		004H4331
	50		004H4332
	60		004H4333
	66		004H4334

Accessories-**Tailpieces**

Picture	Description	Connection	Code No. ¹⁾
	Solder tailpieces	G 3/4/15 mm	004B2945
		G 3/4/18 mm	004B2946
	Weld-on tailpieces	G 3/4/DN 20	004B2944
	Threaded tailpieces	G 3/4/G 3/4	004B2947
		G 3/4/G 1	004B2953

¹⁾ One set contains 2 tailpieces with union nuts and gaskets

Data sheet

Micro Plate Heat Exchanger (MPHE) XB25

Technical data

Type		Heat exchanger XB25H
Max. working pressure	bar	25
Max. operating temp.	°C	DH 180, DC 100
Min. operating temp.		-196
Flow medium	"DH: Circulation water / glycolic water up to 50% transfer media. DC: ethylene-, propylene-glycolic water, ethanol-water solutions and other suitable heat transfer media. (Please contact your Danfoss representative)."	
Volume / Channel	Ltr	0.059
Connection type	Cylindrical external thread acc. to DIN ISO 228/1	
Connection size	G $\frac{3}{4}$ "	
Weight	kg	0.09 x NoP + 0.99
Materials		
Plate	Stainless steel, EN 1.4404 (AISI 316L)	
Brazing	Copper (Cu); CoResist (Cu+)	

* Available on enquiry

Dimension

Type	Connection	E (mm)
XB25	G $\frac{3}{4}$ " ¹⁾	H: 6.5 + 1.55 x n

n = number of plates
¹⁾ Cylindrical external thread acc. to DIN ISO 228/1

Tailpieces

Picture	Description	Connection	a	b	SW ¹⁾	Code No.
			mm			
	Solder tailpieces	G $\frac{3}{4}$ / 15 mm	15	35	32	004B2945
		G $\frac{3}{4}$ / 18 mm	18	35	32	004B2946
	Weld-on tailpieces	G $\frac{3}{4}$ / DN 20	21.2	35	32	004B2944
	Threaded tailpieces	G $\frac{3}{4}$ / G $\frac{3}{4}$	$\frac{3}{4}$ "	40	32	004B2947
		G $\frac{3}{4}$ / G 1	1"	22	32	004B2953

¹⁾ Union nut, width across flats

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.