

Data Sheet

Semi-hermetic filter drier Types **DCR CO₂**

Danfoss **ELIMINATOR**® filter drier **with replaceable solid core.**
Designed for subcritical and transcritical CO₂ applications



Danfoss ELIMINATOR® filter driers with replaceable solid core, type DCR, are for use in liquid and / or suction lines in CO₂ refrigeration systems.

They offer a high system reliability by design and performance with a high flow rate, in a lightweight shape.

All solid cores have an optimized uniform grain size ensuring effective dirt removal and low pressure drop. The robust solid cores withstand pressure surge and vibration.

Features

- Easy handling - compact design.
- Cartridge design – Ease of serviceability.
- Optimized core plate, inlet and outlet design offers higher flow capacity.

DCR housing and top cover:

- PED approved for PS up to 90 bar/1305 Psig.
- No welded joints – High Product Reliability.
- DCR housing (including core holder) are made entirely of steel and are thus compatible with CO₂.
- 100% leak tested.
- Zinc-chromated steel top covers with drain plug for Liquid evacuation.


Inserts for DCR housing:

- 48 - DM - 100% molecular sieve solid core Provides high moisture adsorption at low and high condensing temperatures.
- 48 - DC - 80% molecular sieve and 20% activated alumina solid core adsorbs moisture and acid in the system.
- 48 - F strainer Retains dirt particles larger than 15 µm.
- 48 - DA - 30% molecular sieve and 70% activated alumina solid core suitable after compressor burnout.
- All solid cores have an optimized uniform grain size ensuring effective dirt removal and low pressure drop. The robust solid cores withstand pressure surge and vibration.

Functions


Danfoss ELIMINATOR® filter driers with replaceable solid core, type DCR protect CO₂ refrigeration, systems from moisture, acids, and solid particles. With these contaminants eliminated, systems are safer from harmful chemical reactions and from abrasive impurities.

Figure 1: DCR CO₂



1	Plug for cover	7	Core
2	Cover Bolts	8	Core plate middle
3	Cover plate & core shaft	9	Core holder assembly
4	Cover gasket	9.a	Wing nut
5	Core plate bottom	10	Housing for 2 cores
6	Core felt gasket	11	Housing for 1 core

Applications




Product Specification

Technical data

Table 1: Technical data

Parameter	Specification
Maximum working pressure	90/1305 bar/psig
Temperature range	- 55 to 100 °C / -67 to 212 F
Housing material	G20Mn5+QT 1.6220 EN10213-3
Cover material	G20Mn5+QT 1.6220 EN10213-3
Gasket material	Graflit-EM
Core holder material	11SMn30 1.0715 EN 10087
M12 Bolt material	A2-70

Indentification



Core selection

Table 2: Core selection

Refrigerant and oil types		DC	DM	DA
Refrigerant	CO ₂ (R744)	Recommended	Recommended	Recommended
	Mineralol AB	Recommended	Recommended	Recommended
Oil	POEor PAG, pure	Recommended	Recommended	Recommended
	POEor PAG, with additives	Not recommended ⁽¹⁾	Recommended	Recommended

⁽¹⁾ DC filter driers cores contain activated alumina, which is a polar material used for acid adsorption. Many oil additives are also polar substances and can be adsorbed by the activated alumina, rendering them useless, and reducing the drier's acid capacity, though this is not harmful to the system.

Dimensions and Weights

Figure 2: Dual core housing with DN connection





Figure 3: Dual core housing with ODF Connection



Semi-hermetic filter drier, type DCR for CO2

Figure 4: Single core housing with DN Connection




Figure 5: Single core housing with ODF Connection




Table 3: Dimension and Weight

Type of DCR	Number of core	Dimension in mm / [in.]							Net Weight Kg / lb
		L	L1	L2	L3	L4	H1	H5	
DCR 04811B	1	275.6 / 10.9	154 / 6.1	250 / 9.8	23.0 / 0.9	23.0 / 0.9	125 / 4.9	35.0 / 1.4	13.8 / 30.4
DCR 04811dB	1	275.6 / 10.9	154 / 6.1	250 / 9.8	-	-	125 / 4.9	32.6 / 1.3	13.8 / 30.4
DCR 04807B	1	275.6 / 10.9	154 / 6.1	250 / 9.8	15.4 / 0.6	15.4 / 0.6	125 / 4.9	22.23 / 0.9	13.8 / 30.4
DCR 04807dB	1	275.6 / 10.9	154 / 6.1	250 / 9.8	-	-	125 / 4.9	18.9 / 0.7	13.8 / 30.4
DCR 09613B	2	412.6 / 16.2	291 / 11.5	400 / 15.7	27.0 / 1.1	27.0 / 1.1	125 / 4.9	42.0 / 1.7	19.0 / 42.0
DCR 09613dB	2	412.6 / 16.2	291 / 11.5	400 / 15.7	-	-	125 / 4.9	38.1 / 1.5	19.0 / 42.0
DCR 09617B	2	412.6 / 16.2	291 / 11.5	400 / 15.7	32.0 / 1.3	32.0 / 1.3	125 / 4.9	54 / 2.1	19.0 / 42.0
DCR 09617dB	2	412.6 / 16.2	291 / 11.5	400 / 15.7	-	-	125 / 4.9	49.2 / 1.9	19.0 / 42.0
DCR 09617dB	2	412.6 / 16.2	291 / 11.5	400 / 15.7	-	-	125 / 4.9	49.2 / 1.9	19.0 / 42.0

Ordering

DCR housing and insert are ordered separately. Select housing and top cover from the below table.

Figure 6: DCR housing with DN connection




Figure 7: DCR housing with solder ODF




Table 4: DCR Housing with steel connectors + top cover

Type	Number of cores	Steel connectors		Cover type	Max. working pressure PS [bar]/ Psig	Packing type (Qty)	Code number
		Solder ODF	Butt weld				
		[in.]	[mm]				
DCR 04811B	1	ODF 1 3/8"	-	Plug 1/4" NPT	90 / 1305	Single	023U1008
DCR 04811B	1	ODF 1 3/8"	-	Plug 1/4" NPT	90 / 1305	Industrial (18 pcs)	023U1009
DCR 04811dB	1	-	DN 32	Plug 1/4" NPT	90 / 1305	Single	023U1011
DCR 04811dB	1	-	DN 32	Plug 1/4" NPT	90 / 1305	Industrial	023U1012
DCR 04807B	1	ODF 7/8"	-	Plug 1/4" NPT	90 / 1305	Single	023U1014
DCR 04807B	1	ODF 7/8"	-	Plug 1/4" NPT	90 / 1305	Industrial	023U1015
DCR 04807dB	1	-	DN 20	Plug 1/4" NPT	90 / 1305	Single	023U1017
DCR 04807dB	1	-	DN 20	Plug 1/4" NPT	90 / 1305	Industrial (18 pcs)	023U1018
DCR 09613B	2	ODF 1 5/8"	-	Plug 1/4" NPT	90 / 1305	Single	023U0996
DCR 09613B	2	ODF 1 5/8"	-	Plug 1/4" NPT	90 / 1305	Industrial (12 pcs)	023U0997
DCR 09613dB	2	-	DN 40	Plug 1/4" NPT	90 / 1305	Single	023U0999
DCR 09613dB	2	-	DN 40	Plug 1/4" NPT	90 / 1305	Industrial (12 pcs)	023U1000
DCR 09617B	2	ODF 2 1/8"	-	Plug 1/4" NPT	90 / 1305	Single	023U1002
DCR 09617B	2	ODF 2 1/8"	-	Plug 1/4" NPT	90 / 1305	Industrial (12 pcs)	023U1003
DCR 09617dB	2	-	DN 50	Plug 1/4" NPT	90 / 1305	Single	023U1005
DCR 09617dB	2	-	DN 50	Plug 1/4" NPT	90 / 1305	Industrial (12 pcs)	023U1006
DCR 09617dB	2	-	DN 50	Plug G 1/2	90 / 1305	Single	023U1202
DCR 09617dB	2	-	DN 50	Plug G 1/2	90 / 1305	Industrial (12)	023U1203

Figure 8: DCR insert




Table 5: DCR core surface and volume

Core	surface	volume
	[cm2]	[cm3]
DM048, DC 048 and DA 048	612	727
DM096, DC 096 and DA 096	1225	1454
48-F	405	-

Semi-hermetic filter drier, type DCR for CO2








Table 6: DCR inserts code numbers

Type	Material	Code Number
		Industrial pack (8 pieces)
48-DM solid core ⁽¹⁾	100% molecular sieve	023U1393
48-DC solid core ⁽¹⁾	80% molecular sieve & 20% Al ₃ O ₂	023U4382
48-DA solid core ⁽¹⁾	30% molecular sieve & 70% Al ₃ O ₂	023U5382
48-F strainer ⁽¹⁾	Felt gasket, 15 µm	023U1921

⁽¹⁾ DC filter driers cores contain activated alumina, which is a polar material used for acid adsorption. Many oil additives are also polar substances and can be adsorbed by the activated alumina, rendering them useless, and reducing the drier's acid capacity, though this is not harmful to the system.

Spare parts

Table 7: Spare part list

Part	Description	Code number	Quantity
	Front plate assembly	023U1154	1
	Single core internal parts	023U1155	1
	Two core internal parts	023U1156	1
	1/4" NPT cover	023U1157	1
	1/2" G Thread cover	023U1158	1
	Flat gasket	023U1159	5
	M12 Bolts	023U1160	12

Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Table 8: Certificates, declarations, and approvals

Document type	Document topic	Approval authority
Mechanical - Safety Certificate	c UL us listing	UL
Manufacturers Declaration	RoHS	Danfoss
EU Declaration	PED	Danfoss
Pressure - Safety Certificate	-	NSW

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Coolselector®2 - find the best components for you HVAC/R system



Coolselector®2 makes it easy for engineers, consultants, and designers to find and order the best components for refrigeration and air conditioning systems. Run calculations based on your operating conditions and then choose the best setup for your system design.

Download Coolselector®2 for free at coolselector.danfoss.com.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.