


## Data Sheet

# Micro Channel Heat Exchanger Type **MCHE D1700-C** Bare version

Condenser – standard series



D1700-C is ideal for use in many different applications, such as chillers and commercial split/roof tops.

MCHEs have an ingeniously simple all-aluminum design that is not only lightweight but also prevents galvanic corrosion.

The refrigerant-carrying tubes are formed to optimize heat transfer, enabling the production of more compact, but equally effective, cooling solutions. The smart louvered fin design maximizes surface contact, reducing the air-side pressure loss, improving efficiency and reducing noise levels.

**Features:**

- Reduce refrigerant system charge
- Improve efficiency – More compact/better COP/increased capacity
- Cost - Less sensitive to fluctuations in raw material prices
- Better strength and better anticorrosion characteristic

## Product specification

### Technical data

Table 1: Technical data

| Model   | Coil length            | Coil height           | Core depth            | Fin pitch            | Inlet ID diameter   | Outlet ID diameter     | Continuous operating temperature   | Max. working pressure |
|---------|------------------------|-----------------------|-----------------------|----------------------|---------------------|------------------------|------------------------------------|-----------------------|
| D1700-C | 1324 (mm)<br>52.1 (in) | 639 (mm)<br>25.2 (in) | 25.4 (mm)<br>1.0 (in) | 1.1 (mm)<br>23 (FPI) | 16.1 (mm) 0.63 (in) | 12.9 (mm)<br>0.51 (in) | -40 °C / 121 °C<br>-40 °F / 250 °F | 45 (bar)<br>650 (psi) |

### Weight / internal volume

Coil weight: 9.87 kg / 21.75 lb  
Internal volume: 1.63 l / 99.47 in<sup>3</sup>

### Material specification

MPE Tube: 9153  
Fins: 3003  
Manifold: 3003  
Side plate: 3003  
Inlet/Outlet tubes: Copper

### Performance data

Table 2: Performance data of R410A and R134a

| Air Velocity | Performance [KW/Btu/h×1000] |                |                |                |                |                |                |                |
|--------------|-----------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| [m/s]        | R410A                       |                |                |                | R134a          |                |                |                |
| [ft/min]     | Δ=10 K / 18 °F              | Δ=15 K / 27 °F | Δ=20 K / 36 °F | Δ=25 K / 45 °F | Δ=10 K / 18 °F | Δ=15 K / 27 °F | Δ=20 K / 36 °F | Δ=25 K / 45 °F |
| 1.0/197      | 8.66/29.55                  | 13.17/44.94    | 17.88/61.01    | 22.5/76.77     | 8.31/28.35     | 12.64/43.13    | 16.94/57.8     | 21.37/72.91    |
| 1.5/295      | 12.36/42.17                 | 19.13/65.27    | 25.77/87.93    | 32.45/110.72   | 11.72/39.99    | 17.91/61.11    | 24.27/82.81    | 30.53/104.17   |
| 2.0/394      | 16.01/54.63                 | 24.53/83.7     | 32.98/112.53   | 41.6/141.94    | 14.74/50.29    | 22.6/77.11     | 30.76/104.95   | 38.75/132.22   |
| 2.5/492      | 19.25/65.68                 | 29.5/100.65    | 39.7/135.46    | 50.06/170.8    | 17.44/59.51    | 27.16/92.67    | 36.62/124.95   | 45.81/156.3    |
| 3.0/591      | 22.26/75.95                 | 34.03/116.11   | 45.89/156.58   | 57.95/197.73   | 19.88/67.83    | 31.08/106.04   | 41.98/143.24   | 52.35/178.62   |

Table 3: Performance data of R404A and R407C


| Air Velocity | Performance [KW/Btu/h×1000] |                |                |                |                |                |                |                |
|--------------|-----------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| [m/s]        | R404A                       |                |                |                | R407C          |                |                |                |
| [ft/min]     | Δ=10 K / 18 °F              | Δ=15 K / 27 °F | Δ=20 K / 36 °F | Δ=25 K / 45 °F | Δ=10 K / 18 °F | Δ=15 K / 27 °F | Δ=20 K / 36 °F | Δ=25 K / 45 °F |
| 1.0/197      | 8.64/29.48                  | 13.36/45.58    | 17.95/61.25    | 22.55/76.94    | 5.81/19.82     | 10.71/36.54    | 15.33/52.31    | 20.04/68.38    |
| 1.5/295      | 12.2/41.63                  | 19.13/65.27    | 25.7/87.69     | 32.36/110.41   | 8.16/27.84     | 15.24/52       | 22.14/75.54    | 28.81/98.3     |
| 2.0/394      | 15.9/54.25                  | 24.41/83.29    | 32.75/111.74   | 41.27/140.81   | 10.21/34.84    | 19.27/65.75    | 28.26/96.42    | 36.68/125.15   |
| 2.5/492      | 19.04/64.96                 | 29.09/99.26    | 39.18/133.68   | 49.39/168.52   | 12.04/41.08    | 23.48/80.11    | 33.87/115.56   | 43.92/149.86   |
| 3.0/591      | 21.91/74.76                 | 33.41/113.99   | 44.95/153.37   | 56.83/193.9    | 13.68/46.68    | 27.05/92.29    | 39.05/133.24   | 50.58/172.58   |

Table 4: Performance data of R454B and R452B

| Air Velocity | Performance [KW/Btu/h×1000] |                |                |                |                |                |                |                |
|--------------|-----------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| [m/s]        | R454B                       |                |                |                | R452B          |                |                |                |
| [ft/min]     | Δ=10 K / 18 °F              | Δ=15 K / 27 °F | Δ=20 K / 36 °F | Δ=25 K / 45 °F | Δ=10 K / 18 °F | Δ=15 K / 27 °F | Δ=20 K / 36 °F | Δ=25 K / 45 °F |
| 1.0/197      | 7.98/27.23                  | 12.5/42.65     | 17.08/58.28    | 21.67/73.94    | 8.06/27.5      | 12.58/42.92    | 17.19/58.65    | 21.78/74.31    |
| 1.5/295      | 11.39/38.86                 | 18.07/61.65    | 24.64/84.07    | 31.22/106.52   | 11.53/39.34    | 18.21/62.13    | 24.79/84.58    | 31.39/107.1    |
| 2.0/394      | 14.5/49.47                  | 23.15/78.99    | 31.59/107.79   | 40.05/136.65   | 14.67/50.05    | 23.34/79.64    | 31.77/108.4    | 40.25/137.33   |
| 2.5/492      | 17.35/59.2                  | 27.85/95.02    | 37.94/129.45   | 48.2/164.46    | 17.53/59.81    | 28.08/95.81    | 38.19/130.3    | 48.46/165.35   |
| 3.0/591      | 20.39/69.57                 | 32.24/110      | 43.89/149.75   | 55.8/190.39    | 20.65/70.46    | 32.5/110.89    | 44.19/150.78   | 56.07/191.31   |


## Dimensions

Figure 1: Dimensions



## Mounting

Figure 2: Mounting



Aluminum MCHEs expand and contract when exposed to big temperature changes. Installation supports/brackets must allow the MCHE to move in two dimensions.

## Standard connections

The product is equipped with standard copper pipe connections for easy mounting. Never bend or stress the inlet/outlet connections during mounting, and design installations to avoid vibration in operation.

## Bending

Micro Channel Heat Exchangers can easily be bent to fit in any application. Ask your local Danfoss Sales representative for advice.

## Availability

Our local stocking and distribution network allows standard MCHEs to be delivered globally with short delivery times. Contact your local Danfoss sales representative for the standard lead times in your region.

## Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at [danfoss.com](https://danfoss.com) or contact your local Danfoss representative if you have any questions.

**Table 5: Certificates, declarations, and approvals**

| File name                                                                         | Document type                 | Document topic | Approvals Authority         |
|-----------------------------------------------------------------------------------|-------------------------------|----------------|-----------------------------|
| UL SA33862                                                                        | Safety certificate            | UL             | UL-CCIC Company Limited     |
| BV CE-0062-PED-H-DMC 001-20-CHN                                                   | Pressure - Safety Certificate | PED            | Bureau Veritas Services SAS |
| EU Declaration Danfoss<br>BF202010en-0001.01                                      | EU Declaration                | PED            | Danfoss                     |
| TSSA CRN 0H22500.512346                                                           | Pressure - Safety Certificate | CRN            | TSSA                        |
| EAC RU Д-ДК.РА01.В.72299_20                                                       | EAC Declaration               | EAC            | CU-TR                       |
| EAC RU Д-ДК.БЛ08.В.00327_18                                                       | EAC Declaration               | EAC            | CU-TR                       |
| EAC RU Д-ДК.БЛ08.В.00162                                                          | EAC Declaration               | EAC            | CU-TR                       |
| Certificate UA TR TOV EVRO-TYSK<br>UA.TR.089.1122.05-19 HE 22.11.19 -<br>21.11.22 | UA Certificate                | UA Conformity  | LLC CDC EURO TYSK           |
| Manufacturers Declaration Danfoss EU-<br>ROHS-DoC-202009-01.01                    | Manufacturer Declaration      | EU ROHS        | Danfoss                     |
| Manufacturers Declaration Danfoss<br>MCHE-RoHS-DOC-201601                         | Manufacturer Declaration      | China RoHS     | Danfoss                     |

3 EAC files are suitable for using different refrigerants.

## Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

### The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at [store.danfoss.com](https://store.danfoss.com).

### Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at [www.danfoss.com/en/service-and-support/documentation](https://www.danfoss.com/en/service-and-support/documentation).

### Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at [www.danfoss.com/en/service-and-support/learning](https://www.danfoss.com/en/service-and-support/learning).

### Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: [www.danfoss.com/en/choose-region](https://www.danfoss.com/en/choose-region).

#### Danfoss A/S

Climate Solutions • [danfoss.com](https://danfoss.com) • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.