



Otter[®] H0364



Engineered to stop the drip

Boston[®] Otter is the superior choice on the market when it comes to a suction and discharge hose for water, mud and slurry solutions. Built with longevity in mind, this hose is manufactured to withstand vigorous applications including mining, agriculture, septic tank cleaning and more.



Markets/Applications

- Agriculture
- Construction
- Equipment rental
- Mining
- Ship building
- Oil and gas exploration
- Tank truck



Sells Against

- Continental Versiflo[®] 150 Water S&D
- Gates Water Master[®] (100-150) SD

Features


- Single helical steel wire provides suction capability
- Constant 150 psi across all sizes
- 3:1 safety factor
- EPDM tube and cover provide chemical-resistance in agricultural applications

Order Fulfillment

- Made to Stock
- Made to Order

Otter H0364

Suction and discharge hose for water, mud and slurry applications



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Minimum Bend Radius		Vacuum		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kPa	in/Hg	kg/m	lbs/ft	mtr	ft
H036420-100	31.8	1.25	42.0	1.65	10.5	150	31.5	450	110	4.33	92.0	27	0.86	0.58	30.5	100
H036424-100	38.1	1.50	49.0	1.89	10.5	150	31.5	450	135	5.31	92.0	27	1.09	0.73	30.5	100
H036432-100	50.8	2.00	62.0	2.44	10.5	150	31.5	450	200	7.87	92.0	27	1.63	1.10	30.5	100
H036440-100	63.5	2.50	75.0	2.95	10.5	150	31.5	450	270	10.63	92.0	27	2.07	1.39	30.5	100
H036448-100	76.2	3.00	89.0	3.50	10.5	150	31.5	450	340	13.39	92.0	27	2.69	1.81	30.5	100
H036464-100	101.6	4.00	115.0	4.53	10.5	150	31.5	450	450	17.72	80.0	24	3.72	2.50	30.5	100
H036496-100	152.4	6.00	168.0	6.61	10.5	150	31.5	450	700	27.56	80.0	24	6.98	4.69	30.5	100

Construction

Tube EPDM rubber

Reinforcement

High-tensile synthetic textile and steel helical wire

Cover EPDM rubber

Operating Temperature

-40°C to +120°C
(-40°F to +248°F)

Packaging

100 ft.

Type of couplings

- Cam and groove
- Combination nipple

Contact coupling manufacturer for attachment procedure and other coupling recommendations

ENGINEERING
TOMORROW



Danfoss Power Solutions, Nordborgvej 81, 6430 Nordborg, Denmark, Tel. +45 74 88 22 22, Fax +45 74 65 25 80
www.danfoss.com, E-mail: info@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.