

Data Sheet

Pressure Transmitter Type **DST P150**

For hydrogen applications (OEM)



The Danfoss DST P150 series pressure transmitter is designed to support your demanding Hydrogen applications, such as:

- Fuel cells
- Hydrogen powered combustion engines
- Electrolysis

Drawn from over 30 years of experience with MEMS pressure sensing, the DST P150 offers outstanding performance in a compact and durable stainless-steel package.

All wetted parts in media contact are made of 316L stainless steel.

Running a powerful ARM-based microcontroller, the DST P150 offers diagnostic features and scalable performance features at a competitive price.

Features

- Hermetically sealed media interface (all stainless steel, fully welded)
- Highest quality standards due to automatic check of all sensors in production
- All wetted parts in media contact 316L stainless steel
- Checked against EC79/2009 standard
- Industry leading accuracy over a broad temperature range
- Compact and cost-effective design for OEM applications
- Self-diagnostics minimize warranty costs
- Superior shock and vibration resistance
- High overload and burst pressure
- Robust electronics platform for harsh electrical environments
- Various electrical and pressure port variants available for product platform
- ATEX Zone 2 (Non standard - available on request)

Product specification

Technical data

Table 1: Performance

Pressure Range⁽¹⁾	0-50 bar (0-725 psi) Absolut and Gauge
Accuracy/Total error band	± 1,5 % FS within specific temperature range 0-85°C (see below)
Response time (10%-90%)	< 2 ms
Overload pressure	4 × FS
Burst pressure	5 × FS, max. 250 bar (3626 psi)
Durability, P: 10-90% FS	>10 mil. Cycles. 10%-110 FS

⁽¹⁾ For higher pressure ranges, max 60 bar(870psi), contact Danfoss sales representative.

Figure 1: Measurement Performance




Table 2: Electrical specifications/ Environmental conditions

Media temperature range (ratiometric output)	-40 – 135 °C	
Media temperature range EC79 certification	-40 – 120 °C	
Ambient temperature range (ratiometric output)	-40 – 125 °C	
Storage temperature range	-40 – 125 °C	
Voltage supply(Vss)	5 V ± 10%	
Load [RL] (load connected to ground)	RL ≥ 2 kΩ at 5 V DC	
Output modes ⁽³⁾	Ratiometric (10-90% Vss)	
Output limiting (clamping)	Low clamp 5% Vss	
Over and reverse voltage	Protected to 16 V	
Short circuit	Protected to 16 V	
Miswiring	Protected	
Diagnostic fault signal	2% Vss	
EMC compatibility	EN 61000-6-3 EN 61000-6-2	
ESD	IEC 61000-4-2 8 kV contact, 15 kV air	
Insulation resistance	>100M Ohm at 500 V DC	
Vibration resistance	16.5 g (20-2000 Hz)	EN 60068-2-64
Shock resistance	1000 g (half sinus, 1 ms)	EN 60068-2-27

⁽³⁾ mA output with reduced media temperature available upon request.

Table 3: Explosive atmospheres (Non standard - available on request)


Zone 2 applications	Ex ec IIC Gc	EN IEC 60079-0:2018; EN IEC 60079-7: 2015/A1:2018
----------------------------	---------------------	---

Table 4: Mechanical characteristics

Enclosure material (housing/electrical connector)	AISI 304L Stainless steel and PBT (30% glass reinforced)
Material with media contact	AISI 316L Stainless steel
Weight	Approx. 62 g
Enclosure (IP Protection)	IP 67 and IP69K

Output and diagnostics

Figure 2: Output and diagnostics



Defines the measuring range of the sensor.

Output clamp level

- Limits the pressure output signal if the pressure falls below the normal range

Sensor fault signal

- Placed below the pressure output range. Output at this level signals a sensor fault

Harness fault detection

- Low leakage current of the sensor allows the controller to recognize harness fault conditions. (Requires a pull-down or pull-up resistor at controller interface).

If the connected controller has an internal pull up or pull down resistor at the analog channel input, then the loss of ground or supply voltage (Vss) connection to the sensor will result in a near Vss or near ground signal voltage. Contact Danfoss sales representative for detailed information and requirements.

Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

File name	Document type	Document topic	Approval authority
075R0030.00	Manufacturers Declaration	PED	Danfoss
075R00110.04	Manufacturers Declaration	EU-UK Declaration (Incl. RoHS)	Danfoss
IECEX_ULD_23.0014U_000 (optionally available)	Explosive Safety Certificate	ATEX Zone 2	UL
UL23UKEX2865U Rev. 0 (optionally available)	Explosive Safety Certificate	UK ATEX Zone 2	UL

Conformity

- CE marked
- RoHS compliant
- EC79 / 2009

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Spare Parts



Get access to the Danfoss spare parts and service kit catalog right from your smartphone. The app contains a wide range of components for air conditioning and refrigeration applications, such as valves, strainers, pressure switches, and sensors.

Download the Spare Parts app for free at www.danfoss.com/en/service-and-support/downloads.

Coolselector2®



For easy and precise selection of valve, use Danfoss' CoolSelector2® software. You can find the ETS valves on the group, "Electronic expansion valves".

you can download it from coolselector.danfoss.com.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.