




Operating Guide

AVQML / 73690560


AVQML DN15 & DN20




AMV(E) 10 +
AVQML











AMV(E) 13 +
AVQML




AMV 150 +
AVQML



QTL +
AVQML



AVQML




DN		15	20
SW		30 (G ¾ A)	37 (G 1 A)
d		21	26
R ¹⁾		½	¾
L		65	82
L1 ²⁾		130	160
L2		114	141
L3	mm	130	160
H		38	44
H1		66	67
D (ISO 228/1)		G ¾ A	G 1 A
k		65	75
d ₂		14	14
n		4	4
Valve weight	kg	0.49	0.66

¹⁾ EN 10226-1

²⁾ EN 10222-2

¹⁾ EN 10226-1²⁾ EN 1092-2

Setting	DN 15			DN 15 HF			DN 20			DN 20 HF		
	L/h	L/s	GPM	L/h	L/s	GPM	L/h	L/s	GPM	L/h	L/s	GPM
10%	80	0.022	0.35	130	0.036	0.57	125	0.035	0.55	190	0.053	0.84
15%	120	0.033	0.53	195	0.054	0.86	188	0.052	0.83	285	0.079	1.25
20%	160	0.044	0.70	260	0.072	1.14	250	0.069	1.10	380	0.106	1.67
25%	200	0.056	0.88	325	0.090	1.43	313	0.087	1.38	475	0.132	2.09
30%	240	0.067	1.06	390	0.108	1.72	375	0.104	1.65	570	0.158	2.51
35%	280	0.078	1.23	455	0.126	2.00	438	0.122	1.93	665	0.185	2.93
40%	320	0.089	1.41	520	0.144	2.29	500	0.139	2.20	760	0.211	3.35
45%	360	0.100	1.59	585	0.163	2.58	563	0.156	2.48	855	0.238	3.76
50%	400	0.111	1.76	650	0.181	2.86	625	0.174	2.75	950	0.264	4.18
55%	440	0.122	1.94	715	0.199	3.15	688	0.191	3.03	1045	0.290	4.60
60%	480	0.133	2.11	780	0.217	3.43	750	0.208	3.30	1140	0.317	5.02
65%	520	0.144	2.29	845	0.235	3.72	813	0.226	3.58	1235	0.343	5.44
70%	560	0.156	2.47	910	0.253	4.01	875	0.243	3.85	1330	0.369	5.86
75%	600	0.167	2.64	975	0.271	4.29	938	0.261	4.13	1425	0.396	6.27
80%	640	0.178	2.82	1040	0.289	4.58	1000	0.278	4.40	1520	0.422	6.69
85%	680	0.189	2.99	1105	0.307	4.87	1063	0.295	4.68	1615	0.449	7.11
90%	720	0.200	3.17	1170	0.325	5.15	1125	0.313	4.95	1710	0.475	7.53
95%	760	0.211	3.35	1235	0.343	5.44	1188	0.330	5.23	1805	0.501	7.95
100%	800	0.222	3.52	1300	0.361	5.72	1250	0.347	5.50	1900	0.528	8.37



DN		15	20
L*	AMV(E) 10	101	111
	AMV(E) 13	105	115
	AMV 150	96	107
	QTL	110	110
L**	AMV(E) 10	159	169
	AMV(E) 13	162	173
	AMV 150	130	140
	QTL	136	147
H*	AMV(E) 10	195	202
	AMV(E) 13	209	216
	AMV 150	182	189
	QTL	216	223
H**	AMV(E) 10	191	197
	AMV(E) 13	194	201
	AMV 150	182	189
	QTL	201	208

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.