

## Datasheet

**Servo-operated 2/2-way solenoid valves for steam**

Type EV225B



EV225B is a servo-operated 2/2-way solenoid valve for use in steam applications.

The design is based on a PTFE diaphragm concept, ensuring highly reliable function when used in connection with contaminated steam.

Each valve body is made of dezincification resistant brass and the valve seats are made of stainless steel.

This ensures a long life even in when used with highly aggressive steam.

**Features and versions**

- Specifically designed for steam applications, 160 °C or 185 °C
- Flow range: 0.9 – 6.0 m<sup>3</sup>/h
- Differential pressure: 0.2 – 10 bar
- Media temperature from 0 – 185 °C
- Ambient temperature: up to 40 °C
- Coil enclosure: up to IP65
- Thread connections: from G 1/4 to G 1
- DN 6 – 25
- DZR brass NC (normally closed)
- EV225B used with BQ coil: AC voltage up to 185 °C
- EV225B used with BN coil: DC voltage up to 160 °C
- EV225B used with BB coil: AC voltage up to 160 °C DC voltage up to 140 °C
- Connection: ISO 228/1


**Approvals**

All valves are UL/UR approved:



**Data sheet | Servo-operated 2/2-way solenoid valves for steam, Type EV225B**

**DZR brass valve body, NC**



Connection ISO228/1	Seal material	Orifice size [mm]	K <sub>V</sub> - value [m <sup>3</sup> /h]	Differential pressure min. to max. [bar]				Media temperature min. to max. [°C]		Code no.
				Coil type BQ AC	Coil type BN DC	Coil type BB AC	Coil type BB DC	AC coil	DC coil	
G 1/4	PTFE	6	0.9	0.2 – 10	0.2 – 5	0.2 – 5	0.2 – 3.6	0 – 185	0 – 160	032U3802
G 3/8		10	2.2							032U3803
G 1/2		10	2.2							032U3804
G 1/2		15	3.0							032U3805
G 3/4		20	5.0							032U3806
G 1		25	6.0							032U3807

**DZR brass valve body, NC  
and BQ clip-on coil**



Connection ISO228/1	Seal material	Orifice size [mm]	K <sub>V</sub> - value [m <sup>3</sup> /h]	Differential pressure min. to max. [bar]	Media temperature min. to max. [°C]	Code no., valve body with coil and power connector		
				Coil type BQ AC		Coil type BQ024CS 24 V 60 Hz 24 V 50 Hz	Coil type BQ120BS 110-120 V 60 Hz	Coil type BQ024 CS 208-240 V 60 Hz 230 V 50 Hz
G 1/2	PTFE	10	2.2	0.2 – 10	0 – 185	032U380416	032U380420	032U380431
G 1/2		15	3.0			032U380516	032U380520	032U380531
G 3/4		20	5.0			032U380616	032U380620	032U380631
G 1		25	6.0			032U380716	032U380720	032U380731

**DZR brass valve body,  
NC and BN clip-on coil**



Connection ISO228/1	Seal material	Orifice size [mm]	K <sub>V</sub> - value [m <sup>3</sup> /h]	Coil voltage [V DC]	Differential pressure min. to max. [bar]	Media temperature min. to max. [°C]	Code no.
G 1/2	PTFE	10	2.2	24	0.2 – 5	0 – 160	032U380402
G 1/2		15	3.0				032U380502
G 3/4		20	5.0				032U380602
G 1		25	6.0				032U380702

## Data sheet | Servo-operated 2/2-way solenoid valves for steam, Type EV225B

### Technical data, NC



<b>Main type</b>	EV225B 6 – EV225B 25
<b>Time to open [ms] <sup>1)</sup></b>	Max. 0.2 s
<b>Time to close [ms] <sup>1)</sup></b>	Max. 0.2 s

<sup>1)</sup> The times are indicative. The exact times will depend on the pressure conditions.

<b>Installation</b>	Vertical solenoid system is recommended		
<b>Max. working pressure (MWP)</b>	10 bar		
<b>Max. test pressure</b>	25 bar (UL 429: 24.1 bar)		
<b>Ambient temperature</b>	Max. 40 °C at a medium temperature of 185 °C		
<b>Viscosity</b>	Max. 50 cSt		
<b>Materials</b>	Valve body	Dezincification resistant brass	
	Armature / armature stop	Stainless steel	W. no. 1.4105 / AISI 430FR
	Spring	Stainless steel	W. no. 1.4306 / AISI 304L
	Armature tube	Stainless steel	W. no. 1.4310 / AISI 301
	Diaphragm	PFTE	
	Valve plate	PFTE	
	Valve seat	Stainless steel	
	External gaskets	O-ring: AFLAS	

**Dimensions and weight**

Type	L [mm]	B [mm]	H [mm]	H <sub>1</sub> [mm]	H <sub>2</sub> [mm]	Weight gross valve body with coil BQ, BB [kg]	Weight gross valve body with coil BN [kg]
EV225B 6 BD	62	46	98	13	85	0.75	1.03
EV225B 10 BD	62	46	98	13	85	0.72	1.00
EV225B 15 BD	81	56	102	15	87	0.86	1.14
EV225B 20 BD	98	72	110	18	92	1.4	1.68
EV225B 25 BD	106	72	117	21	96	1.7	1.98

**Dimensions**

**Mounting angle**


**Data sheet | Servo-operated 2/2-way solenoid valves for steam, Type EV225B**

**Coil type BQ AC**  
**Steam coil to 185 °C**



Type	T ambient [°C]	Supply voltage [V]	Voltage variation	Frequency [Hz]	Power consumption		Approval	Code no.
					[W]	[VA]		
BQ024CS	-40 – 40	24	-15%, 10%	50	10	17		018F4517
		24	-15%, 10%	60	9.0	16		
BQ120BS	-40 – 40	110 / 120	-15%, 6%	60	13.5	19		018F4519
BQ240CS	-40 – 40	230	-15%, 6%	50	10	17		018F4511
		208 / 240	-6%, 6%	60	9.5	16		

**Coil type BN DC**  
**Steam coils to 160 °C**



Type	T ambient [°C]	Supply voltage [V]	Voltage variation	Frequency [Hz]	Power consumption		Approval	Code no.
					[W]	[VA]		
BN024DS	-40 – 50	24	±10%	DC	20	–		018F6968

**Coil type BB AC**  
**Steam coils to 160 °C**



Type	T ambient [°C]	Supply voltage [V]	Voltage variation	Frequency [Hz]	Power consumption		Code no.
					[W]	[VA]	
BB024AS	-40 – 80	24	-15%, 10%	50	11	19	018F7358
BB115AS	-40 – 50	115	-15%, 10%	50	11	19	018F7361
BB230AS	-40 – 80	220 / 230	-15%, 10%	50	11	19	018F7351
BB240AS	-40 – 80	240	-15%, 10%	50	11	19	018F7352
BB440CS	-40 – 80	400	±10%	50	14	24	018F7353
		440	±10%	60	15	24	
BB024BS	-40 – 80	24	-15%, 10%	60	14	23	018F7365
BB110CS	-40 – 50	110	±10%	50	15	28	018F7360
		110	±10%	60	13	22	
BB230CS	-40 – 50	220 / 230	±10%	60	13	24	018F7363
		220 / 230	±10%	50	16	31	

**Type BB DC**  
**Steam coils to 140 °C**


BB012DS	-40 – 50	12	±10%	DC	14	–	018F7396
BB024DS	-40 – 50	24	±10%	DC	16	–	018F7397

Technical data	Type BQ, BN, BB
Insulation of coil windings	Class H according to IEC 85
Connection	GDM 2011 (grey) Cable plug according to DIN 43650-A PG11
Coil enclosure, IEC 529	IP65
Ambient temperature	Max. 40 °C
Duty rating	Continuous


**Accessories:**  
**Cable plug**




Type	Code no.
GDM 2011 (grey), cable plug according to DIN 43650-A PG11	042N0156



Danfoss  
42N256.10



**Spare parts kit for  
EV225B 6 – EV225B 25**



Type	Code no.
EV225B 6 – EV225B 10	032U3171
EV225B 15	032U3172
EV225B 20 – EV225B 25	032U3173




**The spare parts kit comprises:**

An armature with valve plate and spring  
Closing spring  
Diaphragm  
O-ring

**Function NC**

EV225B 6 – EV225B 10




**Coil voltage disconnected (closed):**

When the voltage is disconnected, the valve plate (2) is pressed down against the pilot orifice (3) by the armature spring (4). The pressure across the diaphragm (6) is built up via the equalizing orifice (5). The diaphragm/piston closes the main orifice (7) as soon as the pressure across the diaphragm/piston is equivalent to the inlet pressure. The valve will be closed for as long as the voltage to the coil is disconnected.

**Coil voltage connected (open):**

When voltage is applied to the coil (1), the pilot orifice (3) is opened. As the pilot orifice is larger than the equalizing orifice (5), the pressure across the diaphragm (6) drops and therefore it is lifted clear of the main orifice (7). The valve is now open for unimpeded flow and will be open for as long as the minimum differential pressure across the valve is maintained, and for as long as there is voltage to the coil.

EV225B 15 – EV225B 25



1. Coil
2. Valve plate
3. Pilot orifice
4. Armature spring
5. Equalizing orifice
6. Diaphragm
7. Main orifice
8. Closing spring

## Steam capacity diagrams

### Example

Capacity for EV225 10 BD;  
inlet pressure ( $p_i$ ) of 6 bar absolute;  
differential pressure at 1 bar:  
approx. 100 kg/h / 80 kW

