


Data sheet

# Shut-off ball valve

## Type GBC



Danfoss shut-off ball valves, type GBC, are manually operated shut-off valves suitable for bi-directional flow.

The GBC valves are used in liquid, suction and hotgas lines in refrigeration and air conditioning systems.

The GBC bi-directional ball valves can be delivered with or without external access port.

The valves have one-piece wire seal cap to prevent unintentional cap removal or tampering between services.

### Features

- Broad temperature range equally applicable to freezing, refrigeration and air conditioning applications
- ¼ turn from fully open to fully closed
- Full flow with minimum pressure drop
- Ball status indicator on spindle top indicating open or closed position
- Bi-directional flow, i.e. valve orientation is unimportant
- One-piece seal cap for safety purpose  
Complies with European Safety Directive EN 378 (Safety and environmental requirements)
- Laser welded construction
- Burst-proof spindle design
- Drilled and tapped for panel mounting
- Selected Teflon and O-ring material to secure the best tightness and long lifetime
- Versions with access port helps in reducing cost if service of the system is necessary
- Double O-ring stem seal design
- Customized brass material ensures consistent performance under aggressive environment

Approvals




Technical data

- Refrigerants: R134a, R22/R407C, R404A/R507, R407A, R407F, R410A, R448A, R449A, R450A, R452A, R513A, R1234ze
- GBC 6s - GBC 25s can be used with R32, R454B, R452B, R290
- For a fully updated list of approved refrigerants, visit [www.products.danfoss.com](http://www.products.danfoss.com) and search for individual code numbers, where refrigerants are listed as part of product specifications

Type	Media temperature range	Max. working pressure (PS/MWP)
GBC 6s - GBC 42s	-40 °C – 150 °C (short term for 150 °C) / -40 °F – 300 °F (short term for 300 °F) For long term use in high temperature application, please consult Danfoss.	45 bar / 650 psig
GBC 54s - GBC 79s	-40 – 121 °C / -40 – 250 °F	45 bar / 650 psig


Ordering



GBC without access port, ODF/ODF

Type	Solder ODF/ODF connection		K <sub>v</sub> value <sup>1)</sup> [m <sup>3</sup> /h]	C <sub>v</sub> value <sup>1)</sup> [gal/min]	Code no.
	[inch]	[mm]			
GBC 6s	1/4	–	1.83	2.12	009L7020
	–	6	1.83	2.12	009L7030
GBC 10s	3/8	–	8.04	9.29	009L7021
	–	10	8.04	9.29	009L7031
GBC 12s	1/2	–	13.17	15.22	009L7022
	–	12	13.17	15.22	009L7032
GBC 16s	5/8	16	15.66	18.10	009L7023
	–	–	–	–	–
GBC 18s	3/4	–	21.93	25.35	009L7024
	–	18	21.93	25.35	009L7035
GBC 22s	7/8	22	33.34	38.54	009L7025
	–	–	–	–	–
GBC 28s	1 1/8	–	62.25	71.96	009L7026
	–	28	62.25	71.96	009L7033
GBC 35s	1 3/8	35	92.76	107.23	009L7027
	–	–	–	–	–
GBC 42s	1 5/8	–	134.76	155.78	009L7028
	–	42	134.76	155.78	009L7034
GBC 54s	2 1/8	54	240.11	277.57	009L7029
GBC 67s	2 5/8	–	367.38	424.69	009L7959
GBC 67s RP	2 5/8	–	203.12	234.81	009L7036
GBC 79s	3 1/8	–	528.87	611.37	009L7980
GBC 79s RP	3 1/8	–	171.89	198.70	009L7037

<sup>1)</sup> Calculated based on fluid dynamic equations. RP: Reduced Port




GBC with access port, ODF/ODF

Type	Solder ODF/ODF connection		K <sub>v</sub> value <sup>1)</sup> [m <sup>3</sup> /h]	C <sub>v</sub> value <sup>1)</sup> [gal/min]	Code no.
	[inch]	[mm]			
GBC 6s	1/4	–	1.83	2.12	009L7050
	–	6	1.83	2.12	009L7060
GBC 10s	3/8	–	8.04	9.29	009L7051
	–	10	8.04	9.29	009L7061
GBC 12s	1/2	–	13.17	15.22	009L7052
	–	12	13.17	15.22	009L7062
GBC 16s	5/8	16	15.66	18.10	009L7053
	–	–	–	–	–
GBC 18s	3/4	–	21.93	25.35	009L7054
	–	18	21.93	25.35	009L7065
GBC 22s	7/8	22	33.34	38.54	009L7055
	–	–	–	–	–
GBC 28s	1 1/8	–	62.25	71.96	009L7056
	–	28	62.25	71.96	009L7063
GBC 35s	1 3/8	35	92.76	107.23	009L7057
	–	–	–	–	–
GBC 42s	1 5/8	–	134.76	155.78	009L7058
	–	42	134.76	155.78	009L7064
GBC 54s	2 1/8	54	240.11	277.57	009L7059
GBC 67s	2 5/8	–	367.38	424.69	009L7960
GBC 67s RP	2 5/8	–	203.12	234.81	009L7066
GBC 79s	3 1/8	–	528.87	611.37	009L7981
GBC 79s RP	3 1/8	–	171.89	198.70	009L7067

<sup>1)</sup> calculated based on fluid dynamic equations. RP: Reduced Port

## Data sheet | Shut-off ball valve, type GBC


### Ordering



#### GBC without access port, ODF/ODM

Type	Solder ODF/ODF connection		K <sub>v</sub> value <sup>1)</sup> [m <sup>3</sup> /h]	C <sub>v</sub> value <sup>1)</sup> [gal/min]	Code no.
	[inch]	[mm]			
GBC 22s	7/8	22	33.34	38.54	009L7000
GBC 28s	1 1/8	–	62.25	71.96	009L7001
GBC 35s	1 3/8	35	92.76	107.23	009L7002
GBC 42s	1 5/8	–	134.76	155.78	009L7003
GBC 79s	3 1/8	–	528.87	611.37	009L7969

<sup>1)</sup> calculated based on fluid dynamic equations



#### GBC with access port, ODF/ODM

Type	Solder ODF/ODF connection		K <sub>v</sub> value <sup>1)</sup> [m <sup>3</sup> /h]	C <sub>v</sub> value <sup>1)</sup> [gal/min]	Code no.
	[inch]	[mm]			
GBC 28s	1 1/8	–	62.25	71.96	009L7097
GBC 35s	1 3/8	35	92.76	107.23	009L7098
GBC 42s	1 5/8	–	134.76	155.78	009L7099
GBC 54s	2 5/8	54	240.11	277.57	009L7069
GBC 67s	2 5/8	–	367.38	424.69	009L7958
GBC 79s	3 1/8	–	528.87	611.37	009L7970

<sup>1)</sup> calculated based on fluid dynamic equations

### Spare parts



#### Seal cap kit

Type	Valve connection size		Industrial pack [pcs]	Code no.
	[inch]	[mm]		
GBC 6s - GBC 12s	1/4 - 1/2	6 - 12	6	009L7209
GBC 16s - GBC 22s	5/8 - 7/8	16 - 22	6	009L7210
GBC 28s - GBC 35s	1 1/8 - 1 3/8	28 - 35	4	009L7211
GBC 42s - GBC 79s	1 5/8 - 3 1/8	42 - 79	4	009L7212




#### Bracket kit

Type	Valve connection size		Industrial pack [pcs.]	Code no.
	[inch]	[mm]		
GBC 6s - GBC 12s	1/4 - 1/2	6 - 12	12	009G7089
GBC 16s	5/8	16	12	009G7084
GBC 18s - GBC 22s	3/4 - 7/8	18 - 22	12	009G7085
GBC 28s	1 1/8	28	10	009G7086
GBC 35s	1 3/8	35	5	009G7087
GBC 42s	1 5/8	42	4	009G7088


### Design / Function

1. Connection
2. Valve body
3. Ball seat (modified PTFE)
4. Valve tail
5. Stainless steel ball
6. Double spindle O-ring seal (chloroprene)
7. Cap seal (PTFE)
8. Seal cap
9. Spindle
10. Pin
11. Access port cap
12. Guide ring
13. Schrader valve



Direct flow gives maximum through-flow with minimum pressure drop across valve. The combination of laser-welded valve body (2) and valve tail (4), ball seat/seal (3), double spindle O-ring seal (6), and cap seal (7) gives absolutely minimum leakage.


Dimension and weight



Type	Connection		H	H <sub>1</sub>	L	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	L <sub>4</sub>	L <sub>5</sub>	M	D	d	Weight
	[inch]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg] <sup>1)</sup>
GBC 6s	1/4	6	43	12	139	7	73	73	16.8	31	M3 × 0.5	11.1	1.5	0.1
GBC 10s	3/8	10	43	12	139	9	73	73	16.8	31	M3 × 0.5	11.1	1.5	0.1
GBC 12s	1/2	12	43	12	161	10	84	84	16.8	31	M3 × 0.5	11.1	1.5	0.1
GBC 16s	5/8	16	50	15	161	12	86	84	22	31	M4 × 0.7	14	1.5	0.2
GBC 18s	3/4	18	58	19	185	14	99	96	30	37	M4 × 0.7	19	1.5	0.4
GBC 22s	7/8	22	58	19	185	17	99	96	30	37	M4 × 0.7	19	1.5	0.4
GBC 28s	1 1/8	28	80	25	208	20	112	108	38	44	M4 × 0.7	25.5	1.5	0.9
GBC 35s	1 3/8	35	89	30	251	25	136	130	48	44	M6 × 1.0	32	1.5	1.4
GBC 42s	1 5/8	42	110	35	281	29	151	145	55	56	M6 × 1.0	38	1.5	2.2
GBC 54s	2 1/8	54	131	46	305	34	167	157	74	56	M6 × 1.0	50	1.5	4.2
GBC 67s	2 5/8	–	149	55	343	38	188	172	84	72	M6 × 1.0	60.5	1.5	5.8
GBC 67s RP	2 5/8	–	131	46	305	37	167	157	74	56	M6 × 1.0	50	1.5	4.4
GBC 79s ODF / ODF	3 1/8	–	169	65	416	38	230	214	86	80	M6 × 1.0	73.5	1.5	9.1
GBC 79s ODF / ODM	3 1/8	–	169	65	406	38	220	204	86	80	M6 × 1.0	73.5	1.5	9.1
GBC 79s RP	3 1/8	–	131	46	305	42	167	157	74	56	M6 × 1.0	50	1.5	4.5

<sup>1)</sup> Calculated value  
RP: Reduced Port

**Dimension and weight**



US units

Type	Connection		H	H <sub>1</sub>	L	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	L <sub>4</sub>	L <sub>5</sub>	M	D	d	Weight
	[inch]	[mm]	[inch]	[inch]	[inch]	[inch]	[inch]	[inch]	[inch]	[inch]	[mm]	[inch]	[inch]	[lbs] <sup>1)</sup>
GBC 6s	1/4	6	1.7	0.5	5.5	0.3	2.9	2.9	0.7	1.2	M3 × 0.5	0.4	0.1	0.3
GBC 10s	3/8	10	1.7	0.5	5.5	0.4	2.9	2.9	0.7	1.2	M3 × 0.5	0.4	0.1	0.3
GBC 12s	1/2	12	1.7	0.5	6.3	0.4	3.3	3.3	0.7	1.2	M3 × 0.5	0.4	0.1	0.3
GBC 16s	5/8	16	2.0	0.6	6.3	0.5	3.4	3.3	0.9	1.2	M4 × 0.7	0.6	0.1	0.5
GBC 18s	3/4	18	2.3	0.7	7.3	0.6	3.9	3.8	1.2	1.5	M4 × 0.7	0.7	0.1	1.0
GBC 22s	7/8	22	2.3	0.7	7.3	0.7	3.9	3.8	1.2	1.5	M4 × 0.7	0.7	0.1	1.0
GBC 28s	1 1/8	28	3.1	1.0	8.2	0.8	4.4	4.3	1.5	1.7	M4 × 0.7	1.0	0.1	2.0
GBC 35s	1 3/8	35	3.5	1.2	9.9	1.0	5.4	5.1	1.9	1.7	M6 × 1.0	1.3	0.1	3.1
GBC 42s	1 5/8	42	4.3	1.4	11.1	1.1	5.9	5.7	2.2	2.2	M6 × 1.0	1.5	0.1	4.9
GBC 54s	2 1/8	54	5.2	1.8	12.0	1.3	6.6	6.2	2.9	2.2	M6 × 1.0	2.0	0.1	9.3
GBC 67s	2 5/8	–	5.9	2.2	13.5	1.5	7.4	6.8	3.3	2.8	M6 × 1.0	2.4	0.1	12.8
GBC 67s RP	2 5/8	–	5.2	1.8	12.0	1.5	6.6	6.2	2.9	2.2	M6 × 1.0	2.0	0.1	9.7
GBC 79s ODF / ODF	3 1/8	–	6.7	2.6	16.4	1.5	9.1	8.4	3.4	3.1	M6 × 1.0	2.9	0.1	20.1
GBC 79s ODF / ODM	3 1/8	–	6.7	2.6	16.0	1.5	8.7	8.0	3.4	3.1	M6 × 1.0	2.9	0.1	20.1
GBC 79s RP	3 1/8	–	5.2	1.8	12.0	1.7	6.6	6.2	2.9	2.2	M6 × 1.0	2.0	0.1	9.9

<sup>1)</sup> Calculated value  
RP: Reduced Port