


Ordering from the entire SVL 65 bar (943 psi) Series

Housings

Size (DN)	Size Inch	Parts Program																
		Housing								Top complete								
		ANG				STR				SVA-S (cap)	SVA-L (cap)	SVA-65BT	SCA-X	CHV-X	REG-SA	REG-SB	FIA	
DIN	ANSI	SD	SA	DIN	ANSI	SD	SA											
6	¼	148B6689	148B6687	148B6722	148B6711	148B6693	148B6691	148B6743	148B6732	148B6695								
10	¾	148B6690	148B6688	148B6723	148B6712	148B6694	148B6692	148B6744	148B6733						148B5761	148B5764		
15	½	148B6622	148B6612	148B6724	148B6713	148B6642	148B6632	148B6745	148B6734	148B6652	148B6659			148B5769	148B5776	148B5762	148B5765	148B5783
20	¾	148B6623	148B6613	148B6725	148B6714	148B6643	148B6633	148B6746	148B6735	148B6652	148B6659			148B5769	148B5776	148B5762	148B5765	148B5783
25	1	148B6624	148B6614	148B6726	148B6715	148B6644	148B6634	148B6747	148B6736	148B6653	148B6660			148B5770	148B5777	148B5763	148B5766	148B5784
32	1¼	148B6625	148B6615	148B6727	148B6716	148B6645	148B6635	148B6748	148B6737	148B6653	148B6660			148B5770	148B5777	148B5763	148B5766	148B5784
40	1½	148B6626	148B6616	148B6728	148B6717	148B6646	148B6636	148B6749	148B6738	148B6653	148B6660			148B5770	148B5777	148B5763	148B5766	148B5784
50	2	148B6627	148B6617	148B6718	148B6647	148B6637	148B6739	148B6654		148B6804	148B5771	148B5778			148B5767	148B5785		
65	2½	148B6628	148B6618	148B6729	148B6719	148B6648	148B6638	148B6750	148B6740	148B6655			148B6805	148B5772	148B5779		148B5768	148B5786
80	3	148B6629	148B6619	148B6730	148B6720	148B6649	148B6639	148B6751	148B6741	148B6656			148B6806	148B5773	148B5780			148B5787
100	4	148B6630	148B6620	148B6731	148B6721	148B6650	148B6640	148B6752	148B6742	148B6657			148B6807	148B5774	148B5781			148B5788
125	5	148B6631	148B6621	148B6755		148B6651	148B6641			148B6658				148B5775	148B5782			148B5789
150	6																	
200	8																	



Inserts & Spare Parts

Size (DN)	Size Inch	Service kit			Complete valve																
		O-ring kit* for		Gasket	SVA (cap)				FIA				Filters								
		R717 Heat pump	R1270 Propylene	High temp. for SVA-65BT	ANG		STR		ANG		STR		FIA: Filter insert-plain			FIA: Filter insert-pleated					
			DIN	ANSI	DIN	ANSI	DIN	ANSI	DIN	ANSI	100µ	150µ	250µ	500µ	50µ	150µ	250µ	500µ			
6	¼					148B5033		148B5053													
10	¾	148B6084	148B6085			148B5034		148B5054													
15	½					148B5035		148B5055						148H3122	148H3124	148H3126	148H3128	148H3412	148H3303	148H3363	
20	¾	148B6070	148B6077			148B5036		148B5056													
25	1					148B5037		148B5057													
32	1¼	148B6071***	148B6078**			148B5038		148B5058						148H3123	148H3125	148H3127	148H3129	148H3413	148H3304	148H3269	
40	1½	148B6096***	148B6097***			148B5039		148B5059													
50	2	148B6072	148B6079	148B6808****		148B5040		148B5060						148H3157	148H3130	148H3138	148H3144	148H3414	148H3179	148H3184	148H3189
65	2½	148B6073	148B6080	148B6809****		148B5041		148B5061						148H3131	148H3139	148H3145	148H3415	148H3415	148H3180	148H3185	148H3190
80	3	148B6074	148B6081	148B6810****		148B5042		148B5062						148H3119	148H3120	148H3121	148H3416	148H3181	148H3186	148H3191	
100	4	148B6075	148B6082	148B6811****		148B5043		148B5063						148H3132	148H3140	148H3146	148H3417	148H3182	148H3187	148H3192	
125	5	148B6076	148B6083			148B5044		148B5064						148H3133	148H3141	148H3147	148H3418	148H3183	148H3188	148H3193	
150	6					148B6665	148B6667	148B6666	148B6668	148B6669	148B6671	148B6670	148B6672								
200	8					148B6673	148B6675	148B6674	148B6676	148B6677	148B6679	148B6678	148B6680								

* To be used for SCA-X, CHV-X sizes 15-125 and REG SA/SB sizes 10-40. O-ring kit for R717 Ammonia Heat Pump is applicable for continuous operating temperature between +100°C to 150 °C (212 °F to 302 °F)
 ** to be used for SCA-X, CHV-X, 25-40 | *** to be used for REG SA/SB, 25-40 | **** Max. temperature 190 °C (374 °F)

Danfoss A/S
 Climate Solutions - danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues, descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

AF359543218157en-000401

© Danfoss | Climate Solutions | 2024.12

See how tomorrow's solutions are ready today
 visit www.danfoss.com/IR

ENGINEERING
 TOMORROW

