

Data sheet

Butterfly valve with electrical actuator VFY-WA

Description

**Features:**

- Splined driven one piece shaft connected to spherically machined disc allows high torque transmission i.e. quick response and minimum back-lash
- Long term reliability due to upper and lower anti-friction bearings
- Safe maintenance: shaft blow out protection with circlip
- Manual operation
- Position indicator

- Torque limiter
- Complete installation from factory - ready for installation


Main Data*:

- DN 25-200
- k_{VS} 40-2500 m³/h
- PN 16 (10)
- EPDM Liner
- Stainless steel or Ductile iron Epoxy Coated disc
- Medium:
 - Circulation water or chilled glycolic water up to 50 %
- Medium temperature:
 - 10 ... 120 °C (EP disc)
 - 10 ... 130 °C (SS disc)
- Nominal voltage:
 - 24 V; 50 Hz/60 Hz
 - 230 V; 50 Hz/60 Hz
- Control input signal: On/Off or 3-point
- Torque: 20-600 Nm
- Grade of enclosure: IP66/68
- Ambient temperature: -10 ... 55 °C
- Duty rating IEC34: cycle S4 (50 %)
- Approvals: **CE EAC**

* please check the Directive 2014/68/UE table at the end of the data sheet for appropriate product selection


Ordering

Type VFY-WA 230 V

Picture	DN	k _{vs} (m³/h)	PN	T _{max} (°C)	Opening time (s)	Disc	Code No.	
	25	40	10	130	12	Stainless Steel	082G7350	
	32/40	62	16				082G7351	
	50	79						082G7400
	65	174						
	80	275			082G7402			
	100	496			082G7403			
	125	883	082G7404					
	150	1212	082G7405					
	200	2500	082G7410					
	50	79	16	120	12	Ductile iron Epoxy Coated	065B8440	
	65	174			12		065B8441	
	80	275			7		065B8442	
	100	496			12		065B8443	
	125	883			12		065B8444	
	150	1212			12		065B8445	
	200	2500			30		065B8446	

Ordering (continuous)

Type VFY-WA 24 V

Type VFY-WA24V							
Picture	DN	k_{VS} (m ³ /h)	PN	T _{max} (°C)	Opening time (s)	Disc	Code No.
	25	40	10	130	12	Stainless Steel	082G7361
	32/40	62	16			082G7362	
	50	79	16	120		Ductile iron Epoxy Coated	065B8450
	65	174			065B8451		
	80	275			7		065B8452
	100	496			12		065B8453
	125	883			12		065B8454
	150	1212			12		065B8455
	200	2500			60		065B8456

Spare parts

Replacement actuator AMB-Y

Actuator type	for DN	Torque	Opening time (s)	Power consumption (W)	Supply voltage (V)	Code No.
ER20	25/32/40/50/65	20	12	15	230 V	082G7381
ER35	80	35	7	45		082G7382
ER60	100	60	12	45		082G7383
ER60	125-150	60	12	45		082G7415
VS150	200	150	30	45		082G7398
ER20	25/32/40/50/65	20	12	15	24 V	082G7388
ER35	80	35	7	45		082G7389
ER60	100	60	12	45		082G7390
ER60	125-150	60	12	45		082G7414
VS150	200	150	30	45		082G7399

Note:

Contact Danfoss sales organization regarding information about replacement actuators for VFY butterfly valves purchased before 01/2015.

Replacement Liner VFY-W Liner

DN	PN	Liner	Code No.
25	16	EPDM	065B7580
32/40			065B7581
50			065B7582
65			065B7583
80			065B7584
100			065B7585
125			065B7578
150			065B7579
200			065B7592

Technical data

Actuator

Power supply	DN 25-200	V	100-240 ac; 100-350 dc 15-30 ac; 12-48 dc
Frequency (AC)		Hz	50/60
Control Input	DN 25-200		on/off or 3-point
Torque		Nm	20-150
Ambient temperature		°C	-10 ... 55
Duty Rating IEC34			S4 (50 %)
Grade of enclosure	DN 25-150		IP66
	DN 200		IP68 (1m, 72h)
CE marking in accordance with standards			Low voltage directive (LVD) 2006/95/EC; EN61000-3-2, EN61000-3-3, EN61000-6-4, EN61000-6-2
			EMC Directive 2004/108/EC: EN61010-1


Valve

Nominal diameter		DN	25-200
k _{vs} value		m³/h	40-2500
Rotation angle			90°
Leakage rate			Acc. to PED 2014/68/EU, EN 12266-1, Rate A ¹⁾
Nominal pressure		PN	16 (10)
Medium			Circulation water, chilled glycolic water up to 50%
Medium temperature	EP disc	°C	−10 ... 120 (see PT diagram)
	SS disc		−10 ... 130 (see PT diagram)
Connection			Centering lugs (Wafer type)
Mounting			Mounting between flanges
Material			
Body	DN 25-200		Ductile iron EN GJS 400-15 ²⁾
Disc	Ductile iron EN GJS 400-15 (DIN GGG 40) with Polyamid coating or Stainless Steel		
Shaft	Stainless steel AISI 420		
Liner	EPDM		
Circlip	Steel XC 75 / Stainless steel		
O-ring	Nitrile/Viton		
Upper guide bush	Zinc coated S. + PTFE		
Lower guide bush	Zinc coated S. + PTFE		

¹⁾ No visible detectable leakage during the testing procedure


²⁾ Changed from Cast iron EN GJL 250 (DIN GG25) in Q4/2024

P-T diagram




Headloss diagram

For water at 20°C




Installation positions



Installation conditions


It is recommended that distances indicated below are respected in order to prolong lifetime of the valve. Mounting the valve close to pipework junctions (turbulent zones) increases wear.



Wiring



VFY-WA DN 25-150 (ACTUATOR TYPE ER)



Wiring input / output

1	SN	0 V	Neutral
2	SP	ON/OFF, 3-point	Power supply
3			
4	4 (SP)	SP output - max 5A	Common FC1
5			Feedback FC1
8			Feedback FC1
6	6 (SP)	SP output - max 5A	Common FC2
7			Feedback FC2
9			Feedback FC2

Drives end switches and feedback output

Valve position	Feedback			
	5	7	8	9
Open	1	0	0	1
Close	0	1	1	0
Neutral	0	0	1	1

Wiring (continuous)



VFY-WA DN 200 (ACTUATOR TYPE VS)

3-point

ON/OFF Mode

FC1 - feedback limit switch Open
FC2 - feedback limit switch Close
H - anti-condensation heater

Wiring input / output


1	SN	0 V	Neutral
2	SP	ON/OFF, 3-point	Power supply
3			
4		SP output - max 5A	Common FC1
5			Feedback FC1
8			Feedback FC1
6		SP output - max 5A	Common FC2
7			Feedback FC2
9			Feedback FC2

Drives end switches and feedback output


Valve position	Feedback			
	5	7	8	9
Open	1	0	0	1
Close	0	1	1	0
Neutral	0	0	1	1

Design

- 1. Body
- 2. Disc
- 3. Shaft
- 4. Liner
- 5. Circlip
- 6. O-ring
- 7. Upper guide bush
- 8. Lower guide bush
- 9. Actuator




Dimensions



VFY-WA

(with actuator AMB-Y ER for DN 25 - 150)

DN	Ø	A	B	C	D	E	F	Weight (kg)
25	32	50	277	92	33	45	136	3.2
32/40	43	57	282	92	33	45	136	3.3
50	54	62	288	92	43	45	136	3.4
65	70	70	297	92	46	45	136	4.5
80	85	89	303	92	46	45	136	4.6
100	100	105	351	128	52	55	151	6.4
125	125	120	366	128	56	55	151	8.5
150	150	131	355	128	56	55	151	10.5



VFY-WA

(with actuator AMB-Y VS for DN 200)

DN	Ø	A	B	C	D	F	E	Weight (kg)
200	200	166	426	170	60	174	69	16.8

Data sheet

VFY-WA

Directive 2014/68/UE
Equipments under pressure

Products manufactured in conformity with the requirements of the directive, according to pressure, DN and fluid. Relevant for countries following this Directive (ie, PED)

Family		DN (mm)	Cat.	Mounting	PFA	PS				
					water	L1	L2	G1	G2	
VFY DN25 to 350 mm with EPDM liner	10 bar	25 to 100	4\$3	Flanges	10	10	10	-	10	
				End of line	6	6	6	-	6	
		125 to 350	I	Flanges	10	10	10	-	10	
				End of line	6	6	6	-	6	
	16 bar	32 to 100	4\$3	Flanges	16	16	16	-	10	
				End of line	12	12	12	-	10	
		125	I	Flanges	16	16	16	-	10	
				End of line	12	12	12	-	10	
		150	I	Flanges	16	10	16	-	10	
				End of line	12	6	12	-	10	
		200 to 300	I	Flanges	16	10	16	-	10	
				End of line	10	6	10	-	10	
		350	I	Flanges	16	10	16	-	10	
				End of line	8	6	8	-	8	
	20 bar	32 to 250	4\$3	Flanges	20	-	20	-	-	
				End of line	12	-	12	-	-	
		300 to 350	I	Flanges	20	-	20	-	-	
				End of line	12	-	12	-	-	
		25 bar	32 to 150	4\$3	Flanges	25	-	25	-	-
					End of line	16	-	16	-	-
VFY DN400 to 1200 mm with EPDM liner	10 bar	400 to 1200	I	Flanges	10	10	10	-	-	
				End of line	6	6	6	-	-	
	16 bar	400 to 1200	I	Flanges	16	-	16	-	-	
				End of line	8	-	8	-	-	
	20 bar	400 to 600	I	Flanges	20	-	20	-	-	
				End of line	10	-	10	-	-	
PS: Maximum allowable pressure (bars) in accordance with directive 2014/68/EC PFA: Allowable operating pressure (bars) for supply, distribution and disposal of water				L1: Group 1 liquid - Hazardous fluid category						
				L2: Group 2 liquid - Other fluids						
				G1: Group 1 gas - Hazardous gas category						
				G2: Group 2 gas - Other gasses						

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.