


Data Sheet

MicroPlate Heat Exchanger Type **H39L-EZU**

For more efficient Heat Pumps



The H39L-EZU is new Micro Plate heat exchanger which was designed dedicated to R290 heat pump systems with low charge requirement.

The Z-pattern channel plate technology pushes the performance of heat exchangers to the limits by fully mixing the liquid and gas refrigerant through a “zigzag” flow, which increases the heat transfer coefficient. At the same time, inheriting from dimple plate pattern of the previous generation of MPHE, H39L-EZU reduces the water side pressure drop and the amount of material used. In the reversible mode of the heat pump as a condenser, H39L-EZU also has outstanding performance.

To meet demands for higher seasonal efficiency, the H39L-EZU is designed to work efficiently and increase comfort in modern residential and commercial buildings without increasing the carbon footprint. Helping heat pumps perform more efficiently, it reduces both energy costs and environmental impact. The low hold-up volume reduces the system refrigerant charge and offers valuable savings.

Features

- Minimal hold-up volume – suitable for systems with 152 g propane charge limitations
- Thanks to the mixing chamber, the innovative refrigerant distribution device, the H39L-EZU is applicable as evaporator and condenser with all refrigerant types.
- Improved heat transfer - equals higher efficiency heat pumps
- Reduced water side pressure drop – equals higher efficiency heat pumps
- Smaller footprint - enables more compact heat pumps
- High heat transfer and minimal refrigerant charge - equals a reduced CO footprint

Portfolio overview

The H39L-EZU is single circuit evaporators specifically designed for highly efficient heat pump systems. The evaporator is design to operate also in reversable systems in condenser mode, in co or counter current flow configuration.

H39L-EZU: Evaporator optimized for R290 and could be used with R410A, R32, R452B and R454B

Application

The H39L-EZU is single circuit heat exchanger specifically designed for highly efficient heat pump systems. The heat exchanger is design to operate as an evaporator and condenser also in reversable systems, in co or counter current flow configuration.

Thanksto the mixing chamber, the innovative refrigerant distribution device, the H39L-EZU is applicable with all refrigerants types.

Table 1: Designation

a H b 39 c L d - EZU - f 50		
a Applications C: chiller D: universal H: heat pump HDW: heat pump double wall	d Specific duty E: evaporator C: condenser Plate design Omit L: L-type M: M-type H: H-type W: W-type X: Asymmetric Z: Z flow Configuration Omit: single D: Dual circuit U: Mixing chamber	e Distributor version Omit B F Plate stacking sequence Omit: a-b-a... R: b-a-b... f Number of plates⁽²⁾
b Platform⁽¹⁾ 22, 30, 39, 44, 55, 62, 118...		
c Pressure Service Omit: 30 bar L: 45/49 bar		

⁽¹⁾ heat exchanging surface per plate 1/1000 m²

⁽²⁾ Rule:

- Single: even number
- Dual: even number not multiple of 4

Media

Refrigerants

R290, R410A, R32, R452B, R454B, R454C

For other refrigerants please contact your Danfoss Sales representative.

Product specification

Operating conditions

Preconditions:

N = number of plates

Max number of plates: 120

Pressure and temperature data:⁽¹⁾

Min. working temperature: -196 °C (-320 °F)

Max. working temperature: 200 °C (390 °F)

Max. working pressure: 49 bar (711 psi) refrigerant side** / 25 bar (363 psi) water side

Weight

H39L-EZU: $1.4 + 0.072 \times N$ [kg] / $3.09 + 0.16 \times N$ [lb]

N: Number of Plate

Material specification


Table 2: Standard materials

Item	Material	Specification
Cover plates	Stainless steel	AISI 304L
Plates	Stainless steel	AISI 316L
Connections	Stainless steel	AISI 304L
Brazing filler	Pure copper	Cu

Other material combinations are available on request. Please contact your Danfoss sales representative for more information.

Configuration flow

Figure 1: Configuration flow



Q1 - Q2 [H1 - H2]: brine/secondary side

Q3 - Q4 [H3 - H4]: refrigerant/primary side

Hold up volume

Q1 - Q2 (l): $0.037 \times N/2$


Q3 - Q4 (l): $0.0274 \times (N-2)/2 + 0.012$

N: Number of Plate

¹ For details, refer to the topic [Third party approvals](#)

Dimensions

Figure 2: Dimensions



A: H39L-EZU: $10 + 1.09 \times N$ [mm] // $0.4 + 0.043 \times N$ [inch]

N: Number of Plate

Ordering

Configuring and calculating products

The H39L-EZU can be easily customized based on the application needs; model size can be evaluated using HEXSelector software.

For details, product configuration and code creation please contact your Danfoss Sales representative.

Mechanical connections

Table 3: Mechanical connections

Circuits	Connection type options	Connection size option [in.]
Q1 - Q2 (water-brine side)	G/R/NPT male thread	1/2, 3/4, 1, 1 1/4
	G/R/NPT female thread	1/2, 3/4, 1
	Victaulic	3/4, 1, 1 1/4
Q3 (Refrigerant inlet)	Soldering	1/4, 5/16, 3/8, 1/2
Q4 (Refrigerant outlet)	Soldering	3/8, 1/2, 5/8, 3/4, 7/8, 1 1/8

Accessories and spare parts

MPHE products are not serviceable, i.e. cannot be taken apart and repaired, and there are no spare parts program. As for accessories, stud bolts, feet on front and/or back cover plates for mounting support and handling are available upon request.

Table 4: Stud bolts

Stud bolt position	Bolt sizes
220 mm, middle	M8 x 30 mm
	M6 x 30 mm

Contact your Danfoss sales representative for further information.

Affected products

Customers can calculate the optimal plate combination based on their specific operating conditions with our selection software (HEXSelector) and customize various connections according to their needs. At the same time, we offer a series of standard products listed in the table below for customers to order directly.

Table 5: Affected products

SAP Code	Drawing	Product	Connections and bolts
111B8651	T24020-932	H39L-EZU-16	Q1Q2(G1")/Q3(H1/4B)Q4(H5/8")/2-M8*25
111B8652	T24020-933	H39L-EZU-20	Q1Q2(G1")/Q3(H1/4B)Q4(H5/8")/2-M8*25
111B8653	T24020-934	H39L-EZU-26	Q1Q2(G1")/Q3(T8.2)Q4(H5/8")/2-M8*25
111B8654	T24020-935	H39L-EZU-30	Q1Q2(G1")/Q3(T8.2)Q4(H5/8")/2-M8*25
111B8655	T24020-936	H39L-EZU-36	Q1Q2(G1")/Q3(T8.2)Q4(H5/8")/2-M8*25
111B8656	T24020-937	H39L-EZU-40	Q1Q2(G1")/Q3(H3/8T)Q4(H7/8")/2-M8*25
111B8657	T24020-938	H39L-EZU-46	Q1Q2(G1")/Q3(H3/8T)Q4(H7/8")/2-M8*25
111B8658	T24020-939	H39L-EZU-50	Q1Q2(G1")/Q3(H3/8T)Q4(H7/8E)/2-M8*25
111B8659	T24020-940	H39L-EZU-56	Q1Q2(G1")/Q3(H3/8T)Q4(H7/8E)/2-M8*25
111B8660	T24020-941	H39L-EZU-60	Q1Q2(G1")/Q3(H3/8T)Q4(H7/8E)/2-M8*25
111B8661	T24020-942	H39L-EZU-70	Q1Q2(G1 1/4")/Q3(H1/2)Q4(H1"1/8J)/2-M8*25
111B8662	T24020-943	H39L-EZU-80	Q1Q2(G1 1/4")/Q3(H1/2)Q4(H1"1/8J)/2-M8*25
111B8663	T24020-944	H39L-EZU-90	Q1Q2(G1 1/4")/Q3(H1/2)Q4(H1"1/8J)/2-M8*25
111B8664	T24020-945	H39L-EZU-100	Q1Q2(G1 1/4")/Q3(H1/2)Q4(H1"1/8J)/2-M8*25
111B8665	T24020-946	H39L-EZU-110	Q1Q2(G1 1/4")/Q3(H1/2)Q4(H1"1/8J)/2-M8*25
111B8666	T24020-947	H39L-EZU-120	Q1Q2(G1 1/4")/Q3(H1/2)Q4(H1"1/8J)/2-M8*25

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.


Approvals

The list contains all approvals registered for this product type. Individual code numbers may have some or all of these approvals, some local approvals may not be in the list, and approvals change over time. Check status on www.danfoss.com or contact your local Danfoss representative if in doubt.

Third party approvals

All MPHE and BPHE are certified to European Pressure Equipment Directive (PED) and are approved by Underwriters Laboratories (UL).

Table 6: Third party approvals



Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Hexselector for heat exchangers



Hexselector for heat exchangers helps you identify the best heat exchanger for your chiller, heat pump, or other application based on operating conditions. Works for innovative MPHE and traditional BPHE brazed heat exchangers.

Download Hexselector for free at <http://hexselector.com>

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.