



ENGINEERING
TOMORROW

HIGHLIGHTS

- Ultra compact
- Modular and configurable drive
- STO SIL3 as standard
- Scalable control platform
- Powerful hardware-based security including end-to-end encrypted data transfer
- Connectivity with multiple fieldbuses
- Industrial IoT-ready
- High-torque machine performance
- Superior motor control

Safe
and fast service
access

Fact sheet | iC7-Automation Enclosed Drives

Need **more intelligence**, with **streamlined integration**?

iC7-Automation Enclosed Drives deliver high torque performance in an ultra compact format. iC7-Automation Enclosed Drives open up new application opportunities with flexible system integration in a wide range of industries. Optimized for compact footprint, ease of use and fast serviceability, you can apply these drives to enhance motor control.

Versatile

iC7 Enclosed Drives are available in standard cabinet sizes, configured in the right variant to suit your application:

- 6-pulse, low-harmonic, and regenerative variants
- Wide range of options

Feature	Benefit
Robust by design, high uptime and quality	– Reliable in heavy-duty service
Segregated main cooling channel, (IP21 or IP54) and dedicated PCB area	– Extremely reliable in heavy-duty service
Wide range of pre-designed options	– Flexible to meet any application need
Heat management using heat pipe technology and segregated main cooling channel	– High power density, reduced footprint
Integrated options such as functional extensions, output filters, fuses and disconnects mean no extra external devices are required	– Save cost and time in installation
Installer-friendly design includes pluggable control terminals, easy-access power terminals, and easily replaceable fans	– Save cost and time in installation and service
Modular and scalable solutions for high powers Simplified spare unit handling	– Fast integration and serviceability
Pull-out of power unit without removing motor or mains cables, included with integration unit	– Fast and easy serviceability
Safe door-in-door access to the control compartment	– Safe and fast serviceability

 [Learn more about iC7-Automation drives](#)

iC7.danfoss.com 

Key specifications

Input	
Voltage rating	380-500 V AC, +10%/-15%
Supply frequency	50/60 Hz
Switching on input ¹⁾	6-pulse: 1-2 times per minute Low-harmonic and regenerative: Switch on twice at 60 s interval, followed by 10 minutes cooling-down period
Grid type	TN, TT, IT, Delta
Output	
Output frequency	0-599 Hz
Switching on output	Unlimited
Overload capacity	110/150% – 1 min every 5 min
Environmental conditions	
Rated temperature	-15 to 40 °C (5 to 104 °F)
Maximum temperature with derating	50 °C (122 °F)
Rated altitude	1000 m (3300 feet) or up to 4,000 m (13,124 ft) with derating
Relative humidity	5-95% non condensing
Functional Safety I/O	
STO	Dual-channel, with galvanic isolation
STO feedback	Single channel, with galvanic isolation

External supply	
Rating	24 V/2 A
Basic I/O	
Digital inputs	6, single-ended
Relay outputs	3 • 2 x NO, NC • 1 x NO • 250 V AC 3 A max. (50/60 Hz) • 24 V DC 2
Analog inputs	2 • -20/0 to +20 mA or • -10/0 to +10 V
Analog output	1 • 0-20 mA or • 0-10 V resistive load
Thermistor input	1, isolated
Compliance	
Compliance	IEC 61800-5-1

¹⁾ Refer to Design Guide for more information.


Key specifications for 6-pulse, low-harmonic or regenerative enclosed drives

Environmental	6-pulse	Low-harmonic & regenerative
Voltage rating	3 x 380-500 V AC, -15%/+10%	
Current range	206-588 A	385-1710 A
Overload capacity	110/150% for 1 minute every 5 minutes ¹⁾	
Protection rating	IP21/UL Type 1, IP54	

¹⁾ 1 minute every 10 minutes, for frames FE9 and FE10
1 minute every 5 minutes, for all other frames

Control options

Functional extensions	Description
General Purpose I/O OC7C0	General purpose I/O extension board (3xDI, 2xDO, 2xAI, 1xAO)
Relay Option OC7R0	Relay I/O extension board, with 3 relays
Encoder/Resolver Option OC7M0	Encoder/Resolver extension board (TTL, HTL, SinCos, SSI, HIPERFACE, EnDat, BiSS, resolver)
Temperature Measurement OC7T0	Temperature measurement extension board with 5 channels
I/O and Relay Option OC7C1	I/O extension



Dimensions

Frame		6-pulse enclosed drives		Low-harmonic & regenerative enclosed drives			
		FE09	FE10	AE10 + IE10	AE11 + IE11	2 x AE10 + 2 x IE10	2 x AE11 + 2 x IE11
[mm]	Width	400	600	800	1200	2200	2400
	Height	2300 ¹⁾	2300 ¹⁾	2300 ¹⁾²⁾	2300 ¹⁾²⁾	2300 ¹⁾²⁾	2300 ¹⁾²⁾
	Depth	600	600	600	600	600	600
[in]	Width	15.7	23.6	31.5	47.2	86.6	94.5
	Height	90.6 ¹⁾	90.6 ¹⁾	90.6 ¹⁾²⁾	90.6 ¹⁾²⁾	90.6 ¹⁾²⁾	90.6 ¹⁾²⁾
	Depth	23.6	23.6	23.6	23.6	23.6	23.6

¹⁾ With 200 mm/7.8 in plinth and lifting rails, without lifting rails -101 mm/4.0 in
²⁾ If IP21 cabinet total height is 2400 mm/94.5 in

The Danfoss logo is written in a white, cursive script font on a red rectangular background.

ENGINEERING
TOMORROW



Imagine versatile and highly secure power conversion and motor control. Intensely powerful and compact converters and drives built to optimize a vast range of systems while giving you the flexibility to distribute intelligence the way you want. Paving the way for a new dimension, where open, connected and intelligent systems are the new reality.



 **Open up a new dimension with iC7 series**
iC7-Automation | iC7-Marine | iC7-Hybrid

Contact us 

AM480047856372en-000201 | © Copyright Danfoss Drives | 2025.01

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.