

Data Sheet

ePowerpack ED-EP130

Low voltage motor and converter system

FEATURES

- Competitive and compact size allows for easy installation
- Integrated structure provides up to 93 % efficiency
- High enclosure class IP67 – sealed from moisture and dust
- Embedded with SAE flange for quick coupling
- Package test ensures the whole unit is within higher consistency
- Low energy consumption and environmentally friendly

SOFTWARE FEATURES

- Motor speed control via CANbus / analog signal
- Configurable Power Map curve

TYPICAL APPLICATIONS

- Scissor lift
- Boom lift
- Hydraulic station



GENERAL

Danfoss ePowerpack is intelligently designed for maximizing efficiency and compactness.

ePowerpack consists of a high-performance, interior permanent magnet motor and a high-power, passive air-cooled converter with a full-featured digital signal processor. Variants include optional gear pumps with different power settings in software.

These systems are optimal for MEWP and off-highway applications, providing hydraulic flows that fit demanding criteria.

SPECIFICATIONS

General	
Control mode	Speed
Speed request	CAN / analog
Flange	SAE A
Shaft	ANSI B92.1-9T-16/32 internal spline

Cooling	
Cooling method	Passive air-cooling

Ambient Conditions	
Storage temperature range	-40°C - +85°C
Operating temperature range	-40°C - +65°C
Absolute maximum device internal temperature	Motor +150°C, inverter +95°C
Altitude	2000 m
Relative humidity	< 95 %
Enclosure class	IP67

Connections	
Battery / DC-link side cable cross section	Up to 50 mm ² (Cu)
Battery / DC-link connection	2x M6x16 threaded terminal connection (B+, B-)
Battery / DC-link connections cable lug size	50-6
Battery / DC-link side recommended cable lug	50 mm ² : Druseidt 03227 (straight), 03842 (right-angled 90°) https://druseidt.de
LV connector	8-pin Tyco electronics AMPSEAL connector https://www.te.com
LV connector type	1-776276-1 (see Picture 1)
LV connector pin configuration	See section SIGNAL CONNECTOR PINOUT
LV mating connector type	TE 776286-1
LV mating connector pin type	0.5-1.25 mm ² : TE 770854-3 (gold plated)

Standards and classifications	
EMC requirements: IEC61800-3:2018	
Vibration class IEC 60068-2	
- Vibration (Sinusoidal): IEC 60068-2-6:2007 - Vibration (Broadband random): IEC 60068-2-64 Edition 2.1 2019 - Shock: IEC 60068-2-27:2008 - Bump: IEC 60068-2-27:2008	


ED-EP130-T20-24-3600	
Rated voltage	24 V _{DC}
Operating voltage	16.8-33 V _{DC}
Bus rated current @ rated voltage	92 A _{DC}
Bus maximum current @ rated voltage	180 A _{DC}
Rated phase current (S2-60 min)	65 A _{RMS}
Maximum phase current (S2-30 s)	200 A _{RMS}
Rated torque	6.3 Nm
Maximum torque	20.0 Nm
Rated speed	3000 rpm
Maximum speed	3600 rpm
Power @ S2-60 min	2.0 kW
Power @ S3-55 %	2.5 kW
Weight	11.3 kg
Overall dimensions L x W x H	244 x 138 x 232.5 mm (see Picture 2)

ED-EP130-T22-24-4000	
Rated voltage	24 V _{DC}
Operating voltage	16.8-33 V _{DC}
Bus rated current @ rated voltage	135 A _{DC}
Bus maximum current @ rated voltage	220 A _{DC}
Rated phase current (S2-60 min)	110 A _{RMS}
Maximum phase current (S2-30 s)	220 A _{RMS}
Rated torque	9.6 Nm
Maximum torque	22.0 Nm
Rated speed	3000 rpm
Maximum speed	4000 rpm
Power @ S2-60 min	3.0 kW
Power @ S3-55 %	3.5 kW
Weight	13.5 kg
Overall dimensions L x W x H	269 x 138 x 232.5 mm (see Picture 3)

ED-EP130-T29-48-4000	
Rated voltage	48 V _{DC}
Operating voltage range	36.4 to 57.6 V _{DC}
Bus rated current @ rated voltage	90 A _{DC}
Bus maximum current @ rated voltage	150 A _{DC}
Rated phase current (S2-60 min)	80 A _{RMS}
Maximum phase current (S2-30 s)	200 A _{RMS}
Rated torque	13.0 Nm
Maximum torque	29.0 Nm
Rated speed	3000 rpm
Maximum speed	4000 rpm
Power @ S2-60 min	4.0 kW
Power @ S3-55 %	5.0 kW
Weight	13.5 kg
Overall dimensions L x W x H	269 x 138 x 232.5 mm (see Picture 3)




SIGNAL CONNECTOR PINOUT

PIN	Signal name	Description	Note
1	Main Relay Coil Driver	The main relay is driven (connected to the negative end of the relay drive)	Continuous output current $\leq 1.5A$
2	Key Switch	Key input switch, providing power to logic	Max input current 2A, Voltage: 16.8-33V _{DC}
3	Pot Wiper	Analog throttle signal input	Input impedance 75K Ω $\pm$ 10%, Voltage: 0-5V
4	ENABLE	Enable signal input	Maximum voltage 33V High Level $\geq 7V \pm 0.3V$ Low level: $\leq 4V \pm 0.3V$
5	DIRECTION	Directional signal input	Maximum voltage 33V High Level $\geq 7V \pm 0.3V$ Low level: $\leq 4V \pm 0.3V$
6	CAN_H	CAN H	Max 500Kbs, without 120 Ω inside
7	CAN_L	CAN L	Max 500Kbs, without 120 Ω inside
8	I/O GND	I/O GND	




Picture 1 Connector

PERFORMANCE CURVES




DIMENSIONS



Picture 2 Dimensions for ED-EP130-T20-24-3600

Dimension	Length
L	244 mm
W	138 mm
H	232.5 mm

Table 1 Dimensions for ED-EP130-T20-24-3600



Picture 3 Dimensions for ED-EP130-T22-24-4000 and ED-EP130-T29-48-4000

Dimension	Length
L	269 mm
W	138 mm
H	232.5 mm

Table 2 Dimensions for ED-EP130-T22-24-4000 and ED-EP130-T29-48-4000

PRODUCT CODE AND OPTIONS

Product code	Description
ED-EP130-T20/22/29-24/48-3600/4000	ED - electric sub-system/system products
	EP130 – motor and converter system
	e.g. T20 - peak torque 20 Nm
	e.g. 24 - 24 V _{DC} rated voltage
	e.g. 3600 maximum speed

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.