



# Danfoss Hansen® Universal Quick Disconnect Blind-Mate (UQDB)

One partner, every solution

# Danfoss Hansen® Universal Quick Disconnect Blind-Mate (UQDB)

Danfoss Hansen **Universal Quick Disconnect Blind-Mate (UQDB)** has been designed with OCP (Open Compute Project) community to set industry standard for thermal management application in data centers.

This quick disconnect coupling is available in 4 different sizes (as the UQD: -02/-04/-06/-08) and complies with OCP specification requirements.

Danfoss UQDB offers a self-alignment feature to help connect in location with limited access or visibility and guarantees 100% helium-leak testing on every coupling.



## Features and Benefits

- Designed per OCP UQDB specifications
- “Blind-connection” thanks to self- alignment feature with radial compensation of 1 mm
- Push-to-connect design
- Direct connection between servers and manifolds
- High flow and reduced pressure drop for an improved system efficiency
- Flat-face dry break design to avoid spillage during connection/ disconnection
- Sizes available: -02/-04/-06/-08
- High reliability and 100% helium-leak tested
- Standard material: 303 stainless steel for excellent corrosion resistance
- Standard seal material: EPDM for excellent fluid compatibility
- Terminal ends are ORB
- Operating temperature: 10°C - 65°C (50°F - 149°F)
- Working pressure: min. 10 bar
- QR code marking to help identify and track production parts




# Solutions to your liquid cooling challenges

## Inner Rack Solutions

Danfoss' direct-to-chip cooling solutions extend into the racks through efficient routing of flexible, kink-free hoses, and leak free, helium-tested couplings.

Danfoss has a **comprehensive portfolio of premium fluid conveyance products** to meet your thermal management system needs.



Physical characteristics

Size	Body Size	Nominal Flow Dia-meter	Max operating pressure						Min burst pressure						Rated Flow		Cv Value	Air Inclusion	Fluid Loss	Mis-alignment (radial)
			Connected		Socket / Female Half		Plug / Male Half		Connected		Socket / Female Half		Plug / Male Half							
	(in)	(mm)	(bar)	(psi)	(bar)	(psi)	(bar)	(psi)	(bar)	(psi)	(bar)	(psi)	(bar)	(psi)	(lpm)	(gpm)	-	cc. max.	cc. max.	(mm)
UQDB02	1/8	2.8	20	290	20	290	20	290	60	870	60	870	60	870	2.1	0.55	0.31	0.04	0.02	1
UQDB04	1/4	5.5	16	232	16	232	16	232	48	696	48	696	48	696	6.4	1.7	1.22	0.04	0.025	1
UQDB06	3/8	6.3	10	145	10	145	10	145	30	435	30	435	30	435	11.36	3.0	2.23	0.093	0.035	1
UQDB08	1/2	7.9	10	145	10	145	10	145	30	435	30	435	30	435	17.8	4.7	3.76	0.096	0.044	1



Applications & Markets

- Direct-to-chip liquid cooling
- Thermal management

Seal Elastomer Data


Seal Elastomer	Operation Temperature Range	
	C°	F°
EPDM	-40°C +150°C	-40°F +302°F

Size	Performance Parameters			
	Plug Recommended	Torque	Socket	Torque
	ORB Size	N.m	Recommended ORB Size	N.m
UQDB02	7/16-20 UNF-2A	9-10	9/16-18 UNF-2A	15-17
UQDB04	9/16-18 UNF-2A	15-17	3/4-16 UNF-2A	25-28
UQDB06	3/4-16 UNF-2A	25-28	7/8-14 UNF-2A	30-33
UQDB08	7/8-14 UNF-2A	30-33	1 1/16-12 UNF-2A	48-53

Figure 1  
SocketFigure 2  
Plug

## Dimensions

OCP UQDB size	Part number	Part	Details		Dimensions						E2E length
			Thread/size	Fig.	A		B		C		
			ORB	n°	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
UQDB02	2UQBS56ORM	Socket	9/16"-18	1	33.6	1.32	23.6	0.93	20	0.79	35.8-37.2
UQDB02	2UQBP44ORM	Plug	7/16"-20	2	36.1	1.42	27	1.06	20	0.79	
UQDB04	4UQBS75ORM	Socket	3/4"-16	1	39.6	1.55	28.5	1.12	23.6	0.92	44.0 - 45.4
UQDB04	4UQBP56ORM	Plug	9/16"-18	2	45.32	1.78	35.3	1.39	25	0.98	
UQDB06	6UQBS87ORM	Socket	7/8"-14	1	44.4	1.74	31.7	1.24	28.4	1.11	47.5 - 48.9
UQDB06	6UQBP75ORM	Plug	3/4" -16	2	49.9	1.96	38.9	1.53	28.4	1.11	
UQDB08	8UQBS106ORM	Socket	1 1/16"-12	1	50.7	2.00	35.6	1.40	31.3	1.23	51.8 – 53.2
UQDB08	8UQBP87ORM	Plug	7/8"-14	2	55.6	2.19	42.9	1.69	31.3	1.23	





Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

**Danfoss A/S**  
Nordborgvej 81  
6430 Nordborg  
Denmark  
danfoss@danfoss.com  
CVR reg. no. 20165715