



Gas sensor

DST G290

For general HVAC purposes

Description

The new A3 gas sensor is designed for use in general HVAC applications.

Accurate and compact leak detector designed based on IEC 60355-2-40 and compatible to customer's application specifications both hardware and software.

Photoacoustic technology offers min. 15-year lifetime, immunity to poisoning, fast response time and reliable self-diagnostics.

Features & Benefits

- Designed for use with R290 (others on request)
- Output modes: Modbus RTU on RS485, Relay, Relay & Modbus
- Supply voltage: 5 V DC, 12 – 24 V AC/DC
- Designed for min. 15-year lifetime without calibration
- Self-diagnostics
- CE marked
- ATEX compliant signal relay

Product details

General data

Sensor specifications

Measuring range	0 – 100% LFL
Alarm threshold	15% LFL
Operating temperature	-40 – 80 °C
Maximum temperature (intermittent)	-40 – 105 °C
Storage temperature	-40 – 80 °C
Operating pressure	700 – 1200 mbar
Operating humidity	0 – 100% RH
Enclosure protection (EN 60529)	IP55
Connector protection (EN 60529)	IP56 and IP57

Performance specifications

Accuracy at ambient (15 – 25 °C), 0 – 25% LFL	±2.5% LFL
Accuracy across operating range, 0 – 25% LFL	±5.0% LFL
Response time	< 27 s
Sensor recovery time	< 5 minutes in clean air
Mitigation recovery timer	5 sec can be customized
Alarm response	Depending on the output mode: Relay open – LED red – Alarm flag
Reset setpoint	2.5% LFL below alarm setpoint

Electrical specifications

Output mode	Modbus	Modbus	Modbus and Relay ⁽¹⁾	Relay ⁽¹⁾
Supply voltage	12 – 24 V AC / DC ±10%	5 V DC ±10%	12 – 24 V AC / DC ±10%	12 – 24 V AC / DC ±10%
Power consumption	1.0 W max 0.5 W average	0.4 W max 0.3 W average	1.1 W max 0.6 W average	1.1 W max 0.6 W average
Digital output	RS485, 120 Ω termination included in sensor	RS485, 120 Ω termination included in sensor	RS485, 120 Ω termination included in sensor	–
Code number	073G2060	073G2061	073G2062	073G2063


⁽¹⁾ Relay information: 30 V / 1 A max switching load (signal relay).

Mechanical characteristics

Materials – Enclosure	PA66 25% glass filled (Top), PC(Bottom)
Materials – Electrical connection	Nylon
Net weight (depending on the format)	0.04 – 0.06 kg

Dimensions & weights

Dimensions

**NOTE:**

Dimensions are in mm, unless stated otherwise.

Disclaimer/Information:

Sensor stores diagnostic values for warranty analysis. Data can be provided by returning the product. A service fee may apply.

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
EU Declaration	EU-declaration 073R0004.00	Danfoss	EU RoHS
Manufacturer's Declaration	Manufacturers declaration 073R0007.00	Danfoss	ATEX
Manufacturer's Declaration	Manufacturers declaration 073R0006.00	Danfoss	Compliance misc. Standards
Electrical Safety Certificate	UL TEC-03911-M1	UL - Underwriters Laboratories inc.	Compliance misc. Standards

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.