



Pumps

BFP 52

size 3 and 5

Description

BFP 52E fuel pumps - size 3 and 5 are designed for small/medium-sized 2-stage domestic fuel burners up to 42 l/h.

Features & Benefits

- Light oil, kerosene and biofuel blends hereof
- 1 or 2-pipe operation
- 2-stage
- Two built-in pressure regulators
- Solenoid valve cut-off
- Cartridge filter
- Bio compatible pressure and solenoid valve (Bio100 - version)

Applications

- Small/medium-sized domestic fuel burners up to 42 l/h.



Compatible with heating oil up to 100% biodiesel (FAME and UCOME)

Ordering

Product code numbers

Product Type	Nozzle/pressure outlet	ROTATION	1 or 2 stage	Capacity [l/h]	Biofuel blend	Code number
BFP 52	L	R	2	42.00	10	071N2207
BFP 52	L	L	2	42.00	10	071N2212
BFP 52	L	L	2	24.00	30	071N2218
BFP 52	L	L	2	24.00	10	071N2251
BFP 52	L	L	2	42.00	10	071N2252
BFP 52	L	R	2	24.00	10	071N2253
BFP 52	L	R	2	42.00	10	071N2254
BFP 52	L	R	2	24.00	10	071N2257
BFP 52	L	L	2	24.00	10	071N2264
BFP 52	L	R	2	24.00	10	071N2273
BFP 52	R	L	2	16.00	10	071N2286
BFP 52	R	L	2	24.00	10	071N2299
BFP 52	L	L	2	24.00	10	071N3201
BFP 52	L	L	2	42.00	10	071N3202
BFP 52	L	R	2	24.00	10	071N3203

Identification

Example:

BFP **B** **52** **E** **L** **5** **L**

BFP	
B	B: biofuel ready for up to 100%
5	5: two stages, two pressure regulators
2	2: two solenoid valves
E	E: use electrical air damper
L	R: clockwise rotation L: counter-clockwise rotation
5	3: capacity 24 l/h 5: capacity 42 l/h
L	R: right hand nozzle outlet L: left hand nozzle outlet

Nozzle capacity at 4.3 cSt., 10 bar, 2800 min⁻¹

Accessories code numbers

If your product code is not listed as a related product for any accessories, please reach out to us for assistance.



071G0200

**CABLE FOR NC VALVE,
500 mm OEM**

CABLE FOR NC VALVE, 500
mm OEM

Related products

071N2203

071N2286

071N3204



071G0235

**CABLE FOR NC VALVE, 180
mm OEM**

CABLE FOR NC VALVE, 180 mm OEM

Related products

071N2286

071N3204



071G0202

**CABLE FOR NC VALVE,
280 mm OEM**

CABLE FOR NC VALVE, 280
mm OEM

Related products

071N2203

071N2286

071N3204



071G0204

**CABLE FOR NC VALVE, 710
mm OEM**

CABLE FOR NC VALVE, 710 mm OEM

Related products

071N2203

071N2286

071N3204



071G0205

**CABLE FOR NO VALVE,
710 mm OEM**

CABLE FOR NO VALVE, 710
mm OEM

Related products

071N2203

071N2286

071N3204



071N0007

**NC SERVICE VALVE FOR 24 V
DC**

NC SERVICE VALVE FOR 24 V DC

Related products

071N2203



071N0062

Coil 24 V AC.

Coil 24 V AC.

Related products

071N2203



071N0604

**PLUG 1/8" FOR P AND V
PORTS.**

PLUG 1/8" FOR P AND V PORTS.

Related products

071N2203



071B0011

BUSH 32 x 54 mm.

BUSH 32 x 54 mm.

Related products

071N2203



071N0047

BUSH 32 x 54 mm W. STD. FLANGE.

BUSH 32 x 54 mm W. STD. FLANGE.

Related products

071N2203



071G0201

**CABLE FOR NO VALVE,
500 mm OEM**CABLE FOR NO VALVE, 500
mm OEM

Related products

071N2203



071N0010

COIL 220/240 V AC.

COIL 220/240 V AC.

Related products

071N2203



071N0601

NO COIL 220/240 V

NO COIL 220/240 V

Related products

071N2203



071N0061

COIL 110/120 V AC.

COIL 110/120 V AC.

Related products

071N2203



071N1033

**O-rings for cover (ø54)
and regulator (ø9,75)**O-rings for cover (ø54) and
regulator (ø9,75)

Related products

071N2203



071N1055

**PLUG FOR 1/4"
CONNECTIONS**

PLUG FOR 1/4" CONNECTIONS

Related products

071N2203



071N0050

NC VALVE

NC VALVE

Related products

071N2203



071G2245

CABLE FOR NC VALVE, 2100 mm

CABLE FOR NC VALVE, 2100 mm

Related products

071N2203

If your product code is not listed as a related product for any accessories, please reach out to us for assistance.

Spare parts code numbers

If your product code is not listed as a related product for any accessories, please reach out to us for assistance.



071B0011

BUSH 32 x 54 mm.

BUSH 32 x 54 mm.

Related products

[071N2209](#) [071N2218](#) [071N2257](#) [071N2273](#)
[071N2286](#) [071N2299](#) [071N3201](#) [071N3202](#)
[071N3203](#) [071N3204](#)


071N0041

CHANGE OVER SCREW 2-PIPE OPERATION

CHANGE OVER SCREW 2-PIPE OPERATION

Related products

[071N2209](#) [071N2218](#) [071N2257](#)
[071N2273](#) [071N2286](#) [071N2299](#)
[071N3201](#) [071N3202](#) [071N3203](#)
[071N3204](#)


071N0005

NO SERVICE VALVE FOR USE W. NC COIL

NO SERVICE VALVE FOR USE W. NC COIL

Related products

[071N2209](#) [071N2218](#) [071N2257](#) [071N2273](#)
[071N2286](#) [071N2299](#) [071N3201](#) [071N3202](#)
[071N3203](#) [071N3204](#)


071N3010

NO SERVICE VALVE FOR USE W. NO COIL

NO SERVICE VALVE FOR USE W. NO COIL

Related products

[071N2218](#) [071N2257](#) [071N2273](#)
[071N2286](#) [071N2299](#) [071N3201](#)
[071N3202](#) [071N3203](#) [071N3204](#)



071N0047

**BUSH 32 x 54 mm W. STD.
FLANGE.**

BUSH 32 x 54 mm W. STD.
FLANGE.

Related products

- [071N2218](#)
- [071N2257](#)
- [071N2273](#)
- [071N2286](#)
- [071N2299](#)
- [071N3201](#)
- [071N3202](#)
- [071N3203](#)
- [071N3204](#)



071N3011

NC LE-S SERVICE VALVE

NC LE-S SERVICE VALVE

Related products

- [071N2218](#)
- [071N2257](#)
- [071N2273](#)
- [071N2286](#)
- [071N2299](#)
- [071N3201](#)
- [071N3202](#)
- [071N3203](#)
- [071N3204](#)



071N1033

**O-rings for cover (ø54) and
regulator (ø9,75)**

O-rings for cover (ø54) and
regulator (ø9,75)

Related products

- [071N2218](#)
- [071N2257](#)
- [071N2273](#)
- [071N2286](#)
- [071N2299](#)
- [071N3201](#)
- [071N3202](#)
- [071N3203](#)
- [071N3204](#)



071N0064

**CARTRIDGE STRAINER
BFP**

CARTRIDGE STRAINER BFP

Related products

- [071N2218](#)
- [071N2257](#)
- [071N2273](#)
- [071N2286](#)
- [071N2299](#)
- [071N3201](#)
- [071N3202](#)
- [071N3203](#)
- [071N3204](#)



071N0074

**PLUG FOR CARTRIDGE
FILTER.**

PLUG FOR CARTRIDGE FILTER.

Related products

- [071N2218](#)
- [071N2257](#)
- [071N2273](#)
- [071N2286](#)
- [071N2299](#)
- [071N3201](#)
- [071N3202](#)
- [071N3203](#)
- [071N3204](#)



071N1006

COIL T85 230 V AC

COIL T85 230 V AC

Related products

- [071N2218](#)
- [071N2257](#)
- [071N2273](#)
- [071N2286](#)
- [071N2299](#)
- [071N3201](#)
- [071N3202](#)
- [071N3203](#)
- [071N3204](#)



071N1055

PLUG FOR 1/4"
CONNECTIONS

PLUG FOR 1/4" CONNECTIONS

Related products

071N2218

071N2257

071N2273

071N2286

071N2299

071N3201

071N3202

071N3203

071N3204



071N1007

NO COIL T85 230 V AC

NO COIL T85 230 V AC

Related products

071N2218

071N2257

071N2273

071N2286

071N2299

071N3201

071N3202


071N3203

071N3204

If your product code is not listed as a related product for any accessories, please reach out to us for assistance.

Functions

Operation



From the suction inlet (S) fuel is drawn through the filter (H) to the gear set, where the pressure is increased. By means of the diaphragm (D) in the pressure regulator for stage 1 (T_1), the pressure is kept constant at the value set on adjustment screw (P_1).

When voltage is applied to the NC-valve, it opens and releases fuel to the nozzle outlet.

When voltage is applied to the NO-valve, it closes and puts the pressure regulator (T_1) out of function.

The pressure now rises to the pressure regulator (T_2) value for stage 2 set on adjustment screw (P_2).

In 2-pipe systems the excess fuel is led back to the return outlet (R) and the tank. In 1-pipe systems with plugged return outlet (R) and screw (A) removed, the fuel is returned internally to the gear set (see figure).

Cut-off function, solenoid valve

When the burner stops, the voltage to the solenoid valves is cut off.

The NO-valve opens and the NC-valve closes and cuts off the fuel flow to the nozzle outlet immediately.

Bleeding

In 2-pipe systems the pump is self-priming, i.e. bleeding is performed via the constriction (O) to the return outlet (R).

In 1-pipe systems with plugged return outlet (R), bleeding must be performed through the nozzle outlet (E) or the pressure gauge port (P).

Warranty

For pumps used outside the stated technical data and used with fuel containing abrasive particles Danfoss cannot give any warranty.

Note!

Do not mount the pump with the solenoid valve pointing downwards.

The solenoid valve must be replaced after 250.000 operations or 10 years (approved life expectancy).

By changing the materials of the components within our pumps, in relation to the different types of fuels - we ensure all product components are 100% bio compatible.

Product details

General data


BFP 52E	3	5
Fuel type	Standard fuel according to DIN EN 51603-1 and biofuel according to DIN EN 51603-6;-8 and EN14214	
Viscosity range (measured in suction inlet) ¹⁾	(1.3) 1.8 to 12.0 cSt. (mm ² /s)	
Filter area/mesh	11 cm ² /200 µm	
Pressure range, stage 1 ^{1) 2)}	7 to 15 bar	
Pressure range, stage 2 ^{1) 2)}	10 to 25 bar	
Default setting, stage 1	10 ±1 bar	
Default setting, stage 2	13 ±1 bar	
Max. pressure in suction inlet/return outlet	2 bar	
Speed	2400 to 3450 min ⁻¹	1400 to 3450 min ⁻¹
Max. starting torque	0.1 Nm	0.12 Nm
Ambient/transport temperature	-20 to +70° C	
Temperature of medium	0 to +70° C	
Coil power consumption	9 W	
Rated voltage (other voltages on request)	230 V, 50/60 Hz	
Coil enclosure	IP 40	
Shaft/neck	EN 225	

1) Max. 12 bar at 1.3 cSt., max. 15 bar at 1.8 cSt.

2) If blend oil used, technical data can be different


Capacity

Nozzle capacity [l/h]




Operating torque [Nm]

Power consumption [W]



Dimensions & weights

Weight	Fuel Pump type BFP 52E, size 3 and 5	
	Gross weight	1.144 kg
Net weight	1.143 kg	
Volume	1.203 Liter	



Connections

Example shows BFP 52 L5L

P₁: Pressure adjustment stage 1

P₂: Pressure adjustment stage 2

S: Suction inlet G 1/4


R: Return outlet G 1/4

E: Nozzle outlet G 1/8

P: Pressure gauge port G 1/8

V: Vacuum gauge port G 1/8


H: Filter



Note! Shaft rotation, location of nozzle outlet and other connections are seen from shaft end.

RH: R-rotation

LH: L-rotation




Service

Change-over and filter replacement

H: Filter

A: 2-pipe operation, with screw

1-pipe operation, without screw



Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
Manufacturer's Declaration	Danfoss MD 071NP.05	Danfoss	EU RoHS
EU-UK Declaration	Danfoss EU-UK 071NP.05	Danfoss	LVD
Electrical Safety Certificate	DIN CERTCO 5S222	DIN CERTCO	
Electrical Safety Certificate	SEMKO SE-S-2101293R3	Intertek Semko	
Export Control Declaration	Oil pumps BFP/BFA/BFM	Danfoss	

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Products Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.