

SV

Solenoid Valves



Danfoss

Solenoid Valves


Application Notes

Basic Operation: Solenoid Valves

Solenoid operated poppet and spool valves utilize a coil placed over a tube, in which an armature is attracted to a pole end when the coil is energized. The movement of the armature against a spring either pulls or pushes a poppet or a spool to change the flow path. A spool valve can be 2, 3 or 4-ported with 2 or 3-positions. A direct acting poppet can be 2 or 3-ported with 2-positions. For pilot operated valves, a pilot poppet will open or close an orifice in the main poppet and are limited to 2-port 2-position normally open or closed applications. Poppet type valves have minimal leakage (drops/min), whereas spool valves will leak internally at a much higher rate due to the nature of the design.


Normally Closed Pilot Operated Poppet Type

Normally closed pilot operated poppet type valves are 2-way, 2-position. In the de-energized position, there is free flow from port 1 to 2 and flow is blocked from port 2 to 1. When the coil is energized, the armature pulls the pilot poppet off its seat allowing the main poppet to move back, which allows flow between port 2 and 1. These valves are available in two options in the energized position: 1) Restricted flow from port 1 to 2 or 2) Free flow from port 1 to 2. These valves are commonly used in applications to hold a load, block a flow path, or unload flow to tank.




Normally Open Pilot Operated Poppet Type

Normally open pilot operated poppet type valves are 2-way, 2-position. In the de-energized position, there is free flow from port 2 to 1 and two options for flow from port 1 to 2: 1) restricted flow from port 1 to 2 or 2) free flow from port 1 to 2. When the coil is energized, the armature pushes the pilot poppet onto its seat causing the main poppet to block flow between port 2 and 1. In the energized position, free flow can take place from port 1 to 2. These valves are commonly used in applications to hold a load, block a flow path, or unload flow to tank.



2-Way Normally Open and Normally Closed Spool Type

2-way, 2-position spool type valves are fully open in one condition and closed in both directions in the other condition. These valves are used in a variety of applications where it is important to limit the initial pressure drop when the valve is open. Spool leakage will take place, so to hold a load in place a poppet-type valve is recommended. They can be used in regenerative circuits, pump unloading and in conjunction with a compensator to create two speeds.




Solenoid Valves

Application Notes


Normally Closed Direct Acting Double Blocking Poppet Type

Direct acting double blocking valves are normally closed 2-position, bi-directional poppet type valves. In the de-energized condition, the valve blocks flow in either direction with a very low leakage. When energized, flow passes freely in both directions. These valves are ideal for use as emergency lowering valves or to hold pressure in a cylinder, preventing upstream shock pressures from opening the valve.




Normally Closed and Normally Open Pilot Operated Double Blocking Poppet Type

Pilot operated double blocking valves are 2-position, bi-directional poppet type valves that are fully open in one condition and closed in the opposite condition. These valves are ideal for isolating and holding actuators in position, as they have very low leakage in the closed condition. The pilot operated design provides a high flow capacity in a compact product.




3-Way, 2-Position Spool Type

3-way, 2-position spool type valves are direct acting solenoid operated directional control valves. The valve can be used normally open, normally closed or as a selector and various port configurations are available. Always consult the operating envelope to establish the maximum working parameters for the chosen application. Spool leakage will take place, so to hold a load in place a poppet-type valve is recommended. These valves are commonly used to control single acting cylinders, clutches or motors.



3-Way, 2-Position Poppet Type

3-way, 2-position poppet type valves are direct acting solenoid operated directional control valves. This valve is designed for hydraulic circuits requiring very low leakage and can be used for load holding and blocking applications.




Solenoid Valves

Application Notes


4-Way, 2-Position Spool Type

4-way, 2-position spool type valves are direct acting solenoid operated directional control valves. There are various spool configurations available often used to control double acting cylinders or motor reversing applications.




4-Way, 3-Position Spool Type

4-way, 3-position spool type valves are direct acting solenoid operated directional control valves. They control the direction of the fluid within a system and offer various center configurations when de-energized, including all ports blocked, all ports open, motor spools and pressure to tank. Spool leakage will take place, so additional poppet-type holding valve on the work ports is recommended to hold a load in place. These are commonly used to control double acting cylinders or in motor reversing applications.



5-Way, 3-Position Spool Type

5-way, 3-position spool type valves are direct acting solenoid operated directional control valves. They control the direction of the fluid within a system and offer center configurations where all ports are blocked or with the work ports connected to tank. A load sense port is also included, which is closed until the valve is energized, connecting the load sense port to the inlet port. Spool leakage will take place, so an additional poppet-type holding valve on the work ports is recommended to hold a load in place. These are commonly used to control double acting cylinders or in motor reversing applications.




Application Recommendations

- Always refer to the performance envelope curves when specifying a solenoid valve.
- Over-flowing the valve may result in unsolicited spool movement and reversal of the function.
- Always consider that there may be a pressure limitation on the port connected to the core tube.
- Increase in coil temperature may affect the performance of the valve at the limits of the operating envelope.
- The coil temperature will increase above the ambient, so care should be taken not to exceed the insulation and encapsulation limits of the coil.
- Shifting times will vary when a valve is used with high viscosity fluids or at low temperatures.
- Pilot operated valves may produce a momentary opening as pressures equalize over the main poppet.
- All spool valves will leak internally. The amount of leakage will vary depending on the spool configuration and the direction of leakage.
- 3, 4, and 5-way spool valves are designed with a 'zero overlap' spool transition unless otherwise specified on the individual product page. However, due to manufacturing tolerances, a closed transition or highly restricted open transition could occur.


Solenoid Valves

Application Notes


Typical Applications




▲ Holding and Lowering




▲ Independent Cylinder




▲ Pump Unloading



▲ Regenerative Circuit



▲ Single Acting Cylinder Control




▲ Selector Circuit


Solenoid Valves

Application Notes


Typical Applications




▲ Load Sense



▲ 4-Way, 3-Position



▲ Series (Open Center)



▲ Parallel (Closed)


Solenoid Valves

Manual Override Options


Note: Manual overrides are intended for emergency use only, not for continuous duty operation.

"Omit/PN" - Push Pin

08 and 15 series



10 series



Product Availability


SVP08-CDB	HSV08-23-01	SV15-34-02	SV08-34-05
EVK06/C5	SV10-23-01	SV08-34-03	HSV08-34-05
SVP08-NO/NOR	CP521-21	SV10-34-03	SV10-34-05
SVP10-NO/NOR	SV08-23-03	SV15-34-03	SV15-34-05
SV08-22-01	SV08-34-02	SV08-34-04	SV10-34-11
EVH 06/D5	HSV08-34-02	SV10-34-04	SV10-35-02
SV08-23-01	SV10-34-02	SV15-34-04	SV10-35-05

OPERATION

1. Push the pin toward the valve using a hex key to actuate override
2. Remove the hex key to return to neutral position

"OPS" - Protected Push Pin

08 and 10 Series



Product Availability


SVP08-CDB	SV10-23-01	SV10-34-04
EVK06/C5	SV08-23-03	SV08-34-05
SVP08-NO/NOR	SV08-34-02	SV10-34-05
SVP10-NO/NOR	SV10-34-02	SV10-34-11
SV08-22-01	SV08-34-03	SV10-35-02
EVH 06/D5	SV10-34-03	SV10-35-05
SV08-23-01	SV08-34-04	

OPERATION


1. Screw the nut clockwise to actuate override
2. Unscrew the nut counterclockwise to return to neutral position

"PB" - Push Button

08 series



10 series



Product Availability

SVP08-CDB	SV08-23-01	SV10-34-02	HSV08-34-05
EVK06/C5	HSV08-23-01	SV08-34-03	SV10-34-05
SVP08-NO/NOR	SV10-23-01	SV10-34-03	SV10-34-11
SVP10-NO/NOR	SV08-23-03	SV08-34-04	SV10-35-02
SV08-22-01	SV08-34-02	SV10-34-04	SV10-35-05
EVH 06/D5	HSV08-34-02	SV08-34-05	

Neutral

OPERATION


1. Push the button toward the valve to actuate override
2. Release the button to return to neutral position

Solenoid Valves

Manual Override Options

Note: Manual overrides are intended for emergency use only, not for continuous duty operation.

"SPS" - Screw Type




Product Availability			
SVP08-CDB	HSV08-23-01	SV08-34-03	HSV08-34-05
EVK06/C5	SV10-23-01	SV10-34-03	SV10-34-05
SVP08-NO/NOR	SV08-23-03	SV15-34-03	SV15-34-05
SVP10-NO/NOR	SV08-34-02	SV08-34-04	SV10-34-11
SV08-22-01	HSV08-34-02	SV10-34-04	SV10-35-02
EVH 06/D5	SV10-34-02	SV15-34-04	SV10-35-05
SV08-23-01	SV15-34-02	SV08-34-05	

OPERATION

1. Screw the knob clockwise to actuate override
2. Unscrew the knob counterclockwise to return to neutral position

"PAT" - Push and Twist



Product Availability		
SVP10-NO/NOR	SV10-34-03	SV10-34-11
SV10-23-01	SV10-34-04	SV10-35-02
SV10-34-02	SV10-34-05	SV10-35-05

OPERATION

1. Push the knob toward the valve until it stops.
2. Twist the knob clockwise until the override locks in place (180 degrees).
3. Release the knob to leave in the actuated position.
4. To de-activate, push the knob toward the valve slightly.
5. Twist the knob clockwise until the override returns to the neutral position (180 degrees).


Solenoid Valves

Manual Override Options


Note: Manual overrides are intended for emergency use only, not for continuous duty operation.

"PAP" - Push and Pull



08 series



10 series



Neutral



Actuated

OPERATION


1. Push the knob toward the valve to actuate the override in one direction.
2. Pull the knob away from the valve to actuate the override in the opposite direction.
3. In either direction, release the knob to return the override to the neutral position.

Product Availability


SV10-34-02	SV10-35-05	SV10-34-11
SV10-34-05	SV08-34-02	
SV10-35-02	SV08-34-05	

"M" - Screw Type (Pull)

08 series



10 series





Product Availability

SVP08-NCF
SVP08-NC/NCR
SVP10-NC/NCR

Neutral

OPERATION

1. Unscrew the nut counterclockwise to actuate override.
2. Screw the nut clockwise to return to neutral position.




Actuated

Solenoid Valves

Manual Override Options

Note: Manual overrides are intended for emergency use only, not for continuous duty operation.

"S" - Screw Type




Product Availability		
SV13-10-0	SV13-20-0	SV3-12-0
SV13-12-0	SV15-10-0	SV3-16-0
SV13-16-0	SV15-8-0	SV3-20-0

OPERATION

1. Screw the nut clockwise to actuate override.
2. Unscrew the nut counterclockwise to return to neutral position.

"P" - Push Type



Product Availability		
SV13-10-0	SV13-20-0	SV3-12-0
SV13-12-0	SV15-10-0	SV3-16-0
SV13-16-0	SV15-8-0	SV3-20-0

OPERATION



1. Push the button toward the valve to actuate override
2. Release the button to return to neutral position

Solenoid Valves

Manual Override Options

Note: Manual overrides are intended for emergency use only, not for continuous duty operation.


"M" - Pull and Twist

08 series	10, 12, 16, 20 series	Product Availability			
		SBV11-8-C	SV12-10-C	SV13-12-C	SV3-10-C
		SV11-10-4	SV12-8-4	SV13-16-C	SV3-12-C
		SV11-10-3	SV13-10-C	SV14-10-C	SV1-16-C
		SV11-10-C	SBV11-10-C	SV15-8-C	SV2-20-C
		SBV1-10-C			

OPERATION







1. Pull the knob upward until it stops.
2. Twist the knob clockwise until the override tooth is resting securely on top of the detent base slot.
3. Release the knob to leave in the actuated position.
4. To de-activate, pull the knob upward slightly.
5. Twist the knob clockwise until the override tooth is securely engaged in the detent base slot.

"R" - Cable Type

16 and 20 Series	Product Availability	
	SV1-16-C	
	SV2-20-C	

Solenoid Valves

Quick Reference

Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-NC	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated	35 l/min [9 US gpm]	230 bar [3300 psi]	20
	SV15-8-C	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated	38 l/min [10 US gpm]	350 bar [5000 psi]	21
	SVP10-NC	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated	80 l/min [21 US gpm]	230 bar [3300 psi]	22
	SV11-10-C	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated	45 l/min [12 US gpm]	350 bar [5000 psi]	23
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-NCF	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Flow Control	15 l/min [4 US gpm]	230 bar [3300 psi]	24
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-NCR	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	35 l/min [9 US gpm]	230 bar [3300 psi]	26
	SVP10-NCR	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	80 l/min [21 US gpm]	230 bar [3300 psi]	27
	SV13-10-C	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	45 l/min [12 US gpm]	350 bar [5000 psi]	28
	SLP13-10-C	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	95 l/min [25 US gpm]	350 bar [5000 psi]	29
	SV3-12-C	C-12-2/C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	114 l/min [30 US gpm]	210 bar [3000 psi]	30
	SV13-12-C	C-12-2 / C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	114 l/min [30 US gpm]	350 bar [5000 psi]	31
	SV1-16-C	SDC16-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	132 l/min [35 US gpm]	210 bar [3000 psi]	32
	SV13-16-C	SDC16-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	132 l/min [35 US gpm]	350 bar [5000 psi]	33
	SV2-20-C	SDC20-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	230 l/min [60 US gpm]	210 bar [3000 psi]	34
	SV13-20-C	SDC20-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow	230 l/min [60 US gpm]	350 bar [5000 psi]	35

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves

Quick Reference



Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SBV12-8-C	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Direct Acting, Double Blocking	1 l/min [0.25 US gpm]	350 bar [5000 psi]	36
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-CDB	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Direct Acting, Double Blocking	25 l/min [6.6 US gpm]	230 bar [3300 psi]	37
	EVK 06/C5	NCS 06/2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Direct Acting, Double Blocking	40 l/min [10.6 US gpm]	210 bar [3000 psi]	38
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SBV11-8-C	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking	60 l/min [16 US gpm]	350 bar [5000 psi]	39
	SBV1-10-C	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking	76 l/min [20 US gpm]	210 bar [3000 psi]	40
	SBV11-10-C	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking	76 l/min [20 US gpm]	350 bar [5000 psi]	41
	SBV1-12-C	C-12-2 / C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking	114 l/min [30 US gpm]	210 bar [3000 psi]	42
	SBV11-12-C	C-12-2 / C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking	114 l/min [30 US gpm]	350 bar [5000 psi]	43
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-22-02	SDC08-2	Solenoid Valve, 2-way, Spool Type, Normally Closed	18 l/min [4.7 US gpm]	230 bar [3300 psi]	44
	HSV08-22-02	SDC08-2	Solenoid Valve, 2-way, Spool Type, Normally Closed	20 l/min [5.3 US gpm]	350 bar [5000 psi]	45
	SV10-22-02	SDC10-2	Solenoid Valve, 2-way, Spool Type, Normally Closed	35 l/min [9 US gpm]	230 bar [3300 psi]	46
	SV14-10-C	SDC10-2	Solenoid Valve, 2-way, Spool Type, Normally Closed	23 l/min [6 US gpm]	350 bar [5000 psi]	47
	SV15-22-02	NCS 12/2	Solenoid Valve, 2-way, Spool Type, Normally Closed	60 l/min [16 US gpm]	230 bar [3300 psi]	48

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves

Quick Reference








Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-NO	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated	35 l/min [9 US gpm]	230 bar [3300 psi]	49
	SV15-8-O	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated	38 l/min [10 US gpm]	350 bar [5000 psi]	50
	SVP10-NO	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated	80 l/min [21 US gpm]	230 bar [3300 psi]	51
	SV15-10-O	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated	45 l/min [12 US gpm]	350 bar [5000 psi]	52
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-NOR	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	35 l/min [9 US gpm]	230 bar [3300 psi]	53
	SVP10-NOR	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	80 l/min [21 US gpm]	230 bar [3300 psi]	54
	SV13-10-O	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	45 l/min [12 US gpm]	350 bar [5000 psi]	55
	SLP13-10-O	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	95 l/min [25 US gpm]	350 bar [5000 psi]	56
	SV3-12-O	C-12-2/C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	114 l/min [30 US gpm]	210 bar [3000 psi]	57
	SV13-12-O	C-12-2 / C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	114 l/min [30 US gpm]	350 bar [5000 psi]	58
	SV3-16-O	SDC16-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	132 l/min [35 US gpm]	210 bar [3000 psi]	59
	SV13-16-O	SDC16-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	132 l/min [35 US gpm]	350 bar [5000 psi]	60
	SV3-20-O	SDC20-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	230 l/min [60 US gpm]	210 bar [3000 psi]	61
	SV13-20-O	SDC20-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow	230 l/min [60 US gpm]	350 bar [5000 psi]	62
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-22-01	SDC08-2	Solenoid Valve, 2-way, Spool Type, Normally Open	16 l/min [4.2 US gpm]	230 bar [3300 psi]	63
	HSV08-22-01	SDC08-2	Solenoid Valve, 2-way, Spool Type, Normally Open	20 l/min [5.3 US gpm]	350 bar [5000 psi]	64
	SV10-22-01	SDC10-2	Solenoid Valve, 2-way, Spool Type, Normally Open	35 l/min [9 US gpm]	230 bar [3300 psi]	65
	SV14-10-O	SDC10-2	Solenoid Valve, 2-way, Spool Type, Normally Open	23 l/min [6 US gpm]	350 bar [5000 psi]	66
	SV15-22-01	NCS 12/2	Solenoid Valve, 2-way, Spool Type, Normally Open	60 l/min [16 US gpm]	230 bar [3300 psi]	67

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves





Quick Reference

Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	S207	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Direct Acting, Double Blocking	1 l/min [0.25 US gpm]	350 bar [5000 psi]	68
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SBV11-8-O	SDC08-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated, Double Blocking	60 l/min [16 US gpm]	350 bar [5000 psi]	69
	SBV11-10-O	SDC10-2	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated, Double Blocking	76 l/min [20 US gpm]	350 bar [5000 psi]	70
	SBV11-12-O	C-12-2 / C-12-2U	Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated, Double Blocking	114 l/min [30 US gpm]	350 bar [5000 psi]	71
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SVP08-DDB	SDC08-3	Solenoid Valve, 3-way, 2-position, Poppet Type	3 l/min [0.8 US gpm]	230 bar [3300 psi]	72
	EVH 06/D5	NCS 06/3	Solenoid Valve, 3-way, 2-position, Poppet Type	25 l/min [6.6 US gpm]	230 bar [3300 psi]	73
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-23-01	SDC08-3	Solenoid Valve, 3-way, 2-position, Spool Type	18 l/min [4.8 US gpm]	230 bar [3300 psi]	74
	HSV08-23-01	SDC08-3	Solenoid Valve, 3-way, 2-position, Spool Type	15 l/min [4 US gpm]	350 bar [5000 psi]	75
	SV10-23-01	SDC10-3	Solenoid Valve, 3-way, 2-position, Spool Type	35 l/min [9 US gpm]	230 bar [3300 psi]	76
	CP521-21	CP12-3	Solenoid Valve, 3-way, 2-position, Spool Type	60 l/min [16 US gpm]	240 bar [3500 psi]	77
	SV11M-12-3P	C-12-3	Solenoid Valve, 3-way, 2-position, Spool Type	35 l/min [9 US gpm]	350 bar [5000 psi]	78

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves












Quick Reference

Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV07-23-02	CP07-3	Solenoid Valve, 3-way, 2-position, Spool Type	8 l/min [2.11 US gpm]	80 bar [1160 psi]	79
	SV08-23-02	SDC08-3	Solenoid Valve, 3-way, 2-position, Spool Type	18 l/min [4.8 US gpm]	230 bar [3300 psi]	80
	HSV08-23-02	SDC08-3	Solenoid Valve, 3-way, 2-position, Spool Type	15 l/min [4 US gpm]	350 bar [5000 psi]	81
	SV09-23-02	SDC10-3	Solenoid Valve, 3-way, 2-position, Spool Type	21 l/min [5.5 US gpm]	100 bar [1450 psi]	82
	SV10-23-02	SDC10-3	Solenoid Valve, 3-way, 2-position, Spool Type	28 l/min [7.4 US gpm]	230 bar [3300 psi]	83
	SV11-10-3	SDC10-3	Solenoid Valve, 3-way, 2-position, Spool Type	23 l/min [6 US gpm]	350 bar [5000 psi]	84
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-23-03	SDC08-3	Solenoid Valve, 3-way, 2-position, Spool Type	18 l/min [4.7 US gpm]	230 bar [3300 psi]	85
	SV10-23-03	SDC10-3	Solenoid Valve, 3-way, 2-position, Spool Type	28 l/min [7.4 US gpm]	230 bar [3300 psi]	86
	SV4M-12-3P	C-12-3	Solenoid Valve, 3-way, 2-position, Spool Type	42 l/min [11 US gpm]	210 bar [3000 psi]	87
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-23-04	SDC08-3	Solenoid Valve, 3-way, 2-position, Spool Type	12 l/min [3.2 US gpm]	230 bar [3300 psi]	88
	SV10-23-04	SDC10-3	Solenoid Valve, 3-way, 2-position, Spool Type	20 l/min [5.3 US gpm]	230 bar [3300 psi]	89
	SV15-23-04	NCS 12/3	Solenoid Valve, 3-way, 2-position, Spool Type	50 l/min [13.2 US gpm]	230 bar [3300 psi]	90
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-24-01	SDC08-4	Solenoid Valve, 4-way, 2-position, Spool Type	12 l/min [3.2 US gpm]	230 bar [3300 psi]	91
	HSV08-24-01	SDC08-4	Solenoid Valve, 4-way, 2-position, Spool Type	20 l/min [5.3 US gpm]	350 bar [5000 psi]	92
	SV10-24-01	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	35 l/min [9 US gpm]	230 bar [3300 psi]	93
	SV09-24-01	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	21 l/min [5.5 US gpm]	100 bar [1450 psi]	94
	SV11-10-4	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	23 l/min [6 US gpm]	350 bar [5000 psi]	95
	SV15-24-01	NCS 12/4	Solenoid Valve, 4-way, 2-position, Spool Type	60 l/min [16 US gpm]	230 bar [3300 psi]	96

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves










Quick Reference

Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-24-02	SDC08-4	Solenoid Valve, 4-way, 2-position, Spool Type	12 l/min [3.2 US gpm]	230 bar [3300 psi]	97
	SV12-8-4	SDC08-4	Solenoid Valve, 4-way, 2-position, Spool Type	11 l/min [2.9 US gpm]	350 bar [5000 psi]	98
	SV10-24-02	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	25 l/min [6.6 US gpm]	230 bar [3300 psi]	99
	SV12-10-4	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	23 l/min [6 US gpm]	350 bar [5000 psi]	100
	SV15-24-02	NCS 12/4	Solenoid Valve, 4-way, 2-position, Spool Type	60 l/min [16 US gpm]	230 bar [3300 psi]	101
	SV15-24-03	NCS 12/4	Solenoid Valve, 4-way, 2-position, Spool Type	50 l/min [13.2 US gpm]	230 bar [3300 psi]	102
	SV08-24-04	SDC08-4	Solenoid Valve, 4-way, 2-position, Spool Type	8 l/min [2 US gpm]	230 bar [3300 psi]	103
	SV15-24-04	NCS 12/4	Solenoid Valve, 4-way, 2-position, Spool Type	50 l/min [13.2 US gpm]	230 bar [3300 psi]	104
	SV10-24-05	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	30 l/min [8 US gpm]	230 bar [3300 psi]	105
	SV10-24-06	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	30 l/min [8 US gpm]	230 bar [3300 psi]	106
	SV10-24-07	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	30 l/min [8 US gpm]	230 bar [3300 psi]	107

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves

Quick Reference







Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-24-08	SDC08-4	Solenoid Valve, 4-way, 2-position, Spool Type	18 l/min [4.7 US gpm]	230 bar [3300 psi]	108
	SV10-24-12	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	25 l/min [6.6 US gpm]	230 bar [3300 psi]	109
	SV10-24-13	SDC10-4	Solenoid Valve, 4-way, 2-position, Spool Type	33 l/min [8.7 US gpm]	230 bar [3300 psi]	110
	SV7M-12-4P	C-12-4	Solenoid Valve, 4-way, 2-position, Spool Type	45 l/min [12 US gpm]	210 bar [3000 psi]	111
	SV17M-12-4P	C-12-4	Solenoid Valve, 4-way, 2-position, Spool Type	45 l/min [12 US gpm]	350 bar [5000 psi]	112
	SV08-34-02	SDC08-4	Solenoid Valve, 4-way, 3-position, Spool Type	16 l/min [4.2 US gpm]	230 bar [3300 psi]	113
	HSV08-34-02	SDC08-4	Solenoid Valve, 4-way, 3-position, Spool Type	17 l/min [4.5 US gpm]	350 bar [5000 psi]	114
	SV10-34-02	SDC10-4	Solenoid Valve, 4-way, 3-position, Spool Type	25 l/min [6.6 US gpm]	230 bar [3300 psi]	115
	SV15-34-02	NCS 12/4	Solenoid Valve, 4-way, 3-position, Spool Type	60 l/min [16 US gpm]	230 bar [3300 psi]	116
	SV08-34-03	SDC08-4	Solenoid Valve, 4-way, 3-position, Spool Type	8 l/min [2 US gpm]	230 bar [3300 psi]	117
	SV15-34-03	NCS 12/4	Solenoid Valve, 4-way, 3-position, Spool Type	50 l/min [13.2 US gpm]	230 bar [3300 psi]	118
	SV10-34-03	SDC 10-4	Solenoid Valve, 4-way, 3-position, Spool Type	24 l/min [6.3 US gpm]	230 bar [3300 psi]	119

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves

Quick Reference



Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-34-04	SDC08-4	Solenoid Valve, 4-way, 3-position, Spool Type	8 l/min [2 US gpm]	230 bar [3300 psi]	120
	SV15-34-04	NCS 12/4	Solenoid Valve, 4-way, 3-position, Spool Type	50 l/min [13.2 US gpm]	230 bar [3300 psi]	121
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV10-34-04	SDC10-4	Solenoid Valve, 4-way, 3-position, Spool Type	24 l/min [6.3 US gpm]	230 bar [3300 psi]	122
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV08-34-05	SDC08-4	Solenoid Valve, 4-way, 3-position, Spool Type	12 l/min [3.2 US gpm]	230 bar [3300 psi]	123
	HSV08-34-05	SDC08-4	Solenoid Valve, 4-way, 3-position, Spool Type	17 l/min [4.5 US gpm]	350 bar [5000 psi]	124
	SV10-34-05	SDC10-4	Solenoid Valve, 4-way, 3-position, Spool Type	24 l/min [6.3 US gpm]	230 bar [3300 psi]	125
	SV15-34-05	NCS 12/4	Solenoid Valve, 4-way, 3-position, Spool Type	60 l/min [16 US gpm]	230 bar [3300 psi]	126
	SV10-34-11	SDC10-4	Solenoid Valve, 4-way, 3-position, Spool Type	28 l/min [7.4 US gpm]	230 bar [3300 psi]	127
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV10-35-02	SDC10-5	Solenoid Valve, 5-way, 3-position, Spool Type	30 l/min [8 US gpm]	230 bar [3300 psi]	128
Solenoid Valves	Model No.	Cavity	Description	Flow*	Pressure	Page
	SV10-35-05	SDC10-5	Solenoid Valve, 5-way, 3-position, Spool Type	30 l/min [8 US gpm]	230 bar [3300 psi]	129

*Flow ratings are for reference only. Refer to individual product page for performance information.

Solenoid Valves

SVP08-NC


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated

230 bar [3300 psi] • 35 l/min [9 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 but is restricted in the opposite direction. Some models have the option of a filter at port 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position and bypass excess oil to tank.

■ SCHEMATIC



■ DIMENSIONS



■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Rated flow	35 l/min [9 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0,23 kg [0.51 lbs]
Cavity	SDC08-2


*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 600,000 cycles

■ PERFORMANCE CURVES

Pressure Drop

33 cSt [154 SUS] hyd.oil @ 38°C [100°F]



■ MODEL CODE

SVP08 - NC - 12D - DE - M - B - F - 4S															
Coil Voltage				Housing											
Standard Coil Code	Robust Coil Code	Coil Voltage		Code	Ports	Housing Model Code									
00	R00	No Coil, nut included*		00	No Housing										
10D	R10D	10 VDC		4S	#4 SAE, AL	CP08-2-4S									
12D	R12D	12 VDC		6S	#6 SAE, AL	CP08-2-6S									
20D	R20D	20 VDC		S6S	#6 SAE, Steel	CP08-2-S6S									
24D	R24D	24 VDC		DG2B	1/4 BSP, AL	SDC08-2-DG2B									
110A		110 VAC**		DG3B	3/8 BSP, AL	SDC08-2-DG3B									
220A		220 VAC**		S3B	3/8 BSP, Steel	CP08-2-S3B									
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)															
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)															
**DIN only - external rectifier needed															
Connector Type															
Standard Coil Code	Robust Coil Code	Connector Type		Code	Seal kit										
00	00	No Coil		B-Buna - N	354000119										
AJ		Amp Junior		V-Viton	354000219										
AJD		Amp Junior with Diode													
AS	AS	AMP SuperSeal 1.5													
ASD	ASDB*	AMP SuperSeal with Diode													
DE	DE	Deutsch													
DED	DEDDB*	Deutsch with Diode													
FL	FL	Flying Leads													
FLD	FLDB*	Flying Leads with Diode													
DN		DIN 43650													
*Bi-directional diode															
Manual Override Option															
Omit - No Override															
M - Screw Type (Pull)															

Solenoid Valves

SV15-8-C


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated

350 bar [5000 psi] • 38 l/min [10 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 but is restricted in the opposite direction. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position and bypass excess oil to tank.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	38 l/min [10 US gpm]
Leakage	5 drops/min @ 210 bar [3000 psi]
Coil Options	P series
Weight	0.11 kg [0.25 lb]
Cavity	SDC08-2

■ MODEL CODE

SV15 - 8 - V - C - M - S - 2G - 12D - G - P		
Seal Option		Coil Series
Code	Seal kit	0mit - No coil P - 8 series, 23 W
0mit - Buna - N	02-165875	
V-Viton	02-165877	
Manual Override Option		Connector Type
0mit - No manual override		0mit - No coil
M - Pull and Twist		G - ISO 4400 DIN 43650
Housing Material		Q - Spade terminals
0mit - No housing		W - Flying lead
S - Steel		N - Deutsch (DC only)
Housing		Y - Amp JR (DC only)
Code	Ports	D - Metripack 150 male (DC only)
00	No Housing	J - Metripack 280 male (DC only)
2G	1/4" BSP	
3G	3/8" BSP	
4T	#4 SAE	
6T	#6 SAE	
8T	#8 SAE	
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
* Additional housings available		
*Optional arc suppression diode		
**Internally rectified		
***Other voltage options available		


■ DIMENSIONS

mm [in]

Coil nut torque


5-8 Nm [4-6 ft. lbs]

Installation torque
34-41 Nm [25-30 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to port 2 • B - Port 2 to port 1

Solenoid Valves

SVP10-NC


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated

230 bar [3300 psi] • 80 l/min [21 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 but is restricted in the opposite direction. Some models have the option of a filter at port 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position and bypass excess oil to tank.

■ SCHEMATIC



■ DIMENSIONS



■ PERFORMANCE DATA


Rated Pressure*	230 bar [3300 psi]**
Rated flow	80 l/min [21 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M16, R16
Weight	0.43 kg [0.95 lb]
Cavity	SDC10-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 250,000 cycles

■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SVP10 - NC - 12D - DE - M - B - F - 00							
Coil Voltage							
Standard Coil Code	Robust Coil Code	Coil Voltage					
00	R00	No Coil, nut included*					
10D	R10D	10 VDC					
12D	R12D	12 VDC					
20D	R20D	20 VDC					
24D	R24D	24 VDC					
110A		110 VAC**					
220A		220 VAC**					
*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)							
**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)							
**DIN only - external rectifier needed							
Connector Type							
Standard Coil Code	Robust Coil Code	Connector Type					
00	00	No Coil					
AJ		Amp Junior					
AJD		Amp Junior with Diode					
AS	AS	AMP SuperSeal 1.5					
ASD	ASDB*	AMP SuperSeal with Diode					
DE	DE	Deutsch					
DED	DEDB*	Deutsch with Diode					
FL	FL	Flying Leads					
FLD	FLDB*	Flying Leads with Diode					
DN		DIN 43650					
*Bi-directional diode							
Housing							
Code	Ports	Housing Model Code					
00	No Housing						
6S	#6 SAE, AL	CP10-2-6S					
8S	#8 SAE, AL	CP10-2-8S					
S8S	#8 SAE, Steel	CP10-2-S8S					
DG3B	3/8 BSP, AL	SDC10-2-DG3B					
DG4B	1/2 BSP, AL	SDC10-2-DG4B					
S4B	1/2 BSP, Steel	CP10-2-S4B					
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].							
* Additional housings available							
Filter Option							
Omit	- No filter						
F	- Filter 300 µm						
Seal Option							
Code	Seal kit						
B-Buna - N	354000719						
V-Viton	354000819						
Manual Override Option							
Omit	- No Override						
M	- Screw Type (Pull)						

Solenoid Valves

SV11-10-C


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated

350 bar [5000 psi] • 45 l/min [12 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 but is restricted in the opposite direction. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position and bypass excess oil to tank.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	45 l/min [12 US gpm]
Leakage	5 drops/min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0,18 kg [0.39 lbs]
Cavity	SDC10-2

■ MODEL CODE


SV11 - 10 - V - C - M - S - 2G - 12D - G - H	Seal Option Code Seal kit Omit - Buna - N 565803 V - Viton 566086	Coil Series Omit - No coil H - 10 series, 29 W
Manual Override Option Omit - No manual override M - Pull and Twist		
Connector Type Omit - No coil G - ISO 4400 DIN 43650 Q - Spade terminals W - Flying lead N - Deutsch (DC only) Y - Amp JR (DC only) D - Metripack 150 male (DC only) J - Metripack 280 male (DC only)		
Housing Material Omit - No housing S - Steel		
Housing Code Ports Steel 00 No Housing 2G 1/4" BSP 02-175102 3G 3/8" BSP 02-175103 6T #6 SAE 02-175100 8T #8 SAE 02-175101		
Coil Voltage Code Coil Voltage 00 No Coil, nut included, (p/n 02-175698) 12D 12 VDC 24D 24 VDC 115A 115 VAC** 230A 230 VAC** 12B 2VDC/w diode* 24B 24 VDC/w diode*		
*Aluminum bodies are to be used for pressures less than 210 bar [3000 psi]. **Additional housings available *Optional arc suppression diode **Internally rectified ***Other voltage options available		

■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]




Installation torque

68-75 Nm [50-55 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to 2 de-energized • B - Port 2 to 1 energized

Solenoid Valves

SVP08-NCF


Solenoid Valve, Poppet Type, Normally Closed, Pilot Operated, Flow Control

230 bar [3300 psi] • 15 l/min 4 US gpm

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 1 to 2 but is restricted by a pre-determined orifice in the opposite direction. Some models have the option of a filter at port 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position and then provide controlled lowering in applications such as scissor lifts or man lifts.

■ SCHEMATIC





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]
Rated flow	15 l/min 4 US gpm
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0.23 kg [0.51 lb]
Cavity	SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)


■ DIMENSIONS

mm [in]




■ PERFORMANCE CURVES

Pressure drop (1 to 2)
26 cSt [121 SUS] hyd.oil at 50°C [122 °F]



Pressure drop (2 to 1)
26 cSt [121 SUS] hyd.oil at 50°C [122 °F]





Solenoid Valves

SVP08-NCF

Solenoid Valve, Poppet Type, Normally Closed, Pilot Operated, Flow Control

230 bar [3300 psi] • 15 l/min [4 US gpm]

■ MODEL CODE

SVP08 - NCF - 1.0 - 12D - DE - M4 - B - F - 6S																																								
Orifice Size																																								
<table border="1"> <thead> <tr> <th>Code [mm]</th><th>Flow @ 7 bar [100 psi]</th></tr> </thead> <tbody> <tr> <td>1.0</td><td>1.3 LPM [0.34 GPM]</td></tr> <tr> <td>1.2</td><td>2.2 LPM [0.58 GPM]</td></tr> <tr> <td>1.4</td><td>2.7 LPM [0.71 GPM]</td></tr> <tr> <td>1.7</td><td>4 LPM [1.06 GPM]</td></tr> <tr> <td>2.0</td><td>5.8 LPM [1.54 GPM]</td></tr> </tbody> </table>							Code [mm]	Flow @ 7 bar [100 psi]	1.0	1.3 LPM [0.34 GPM]	1.2	2.2 LPM [0.58 GPM]	1.4	2.7 LPM [0.71 GPM]	1.7	4 LPM [1.06 GPM]	2.0	5.8 LPM [1.54 GPM]																						
Code [mm]	Flow @ 7 bar [100 psi]																																							
1.0	1.3 LPM [0.34 GPM]																																							
1.2	2.2 LPM [0.58 GPM]																																							
1.4	2.7 LPM [0.71 GPM]																																							
1.7	4 LPM [1.06 GPM]																																							
2.0	5.8 LPM [1.54 GPM]																																							
Coil Voltage																																								
<table border="1"> <thead> <tr> <th>Standard Coil Code</th><th>Robust Coil Code</th><th>Coil Voltage</th></tr> </thead> <tbody> <tr> <td>00</td><td>R00</td><td>No Coil, nut included*</td></tr> <tr> <td>10D</td><td>R10D</td><td>10 VDC</td></tr> <tr> <td>12D</td><td>R12D</td><td>12 VDC</td></tr> <tr> <td>20D</td><td>R20D</td><td>20 VDC</td></tr> <tr> <td>24D</td><td>R24D</td><td>24 VDC</td></tr> <tr> <td>110A</td><td></td><td>110 VAC**</td></tr> <tr> <td>220A</td><td></td><td>220 VAC**</td></tr> </tbody> </table>							Standard Coil Code	Robust Coil Code	Coil Voltage	00	R00	No Coil, nut included*	10D	R10D	10 VDC	12D	R12D	12 VDC	20D	R20D	20 VDC	24D	R24D	24 VDC	110A		110 VAC**	220A		220 VAC**										
Standard Coil Code	Robust Coil Code	Coil Voltage																																						
00	R00	No Coil, nut included*																																						
10D	R10D	10 VDC																																						
12D	R12D	12 VDC																																						
20D	R20D	20 VDC																																						
24D	R24D	24 VDC																																						
110A		110 VAC**																																						
220A		220 VAC**																																						
<small>*Standard Coil - Plastic coil nut and o-rings (p/n 173800588) *Robust Coil - Steel coil nut and no o-rings (p/n 173800539) **DIN only - external rectifier needed</small>																																								
Connector Type																																								
<table border="1"> <thead> <tr> <th>Standard Coil Code</th><th>Robust Coil Code</th><th>Connector Type</th></tr> </thead> <tbody> <tr> <td>00</td><td>00</td><td>No Coil</td></tr> <tr> <td>AJ</td><td></td><td>Amp Junior</td></tr> <tr> <td>AJD</td><td></td><td>Amp Junior with Diode</td></tr> <tr> <td>AS</td><td>AS</td><td>AMP SuperSeal 1.5</td></tr> <tr> <td>ASD</td><td>ASDB*</td><td>AMP SuperSeal with Diode</td></tr> <tr> <td>DE</td><td>DE</td><td>Deutsch</td></tr> <tr> <td>DED</td><td>DED*</td><td>Deutsch with Diode</td></tr> <tr> <td>FL</td><td>FL</td><td>Flying Leads</td></tr> <tr> <td>FLD</td><td>FLDB*</td><td>Flying Leads with Diode</td></tr> <tr> <td>DN</td><td></td><td>DIN 43650</td></tr> </tbody> </table>								Standard Coil Code	Robust Coil Code	Connector Type	00	00	No Coil	AJ		Amp Junior	AJD		Amp Junior with Diode	AS	AS	AMP SuperSeal 1.5	ASD	ASDB*	AMP SuperSeal with Diode	DE	DE	Deutsch	DED	DED*	Deutsch with Diode	FL	FL	Flying Leads	FLD	FLDB*	Flying Leads with Diode	DN		DIN 43650
Standard Coil Code	Robust Coil Code	Connector Type																																						
00	00	No Coil																																						
AJ		Amp Junior																																						
AJD		Amp Junior with Diode																																						
AS	AS	AMP SuperSeal 1.5																																						
ASD	ASDB*	AMP SuperSeal with Diode																																						
DE	DE	Deutsch																																						
DED	DED*	Deutsch with Diode																																						
FL	FL	Flying Leads																																						
FLD	FLDB*	Flying Leads with Diode																																						
DN		DIN 43650																																						
<small>*Bi-directional diode</small>																																								
Housing																																								
<table border="1"> <thead> <tr> <th>Code</th><th>Ports</th><th>Housing Model Code</th></tr> </thead> <tbody> <tr> <td>00</td><td>No Housing</td><td></td></tr> <tr> <td>4S</td><td>#4 SAE, AL</td><td>CP08-2-4S</td></tr> <tr> <td>6S</td><td>#6 SAE, AL</td><td>CP08-2-6S</td></tr> <tr> <td>S6S</td><td>#6 SAE, Steel</td><td>CP08-2-S6S</td></tr> <tr> <td>2B</td><td>1/4 BSP, AL</td><td>SDC08-2-2B</td></tr> <tr> <td>3B</td><td>3/8 BSP, AL</td><td>SDC06-2-3B</td></tr> <tr> <td>S3B</td><td>3/8 BSP, Steel</td><td>CP08-2-S3B</td></tr> </tbody> </table>							Code	Ports	Housing Model Code	00	No Housing		4S	#4 SAE, AL	CP08-2-4S	6S	#6 SAE, AL	CP08-2-6S	S6S	#6 SAE, Steel	CP08-2-S6S	2B	1/4 BSP, AL	SDC08-2-2B	3B	3/8 BSP, AL	SDC06-2-3B	S3B	3/8 BSP, Steel	CP08-2-S3B										
Code	Ports	Housing Model Code																																						
00	No Housing																																							
4S	#4 SAE, AL	CP08-2-4S																																						
6S	#6 SAE, AL	CP08-2-6S																																						
S6S	#6 SAE, Steel	CP08-2-S6S																																						
2B	1/4 BSP, AL	SDC08-2-2B																																						
3B	3/8 BSP, AL	SDC06-2-3B																																						
S3B	3/8 BSP, Steel	CP08-2-S3B																																						
<small>*Aluminum bodies are to be used for pressures less than 210 bar [3000 psi]. * Additional housings available</small>																																								
Filter Option																																								
<small>Omit - No filter F - Filter 300 µm</small>																																								
Seal Option																																								
<table border="1"> <thead> <tr> <th>Code</th><th>Seal kit</th></tr> </thead> <tbody> <tr> <td>B-Buna - N</td><td>364000119</td></tr> <tr> <td>V-Viton</td><td>364000219</td></tr> </tbody> </table>							Code	Seal kit	B-Buna - N	364000119	V-Viton	364000219																												
Code	Seal kit																																							
B-Buna - N	364000119																																							
V-Viton	364000219																																							
Manual Override Option																																								
<small>Omit - No Override M - Screw Type (Pull) M4 - Pull Override (M4 Thread) PG - Pull Override with Knob</small>																																								

Solenoid Valves

SVP08-NCR


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow

230 bar [3300 psi] • 35 l/min [9 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Some models have the option of a filter at port 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ DIMENSIONS



■ PERFORMANCE DATA


Rated Pressure*	230 bar [3300 psi]**
Rated flow	35 l/min [9 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0.23 kg [0.51 lb]
Cavity	SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 600,000 cycles

■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SVP08 - NCR - 12D - DE - M - B - F - 00								
Coil Voltage								
Standard Coil Code	Robust Coil Code	Coil Voltage						
00	R00	No Coil, nut included*						
10D	R10D	10 VDC						
12D	R12D	12 VDC						
20D	R20D	20 VDC						
24D	R24D	24 VDC						
110A		110 VAC**						
220A		220 VAC**						
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)								
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)								
**DIN only - external rectifier needed								
Connector Type								
Standard Coil Code	Robust Coil Code	Connector Type						
00	00	No Coil						
AJ		Amp Junior						
AJD		Amp Junior with Diode						
AS	AS	AMP SuperSeal 1.5						
ASD	ASDB*	AMP SuperSeal with Diode						
DE	DE	Deutsch						
DED	DEDB*	Deutsch with Diode						
FL	FL	Flying Leads						
FLD	FLDB*	Flying Leads with Diode						
DN		DIN 43650						
*Bi-directional diode								
Housing								
Code	Ports	Housing Model Code						
00	No Housing							
4S	#4 SAE, AL	CP08-2-6S						
6S	#6 SAE, AL	CP08-2-6S						
S6S	#6 SAE, Steel	CP08-2-S6S						
DG2B	1/4 BSP, AL	SDC08-2-DG2B						
DG3B	3/8 BSP, AL	SDC08-2-DG3B						
S3B	3/8 BSP, Steel	CP08-2-S3B						
*Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].								
* Additional housings available								
Filter Option								
Omit	- No filter							
F	- Filter 300 µm							
Seal Option								
Code	Seal kit							
B-Buna - N	354000119							
V-Viton	354000219							
Manual Override Option								
Omit	- No Override							
M	- Screw Type (Pull)							

Solenoid Valves

SVP10-NCR


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow

230 bar [3300 psi] • 80 l/min [21 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Some models have the option of a filter at port 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Rated flow	80 l/min [21 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M16, R16
Weight	0.43 kg [0.95 lb]
Cavity	SDC10-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 250,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SVP10 - NCR - 12D - DE - M - B - F - 6S					
Coil Voltage					
Standard Coil Code	Robust Coil Code	Coil Voltage			
00	R00	No Coil, nut included*			
10D	R10D	10 VDC			
12D	R12D	12 VDC			
20D	R20D	20 VDC			
24D	R24D	24 VDC			
110A		110 VAC**			
220A		220 VAC**			
*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)					
*Robust Coil - Steel coil nut and no o-rings (p/n 173804910)					
**DIN only - external rectifier needed					
Connector Type					
Standard Coil Code	Robust Coil Code	Connector Type			
00	00	No Coil			
AJ		Amp Junior			
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode					
Housing					
Code	Ports	Housing Model Code			
00	No Housing				
6S	#6 SAE, AL	CP10-2-6S			
8S	#8 SAE, AL	CP10-2-8S			
S8S	#8 SAE, Steel	CP10-2-S8S			
DG3B	3/8 BSP, AL	SDC10-2-DG3B			
DG4B	1/2 BSP, AL	SDC10-2-DG4B			
S4B	1/2 BSP, Steel	CP10-2-S4B			
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].					
* Additional housings available					
Filter Option					
Omit	- No filter				
F	- Filter 300 µm				
Seal Option					
Code	Seal kit				
B-Buna - N	354000719				
V-Viton	354000819				
Manual Override Option					
Omit	- No manual override				
M	- Screw Type (Pull)				

Solenoid Valves


SV13-10-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
350 bar [5000 psi] • 45 l/min [12 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC




■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	45 l/min [12 US gpm]
Leakage	5 drops/min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2

■ MODEL CODE


SV13 - 10 - V - C - M - S - 2G - 12D - G - H	
Seal Option	
Code	Seal kit
0mit-Buna - N	565803
V-Viton	566086
Manual Override Option	
0mit - No manual override	
M - Pull and Twist	
Housing Material	
0mit	- No housing
S	- Steel
Housing	
Code	Ports
0	No Housing
2G	1/4" BSP
3G	3/8" BSP
6T	#6 SAE
8T	#8 SAE
*Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].	
* Additional housings available	
Coil Series	
0mit - No coil	
H - 10 series, 29 W	
Connector Type	
0mit - No coil	
G - ISO 4400 DIN 43650	
Q - Spade terminals	
W - Flying lead	
N - Deutsch (DC only)	
Y - Amp JR (DC only)	
D - Metripack 150 male (DC only)	
J - Metripack 280 male (DC only)	
Coil Voltage	
Code	Coil Voltage
00	No Coil, nut included, (p/n 02-175698)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*
*Optional arc suppression diode	
**Internally rectified	
***Other voltage options available	

■ DIMENSIONS



■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to port 2 • B - Port 2 to port 1 energized

Solenoid Valves

SLP13-10-C


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow

350 bar [5000 psi] • 95 l/min [25 US gpm]


■ DESCRIPTION AND OPERATION

This is a 2-way, 2-position, poppet type, normally closed solenoid valve. In its de-energized condition flow can take place from port 1 to 2, but flow is blocked from port 2 to 1 with minimum leakage due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions. Due to its low power coil and low pressure drop, these valves are suitable for high ambient temperature applications, space savers in a HIC design or where reducing power consumption is important.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated pressure*	350 bar [5000 psi]
Rated flow	95 l/min [25 US gpm]
Leakage	10 drops/min @ 350 bar [5000 psi]
Coil Options	K series, 10 W
Weight	0.16 kg [0.35 lb]
Cavity	SDC10-2

*Note: Rated pressure based on NFPA fatigue test standard [at 1 million cycles]

■ PERFORMANCE CURVES



■ MODEL CODE

SLP13 - 10 - V - C - S - 2G - 12D - N - K																																																																																																																																																																																																																																																																																																																															
<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Seal Option</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>Code</td> <td colspan="3">Seal Kit</td> <td colspan="6"></td> </tr> <tr> <td>0mit-Buna-N</td> <td colspan="3">565803</td> <td colspan="6"></td> </tr> <tr> <td>V-Viton</td> <td colspan="3">566086</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: center;">Housing Material</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Housing</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>Code</td> <td>Ports</td> <td>Aluminum Standard Duty</td> <td>Aluminum Heavy Duty</td> <td>Steel Heavy Duty</td> <td colspan="5"></td> </tr> <tr> <td>0</td> <td>No Housing</td> <td colspan="3"></td> <td colspan="5"></td> </tr> <tr> <td>3B</td> <td>3/8" BSP</td> <td>02-175462</td> <td colspan="3"></td> <td colspan="4"></td> </tr> <tr> <td>2G</td> <td>1/4" BSP</td> <td></td> <td>876702</td> <td>02-175102</td> <td colspan="5"></td> </tr> <tr> <td>3G</td> <td>3/8" BSP</td> <td></td> <td>876703</td> <td>02-175103</td> <td colspan="5"></td> </tr> <tr> <td>6H</td> <td>#6 SAE</td> <td></td> <td>876700</td> <td colspan="6"></td> </tr> <tr> <td>8H</td> <td>#8 SAE</td> <td></td> <td>876701</td> <td colspan="6"></td> </tr> <tr> <td>6T</td> <td>#6 SAE</td> <td>566151</td> <td></td> <td>02-175100</td> <td colspan="5"></td> </tr> <tr> <td>8T</td> <td>#8 SAE</td> <td></td> <td>02-175101</td> <td colspan="6"></td> </tr> </table> </td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Series</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>K</td> <td colspan="3">- K Series, 10W</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: center;">Connector Type</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Connector Type</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>N</td> <td colspan="3">- Deutsch</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: right;">* Additional connectors available. Contact technical support.</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table> </td> </tr> </table></td> </tr> </table> </td> </tr> </table>										Seal Option										Code	Seal Kit									0mit-Buna-N	565803									V-Viton	566086									Housing Material										<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Housing</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>Code</td> <td>Ports</td> <td>Aluminum Standard Duty</td> <td>Aluminum Heavy Duty</td> <td>Steel Heavy Duty</td> <td colspan="5"></td> </tr> <tr> <td>0</td> <td>No Housing</td> <td colspan="3"></td> <td colspan="5"></td> </tr> <tr> <td>3B</td> <td>3/8" BSP</td> <td>02-175462</td> <td colspan="3"></td> <td colspan="4"></td> </tr> <tr> <td>2G</td> <td>1/4" BSP</td> <td></td> <td>876702</td> <td>02-175102</td> <td colspan="5"></td> </tr> <tr> <td>3G</td> <td>3/8" BSP</td> <td></td> <td>876703</td> <td>02-175103</td> <td colspan="5"></td> </tr> <tr> <td>6H</td> <td>#6 SAE</td> <td></td> <td>876700</td> <td colspan="6"></td> </tr> <tr> <td>8H</td> <td>#8 SAE</td> <td></td> <td>876701</td> <td colspan="6"></td> </tr> <tr> <td>6T</td> <td>#6 SAE</td> <td>566151</td> <td></td> <td>02-175100</td> <td colspan="5"></td> </tr> <tr> <td>8T</td> <td>#8 SAE</td> <td></td> <td>02-175101</td> <td colspan="6"></td> </tr> </table>										Housing										Code	Ports	Aluminum Standard Duty	Aluminum Heavy Duty	Steel Heavy Duty						0	No Housing									3B	3/8" BSP	02-175462								2G	1/4" BSP		876702	02-175102						3G	3/8" BSP		876703	02-175103						6H	#6 SAE		876700							8H	#8 SAE		876701							6T	#6 SAE	566151		02-175100						8T	#8 SAE		02-175101							<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Series</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>K</td> <td colspan="3">- K Series, 10W</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: center;">Connector Type</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Connector Type</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>N</td> <td colspan="3">- Deutsch</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: right;">* Additional connectors available. Contact technical support.</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table> </td> </tr> </table></td> </tr> </table>										Coil Series										0mit	- No coil									K	- K Series, 10W									Connector Type										<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Connector Type</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>N</td> <td colspan="3">- Deutsch</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: right;">* Additional connectors available. Contact technical support.</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table> </td> </tr> </table>										Connector Type										0mit	- No coil									N	- Deutsch									* Additional connectors available. Contact technical support.										<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table>										Coil Voltage										00	- No Coil									12D	- 12 VDC									24D	- 24 VDC								
Seal Option																																																																																																																																																																																																																																																																																																																															
Code	Seal Kit																																																																																																																																																																																																																																																																																																																														
0mit-Buna-N	565803																																																																																																																																																																																																																																																																																																																														
V-Viton	566086																																																																																																																																																																																																																																																																																																																														
Housing Material																																																																																																																																																																																																																																																																																																																															
<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Housing</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>Code</td> <td>Ports</td> <td>Aluminum Standard Duty</td> <td>Aluminum Heavy Duty</td> <td>Steel Heavy Duty</td> <td colspan="5"></td> </tr> <tr> <td>0</td> <td>No Housing</td> <td colspan="3"></td> <td colspan="5"></td> </tr> <tr> <td>3B</td> <td>3/8" BSP</td> <td>02-175462</td> <td colspan="3"></td> <td colspan="4"></td> </tr> <tr> <td>2G</td> <td>1/4" BSP</td> <td></td> <td>876702</td> <td>02-175102</td> <td colspan="5"></td> </tr> <tr> <td>3G</td> <td>3/8" BSP</td> <td></td> <td>876703</td> <td>02-175103</td> <td colspan="5"></td> </tr> <tr> <td>6H</td> <td>#6 SAE</td> <td></td> <td>876700</td> <td colspan="6"></td> </tr> <tr> <td>8H</td> <td>#8 SAE</td> <td></td> <td>876701</td> <td colspan="6"></td> </tr> <tr> <td>6T</td> <td>#6 SAE</td> <td>566151</td> <td></td> <td>02-175100</td> <td colspan="5"></td> </tr> <tr> <td>8T</td> <td>#8 SAE</td> <td></td> <td>02-175101</td> <td colspan="6"></td> </tr> </table>										Housing										Code	Ports	Aluminum Standard Duty	Aluminum Heavy Duty	Steel Heavy Duty						0	No Housing									3B	3/8" BSP	02-175462								2G	1/4" BSP		876702	02-175102						3G	3/8" BSP		876703	02-175103						6H	#6 SAE		876700							8H	#8 SAE		876701							6T	#6 SAE	566151		02-175100						8T	#8 SAE		02-175101																																																																																																																																																																																																																								
Housing																																																																																																																																																																																																																																																																																																																															
Code	Ports	Aluminum Standard Duty	Aluminum Heavy Duty	Steel Heavy Duty																																																																																																																																																																																																																																																																																																																											
0	No Housing																																																																																																																																																																																																																																																																																																																														
3B	3/8" BSP	02-175462																																																																																																																																																																																																																																																																																																																													
2G	1/4" BSP		876702	02-175102																																																																																																																																																																																																																																																																																																																											
3G	3/8" BSP		876703	02-175103																																																																																																																																																																																																																																																																																																																											
6H	#6 SAE		876700																																																																																																																																																																																																																																																																																																																												
8H	#8 SAE		876701																																																																																																																																																																																																																																																																																																																												
6T	#6 SAE	566151		02-175100																																																																																																																																																																																																																																																																																																																											
8T	#8 SAE		02-175101																																																																																																																																																																																																																																																																																																																												
<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Series</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>K</td> <td colspan="3">- K Series, 10W</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: center;">Connector Type</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Connector Type</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>N</td> <td colspan="3">- Deutsch</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: right;">* Additional connectors available. Contact technical support.</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table> </td> </tr> </table></td> </tr> </table>										Coil Series										0mit	- No coil									K	- K Series, 10W									Connector Type										<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Connector Type</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>N</td> <td colspan="3">- Deutsch</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: right;">* Additional connectors available. Contact technical support.</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table> </td> </tr> </table>										Connector Type										0mit	- No coil									N	- Deutsch									* Additional connectors available. Contact technical support.										<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table>										Coil Voltage										00	- No Coil									12D	- 12 VDC									24D	- 24 VDC																																																																																																																																																																																		
Coil Series																																																																																																																																																																																																																																																																																																																															
0mit	- No coil																																																																																																																																																																																																																																																																																																																														
K	- K Series, 10W																																																																																																																																																																																																																																																																																																																														
Connector Type																																																																																																																																																																																																																																																																																																																															
<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Connector Type</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>0mit</td> <td colspan="3">- No coil</td> <td colspan="6"></td> </tr> <tr> <td>N</td> <td colspan="3">- Deutsch</td> <td colspan="6"></td> </tr> <tr> <td colspan="10" style="text-align: right;">* Additional connectors available. Contact technical support.</td> </tr> <tr> <td colspan="10"> <table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table> </td> </tr> </table>										Connector Type										0mit	- No coil									N	- Deutsch									* Additional connectors available. Contact technical support.										<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table>										Coil Voltage										00	- No Coil									12D	- 12 VDC									24D	- 24 VDC																																																																																																																																																																																																																																				
Connector Type																																																																																																																																																																																																																																																																																																																															
0mit	- No coil																																																																																																																																																																																																																																																																																																																														
N	- Deutsch																																																																																																																																																																																																																																																																																																																														
* Additional connectors available. Contact technical support.																																																																																																																																																																																																																																																																																																																															
<table border="0" style="width: 100%;"> <tr> <td style="width: 15%;">Coil Voltage</td> <td colspan="3"></td> <td colspan="6"></td> </tr> <tr> <td>00</td> <td colspan="3">- No Coil</td> <td colspan="6"></td> </tr> <tr> <td>12D</td> <td colspan="3">- 12 VDC</td> <td colspan="6"></td> </tr> <tr> <td>24D</td> <td colspan="3">- 24 VDC</td> <td colspan="6"></td> </tr> </table>										Coil Voltage										00	- No Coil									12D	- 12 VDC									24D	- 24 VDC																																																																																																																																																																																																																																																																																						
Coil Voltage																																																																																																																																																																																																																																																																																																																															
00	- No Coil																																																																																																																																																																																																																																																																																																																														
12D	- 12 VDC																																																																																																																																																																																																																																																																																																																														
24D	- 24 VDC																																																																																																																																																																																																																																																																																																																														

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Solenoid Valves


SV3-12-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
210 bar [3000 psi] • 114 l/min [30 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ DIMENSIONS


mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque


A - 81-95 Nm [60-70 ft. lbs]
 S - 102-115 Nm [75-85 ft. lbs]



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	114 l/min [30 US gpm]
Leakage	5 drops/min @ 210 bar [3000 psi]
Coil Options	J series
Weight	0.34 kg [0.74 lb]
Cavity	C-12-2/C-12-2U

■ PERFORMANCE CURVES



A - Port 1 to port 2 de-energized • **B** - Port 2 to port 1 energized

■ MODEL CODE

SV3 - 12 - V - C - M - A - 4G - U - 12D - G									
Seal Option									
Code Seal kit									
Omit - Buna - N 02-165889									
V - Viton 02-165888									
Manual Override Option									
Omit - No manual override				Housing Material					
M - Pull and Twist				0 - No housing					
				A - Aluminium					
				S - Steel					
Housing									
Code	Ports	C-12-2 Aluminum Heavy Duty	C-12-2U Aluminum Heavy Duty	C-12-2 Steel Heavy Duty	C-12-2U Steel Heavy Duty				
0	No Housing								
4G	1/2" BSP	02-161118	02-161116	02-172062	02-172512				
6G	3/4" BSP	02-161117	02-161115	02-169665	02-162922				
10T	#10 SAE	02-160640	02-160641	02-169744	02-169817				
12T	#12 SAE	02-160644	02-160645	02-169782	02-169790				
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].									
* Additional housings available									
Connector Type									
Omit - No coil									
G - ISO 4400 DIN 43650									
Q - Spade terminals									
W - Flying lead									
N - Deutsch (DC only)									
Y - Amp JR (DC only)									
D - Metripack 150 male (DC only)									
J - Metripack 280 male (DC only)									
Coil Voltage									
Code		Coil Voltage							
00		No Coil, nut included (p/n 565558)							
12D		12 VDC							
24D		24 VDC							
115A		115 VAC**							
230A		230 VAC**							
12B		2VDC/w diode*							
24B		24 VDC/w diode*							
*Optional arc suppression diode									
**Internally rectified									
***Other voltage options available									
Cavity									
Omit - Cavity without undercut/No housing									
U - Cavity with undercut									

Solenoid Valves


SV13-12-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
350 bar [5000 psi] • 114 l/min [30 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	114 l/min [30 USgpm]
Leakage	5 drops/ min @ 350 bar (5000 psi)
Coil Options	H series
Weight	0.27 kg [0.59 lb]
Cavity	C-12-2 / C-12-2U


■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque
A - 81-95 Nm [60-70 ft. lbs]
S - 102-115 Nm [75-85 ft. lbs]



■ PERFORMANCE CURVES



■ MODEL CODE

SV13 - 12 - V - C - M - S - 4G - U - 12D - G - H									
Seal Option					Coil Series				
Code Seal kit					Omit - No coil				
Omit - Buna - N 02-165889					H - 10 series, 29 W				
V - Viton 02-165888					Connector Type				
Manual Override Option					Omit - No coil				
Omit - No manual override					G - ISO 4400 DIN 43650				
M - Pull and Twist					Q - Spade terminals				
Housing Material					W - Flying lead				
O - No Housing					N - Deutsch (DC only)				
4G - 1/2" BSP 02-161118					Y - Amp JR (DC only)				
6G - 3/4" BSP 02-161117					D - Metripack 150 male (DC only)				
10T - #10 SAE 02-160640					J - Metripack 280 male (DC only)				
12T - #12 SAE 02-160644					Coil Voltage				
C-12-2 Aluminum Heavy Duty					Code Coil Voltage				
C-12-2U Aluminum Heavy Duty					00 No Coil, nut included, (p/n 02-175698)				
C-12-2 Steel Heavy Duty					12D 12 VDC				
C-12-2U Steel Heavy Duty					24D 24 VDC				
0 No Housing					115A 115 VAC**				
4G 1/2" BSP 02-161118					230A 230 VAC**				
6G 3/4" BSP 02-161117					12B 2VDC/w diode*				
10T #10 SAE 02-160640					24B 24 VDC/w diode*				
12T #12 SAE 02-160644					*Optional arc suppression diode				
Code					**Internally rectified				
Ports					***Other voltage options available				
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									
10T #10 SAE 02-160640									
12T #12 SAE 02-160644									
Code									
Ports									
O No Housing									
4G 1/2" BSP 02-161118									
6G 3/4" BSP 02-161117									

Solenoid Valves


SV1-16-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
210 bar [3000 psi] • 132 l/min [35 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ DIMENSIONS


mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque

108-122 Nm [80-90 ft. lbs]




■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	132 l/min [35 US gpm]
Leakage	5 drops/min @ 210 bar [3000 psi]
Coil Options	J Series
Weight	1.15 kg [2.53 lb]
Cavity	SDC16-2

■ PERFORMANCE CURVES

Pressure Drop



A - Port 2 to 1 energized • B - Port 1 to 2 de-energized

■ MODEL CODE

SV1 - 16 - V - C - M - 6B - 12D - G							
Seal Option			Connector Type				
Code Seal kit			Omit - No coil				
Omit - Buna - N 565810			G - ISO 4400 DIN 43650				
V - Viton 02-889609			Q - Spade terminals				
Manual Override Option			W - Flying lead				
Omit - No manual override			N - Deutsch (DC only)				
M - Pull and Twist			Y - Amp JR (DC only)				
R - Cable type			D - Metripack 150 male (DC only)				
Housing			J - Metripack 280 male (DC only)				
Code	Ports	Aluminum Standard duty	Aluminum Heavy duty				
0	No Housing						
6B	3/4" BSP	02-175463					
12T	#12 SAE	566149					
6G	3/4" BSP		876718				
10H	#10 SAE		876717				
12H	#12 SAE		566113				
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].							
* Additional housings available							
*Optional arc suppression diode							
**Internally rectified							
***Other voltage options available							

Solenoid Valves


SV13-16-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
350 bar [5000 psi] • 132 l/min [35 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC




■ DIMENSIONS

mm [in]

Coil Nut Torque

5-8 Nm [4-6 ft. lbs]


Installation torque
136-149 Nm [100-110 ft. lbs]



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	132 l/min [35 US gpm]
Leakage	5 drops/min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.39 kg [0.85 lb]
Cavity	SDC16-2

■ PERFORMANCE CURVES



■ MODEL CODE

SV13 - 16 - V - C - M - S - 4G - 12D - G - H																			
Seal Option <table border="1"> <tr> <td>Code</td> <td>Seal kit</td> </tr> <tr> <td>Omit-Buna - N</td> <td>565810</td> </tr> <tr> <td>V-Viton</td> <td>889609</td> </tr> </table>		Code	Seal kit	Omit-Buna - N	565810	V-Viton	889609												
Code	Seal kit																		
Omit-Buna - N	565810																		
V-Viton	889609																		
Manual Override Option <table border="1"> <tr> <td>Omit - No manual override</td> </tr> <tr> <td>M - Pull and Twist</td> </tr> </table>		Omit - No manual override	M - Pull and Twist																
Omit - No manual override																			
M - Pull and Twist																			
Housing Material <table border="1"> <tr> <td>Omit - No Housing</td> </tr> <tr> <td>S - Steel</td> </tr> </table>		Omit - No Housing	S - Steel																
Omit - No Housing																			
S - Steel																			
Housing <table border="1"> <tr> <td>Code</td> <td>Ports</td> <td>Steel</td> </tr> <tr> <td>0</td> <td>No Housing</td> <td></td> </tr> <tr> <td>4G</td> <td>1/2" BSP</td> <td>02-175106</td> </tr> <tr> <td>6G</td> <td>3/4" BSP</td> <td>02-175107</td> </tr> <tr> <td>10T</td> <td>#10 SAE</td> <td>02-175104</td> </tr> <tr> <td>12T</td> <td>#12 SAE</td> <td>02-175105</td> </tr> </table>		Code	Ports	Steel	0	No Housing		4G	1/2" BSP	02-175106	6G	3/4" BSP	02-175107	10T	#10 SAE	02-175104	12T	#12 SAE	02-175105
Code	Ports	Steel																	
0	No Housing																		
4G	1/2" BSP	02-175106																	
6G	3/4" BSP	02-175107																	
10T	#10 SAE	02-175104																	
12T	#12 SAE	02-175105																	
Coil Series <table border="1"> <tr> <td>Omit - No coil</td> </tr> <tr> <td>H - 10 series, 29 W</td> </tr> </table>		Omit - No coil	H - 10 series, 29 W																
Omit - No coil																			
H - 10 series, 29 W																			
Connector Type <table border="1"> <tr> <td>Omit - No coil</td> </tr> <tr> <td>G - ISO 4400 DIN 43650</td> </tr> <tr> <td>Q - Spade terminals</td> </tr> <tr> <td>W - Flying lead</td> </tr> <tr> <td>N - Deutsch (DC only)</td> </tr> <tr> <td>Y - Amp JR (DC only)</td> </tr> <tr> <td>D - Metripack 150 male (DC only)</td> </tr> <tr> <td>J - Metripack 280 male (DC only)</td> </tr> </table>		Omit - No coil	G - ISO 4400 DIN 43650	Q - Spade terminals	W - Flying lead	N - Deutsch (DC only)	Y - Amp JR (DC only)	D - Metripack 150 male (DC only)	J - Metripack 280 male (DC only)										
Omit - No coil																			
G - ISO 4400 DIN 43650																			
Q - Spade terminals																			
W - Flying lead																			
N - Deutsch (DC only)																			
Y - Amp JR (DC only)																			
D - Metripack 150 male (DC only)																			
J - Metripack 280 male (DC only)																			
Coil Voltage <table border="1"> <tr> <td>Code</td> <td>Coil Voltage</td> </tr> <tr> <td>00</td> <td>No Coil, nut included, (p/n 02-175698)</td> </tr> <tr> <td>12D</td> <td>12 VDC</td> </tr> <tr> <td>24D</td> <td>24 VDC</td> </tr> <tr> <td>115A</td> <td>115 VAC**</td> </tr> <tr> <td>230A</td> <td>230 VAC**</td> </tr> <tr> <td>12B</td> <td>2VDC/w diode*</td> </tr> <tr> <td>24B</td> <td>24 VDC/w diode*</td> </tr> </table>		Code	Coil Voltage	00	No Coil, nut included, (p/n 02-175698)	12D	12 VDC	24D	24 VDC	115A	115 VAC**	230A	230 VAC**	12B	2VDC/w diode*	24B	24 VDC/w diode*		
Code	Coil Voltage																		
00	No Coil, nut included, (p/n 02-175698)																		
12D	12 VDC																		
24D	24 VDC																		
115A	115 VAC**																		
230A	230 VAC**																		
12B	2VDC/w diode*																		
24B	24 VDC/w diode*																		
<small>* Optional arc suppression diode ** Internally rectified *** Other voltage options available</small>																			

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].
* Additional housings available

Solenoid Valves


SV2-20-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
210 bar [3000 psi] • 230 l/min [60 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	230 l/min [60 USgpm]
Leakage	5 drops/ min @ 210 bar [3000 psi]
Coil Options	J series
Weight	1.2 kg [2.70 lb]
Cavity	SDC20-2

■ DIMENSIONS


mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]


Installation torque
 128-155 Nm [95-115 ft. lbs]

0 36,47 (1.436)



■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to 2 de-energized • B - Port 2 to 1 energized

■ MODEL CODE

SV2 - 20 - V - C - M - 8B - 12D - G

Seal Option

Code	Seal
Omit-Buna - N	889615
V-Viton	889619

Manual Override Option

Omit - No manual override
 M - Pull and Twist
 R - Cable type

Housing

Code	Ports	Aluminum Standard duty	Aluminum Heavy duty
0	No Housing		
8B	1" BSP	02-175464	
16T	#16 SAE	566409	
6G	3/4" BSP		876732
8G	1" BSP		876734
12H	#12 SAE		876733
16H	#16 SAE		876735

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].
 * Additional housings available

Connector Type

Omit - No coil
G - ISO 4400 DIN 43650
Q - Spade terminals
W - Flying lead
N - Deutsch (DC only)
Y - Amp JR (DC only)
D - Metripack 150 male (DC only)
J - Metripack 280 male (DC only)

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included (p/n 565558)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*

*Optional arc suppression diode

**Internally rectified

***Other voltage options available

Solenoid Valves

SV13-20-C


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow

350 bar [5000 psi] • 230 l/min [60 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed solenoid valve. In its de-energized condition, flow passes from port 1 to 2 but is blocked in the opposite direction. When energized, flow passes from port 2 to 1 and from 1 to 2. Due to the low leakage provided by the poppet design, these valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]

Ø 38,9 (1.53)

22,2 (0.875) hex


47,6 (1.875) hex

1.625" - 12 Thd.

0 36,47 (1.436)

Installation torque

163-183 Nm [120-135 ft. lbs]




■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	230 l/min [60 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.62 kg [1.37 lb]
Cavity	SDC20-2

■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to 2 de-energized • B - Port 2 to 1 energized

■ MODEL CODE

SV13 - 20 - V - C - M - S - 6G - 12D - G - H

Seal Option

Code	Seal kit
Omit - Buna - N	889615
V - Viton	889619

Manual Override Option

Omit	No manual override
M	Pull and Twist

Housing Material

Omit	No Housing
S	Steel

Housing

Code	Ports	Steel
0	No Housing	
6G	3/4" BSP	02-175110
8G	1" BSP	02-175111
12T	#12 SAE	02-175108
16T	#16 SAE	02-175109

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].
* Additional housings available

Coil Series

Omit	No coil
H	10 series, 29 W

Connector Type

Omit	No coil
G	ISO 4400 DIN 43650
Q	Spade terminals
W	Flying lead
N	Deutsch (DC only)
Y	Amp JR (DC only)
D	Metripack 150 male (DC only)
J	Metripack 280 male (DC only)

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included, (p/n 02-175698)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*

*Optional arc suppression diode

**Internally rectified

***Other voltage options available

Solenoid Valves

SBV12-8-C


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Direct Acting, Double Blocking

350 bar [5000 psi] • 1 l/min [0.25 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, direct acting, normally closed, bi-directional solenoid valve for low flow applications. In its de-energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position, provide controlled lowering, or as a pilot valve for larger valves such as ventable relief valves or logic elements.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	1 l/min [0.25 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	P series
Weight	0.120 kg [0.26 lb]
Cavity	SDC08-2

■ DIMENSIONS


mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]


Installation torque

34-41 Nm [25-30 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SVB12 - 8 - V - C - M - A - 2G - 12D - G - P	
Seal Option	Coil Series
Code	Seal kit
0 - Buna - N	02-160777
V - Viton	02-160778
Manual Override Option	Connector Type
0 - No manual override	0 - No coil
M - Pull and Twist	G - ISO 4400 DIN 43650
Housing Material	Q - Spade terminals
0 - No Housing	W - Flying lead
A - Aluminum	N - Deutsch (DC only)
S - Steel	Y - Amp JR (DC only)
Housing	D - Metripack 150 male (DC only)
Code	J - Metripack 280 male (DC only)
Ports	
Aluminium	
Steel	
0	No Housing
2G	1/4" BSP
3G	3/8" BSP
4T	#4 SAE
6T	#6 SAE
8T	#8 SAE
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].	
* Additional housings available	
Code	Coil Voltage
00	No Coil, nut included (p/n 565558)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*
*Optional arc suppression diode	
**Internally rectified	
***Other voltage options available	

Solenoid Valves

SVP08-CDB


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Direct Acting, Double Blocking

230 bar [3300 psi] • 25 l/min [6.6 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, poppet type, direct acting, normally closed, bi-directional solenoid valve. In its de-energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves come standard with a push pin manual override. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition. They do not suffer from momentary opening due to shock pressures.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]
Flow Capability	25 l/min [6.6 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0.32 kg [0.71 lb]
Cavity	SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

SVP08 - CDB - 12D - DE - PB - B - F - 4S															
Coil Voltage				Housing											
Standard Coil Code	Robust Coil Code	Coil Voltage		Code	Ports	Housing Model Code									
00	R00	No Coil, nut included*		00	No Housing										
10D	R10D	10 VDC		4S	#4 SAE, AL	CP08-2-4S									
12D	R12D	12 VDC		6S	#6 SAE, AL	CP08-2-6S									
20D	R20D	20 VDC		S6S	#6 SAE, Steel	CP08-2-S6S									
24D	R24D	24 VDC		DG2B	1/4 BSP, AL	SDC08-2-DG2B									
110A		110 VAC**		DG3B	3/8 BSP, AL	SDC08-2-DG3B									
220A		220 VAC**		S3B	3/8 BSP, Steel	CP08-2-S3B									
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)															
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)															
**DIN only - external rectifier needed															
Connector Type															
Standard Coil Code	Robust Coil Code	Connector Type		Code	Seal kit										
00	00	No Coil		B-Buna - N	354001619										
AJ		Amp Junior		V-Viton	354001719										
AJD		Amp Junior with Diode													
AS	AS	AMP SuperSeal 1.5													
ASD	ASDB*	AMP SuperSeal with Diode													
DE	DE	Deutsch													
DED	DEDB*	Deutsch with Diode													
FL	FL	Flying Leads													
FLD	FLDB*	Flying Leads with Diode													
DN		DIN 43650													
*Bi-directional diode															
Manual Override Option															
Omit - Push Pin															
PB - Push Button															
SPS - Screw Type															

Solenoid Valves


EVK 06/C5

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Direct Acting, Double Blocking
210 bar [3000 psi] • 40 l/min [10.6 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, direct acting, normally closed, bi-directional solenoid valve. In its de-energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves come standard with a push pin manual override. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition. They do not suffer from momentary opening due to shock pressures.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	210 bar [3000 psi]
Flow Capability	40 l/min [10.6 US gpm]
Leakage	
Coil Options	M16, R16
Weight	0.43 kg [0.95 lb]
Cavity	NCS06/2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

EVK 06/C5 - F - 12D - DE - PB - 00 - B

Filter Option

Omit - No filter
F - Filter 300 µm

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASD*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLD*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Seal Option

Code	Seal kit
B-Buna - N	230000440
V-Viton	230000710

Housing

Code	Ports	Housing Model Code
00	No Housing	
DG6S	#6 SAE, AI	NCS06/2 - DG -6S
DG8S	#8 SAE, AI	NCS06/2 - DG -8S
DG3/8	3/8 BSP, AI	NCS06/2 - DG -3/8
DG1/2	1/2 BSP, AI	NCS06/2 - DG -1/2

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Manual Override Option

Omit - Push Pin
PB - Push Button
SPS - Screw Type
OPS - Protected Push Pin
PAT - Push and Twist

Solenoid Valves


SBV11-8-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking
350 bar [5000 psi] • 45 l/min [12 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed, bi-directional solenoid valve. In its de-energized condition flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	45 l/min [12 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	P series
Weight	0.12 kg [0.26 lb]
Cavity	SDC08-2

■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque
34-41 Nm [25-30 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to 2• B - Port 2 to 1

■ MODEL CODE

SBV11 - 8 - V - C - M - A - 2G - 12D - W - P							
Seal Option				Coil Series			
Code Seal kit				Omit - No coil P - 8 Series, 23 W			
Omit - Buna - N 02-160777							
V - Viton 02-160778				Connector Type			
Manual Override Option				Omit - No manual override G - ISO 4400 DIN 43650 Q - Spade terminals W - Flying lead N - Deutsch (DC only) Y - Amp JR (DC only) D - Metripack 150 male (DC only) J - Metripack 280 male (DC only)			
Omit - No manual override							
M - Pull and Twist				Coil Voltage			
Housing Material				Code Coil Voltage			
Omit - No Housing				00 No Coil, nut included (p/n 565558)			
A - Aluminum				12D 12 VDC			
S - Steel				24D 24 VDC			
Housing				115A 115 VAC**			
Code	Ports	Aluminium	Steel	230A 230 VAC**			
0	No Housing			12B 2VDC/w diode*			
2G	1/4" BSP	02-160727	02-160733	24B 24 VDC/w diode*			
3G	3/8" BSP	02-160728	02-160734	*Optional arc suppression diode			
4T	#4 SAE	02-160730	02-160736	**Internally rectified			
6T	#6 SAE	02-160731	02-160737	***Other voltage options available			
8T	#8 SAE	02-160732	02-160738				

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Solenoid Valves


SBV1-10-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking
210 bar [3000 psi] • 76 l/min [20 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed, bi-directional solenoid valve. In its de-energized condition flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	76 l/min [20 US gpm]
Leakage	5 drops/min @ 210 bar [3000 psi]
Coil Options	J series
Weight	0.18 kg [0.39 lb]
Cavity	SDC 10-2

■ DIMENSIONS


mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque


47-54 Nm [35-40 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



Flow - USgpm (105 SUS oil @ 120°F)

A - Port 1 to port 2 • B - Port 2 to port 1

■ MODEL CODE

SBV1 - 10 - V - C - M - A - 2G - 12D - G - J

Seal Option

Code	Seal kit
Omit-Buna - N	565806
V-Viton	889627

Manual Override Option

Omit - No manual override
M - Pull and Twist

Housing Material

O - No Housing
A - Aluminum
S - Steel

Housing

Code	Ports	Aluminum Standard Duty	Aluminum Heavy Duty	Steel
0	No Housing			
2G	1/4" BSP	876702	02-175102	
3G	3/8" BSP	876703	02-175103	
3B	3/8" BSP	02-175462		
6H	#6 SAE	876700		
6T	#6 SAE	566151	02-175100	
8H	#8 SAE	876701		
8T	#8 SAE		02-175101	

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi]

* Additional housings available

Coil Series

Omit - No coil
J - 10 Series, 23 W

Connector Type

Omit - No coil
G - ISO 4400 DIN 43650
Q - Spade terminals
W - Flying lead
N - Deutsch (DC only)
Y - Amp JR (DC only)
D - Metripack 150 male (DC only)
J - Metripack 280 male (DC only)

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included (p/n 565558)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*

*Optional arc suppression diode

**Internally rectified

***Other voltage options available

Solenoid Valves


SBV11-10-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking
350 bar [5000 psi] • 76 l/min [20 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed, bi-directional solenoid valve. In its de-energized condition flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA


Rated Pressure	350 bar [5000 psi]
Rated flow	76 l/min [20 USgpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2

■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]



■ Installation torque


A - 47-54 Nm [35-40 ft. lbs]

S - 68-75 Nm [50-55 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



■ MODEL CODE

SBV11 - 10 - V - C - A - 2G - 12D - G - H

Seal Option

Code	Seal kit
Omit - Buna - N	565806
V-Viton	889627

Housing Material

Omit - No Housing
A - Aluminum
S - Steel

Housing

Code	Ports	Aluminum Standard Duty	Aluminum Heavy Duty	Steel
0	No Housing			
2G	1/4" BSP	876702	02-175102	
3G	3/8" BSP	876703	02-175103	
3B	3/8" BSP	02-175462		
6H	#6 SAE	876700		
6T	#6 SAE	566151	02-175100	
8H	#8 SAE	876701		
8T	#8 SAE	02-175101		

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Coil Series

Omit	No coil
G	10 series, 29 W

Connector Type

Omit	No coil
G	ISO 4400 DIN 43650
Q	Spade terminals
W	Flying lead
N	Deutsch (DC only)
Y	Amp JR (DC only)
D	Metripack 150 male (DC only)
J	Metripack 280 male (DC only)

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included, [p/n 02-175698]
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC***
12B	2VDC/w diode*
24B	24 VDC/w diode*

*Optional arc suppression diode

**Internally rectified

***Other voltage options available

Solenoid Valves


SBV1-12-C

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking
210 bar [3000 psi] • 114 l/min [30 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed, bi-directional solenoid valve. In its de-energized condition flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	114 l/min [30 US gpm]
Leakage	5 drops/ min @ 210 bar [3000 psi]
Coil Options	J series
Weight	0.27 kg [0.59 lb]
Cavity	C-12-2 / C-12-2U

■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque

A - 81-95 Nm [60-70 ft lbs]


S - 102-115 Nm [75-85 ft lbs]



■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



Flow - USgpm (105 SUS oil @ 120°F)

A - Port 1 to port 2 • **B** - Port 2 to port 1

■ MODEL CODE

SBV1 - 12 - V - C - A - 4G - U - 12D - N - J																							
Seal Option																							
Code	Seal kit						Coil Series																
0mit-Buna - N	02-165889						0mit - No coil																
Housing Material																							
V-Viton		0mit - No housing					J - 10 Series, 23 W																
		A - Aluminum					Connector Type																
		S - Steel					G - ISO 4400 DIN 43650																
Housing							Q - Spade terminals																
Code	Ports	C-12-2 Aluminum Heavy Duty	C-12-2U Aluminum Heavy Duty	C-12-2 Steel Heavy Duty	C-12-2U Steel Heavy Duty																		
0	No Housing																						
4G	1/2" BSP	02-161118	02-161116	02-172062	02-172512																		
6G	3/4" BSP	02-161117	02-161115	02-169665	02-162922																		
10T	#10 SAE	02-160640	02-160641	02-169744	02-169817																		
12T	#12 SAE	02-160644	02-160645	02-169782	02-169790																		
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].																							
* Additional housings available																							
Cavity																							
Omit - Cavity without undercut/No housing																							
U - Cavity with undercut																							
Coil Voltage																							
Code	Coil Voltage																						
00	No Coil, nut included (p/n 565558)																						
12D	12 VDC																						
24D	24 VDC																						
115A	115 VAC**																						
230A	230 VAC**																						
12B	2VDC/w diode*																						
24B	24 VDC/w diode*																						
*Optional arc suppression diode																							
**Internally rectified																							
***Other voltage options available																							

Solenoid Valves

SBV11-12-C


Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated, Double Blocking

350 bar [5000 psi] • 114 l/min [30 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally closed, bi-directional solenoid valve. In its de-energized condition flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. When energized, flow can take place from port 2 to 1 and from 1 to 2. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	114 l/min [30 USgpm]
Leakage	5 drops/ min @ 350 bar [3000 psi]
Coil Options	H series
Weight	0.27 kg [0.59 lb]
Cavity	C-12-2 / C-12-2U

■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque


A - 81-95 Nm [60-70 ft lbs]

S - 102-115 Nm [75-85 ft lbs]

■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



A - Port 1 to 2 • B - Port 2 to 1

■ MODEL CODE

SBV11 - 12 - V - C - A - 4G - U - 12D - G - H																						
Seal Option																						
Code	Seal kit																					
Omit -Buna - N	02-165889																					
V -Viton	02-165888																					
Housing Material																						
Omit - No Housing																						
A - Aluminum																						
S - Steel																						
Housing																						
Code	Ports	C-12-2 Aluminum Heavy Duty	C-12-2U Aluminum Heavy Duty	C-12-2 Steel Heavy Duty	C-12-2U Steel Heavy Duty																	
0	No Housing																					
4G	1/2" BSP	02-161118	02-161116	02-172062	02-172512																	
6G	3/4" BSP	02-161117	02-161115	02-169665	02-162922																	
10T	#10 SAE	02-160640	02-160641	02-169744	02-169817																	
12T	#12 SAE	02-160644	02-160645	02-169782	02-169790																	
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].																						
* Additional housings available																						
Cavity																						
Omit - Cavity without undercut/No housing																						
U - Cavity with undercut																						
Coil Series																						
Omit - No coil																						
H - 10 series, 29 W																						
Connector Type																						
Omit - No coil																						
G - ISO 4400 DIN 43650																						
Q - Spade terminals																						
W - Flying lead																						
N - Deutsch (DC only)																						
Y - Amp JR (DC only)																						
D - Metripack 150 male (DC only)																						
J - Metripack 280 male (DC only)																						
Coil Voltage																						
Code	Coil Voltage																					
00	No Coil, nut included. (p/n 02-175698)																					
12D	12 VDC																					
24D	24 VDC																					
115A	115 VAC**																					
230A	230 VAC**																					
12B	2VDC/w diode*																					
24B	24 VDC/w diode*																					
*Optional arc suppression diode																						
**Internally rectified																						
***Other voltage options available																						

Solenoid Valves

SV08-22-02


Solenoid Valve, 2-way, Spool Type, Normally Closed

230 bar [3300 psi] • 18 l/min [4.7 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, spool type, normally closed solenoid valve. In its de-energized condition flow is blocked in both directions. When energized, flow can take place from port 2 to 1 and from 1 to 2. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	18 l/min [4.7 US gpm]
Leakage	
Coil Options	M13, R13
Weight	0.29 kg [0.64 lb]
Cavity	SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 22 - 02 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-2-4S
6S	#6 SAE, AL	CP08-2-6S
S6S	#6 SAE, Steel	CP08-2-S6S
DG2B	1/4 BSP, AL	SDC08-2-DG2B
DG3B	3/8 BSP, AL	SDC08-2-DG3B
S3B	3/8 BSP, Steel	CP08-2-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003119
V-Viton	354003619

Solenoid Valves

HSV08-22-02


Solenoid Valve, 2-way, Spool Type, Normally Closed

350 bar [5000 psi] • 20 l/min [5.3 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, spool type, normally closed solenoid valve. In its de-energized condition flow is blocked in both directions. When energized, flow can take place from port 2 to 1 and from 1 to 2. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	350 bar [5000 psi]
Flow Capability	20 l/min [5.3 US gpm]
Leakage	
Coil Options	M13, R13
Weight	0.35 kg [0.77 lb]
Cavity	SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 22 - 02 - 12D - DE - XC - P - S3B																																								
Coil Voltage			Housing																																					
<table border="1"> <thead> <tr><th>Standard Coil Code</th><th>Robust Coil Code</th><th>Coil Voltage</th></tr> </thead> <tbody> <tr><td>00</td><td>R00</td><td>No Coil, nut included*</td></tr> <tr><td>10D</td><td>R10D</td><td>10 VDC</td></tr> <tr><td>12D</td><td>R12D</td><td>12 VDC</td></tr> <tr><td>20D</td><td>R20D</td><td>20 VDC</td></tr> <tr><td>24D</td><td>R24D</td><td>24 VDC</td></tr> <tr><td>110A</td><td></td><td>110 VAC**</td></tr> <tr><td>220A</td><td></td><td>220 VAC**</td></tr> </tbody> </table>			Standard Coil Code	Robust Coil Code	Coil Voltage	00	R00	No Coil, nut included*	10D	R10D	10 VDC	12D	R12D	12 VDC	20D	R20D	20 VDC	24D	R24D	24 VDC	110A		110 VAC**	220A		220 VAC**	<table border="1"> <thead> <tr><th>Code Ports</th><th>Housing Model Code</th></tr> </thead> <tbody> <tr><td>00</td><td>No Housing</td></tr> <tr><td>S3B</td><td>3/8 BSP, Steel CP10-2-S3B</td></tr> <tr><td>S4B</td><td>1/2 BSP, Steel CP08-2-S4S</td></tr> <tr><td>S6S</td><td>#6 SAE, Steel CP08-2-S6S</td></tr> </tbody> </table>			Code Ports	Housing Model Code	00	No Housing	S3B	3/8 BSP, Steel CP10-2-S3B	S4B	1/2 BSP, Steel CP08-2-S4S	S6S	#6 SAE, Steel CP08-2-S6S	
Standard Coil Code	Robust Coil Code	Coil Voltage																																						
00	R00	No Coil, nut included*																																						
10D	R10D	10 VDC																																						
12D	R12D	12 VDC																																						
20D	R20D	20 VDC																																						
24D	R24D	24 VDC																																						
110A		110 VAC**																																						
220A		220 VAC**																																						
Code Ports	Housing Model Code																																							
00	No Housing																																							
S3B	3/8 BSP, Steel CP10-2-S3B																																							
S4B	1/2 BSP, Steel CP08-2-S4S																																							
S6S	#6 SAE, Steel CP08-2-S6S																																							
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)			* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].																																					
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)			* Additional housings available																																					
**DIN only - external rectifier needed			Seal Option																																					
Connector Type			<table border="1"> <thead> <tr><th>Code</th><th>Seal kit</th></tr> </thead> <tbody> <tr><td>P-Polyurethane Single Seal</td><td>11167278</td></tr> </tbody> </table>			Code	Seal kit	P-Polyurethane Single Seal	11167278																															
Code	Seal kit																																							
P-Polyurethane Single Seal	11167278																																							
<table border="1"> <thead> <tr><th>Standard Coil Code</th><th>Robust Coil Code</th><th>Connector Type</th></tr> </thead> <tbody> <tr><td>00</td><td>00</td><td>No Coil</td></tr> <tr><td>AJ</td><td></td><td>Amp Junior</td></tr> <tr><td>AJD</td><td></td><td>Amp Junior with Diode</td></tr> <tr><td>AS</td><td>AS</td><td>AMP SuperSeal 1.5</td></tr> <tr><td>ASD</td><td>ASDB*</td><td>AMP SuperSeal with Diode</td></tr> <tr><td>DE</td><td>DE</td><td>Deutsch</td></tr> <tr><td>DED</td><td>DED*</td><td>Deutsch with Diode</td></tr> <tr><td>FL</td><td>FL</td><td>Flying Leads</td></tr> <tr><td>FLD</td><td>FLDB*</td><td>Flying Leads with Diode</td></tr> <tr><td>DN</td><td></td><td>DIN 43650</td></tr> </tbody> </table>			Standard Coil Code	Robust Coil Code	Connector Type	00	00	No Coil	AJ		Amp Junior	AJD		Amp Junior with Diode	AS	AS	AMP SuperSeal 1.5	ASD	ASDB*	AMP SuperSeal with Diode	DE	DE	Deutsch	DED	DED*	Deutsch with Diode	FL	FL	Flying Leads	FLD	FLDB*	Flying Leads with Diode	DN		DIN 43650	<table border="1"> <thead> <tr><th colspan="2">*Bi-directional diode</th></tr> </thead> </table>			*Bi-directional diode	
Standard Coil Code	Robust Coil Code	Connector Type																																						
00	00	No Coil																																						
AJ		Amp Junior																																						
AJD		Amp Junior with Diode																																						
AS	AS	AMP SuperSeal 1.5																																						
ASD	ASDB*	AMP SuperSeal with Diode																																						
DE	DE	Deutsch																																						
DED	DED*	Deutsch with Diode																																						
FL	FL	Flying Leads																																						
FLD	FLDB*	Flying Leads with Diode																																						
DN		DIN 43650																																						
*Bi-directional diode																																								

Solenoid Valves

SV10-22-02


Solenoid Valve, 2-way, Spool Type, Normally Closed

230 bar [3300 psi] • 35 l/min [9 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, spool type, normally closed solenoid valve. In its de-energized condition flow is blocked in both directions. When energized, flow can take place from port 2 to 1 and from 1 to 2. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ DIMENSIONS

mm [in]



■ PERFORMANCE DATA


Rated Pressure*	230 bar [3300 psi]**
Flow Capability	35 l/min [9 US gpm]
Coil Options	M16, R16
Weight	0.43 kg [0.95 lb]
Cavity	SDC10-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)


**Valve can operate at 315 bar [4600 psi] for 120,000 cycles. With inlet at port 2, this value is increased to 500,000 cycles.

■ PERFORMANCE CURVES

Pressure drop



Operating envelope



■ MODEL CODE

SV10 - 22 - 02 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP08-2-6S
8S	#8 SAE, AL	CP10-2-8S
58S	#8 SAE, Steel	CP10-2-58S
DG3B	3/8 BSP, AL	SDC10-2-DG3B
DG4B	1/2 BSP, AL	SDC10-2-DG4B
S4B	1/2 BSP, AL	CP10-2-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354004019
V-Viton	354003419

Solenoid Valves

SV14-10-C


Solenoid Valve, 2-way, Spool Type, Normally Closed

350 bar [5000 psi] • 23 l/min [6 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, spool type, normally closed solenoid valve. In its de-energized condition flow is blocked in both directions. When energized, flow can take place from port 2 to 1 and from 1 to 2. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC




■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]




Installation torque

68-75 Nm [50-55 ft lbs]

■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Flow Capability	23 l/min [6 US gpm]
Leakage	140 ml/min (8.5 in³/min) max @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2

■ PERFORMANCE CURVES



■ MODEL CODE

SV14 - 10 - V - C - M - S - 2G - 12D - G - H	
Seal Option	Coil Series
Code	Seal kit
Omit-Buna - N	565806
V-Viton	889627
Manual Override Option	Omit - No coil H - 10 series, 29 W
Omit - No manual override	
M - Pull and Twist	
Housing Material	Connector Type
Omit - No Housing	Omit - No coil G - ISO 4400 DIN 43650 Q - Spade terminals W - Flying lead N - Deutsch (DC only) Y - Amp JR (DC only)
S - Steel	D - Metripack 150 male (DC only) J - Metripack 280 male (DC only)
Housing	Coil Voltage
Code	Coil Voltage
Ports	00 No Coil, nut included, (p/n 02-175698)
0	12D 12 VDC
2G	24D 24 VDC
3G	115A 115 VAC**
6T	230A 230 VAC**
8T	12B 2VDC/w diode*
#6 SAE	24B 24 VDC/w diode*
#8 SAE	*Optional arc suppression diode
	**Internally rectified
	***Other voltage options available
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].	
* Additional housings available	

Solenoid Valves

SV15-22-02


Solenoid Valve, 2-way, Spool Type, Normally Closed

230 bar [3300 psi] • 60 l/min [16 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, spool type, normally closed solenoid valve. In its de-energized condition flow is blocked in both directions. When energized, flow can take place from port 2 to 1 and from 1 to 2. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the de-energized condition.

■ SCHEMATIC



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	60 l/min [16 US gpm]
Coil Options	M19
Weight	0.65 kg [1.65 lb]
Cavity	NCS 12/2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 100,000 cycles. With inlet at port 2, this can be increased to 300,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 22 - 02 - 12D - DE - B - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800968)

**DIN only - external rectifier needed

Connector Type

Code
00
AJ
AJD
DE
DED
FL
DN

Housing

Code	Ports	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS 12/2-DG-8S
12S	#12 SAE, Steel	NCS 12/2-DG-12S
4B	1/2 BSP, AL	NCS 12/2-DG-1/2
6B	3/4 BSP, AL	NCS 12/2-DG-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115411
V-Viton	11115413

Solenoid Valves

SVP08-NO


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated

230 bar [3300 psi] • 35 l/min [9 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. In its de-energized condition, flow can take place from port 2 to 1 but is restricted in the other direction. When energized, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. Some models have the option of a filter around port 2, and these come standard with a push pin manual override. These valves can be used to hold loads in position when energized or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Rated flow	35 l/min [9 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0.23 kg [0.51 lb]
Cavity	SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] on port 2 for 600,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SVP08 - NO - 12D - DE - PB - B - F - 00					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	CP08-2-4S
10D	R10D	10 VDC	4S	#4 SAE, AL	CP08-2-4S
12D	R12D	12 VDC	6S	#6 SAE, AL	CP08-2-6S
20D	R20D	20 VDC	S6S	#6 SAE, Steel	CP08-2-S6S
24D	R24D	24 VDC	DG2B	1/4 BSP, AL	SDC08-2-DG2B
110A		110 VAC**	DG3B	3/8 BSP, AL	SDC08-2-DG3B
220A		220 VAC**	S3B	3/8 BSP, Steel	CP08-2-S3B
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588) **Robust Coil - Steel coil nut and no o-rings (p/n 173800539) **DIN only - external rectifier needed					
Connector Type			Filter Option		
Standard Coil Code	Robust Coil Code	Connector Type	Omit	No filter	
00	00	No Coil	F	Filter 300 µm	
AJ		Amp Junior			
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode					
Seal Option					
Code	Seal kit				
B-Buna - N	354000119				
V-Viton	354000219				
Manual Override					
Omit	- Push Pin				
PB	- Push Button				
SPS	- Screw Type				

Solenoid Valves

SV15-8-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated

350 bar [5000 psi] • 38 l/min [10 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. In its de-energized condition flow can take place from port 2 to 1 but is restricted in the other direction. When energized flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA


Rated Pressure	350 bar [5000 psi]
Rated flow	38 l/min [10 US gpm]
Leakage	5 drops/ min @ 210 bar [3000 psi]
Coil Options	P series
Weight	0.11 kg [0.25 lb]
Cavity	SDC08-2

■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]



Installation torque
34-41 Nm [25-30 ft. lbs]

■ PERFORMANCE CURVES



A - Port 1 to 2 energized • B - Port 2 to 1 de-energized

■ MODEL CODE

SV15 - 8 - V - O - P - S - 2G - 12D - G - P		
Seal Option		Coil Series
Code	Seal kit	0mit - No coil P - 8 Series, 23 W
0mit - Buna - N	02-165875	
V-Viton	02-165877	
Manual Override Option		Connector Type
0mit - No manual override		0mit - No coil G - ISO 4400 DIN 43650
P - Push type		Q - Spade terminals
S - Screw type		W - Flying lead
Housing Material		N - Deutsch (DC only)
0mit - No Housing		Y - Amp JR (DC only)
S - Steel		D - Metripack 150 male (DC only)
Housing		J - Metripack 280 male (DC only)
Code	Ports	Coil Voltage
00	Steel	00 No Coil, nut included (p/n 565558)
2G	1/4" BSP	12D 12 VDC
3G	3/8" BSP	24D 24 VDC
4T	#4 SAE	115A 115 VAC**
6T	#6 SAE	230A 230 VAC**
8T	#8 SAE	12B 2VDC/w diode*
		24B 24 VDC/w diode*
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
** Internal rectified		
*** Other voltage options available		

Solenoid Valves

SVP10-NO


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated

230 bar [3300 psi] • 80 l/min [21 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. In its de-energized condition, flow can take place from port 2 to 1 but is restricted in the other direction. When energized, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. Some models have the option of a filter around port 2, and these come standard with a push pin manual override. These valves can be used to hold loads in position when energized or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ DIMENSIONS



■ PERFORMANCE DATA


Rated Pressure*	230 bar [3300 psi]**
Rated flow	80 l/min [21 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M16, R16
Weight	0.43 kg [0.95 lb]
Cavity	SDC10-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] on port 2 for 300,000 cycles.

■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SVP10 - NO - 12D - DE - PB - B - F - 6S					
Coil Voltage					
Standard Coil Code	Robust Coil Code	Coil Voltage			
00	R00	No Coil, nut included*			
10D	R10D	10 VDC			
12D	R12D	12 VDC			
20D	R20D	20 VDC			
24D	R24D	24 VDC			
110A		110 VAC**			
220A		220 VAC**			
*Standard Coil - Plastic coil nut and o-rings (p/n 1740002)					
*Robust Coil - Steel coil nut and no o-rings (p/n 173804910)					
**DIN only - external rectifier needed					
Connector Type					
Standard Coil Code	Robust Coil Code	Connector Type			
00	00	No Coil			
AJ		Amp Junior			
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DED*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode					
Housing					
Code	Ports	Housing Model Code			
00	No Housing				
6S	#6 SAE, AL	CP10-2-6S			
8S	#8 SAE, AL	CP10-2-8S			
S8S	#8 SAE, Steel	CP10-2-S8S			
DG3B	3/8 BSP, AL	SDC10-2-DG3B			
DG3B	1/2 BSP, AL	SDC10-2-DG4B			
S4B	1/2 BSP, Steel	CP10-2-S4B			
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].					
* Additional housings available					
Filter Option					
Omit	- No filter				
F	- Filter 300 µm				
Seal Option					
Code	Seal kit				
B-Buna - N	354000719				
V-Viton	354000819				
Manual Override					
Omit	- Push Pin				
PB	- Push Button				
SPS	- Screw Type				
OPS	- Protected Push Pin				
PAT	- Push and Twist				

Solenoid Valves

SV15-10-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated

350 bar [5000 psi] • 45 l/min [12 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. In its de-energized condition, flow can take place from port 2 to 1 but is restricted in the other direction. When energized, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	45 l/min [12 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2


■ DIMENSIONS

mm [in]

Coil nut torque


5-8 Nm [4-6 ft. lbs]

Installation torque
68-75 Nm [50-55 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SV15 - 10 - V - O - P - S - 2G - 12D - G - H	
Seal Option	Coil Series
Code	Seal kit
Omit -Buna - N	565803
V -Viton	566086
Manual Override Option	Connector Type
Omit - No manual override	Omit - No coil
P - Push type	G - ISO 4400 DIN 43650
S - Screw type	Q - Spade terminals
Housing	W - Flying lead
Code	N - Deutsch (DC only)
Ports	Y - Amp JR (DC only)
00	D - Metripack 150 male (DC only)
No Housing	J - Metripack 280 male (DC only)
2G	
1/4" BSP	
3G	
3/8" BSP	
6T	
#6 SAE	
8T	
#8 SAE	
Housing Material	
Omit - No Housing	
S - Steel	
Code	Coil Voltage
00	No Coil, nut included, (p/n 02-175698)
No Housing	12D 12 VDC
2G	24 VDC
1/4" BSP	115A 115 VAC**
3G	230A 230 VAC**
3/8" BSP	12B 2VDC/w diode*
6T	24B 24 VDC/w diode*
#6 SAE	
8T	
#8 SAE	
<small>* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].</small>	<small>*Optional arc suppression diode</small>
<small>* Additional housings available</small>	<small>**Internally rectified</small>
	<small>***Other voltage options available</small>

Solenoid Valves

SVP08-NOR


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow

230 bar [3300 psi] • 35 l/min [9 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. Some models have the option of a filter around port 2, and these come standard with a push pin manual override. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Rated flow	35 l/min [9 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0.23 kg [0.51 lb]
Cavity	SDC08-2


*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] on port 2 for 600,000 cycles.

■ DIMENSIONS



■ PERFORMANCE CURVES



■ MODEL CODE

SVP08 - NOR - 12D - DE - PB - B - F - 4S					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	
10D	R10D	10 VDC	4S	#4 SAE, AL	CP08-2-4S
12D	R12D	12 VDC	6S	#6 SAE, AL	CP08-2-6S
20D	R20D	20 VDC	S6S	#6 SAE, Steel	CP08-2-S6S
24D	R24D	24 VDC	DG2B	1/4 BSP, AL	SDC08-2-DG2B
110A		110 VAC**	DG3B	3/8 BSP, AL	SDC08-2-DG3B
220A		220 VAC**	S3B	3/8 BSP, Steel	CP08-2-S3B
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)					
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)					
**DIN only - external rectifier needed					
Connector Type			Filter Option		
Standard Coil Code	Robust Coil Code	Connector Type	Omit	- No filter	
00	00	No Coil	F	- Filter 300 µm	
AJ		Amp Junior			
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DED*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode					
Seal Option					
Code	Seal kit				
B-Buna - N	354000119				
V-Viton	354000219				
Manual Override Option					
Omit	- Push Pin				
PB	- Push Button				
SPS	- Screw Type				

Solenoid Valves

SVP10-NOR


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow

230 bar [3300 psi] • 80 l/min [21 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. Some models have the option of a filter around port 2, and these come standard with a push pin manual override. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ DIMENSIONS

mm [in]



■ PERFORMANCE DATA


Rated Pressure*	230 bar [3300 psi]**
Rated flow	80 l/min [21 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M16, R16
Weight	0.43 kg [0.95 lb]
Cavity	SDC10-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] on port 2 for 300,000 cycles.

■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SVP10 - NOR - 12D - DE - PB - B - F - 6S						
Coil Voltage						
Standard Coil Code	Robust Coil Code	Coil Voltage				
00	R00	No Coil, nut included*				
10D	R10D	10 VDC				
12D	R12D	12 VDC				
20D	R20D	20 VDC				
24D	R24D	24 VDC				
110A		110 VAC**				
220A		220 VAC**				
*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)						
*Robust Coil - Steel coil nut and no o-rings (p/n 173804910)						
**DIN only - external rectifier needed						
Connector Type						
Standard Coil Code	Robust Coil Code	Connector Type				
00	00	No Coil				
AJ		Amp Junior				
AJD		Amp Junior with Diode				
AS	AS	AMP SuperSeal 1.5				
ASD	ASDB*	AMP SuperSeal with Diode				
DE	DE	Deutsch				
DED	DED*	Deutsch with Diode				
FL	FL	Flying Leads				
FLD	FLD*	Flying Leads with Diode				
DN		DIN 43650				
*Bi-directional diode						
Housing						
Code	Ports	Housing Model Code				
00	No Housing					
6S	#6 SAE, AL	CP10-2-6S				
8S	#8 SAE, AL	CP10-2-8S				
S8S	#8 SAE, Steel	CP10-2-S8S				
DG3B	3/8 BSP, AL	SDC10-2-DG3B				
DG4B	1/2 BSP, AL	SDC10-2-DG4B				
S4B	1/2 BSP, Steel	CP10-2-S4B				
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].						
* Additional housings available						
Filter Option						
Omit	- No filter					
F	- Filter 300 µm					
Seal Option						
Code	Seal kit					
B-Buna - N	354000719					
V-Viton	354000819					
Manual Override Option						
Omit	- Push Pin					
PB	- Push Button					
SPS	- Screw Type					
OPS	- Protected Push Pin					
PAT	- Push and Twist					

Solenoid Valves

SV13-10-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow

350 bar [5000 psi] • 45 l/min [12 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA



Rated Pressure	350 bar [5000 psi]
Rated flow	45 l/min [12 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2

■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop



Port 1 to 2 and port 2 to 1 de-energized

■ MODEL CODE

SV13 - 10 - V - O - P - S - 2G - 12D - G - H																						
Seal Option					Coil Series																	
Code Seal kit					Omit - No coil																	
Omit-Buna - N 565803					H - 10 series, 29 W																	
V-Viton 566086					Connector Type																	
Manual Override Option					Omit - No manual override																	
Omit - No manual override					G - ISO 4400 DIN 43650																	
P - Push type					Q - Spade terminals																	
S - Screw type					W - Flying lead																	
Housing Material					N - Deutsch (DC only)																	
Omit - No Housing					Y - Amp JR (DC only)																	
S - Steel					D - Metripack 150 male (DC only)																	
Housing					J - Metripack 280 male (DC only)																	
Code	Ports	Steel																				
0	No Housing																					
2G	1/4" BSP	02-175102																				
3G	3/8" BSP	02-175103																				
6T	#6 SAE	02-175100																				
8T	#8 SAE	02-175101																				
*Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].																						
* Additional housings available																						
Coil Voltage																						
Code	Coil Voltage																					
00	No Coil, nut included, (p/n 02-175698)																					
12D	12 VDC																					
24D	24 VDC																					
115A	115 VAC**																					
230A	230 VAC**																					
12B	2VDC/w diode*																					
24B	24 VDC/w diode*																					
*Optional arc suppression diode																						
**Internally rectified																						
***Other voltage options available																						

Solenoid Valves

SLP13-10-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow

350 bar [5000 psi] • 95 l/min [25 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, normally open solenoid valve. In its de-energized condition flow can take place from port 2 to 1 and from 1 to 2. When energized, flow can take place from port 1 to 2, but flow is blocked from port 2 to 1 with minimum leakage due to the poppet design. These valves can be used to hold loads in position or to interrupt a pressure line where flow normally passes in both directions. Due to its low power coil and low pressure drop, these valves are suitable for high ambient temperature applications, as space savers in a HIC design, or where reducing power consumption is important.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated pressure*	350 bar [5000 psi]
Rated flow	95 l/min [25 US gpm]
Leakage	10 drops/min @ 350 bar [5000 psi]
Coil Options	K series, 10 W
Weight	0.16 kg [0.35 lb]
Cavity	SDC10-2

*Note: Rated pressure based on NFPA fatigue test standard [at 1 million cycles]

■ PERFORMANCE CURVES



■ MODEL CODE

SLP13 - 10 - V - O - S - 2G - 12D - N - K										
Seal Option										
Code	Seal Kit									
Omit-Buna	565803									
V-Viton	566086									
Housing Material										
Omit - No housing A - Aluminum S - Steel										
Housing										
Code	Aluminum Standard Duty	Aluminum Heavy Duty	Steel Heavy Duty							
0	No Housing									
3B	3/8" BSP	02-175462								
2G	1/4" BSP	876702	02-175102							
3G	3/8" BSP	876703	02-175103							
6H	#6 SAE	876700								
8H	#8 SAE	876701								
6T	#6 SAE	566151	02-175100							
8T	#8 SAE		02-175101							
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi]										
* Additional housings available										
Coil Series										
Omit - No coil K - K series, 10W										
Connector Type										
Omit - No connector N - Deutsch										
* Additional connectors available. Contact technical support.										
Coil Voltage										
00 - No Coil 12D - 12 VDC 24D - 24 VDC										

Solenoid Valves


SV3-12-O

Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow
210 bar [3000 psi] • 114 l/min [30 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	114 l/min [30 US gpm]
Leakage	5 drops/ min @ 210 bar [3000 psi]
Coil Options	J series
Weight	0.34 kg [0.74 lb]
Cavity	C-12-2/C-12-2U

■ DIMENSIONS


mm [in]

Coil nut torque


5-8 Nm [4-6 ft. lbs]

Installation torque

81-95 Nm [60-70 ft. lbs]



■ PERFORMANCE CURVES



■ MODEL CODE

SV3 - 12 - V - O - P - A - 4G - U - 12D - G									
Seal Option					Connector Type				
Code Seal kit					Code Connector				
Omit-Buna - N 02-165889					Omit - No coil				
V-Viton 02-165888					G - ISO 4400 DIN 43650				
Manual Override Option					Q - Spade terminals				
Omit - No manual override					W - Flying lead				
P - Push type					N - Deutsch (DC only)				
S - Screw type					Y - Amp JR (DC only)				
Housing					D - Metripack 150 male (DC only)				
Code Ports					J - Metripack 280 male (DC only)				
C-12-2 Aluminum Heavy Duty					Coil Voltage				
C-12-2U Aluminum Heavy Duty					Code Coil Voltage				
0 No Housing					00 No Coil, nut included (p/n 565559)				
4G 1/2" BSP					12D 12 VDC				
6G 3/4" BSP					24D 24 VDC				
10T #10 SAE					115A 115 VAC**				
12T #12 SAE					230A 230 VAC**				
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].					12B 2VDC/w diode*				
* Additional housings available					24B 24 VDC/w diode*				
Cavity					*Optional arc suppression diode				
Omit - Cavity without undercut/No housing					**Internally rectified				
U - Cavity with undercut					***Other voltage options available				

Solenoid Valves


SV13-12-O

Solenoid Valve, 2-way, Poppet Type, Normally Closed, Pilot Operated with Reverse Free Flow
350 bar [5000 psi] • 114 l/min [30 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	114 l/min [30 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.27 kg [0.59 lb]
Cavity	C-12-2 / C-12-2U

■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque


102-115 Nm [75-85 ft. lbs]

2



■ PERFORMANCE CURVES

Pressure Drop



A - Port 1 to 2 energized • B - Port 2 to 1 de-energized

■ MODEL CODE

SV13 - 12 - V - O - P - S - 4G - U - 12D - G - H																		
Seal Option																		
Code Seal kit																		
Omit-Buna - N 02-165889																		
V-Viton 02-165888																		
Manual Override Option																		
Omit - No manual override					Housing Material													
P - Push type					Omit - No Housing													
S - Screw type					S - Steel													
Housing																		
Code	Ports	C-12-2 Heavy Duty	C-12-2U Heavy Duty															
0	No Housing																	
4G	1/2" BSP	02-172062	02-172512															
6G	3/4" BSP	02-169665	02-162922															
10T	#10 SAE	02-169744	02-169817															
12T	#12 SAE	02-169782	02-169790															
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].																		
* Additional housings available																		
Cavity																		
Omit - Cavity without undercut/No housing																		
U - Cavity with undercut																		
Coil Series																		
Omit - No coil																		
H - 10 series, 29 W																		
Connector Type																		
Omit - No coil																		
G - ISO 4400 DIN 43650																		
Q - Spade terminals																		
W - Flying lead																		
N - Deutsch (DC only)																		
Y - Amp JR (DC only)																		
D - Metripack 150 male (DC only)																		
J - Metripack 280 male (DC only)																		
Coil Voltage																		
Code	Coil Voltage																	
00	No Coil, nut included, (p/n 02-175698)																	
12D	12 VDC																	
24D	24 VDC																	
115A	115 VAC**																	
230A	230 VAC**																	
12B	2VDC/w diode*																	
24B	24 VDC/w diode*																	
*Optional arc suppression diode																		
**Internally rectified																		
***Other voltage options available																		

Solenoid Valves


SV3-16-O

Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow
210 bar [3000 psi] • 132 l/min [35 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	132 l/min [35 US gpm]
Leakage	5 drops/min @ 210 bar [3000 psi]
Coil Options	J series
Weight	0.9 kg [1.98 lb]
Cavity	SDC16-2

■ MODEL CODE

SV3 - 16 - V - O - P - A - 6B - 12D - G											
Seal Option				Connector Type							
Code Seal kit				Omit - No coil G - ISO 4400 DIN 43650 Q - Spade terminals W - Flying lead N - Deutsch (DC only) Y - Amp JR (DC only) D - Metripack 150 male (DC only) J - Metripack 280 male (DC only)							
Omit - Buna - N 565810 V - Viton 889609											
Manual Override Option				Coil Voltage							
Omit - No manual override P - Push type S - Screw type				Code Coil Voltage							
				00 No Coil, nut included, (p/n 565559)							
				12D 12 VDC							
				24D 24 VDC							
				115A 115 VAC**							
				230A 230 VAC**							
				12B 2VDC/w diode*							
				24B 24 VDC/w diode*							
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].											
** Additional housings available											
* Optional arc suppression diode											
** Internally rectified											
*** Other voltage options available											

Solenoid Valves


SV13-16-O

Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow
350 bar [5000 psi] • 132 l/min [35 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	132 l/min [35 US gpm]
Leakage	5 drops/min max @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.39 kg [0.85 lb]
Cavity	SDC16-2

■ MODEL CODE

SV13 - 16 - V - O - P - S - 4G - 12D - G - H		
Seal Option		
Code	Seal kit	
Omit-Buna - N	565810	
V-Viton	889609	
Manual Override Option		
Omit	- No manual override	
P	- Push type	
S	- Screw type	
Housing Material		
Omit	- No Housing	
S	- Steel	
Housing		
Code	Ports	Steel
0	No Housing	
4G	1/2" BSP	02-175106
6G	3/4" BSP	02-175107
10T	#10 SAE	02-175104
12T	#12 SAE	02-175105
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
* Additional housings available		
Coil Series		
Omit	- No coil	
H	- 10 series, 29 W	
Connector Type		
Omit	- No coil	
G	- ISO 4400 DIN 43650	
Q	- Spade terminals	
W	- Flying lead	
N	- Deutsch (DC only)	
Y	- Amp JR (DC only)	
D	- Metripack 150 male (DC only)	
J	- Metripack 280 male (DC only)	
Coil Voltage		
Code	Coil Voltage	
00	No Coil, nut included, (p/n 02-175698)	
12D	12 VDC	
24D	24 VDC	
115A	115 VAC**	
230A	230 VAC**	
12B	2VDC/w diode*	
24B	24 VDC/w diode*	
*Optional arc suppression diode		
**Internally rectified		
***Other voltage options available		

Solenoid Valves


SV3-20-O

Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow
210 bar [3000 psi] • 230 l/min [60 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Rated flow	230 l/min [60 US gpm]
Leakage	5 drops/min max @ 210 bar [3000 psi]
Coil Options	J series
Weight	1.2 kg [2.70 lb]
Cavity	SDC20-2

■ DIMENSIONS

mm [in]

Coil nut torque


5-8 Nm [4-6 ft. lbs]

Installation torque
128-155 Nm [95-115 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



A - Port 2 to 1 and port 1 to 2 de-energized • **B** - Port 1 to 2 energized

■ MODEL CODE

SV3 - 20 - V - O - P - 8G - 12D - G

Seal Option

Code	Seal kit
Omit-Buna - N	889615
V-Viton	889619

Manual Override Option

Omit - No manual override
 P - Push type
 S - Screw type

Housing

Code	Ports	Aluminum Standard duty	Aluminum Heavy duty
0	Cartridge only		
8B	1" BSPP	02-175464	
16T	SAE 16	566409	
6G	3/4" BSPP		876732
8G	1" BSPP		876734
12H	SAE 12		876733
16H	SAE 16		876735

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Connector Type

Omit	No coil
G	ISO 4400 DIN 43650
Q	Spade terminals
W	Flying lead
N	Deutsch (DC only)
Y	Amp JR (DC only)
D	Metripack 150 male (DC only)
J	Metripack 280 male (DC only)

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included, (p/n 565559)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*

*Optional arc suppression diode

**Internally rectified

***Other voltage options available

Solenoid Valves

SV13-20-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated with Reverse Free Flow

350 bar [5000 psi] • 230 l/min [60 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition flow can take place from port 1 to 2 but is blocked in the other direction. Leakage is kept to a minimum due to the poppet design. These valves can be used to hold loads in position when energized, interrupt a pressure line where flow normally passes in both directions, or bypass excess oil to tank in a fail-safe way.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	230 l/min [60 US gpm]
Leakage	5 drops/min max @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.62 kg [1.37 lb]
Cavity	SDC20-2

■ DIMENSIONS


mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]


Installation torque

163-183 Nm [120-135 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop



A - Port 2 to 1 de-energized • B - Port 1 to 2 energized

■ MODEL CODE

SV13 - 20 - V - O - P - S - 6G - 12D - G - H		
Seal Option	Coil Series	
Code	Seal kit	
Omit - Buna - N	889615	
V-Viton	889619	
Manual Override Option	Connector Type	
Omit - No manual override	Omit - No coil	
P - Push type	G - ISO 4400 DIN 43650	
S - Screw type	Q - Spade terminals	
Housing Material	W - Flying lead	
Omit - No Housing	N - Deutsch (DC only)	
S - Steel	Y - Amp JR (DC only)	
Housing	D - Metripack 150 male (DC only)	
Code	J - Metripack 280 male (DC only)	
Ports	Coil Voltage	
0	Code	
No Housing	Coil Voltage	
6G	00	No Coil, nut included, (p/n 02-175698)
3/4" BSP	12D	12 VDC
8G	24D	24 VDC
1" BSP	115A	115 VAC**
12T	230A	230 VAC**
#12 SAE	12B	2VDC/w diode*
16T	24B	24 VDC/w diode*
#16 SAE		*Optional arc suppression diode
		**Internally rectified
		***Other voltage options available

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Solenoid Valves

SV08-22-01


Solenoid Valve, 2-way, Spool Type, Normally Open

230 bar [3300 psi] • 16 l/min [4.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, spool type, direct acting, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. They come standard with a push pin manual override. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	16 l/min [4.2 US gpm]
Coil Options	M13, R13
Weight	0.29 kg [0.64 lb]
Cavity	SDC08-2


*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES



Operating envelope



■ MODEL CODE

SV08 - 22 - 01 - 12D - DE - PB - B - 4S					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	
10D	R10D	10 VDC	4S	#4 SAE, AL	CP08-2-4S
12D	R12D	12 VDC	6S	#6 SAE, AL	CP08-2-6S
20D	R20D	20 VDC	S6S	#6 SAE, Steel	CP08-2-S6S
24D	R24D	24 VDC	DG2B	1/4 BSP, AL	SDC08-2-DG2B
110A		110 VAC**	DG3B	3/8 BSP, AL	SDC08-2-DG3B
220A		220 VAC**	S3B	3/8 BSP, Steel	CP08-2-S3B
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)			* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)			* Additional housings available		
**DIN only - external rectifier needed					
Connector Type			Seal Option		
Standard Coil Code	Robust Coil Code	Connector Type	Code	Seal kit	
00	00	No Coil	B-Buna - N	354003119	
AJ		Amp Junior	V-Viton	354003619	
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode			Manual Override Option		
Omit - Push Pin			Code	Option	
PB - Push Button			B	Push Pin	
SPS - Screw Type			P	Push Button	
			S	Screw Type	

Solenoid Valves

HSV08-22-01


Solenoid Valve, 2-way, Spool Type, Normally Open

350 bar [5000 psi] • 20 l/min [5.3 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, spool type, direct acting, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure* 350 bar [5000 psi]**
Flow Capability 20 l/min [5.3 US gpm]

Coil Options M13, R13
Weight 0.35 kg [0.77 lb]
Cavity SDC08-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 22 - 01 - 12D - DE - XC - P - S3B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
S3B	3/8 BSP, Steel	CP08-2-S3B
S4B	1/2 BSP, Steel	CP08-2-S4B
S6S	#6 SAE, Steel	CP08-2-S6S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
P-Polyurethane Single Seal	11167278

Solenoid Valves

SV10-22-01


Solenoid Valve, 2-way, Spool Type, Normally Open

230 bar [3300 psi] • 35 l/min [9 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, spool type, direct acting, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. They come standard with a push pin manual override. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ DIMENSIONS

mm [in]



■ PERFORMANCE DATA

Rated Pressure* 230 bar [3300 psi]**
Flow Capability 35 l/min [9 US gpm]



Coil Options M16, R16
Weight 0.43 kg [0.95 lb]

Cavity SDC10-2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 120,000 cycles. With inlet at port 2, this can be increased to 500,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 22 - 01 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
65	#6 SAE, AL	CP10-2-6S
85	#8 SAE, AL	CP10-2-8S
S8S	#8 SAE, Steel	CP10-2-S8S
DG3B	3/8 BSP, AL	SDC10-2-DG3B
DG4B	1/2 BSP, AL	SDC10-2-DG4B
S4B	1/2 BSP, Steel	CP10-2-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354004019
V-Viton	354003419

Solenoid Valves

SV14-10-O


Solenoid Valve, 2-way, Spool Type, Normally Open

350 bar [5000 psi] • 23 l/min [6 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, spool type, direct acting, normally open solenoid valve. When de-energized, flow can take place from port 1 to 2. In its energized condition, flow is blocked in both directions. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Flow Capability	23 l/min [6 US gpm]
Leakage	140 ml/min (8.5 in ³ /min) @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2


■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]


Installation torque
68-75 Nm [50-55 ft. lbs]



■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



Flow - USgpm (105 SUS oil @ 120°F)

Port 2 to port 1 or Port 1 to port 2 de-energized

■ MODEL CODE

SV14 - 10 - V - O - M - S - 2G - 12D - G - H	
Seal Option	Coil Series
Code	Seal kit
Omit-Buna - N	566806
V-Viton	889627
Manual Override Option	Connector Type
Omit - No manual override	Omit - No coil
M - Pull and Twist	G - ISO 4400 DIN 43650
Housing Material	Q - Spade terminals
Omit - No housing	W - Flying lead
S - Steel	N - Deutsch (DC only)
Housing	Y - Amp JR (DC only)
Code	D - Metripack 150 male (DC only)
Ports	J - Metripack 280 male (DC only)
0	No Housing
2G	1/4" BSP
3G	3/8" BSP
6T	#6 SAE
8T	#8 SAE
6H	#6 SAE
8H	#8 SAE
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].	
* Additional housings available	
Code	Coil Voltage
00	No Coil, nut included, (p/n 02-175698)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode**
*Optional arc suppression diode	
**Internally rectified	
***Other voltage options available	

Solenoid Valves

SV15-22-01


Solenoid Valve, 2-way, Spool Type, Normally Open

230 bar [3300 psi] • 60 l/min [16 US gpm]

■ OPERATION AND DESCRIPTION


This is a 2-way, 2-position, spool type, direct acting, normally open solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. The valve will be subject to normal spool leakage dependent on the pressure difference between the ports. These valves can be used to interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	60 l/min [16 US gpm]
Coil Options	M19
Weight	0.65 kg [1.65 lb]
Cavity	NCS 12/2

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 100,000 cycles. With inlet at port 2, this can be increased to 300,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 22 - 01 - 12D - DE - B - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800968)

**DIN only - external rectifier needed

Connector Type

Code	Connector
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports	Housing Model Code
00	No Housing	
85	#8 SAE, AL	NCS 12/2-DG-8S
12S	#12 SAE, AL	NCS 12/2-DG-12S
4B	1/2 BSP, Steel	NCS 12/2-DG-1/2
6B	3/4 BSP, Steel	NCS 12/2-DG-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

** Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115411
V-Viton	11115413

Solenoid Valves

S207


Solenoid Valve, 2-way, Poppet Type, Normally Open, Direct Acting, Double Blocking

350 bar [5000 psi] • 1 l/min [0.25 US gpm]


■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, direct acting, normally open, bi-directional solenoid valve for low flow applications. When energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. These valves can be used to hold loads in position, provide controlled lowering or as a pilot valve for larger valves such as ventable relief valves or logic elements.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	350 bar [5000 psi]
Rated flow	1 l/min [0.25 US gpm]
Leakage	0.3 drops/min [5 dpm] @ 210 bar [3000 psi]
Coil Options	C13
Weight	0.1 kg [0.2 lb]
Cavity	SDC08-2

*Max pressure at port 2 is 210 bar [3000 psi]

■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

S207 - V - 24 - H - 3W - 377			
Seal Option		Housing Material	
Code Seal kit		Omit - Aluminum / No housing	
V-Viton® SK1043V		377 - Steel	
Coil Voltage		Housing	
12 - 12 VDC		Code Ports Aluminium Steel	
24 - 24 VDC		0mit No Housing	
110 - 110 VAC*		2W 1/4" BSP A1485	
220 - 220 VAC*		3W 3/8" BSP A1043 A14175	
*External rectifier needed		6T 3/8" SAE A15676 A14843	
Connector Type		* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].	
H - DIN43650		* Additional housings available	
F - Flying lead			
DM - Deutsch moulded			

Solenoid Valves

SBV11-8-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated, Double Blocking

350 bar [5000 psi] • 60 l/min [16 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open, bi-directional solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	60 l/min [16 US gpm]
Leakage	5 drops/min @ 350 bar [5000 psi]
Coil Options	P series
Weight	0.12 kg [0.26 lb]
Cavity	SDC08-2

■ DIMENSIONS


mm [in]

Coil nut torque


5-8 Nm [4-6 ft. lbs]

Installation torque

34-41 Nm [25-30 ft. lbs]



■ PERFORMANCE CURVES



■ MODEL CODE

SBV11 - 8 - V - O - A - 2G - 12D - G - P

Seal Option

Code	Seal kit
Omit-Buna - N	02-160777
V-Viton	02-160778

Housing Material

Omit - No Housing
A - Aluminum
S - Steel

Housing

Code	Ports	Aluminium	Steel
0	No Housing		
2G	1/4" BSP	02-160727	02-160733
3G	3/8" BSP	02-160728	02-160734
4T	#4 SAE	02-160730	02-160736
6T	#6 SAE	02-160731	02-160737
8T	#8 SAE	02-160732	02-160738

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Coil Series

Omit - No coil
P - 8 series, 23W

Connector Type

Omit - No coil
G - ISO 4400 DIN 43650
Q - Spade terminals
W - Flying lead
N - Deutsch (DC only)
Y - Amp JR (DC only)
D - Metripack 150 male (DC only)
J - Metripack 280 male (DC only)

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included (p/n 565558)
12D	12 VDC
24D	24 VDC
115A	115 VAC**
230A	230 VAC**
12B	2VDC/w diode*
24B	24 VDC/w diode*

*Optional arc suppression diode

**Internally rectified

***Other voltage options available

Solenoid Valves

SBV11-10-O


Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated, Double Blocking

350 bar [5000 psi] • 76 l/min [20 USgpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open, bi-directional solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Rated flow	76 l/min [20 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.18 kg [0.39 lb]
Cavity	SDC10-2

■ MODEL CODE

SBV11 - 10 - V - O - A - 2G - 12D - G - H				
Seal Option				
Code	Seal kit			
Omit - Buna - N	565806			
V-Viton	889627			
Housing Material				
omit - No Housing				
A - Aluminum				
S - Steel				
Housing				
Code	Ports	Aluminum Standard Duty	Aluminum Heavy Duty	Steel
0	No Housing			
2G	1/4" BSP		876702	02-175102
3G	3/8" BSP		876703	02-175103
3B	3/8" BSP	02-175462		
6H	#6 SAE		876700	
6T	#6 SAE	566151		02-175100
8H	#8 SAE		876701	
8T	#8 SAE			02-175101
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].				
* Additional housings available				
Coil Series				
Omit - No coil				
H - 10 series, 29 W				
Connector Type				
Omit - No coil				
G - ISO 4400 DIN 43650				
Q - Spade terminals				
W - Flying lead				
N - Deutsch (DC only)				
Y - Amp JR (DC only)				
D - Metripack 150 male (DC only)				
J - Metripack 280 male (DC only)				
Coil Voltage				
Code	Coil Voltage			
00	No Coil, nut included, (p/n 02-175698)			
12D	12 VDC			
24D	24 VDC			
36D	36 VDC			
115A	115 VAC**			
230A	230 VAC**			
12B	24 VDC/w diode*			
24B	24 VDC/w diode*			
*Optional arc suppression diode				
**Internally rectified				
***Other voltage options available				

Solenoid Valves


SBV11-12-O

Solenoid Valve, 2-way, Poppet Type, Normally Open, Pilot Operated, Double Blocking
350 bar [5000 psi] • 114 l/min [30 US gpm]

■ OPERATION AND DESCRIPTION

This is a 2-way, 2-position, poppet type, pilot operated, normally open, bi-directional solenoid valve. When de-energized, flow can take place from port 2 to 1 and from 1 to 2. In its energized condition, flow is blocked in both directions. Leakage in either direction is kept to a minimum due to the poppet design. These valves can be used to hold loads in position or interrupt a pressure line where flow is expected to pass in both directions in the energized condition.

■ SCHEMATIC



■ PERFORMANCE DATA


Rated Pressure	350 bar [5000 psi]
Rated flow	114 l/min [30 US gpm]
Leakage	5 drops/ min @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.27 kg [0.59 lb]
Cavity	C-12-2 / C-12-2U

■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]



Installation torque


A - 81-95 Nm [60-70 ft. lbs]

S - 102-115 Nm [75-85 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop

Flow - L/min (21.8 cSt oil @ 49°C)



Flow - USgpm (105 SUS oil @ 120°F)

A - Port 1 to 2 • B - Port 2 to 1

■ MODEL CODE

SBV11 - 12 - V - O - A - 4G - U - 12D - G - H									
Seal Option					Coil Series				
Code Seal kit					Omit - No coil				
Omit-Buna - N 02-165889					H - 10 series, 29 W				
V-Viton 02-165888					Connector Type				
Housing Material					Omit - No coil				
Omit - No Housing					G - ISO 4400 DIN 43650				
A- Aluminum					Q - Spade terminals				
S- Steel					W - Flying lead				
Housing					N - Deutsch (DC only)				
Code Ports					Y - Amp JR (DC only)				
C-12-2 Aluminum Heavy Duty					D - Metripack 150 male (DC only)				
C-12-2U Aluminum Heavy Duty					J - Metripack 280 male (DC only)				
C-12-2 Steel Heavy Duty					Coil Voltage				
C-12-2U Steel Heavy Duty					Code	Coil Voltage			
0 No Housing					00	No Coil, nut included, (p/n 02-175698)			
4G 1/2" BSP 02-161118 02-161116 02-172062 02-172512					12D	12 VDC			
6G 3/4" BSP 02-161117 02-161115 02-169665 02-162922					24D	24 VDC			
10T #10 SAE 02-160640 02-160641 02-169744 02-169817					115A	115 VAC**			
12T #12 SAE 02-160644 02-160645 02-169782 02-169790					230A	230 VAC**			
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].									
* Additional housings available									
Cavity									
Omit - Cavity without undercut/No housing									
U - Cavity with undercut									
* Optional arc suppression diode									
** Internally rectified									
*** Other voltage options available									

Solenoid Valves

SVP08-DDB


Solenoid Valve, 3-way, 2-position, Poppet Type

230 bar [3300 psi] • 3 l/min [0.8 US gpm]


■ OPERATION AND DESCRIPTION

This is a 3-way, 2-position, poppet type, direct acting solenoid valve. When de-energized, the valve blocks flow from port 1 while allowing flow between port 2 and 3. When energized, the valve poppet blocks flow from port 3 while allowing flow between port 1 and 2. This valve is ideal for low leakage requirements to hold a load in position.


■ SCHEMATIC



Transition:



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]
Flow Capability	3 l/min [0.8 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M13, R13
Weight	0.35kg [0.77 lb]
Cavity	SDC08-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

SVP08 - DDB - 12D - DE - M - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	No Housing
4S	#4 SAE, AL	CP08-3-4S
6S	#6 SAE, AL	CP08-3-6S
S6S	#6 SAE, Steel	CP08-3-S6S
SE2B	1/4 BSP, AL	SDC08-3-SE2B
SE3B	3/8 BSP, AL	SDC08-3-SE3B
S3B	3/8 BSP, Steel	CP08-3-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

Seal Option

Code	Seal kit
B-Buna - N	354003210
V-Viton	354003819

Manual Override Option

Omit - No Override
M - Screw Type

Solenoid Valves

EVH 06/D5


Solenoid Valve, 3-way, 2-position, Poppet Type

230 bar [3300 psi] • 25 l/min [6.6 US gpm]


■ OPERATION AND DESCRIPTION

This is a 3-way, 2-position, poppet type, direct acting solenoid valve. When de-energized, the valve blocks flow from port 3 while allowing flow between port 1 and 2. When energized, the valve poppet blocks flow from port 1 while allowing flow between port 2 and 3. These valves come standard with a push pin manual override. This valve is ideal for low leakage requirements to hold a load in position.

■ SCHEMATIC




Transition:



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]
Flow Capability	25 l/min [6.6 US gpm]
Leakage	6 drops/min @ Rated Pressure
Coil Options	M16, R16
Weight	0.44 kg [0.97 lb]
Cavity	NCS06/3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

EVH 06/D5 - 12D - DE - PB - SE6S - B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Seal Option

Code	Seal kit
B-Buna - N	230000590
V-Viton	230000430

Housing

Code	Ports	Housing Model Code
00	No Housing	
SE6S	#6 SAE, AL	NCS06/3-SE-6S
SE8S	#8 SAE, AL	NCS06/3-SE-8S
SE3/8	3/8 BSP, AL	NCS06/3-SE-3/8
SE1/2	1/2 BSP, AL	NCS06/3-SE-1/2

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Manual Override Option

- Omit - Push Pin
- PB - Push Button
- SPS - Screw Type
- OPS - Protected Push Pin
- PAT - Push and Twist

Solenoid Valves

SV08-23-01


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 18 l/min [4.8 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. They come standard with a push pin manual override. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]



■ PERFORMANCE DATA

Rated Pressure* 230 bar [3300 psi]**

Flow Capability 18 l/min [4.8 US gpm]

Coil Options M13, R13

Weight 0.31 kg [0.68 lb]


Cavity SDC08-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES

Operating envelope



■ MODEL CODE

SV08 - 23 - 01 - 12D - DE - PB - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-3-4S
6S	#6 SAE, AL	CP08-3-6S
S6S	#6 SAE, Steel	CP08-3-S6S
SE2B	1/4 BSP, Steel	SDC08-3-SE2B
SE3B	3/8 BSP, Steel	SDC08-3-SE3B
S3B	3/8 BSP, Steel	CP08-3-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003210
V-Viton	354003819

Manual Override

Omit-Push Pin

PB-Push Button

SPS-Screw Type

Solenoid Valves

HSV08-23-01


Solenoid Valve, 3-way, 2-position, Spool Type

350 bar [5000 psi] • 15 l/min [4 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. They come standard with a push pin manual override. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	350 bar [5000 psi]
Flow Capability	15 l/min [4 US gpm]
Coil Options	M13, R13
Weight	0.35 kg [0.77 lb]
Cavity	SDC08-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 23 - 01 - 12D - DE - PN - P - S3B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
S3B	3/8 BSP, Steel	CP08-3-S3B
S4S	#4 SAE, Steel	CP08-3-S4S
S6S	#6 SAE, Steel	CP08-3-S6S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
P-Polyurethane Single Seal	11167282

Solenoid Valves

SV10-23-01


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 35 l/min [9 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. They come standard with a push pin manual override. Always check the operating envelope to make sure the valve will work under the required application conditions. An open spool transition option is available for this valve (check model code for details).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	35 l/min [9 US gpm]
Coil Options	M16, R16
Weight	0.42 kg [0.93 lb]
Cavity	SDC10-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES



Note: Performance curves apply to the "-01" spool transition option only. For "-C01" performance curves, contact technical support.

■ MODEL CODE

Spool Transition

01 - Zero overlap
C01 - Open

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

SV10 - 23 - 01 - 12D - DE - PB - B - 6S

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-3-6S
8S	#8 SAE, AL	CP10-3-8S
S8S	#8 SAE, Steel	CP10-3-S8S
DG3B	3/8 BSP, AL	SDC10-3-DG3B
DG4B	1/2 BSP, AL	SDC10-3-DG4B
S4B	1/2 BSP, Steel	CP10-3-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354004210
V-Viton	354003719

Manual Override

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type
- OPS-Protected Push Pin
- PAT-Push and Twist

Solenoid Valves

CP521-21


Solenoid Valve, 3-way, 2-position, Spool Type

240 bar [3500 psi] • 60 l/min [16 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. This valve has an open transition, which reduces pressure spikes when changing flow direction. They come standard with a push pin manual override. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	240 bar [3500 psi]
Flow Capability	60 l/min [16 US gpm]
Coil Options	D14E [30W]
Weight	0.80 kg [1.76 lb]
Cavity	CP12-3

*Rated Pressure based on NFPA fatigue test standards
(at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

CP521 - 21 - B - 10S - 24D - S

Seal Option

Code	Seal
B-Buna - N	120053
V-Viton	120052

Housing

Code	Ports
0	No Housing
4B	AL, 1/2 BSP CP12-3-4B
6B	AL, 3/4 BSP CP12-3-6B
10S	AL, #10 SAE CP12-3-10S
12S	AL, #12 SAE CP12-3-12S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Connector Type

0 - No connector
S - Spade
L - Lead wire
H - DIN43650
M2 - Metripak 150 Type 1
DE - Deutsch
AJ - Amp Junior
DED - Deutsch with diode

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
24D	24 VDC

*Coil nut and o-ring (p/n 321567)

Solenoid Valves

SV11M-12-3P


Solenoid Valve, 3-way, 2-position, Spool Type

350 bar [5000 psi] • 35 l/min [11 US gpm]

■ OPERATION AND DESCRIPTION

This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 1 is open to port 3 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ PERFORMANCE DATA


Rated Pressure	350 bar [5000 psi]
Flow Capability	35 l/min [9 US gpm]
Leakage	350 ml/min [21.5 in ³ /min] @ 210 bar [3000 psi]
Coil Options	R series
Weight	0.86 kg [1.9 lb]
Cavity	C-12-3

■ DIMENSIONS

mm [in]

Coil nut torque


2.5-3 Nm [1.8-2.2 ft. lbs]



Installation torque
81-95 Nm [60-70 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop



A - Port 3 to 1 energized • **B** - Port 1 to 2 de-energized

■ MODEL CODE

SV11M - 12 - V - 3P - A - 6G - 12D - N - R	
Seal Option	
Code	Seal kit
Omit-Buna - N	9900171-000
V-Viton	9900172-000
Housing	
Code	Ports
	Aluminium Steel
0	No Housing
6G	3/4" BSP 02-161816
12H	#12 SAE 02-160646
4G	1/2" BSP 02-169815
6G	3/4" BSP 02-169814
10T	#10 SAE 02-161070
12T	#12 SAE 02-169816
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].	
* Additional housings available	
Coil Series	
Omit	-No coil
R	-R series, 30W
Connector Type	
Omit	-No coil
N	-Deutsch male, DT04-2P, integrated
Coil Voltage	
Code	Coil Voltage
00	No Coil, nut included, (p/h 6036194-001)
12D	12 VDC
24D	24 VDC
12B	2VDC/w diode*
24B	24 VDC/w diode*
*Optional arc suppression diode.	

Solenoid Valves

SV07-23-02


Solenoid Valve, 3-way, 2-position, Spool Type

80 bar [1160 psi] • 8 l/min [2.11 US gpm]


OPERATION AND DESCRIPTION

This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

SCHEMATIC



DIMENSIONS




PERFORMANCE DATA


Rated Pressure*	80 bar [1160 psi]
Flow Capability	8 l/min [2.11 US gpm]
Coil Options	M13, R13
Weight	0.32 kg [0.72 lb]
Cavity	CP07-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

PERFORMANCE CURVES



Operating envelope



MODEL CODE

SV07 - 23 - 02 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP07-3-4S
6S	#6 SAE, AL	CP07-3-6S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Seal Option

Code	Seal kit
B-Buna - N	11361898
V-Viton	11361899

Solenoid Valves

SV08-23-02


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 18 l/min [4.7 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	18 l/min [4.7 US gpm]
Coil Options	M13, R13
Weight	0.31 kg [0.68 lb]
Cavity	SDC08-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 23 - 02 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-3-4S
6S	#6 SAE, AL	CP08-3-6S
S6S	#6 SAE, Steel	CP08-3-S6S
SE2B	1/4 BSP, AL	SDC08-3-SE2B
SE3B	3/8 BSP, AL	SDC08-3-SE3B
S3B	3/8 BSP, Steel	CP08-3-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003210
V-Viton	354003819

Solenoid Valves

HSV08-23-02


Solenoid Valve, 3-way, 2-position, Spool Type

350 bar [5000 psi] • 15 l/min [4 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	350 bar [5000 psi]
Flow Capability	15 l/min [4 US gpm]
Coil Options	M13, R13
Weight	0.35 kg [0.77 lb]
Cavity	SDC08-3

*Rated Pressure based on NFPA fatigue test standards
(at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 23 - 02 - 12D - DE - XC - P - S3B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
S3B	3/8 BSP, Steel	CP08-3-S3B
S4S	#4 SAE, Steel	CP08-3-S4S
S6S	#6 SAE, Steel	CP08-3-S6S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
P-Polyurethane Single Seal	11167282

Solenoid Valves

SV09-23-02


Solenoid Valve, 3-way, 2-position, Spool Type

100 bar [1450 psi] • 21 l/min [5.5 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions. This valve is ideal for low pressure on-off control of single acting cylinders, clutches, and brake applications.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	100 bar [1450 psi]
Flow Capability	21 l/min [5.5 US gpm]
Leakage	20 ml/min [1.22 in³/min] at Rated Pressure
Coil Options	M13, R13
Weight	0.35 kg [0.78 lb]
Cavity	SDC10-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

SV09 - 23 - 02 - 12D - DE - B - F - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP10-3-4S
6S	#6 SAE, AL	CP10-3-6S
SE2B	1/4 BSP, AL	SDC10-3-SE2B
SE3B	3/8 BSP, AL	SDC10-3-SE3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Filter Option

Omit - No Filter
F-Filter 500 µm

Seal Option

Code	Seal kit
B-Buna - N	354004210
V-Viton	354003719

Solenoid Valves

SV10-23-02


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 28 l/min [7.4 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 1 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	28 l/min [7.4 US gpm]
Coil Options	M16, R16
Weight	0.42 kg [0.93 lb]
Cavity	SDC10-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 500,000 cycles. With inlet at port 2, this can be increased to 300,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 23 - 02 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-3-6S
8S	#8 SAE, AL	CP10-3-8S
S8S	#8 SAE, Steel	CP10-3-S8S
SE3B	3/8 BSP, AL	SDC10-3-SE3B
SE4B	1/2 BSP, AL	SDC10-3-SE4B
S4B	1/2 BSP, Steel	CP10-3-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354004210
V-Viton	354003719

Solenoid Valves

SV11-10-3


Solenoid Valve, 3-way, 2-position, Spool Type

350 bar [5000 psi] • 23 l/min [6 US gpm]

■ OPERATION AND DESCRIPTION

This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 1 is open to port 3 and port 2 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS



mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque


68-75 Nm [50-55 ft. lbs]




■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Flow Capability	23 l/min [6 US gpm]
Leakage	164 ml/min (10 in³/min) at 350 bar [5000 psi]
Coil Options	H series
Weight	0.19 kg [0.42 lb]
Cavity	SDC10-3

■ PERFORMANCE CURVES



■ Operating Envelope



A - Port 3 to port 1

B - Port 1 to port 2

A - Normally open, normally closed

B - Selector 1 to 2

■ MODEL CODE

SV11-10 - V - 3 - M - S - 2G - 12D - G - H		
Seal Option		
Code	Seal kit	
Omit-Buna - N	889624	
V-Viton	889628	
Manual Override Option		
Omit	- No manual override	
M	- Pull and Twist	
Housing Material		
Omit	- No Housing	
S	- Steel	
Housing		
Code	Ports	Steel
0	No Housing	
2G	1/4" BSP	02-175127
3G	3/8" BSP	02-175128
6T	#6 SAE	02-175124
8T	#8 SAE	02-175125
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
* Additional housings available		
Coil Series		
Omit	- No coil	
H	- 10 series, 29 W	
Connector Type		
Omit	- No coil	
G	- ISO 4400 DIN 43650	
Q	- Spade terminals	
W	- Flying lead	
N	- Deutsch (DC only)	
Y	- Amp JR (DC only)	
D	- Metripack 150 male (DC only)	
J	- Metripack 280 male (DC only)	
Coil Voltage		
Code	Coil Voltage	
00	No Coil, nut included, (p/n 02-175698)	
12D	12 VDC	
24D	24 VDC	
115A	115 VAC**	
230A	230 VAC**	
12B	2VDC/w diode*	
24B	24 VDC/w diode*	
*Optional arc suppression diode		
**Internally rectified		
***Other voltage options available		

Solenoid Valves

SV08-23-03


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 18 l/min [4.7 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 2 and port 1 is blocked. These valves can be used in normally open, normally closed or selector modes. They come standard with a push pin manual override. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	18 l/min [4.7 US gpm]
Coil Options	M13, R13
Weight	0.31 kg [0.68 lb]
Cavity	SDC08-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 23 - 03 - 12D - DE - PB - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-3-4S
6S	#6 SAE, AL	CP08-3-6S
S6S	#6 SAE, Steel	CP08-3-S6S
SE2B	1/4 BSP, AL	SDC08-3-SE2B
SE3B	3/8 BSP, AL	SDC08-3-SE3B
S3B	3/8 BSP, Steel	CP08-3-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003210
V-Viton	354003819

Manual Override Option

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type

Solenoid Valves

SV10-23-03


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 28 l/min [7.4 US gpm]


■ OPERATION AND DESCRIPTION

This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 2 and port 1 is blocked. These valves can be used in normally open, normally closed or selector modes. They come standard with a push pin manual override. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]
Flow Capability	28 l/min [7.4 US gpm]
Coil Options	M16, R16
Weight	0.42 kg [0.93 lb]
Cavity	SDC10-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 23 - 03 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-3-6S
8S	#8 SAE, AL	CP10-3-8S
S8S	#8 SAE, Steel	CP10-3-S8S
SE3B	3/8 BSP, AL	SDC10-3-SE3B
SE4B	1/2 BSP, AL	SDC10-3-SE4B
S4B	1/2 BSP, Steel	CP10-3-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354004210
V-Viton	354003719

Solenoid Valves

SV4M-12-3P


Solenoid Valve, 3-way, 2-position, Spool Type

210 bar [3000 psi] • 42 l/min [11 US gpm]

■ OPERATION AND DESCRIPTION

This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 1 is open to port 2 and port 3 is blocked. When energized, port 3 is open to port 2 and port 1 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS


mm [in]

Coil nut torque

2.5-3 Nm [1.8-2.2 ft. lbs]

Installation torque

81-95 Nm [60-70 ft. lbs]




■ PERFORMANCE DATA

Rated Pressure	210 bar [3000 psi]
Flow Capability	42 l/min [11 US gpm]
Leakage	300 ml/min (21.5 in ³ /min) @ 210 bar [3000 psi]
Coil Options	R series
Weight	0.86 kg [1.9 lb]
Cavity	C-12-3

■ PERFORMANCE CURVES

Pressure Drop



A - Port 3 to 2 energized • B - Port 2 to 1 de-energized

■ MODEL CODE

SV4M - 12 - V - 3P - A - 0 - 12D - N - R									
Seal Option									
Code	Seal kit								
Omit-Buna - N	9900171-000								
V-Viton	9900172-000								
Housing Material									
Omit - No housing									
A - Aluminium									
Housing									
Code	Ports	Aluminum							
0	No Housing								
6G	3/4" BSP	02-161816							
12H	#12 SAE	02-160646							
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].									
* Additional housings available									
Coil Series									
Omit - No coil									
R - R series, 30W									
Connector Type									
Omit - No coil									
N - Deutsch (DC only)									
Coil Voltage									
Code	Coil Voltage								
00	No Coil, nut included, (p/n 6036194-001)								
12D	12 VDC								
24D	24 VDC								
12B	2VDC/w diode*								
24B	24 VDC/w diode*								
*Optional arc suppression diode.									

Solenoid Valves

SV08-23-04


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 12 l/min [3.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to port 2 and port 1 is blocked. When energized, port 2 is open to port 1 and port 3 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	12 l/min [3.2 US gpm]
Coil Options	M13, R13
Weight	0.31 kg [0.68 lb]
Cavity	SDC08-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 400,000 cycles. With inlet at port 2, this can be increased to 600,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 23 - 04 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A	110 VAC**	
220A	220 VAC**	

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	CP08-3-4S
4S	#4 SAE, AL	CP08-3-6S
6S	#6 SAE, AL	CP08-3-S6S
SE2B	1/4 BSP, AL	SDC08-3-SE2B
SE3B	3/8 BSP, AL	SDC08-3-SE3B
S3B	3/8 BSP, Steel	CP08-3-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003210
V-Viton	354003819

Solenoid Valves

SV10-23-04


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 20 l/min [5.3 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to port 2 and port 1 is blocked. When energized, port 2 is open to port 1 and port 3 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	20 l/min [5.3 US gpm]
Coil Options	M16, R16
Weight	0.42 kg [0.93 lb]
Cavity	SDC10-3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] on port 2 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 23 - 04 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	R00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-3-6S
8S	#8 SAE, AL	CP10-3-8S
S8S	#8 SAE, Steel	CP10-3-S8S
SE3B	3/8 BSP, AL	SDC10-3-SE3B
SE4B	1/2 BSP, AL	SDC10-3-SE4B
S4B	1/2 BSP, Steel	CP10-3-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354004210
V-Viton	354003719

Solenoid Valves

SV15-23-04


Solenoid Valve, 3-way, 2-position, Spool Type

230 bar [3300 psi] • 50 l/min [13.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 3-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to port 2 and port 1 is blocked. When energized, port 2 is open to port 1 and port 3 is blocked. These valves can be used in normally open, normally closed or selector modes. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	50 l/min [13.2 US gpm]
Coil Options	M19
Weight	0.89 kg [1.96 lb]
Cavity	NCS 12/3

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] for 100,000 cycles. With inlet at port 2, this can be increased to 300,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 23 - 04 - 12D - DE - B - 8S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800968)

**DIN only - external rectifier needed

Connector Type

Code	
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports	Housing Model Code
00	No Housing	
85	#8 SAE, AL	NCS 12/3-SE-8S
12S	#12 SAE, AL	NCS 12/3-DG-12S
4B	1/2 BSP, AL	NCS 12/3-DG-1/2
6B	3/4 BSP, AL	NCS 12/3-DG-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115764
V-Viton	11115765

Solenoid Valves

SV08-24-01


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 12 l/min [3.2 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized, condition port 3 is open to 2 and port 4 to 1. When energized port 3 is open to 4 and port 2 to 1. These valves are used to control the movement of cylinders or motors able to reverse the motion. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	12 l/min [3.2 US gpm]
Coil Options	M13, R13
Weight	0.32 kg [0.71 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 24 - 01 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-4-4S
6S	#6 SAE, AL	CP08-4-6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003919

Solenoid Valves

HSV08-24-01


Solenoid Valve, Spool Type, 4-Way, 2-Position

350 bar [5000 psi] • 20 l/min [5.3 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized, condition port 3 is open to 2 and port 4 to 1. When energized port 3 is open to 4 and port 2 to 1. These valves are used to control the movement of cylinders or motors able to reverse the motion. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	350 bar [5000 psi]
Flow Capability	20 l/min [5.3 US gpm]
Coil Options	M13, R13
Weight	0.35 kg [0.77 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 24 - 01 - 12D - DE - XC - P - S3B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
S3B	3/8 BSP, Steel	CP08-4-S3B
S6S	#6 SAE, Steel	CP08-4-S6S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
P-Polyurethane Single Seal	11167316

Solenoid Valves

SV10-24-01


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 35 l/min [9 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized, condition port 3 is open to 2 and port 4 to 1. When energized port 3 is open to 4 and port 2 to 1. These valves are used to control the movement of cylinders or motors able to reverse the motion. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as an inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	35 l/min [9 US gpm]
Coil Options	M16, R16
Weight	0.45 kg [0.99 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 24 - 01 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

*DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	R00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
65	#6 SAE, AL	CP10-4-6S
85	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Solenoid Valves

SV09-24-01


Solenoid Valve, 4-way, 2-position, Spool Type

100 bar [1450 psi] • 21 l/min [5.5 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to 2 and port 4 to 1. When energized, port 3 is open to 4 and port 2 to 1. These valves are used in low pressure, on/off control of dual clutch applications. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	100 bar [1450 psi]
Flow Capability	21 l/min [5.5 US gpm]
Leakage	75 ml/min [5.6 in³/min]
Coil Options	M13, R13
Weight	0.37 kg [0.78 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards
(at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

SV09 - 24 - 01 - 12D - DE - B - F - 4S					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports & Material	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	
10D	R10D	10 VDC	4S	#4 SAE, AL	CP08-3-4S
12D	R12D	12 VDC	6S	#6 SAE, AL	CP08-3-6S
20D	R20D	20 VDC	SE2B	1/4 BSP, AL	SDC08-3-SE2B
24D	R24D	24 VDC	SE3B	3/8 BSP, AL	SDC08-3-SE3B
110A		110 VAC**			
220A		220 VAC**			
*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)					
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)					
**DIN only - external rectifier needed					
Connector Type			Filter Option		
Standard Coil Code	Robust Coil Code	Connector Type	Omit	Omit	
00	00	No Coil	F	500 µm	
AJ		Amp Junior			
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode					
Seal Option					
Code	Seal kit				
B-Buna - N	354001919				
V-Viton	354002019				

Solenoid Valves

SV11-10-4


Solenoid Valve, 4-way, 2-position, Spool Type

350 bar [5000 psi] • 23 l/min [6 USgpm]

■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized, condition port 3 is open to 2 and port 4 to 1. When energized port 3 is open to 4 and port 2 to 1. These valves are used to control the movement of cylinders or motors able to reverse the motion. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]


Coil nut torque

5-8 Nm [4-6 ft. lbs]

Installation torque

68-75 Nm [50-55 ft. lbs]

29,6 (1.16)




■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Flow Capability	23 l/min [6 USgpm]
Leakage	82 ml/min (5 in³/min) @ 350 bar [5000 psi]
Coil Options	H series
Weight	0.21 kg [0.46 lb]
Cavity	SDC10-4

■ PERFORMANCE CURVES

Pressure Drop



A - Port 3 to 2 • B - Port 2 to 1

■ MODEL CODE

SV11 - 10 - V - 4 - M - S - 2G - 12D - G - H		
Seal Option		
Code	Seal kit	
Omit - Buna - N	889625	
V-Viton	566080	
Manual Override Option		
Omit - No manual override		
M - Pull and Twist		
Housing Material		
Omit - No Housing		
S - Steel		
Housing		
Code	Ports	Steel
00	No Housing	
2G	1/4" BSP	02-175139
3G	3/8" BSP	02-175140
6T	#6 SAE	02-175137
8T	#8 SAE	02-175138
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
* Additional housings available		
Coil Series		
Omit - No coil		
H - 10 series, 29 W		
Connector Type		
Coil Voltage		
Code	Coil Voltage	
00	No Coil, nut included, (p/n 02-175698)	
12D	12 VDC	
24D	24 VDC	
115A	115 VAC**	
230A	230 VAC**	
12B	2VDC/w diode*	
24B	24 VDC/w diode*	
*Optional arc suppression diode		
**Internally rectified		
***Other voltage options available		

Solenoid Valves

SV15-24-01


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 60 l/min [16 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized, condition port 3 is open to 2 and port 4 to 1. When energized port 3 is open to 4 and port 2 to 1. These valves are used to control the movement of cylinders or motors able to reverse the motion. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	60 l/min [16 US gpm]
Coil Option	M19
Weight	0.95 kg [2.09 lb]
Cavity	NCS 12/4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate at 315 bar [4600 psi] with an inlet at port 3 for 300,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 24 - 01 - 12D - DE - B - F - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil – Plastic coil nut and o-rings (p/n 173800978)
**DIN only – external rectifier needed

Connector Type

Code	Connector Type
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

** Additional housings available

Filter Option

Omit - Omit
F - 300 µm

Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885

Solenoid Valves

SV08-24-02


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 12 l/min [3.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are blocked. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to isolate a function until required. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	12 l/min [3.2 US gpm]
Coil Option	M13, R13
Weight	0.31 kg [0.68 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] on port 3 for 500,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 24 - 02 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	CP08-4-4S
4S	#4 SAE, AL	CP08-4-4S
6S	#6 SAE, AL	CP08-4-6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003919

Solenoid Valves

SV12-8-4


Solenoid Valve, 4-way, 2-position, Spool Type

350 bar [5000 psi] • 11 l/min [2.9 US gpm]

■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are blocked. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to isolate a function until required. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ PERFORMANCE DATA



Rated Pressure	350 bar [5000 psi]
Flow Capability	11 l/min [2.9 US gpm]
Leakage	82 ml/min (5 in ³ /min) @ 350 bar [5000 psi]
Coil Options	P series
Weight	0.14 kg [0.30 lb]
Cavity	SDC08-4

■ DIMENSIONS


mm [in]

Coil nut torque


5-8 Nm [4-6 ft. lbs]



■ PERFORMANCE CURVES



A - Port 3 to 4 • B - Port 2 to 1



A - Port 2 to port 1 • B - Port 3 to port 4

■ MODEL CODE

SV12 - 8 - V - 4 - M - S - 2G - 12D - G - P		
Seal Option		
Code	Seal kit	
Omit-Buna - N	02-160757	
V-Viton	02-160758	
Manual Override Option		
Omit - No manual override		
M - Pull and Twist		
Housing Material		
Omit - No Housing		
S - Steel		
Housing		
Code	Ports	Steel
00	No Housing	
2G	1/4" BSP	02-160751
3G	3/8" BSP	02-160752
4T	#4 SAE	02-160753
6T	#6 SAE	02-160754
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
* Additional housings available		
Coil Series		
Omit - No coil		
G - ISO 4400 DIN 43650		
Q - Spade terminals		
W - Flying lead		
N - Deutsch male, DT04-2P, integrated		
Y - Amp JR (DC only)		
D - Metripack 150 male DC only		
J - Metripack 280 male (DC only)		
Connector Type		
Omit - No coil		
G - ISO 4400 DIN 43650		
Q - Spade terminals		
W - Flying lead		
N - Deutsch male, DT04-2P, integrated		
Y - Amp JR (DC only)		
D - Metripack 150 male DC only		
J - Metripack 280 male (DC only)		
Coil Voltage		
Code	Coil Voltage	
00	No Coil, nut included (p/n 565558)	
12D	12 VDC	
24D	24 VDC	
115A	115 VAC**	
230A	230 VAC**	
12B	12 VDC/w diode*	
24B	24 VDC/w diode*	
*Optional arc suppression diode		
**Internally rectified		
***Other voltage options available		

Solenoid Valves

SV10-24-02


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 25 l/min [6.6 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are blocked. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to isolate a function until required. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	25 l/min [6.6 US gpm]
Coil Option	M16, R16
Weight	0.45 kg [1 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 24 - 02 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Solenoid Valves

SV12-10-4


Solenoid Valve, 4-way, 2-position, Spool Type

350 bar [5000 psi] • 23 l/min [6 USgpm]

■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are blocked. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to isolate a function until required. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC




■ DIMENSIONS

mm [in]

Coil nut torque

5-8 Nm [4-6 ft. lbs]



Installation torque


81-95 Nm [60-70 ft. lbs]

■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]
Flow Capability	23 l/min [6 USgpm]
Leakage	140 ml/min [8.5 in³] at 350 bar [5000 psi]
Coil Options	H series
Weight	0.44 kg [1 lb]
Cavity	SDC10-4

■ PERFORMANCE CURVES

Pressure Drop



■ MODEL CODE

SV12 - 10 - V - 4 - M - S - 2G - 12D - G - H		
Seal Option		
Code	Seal kit	
Omit - Buna - N	889625	
V - Viton	566080	
Manual Override Option		
Omit - No manual override		
M - Pull and Twist		
Housing Material		
Omit - No Housing		
S - Steel		
Housing		
Code	Ports	Steel
0	No Housing	
2G	1/4" BSP	02-175102
3G	3/8" BSP	02-175103
6T	#6 SAE	02-175100
8T	#8 SAE	02-175101
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
* Additional housings available		
Coil Series		
Omit - No coil		
H - 10 series, 29 W		
Connector Type		
Omit - No coil		
G - ISO 4400 DIN 43650		
W - Flying lead		
N - Deutsch (DC only)		
Y - Amp JR (DC only)		
D - Metripack 150 male DC only)		
J - Metripack 280 male (DC only)		
E - Weather Pack (Packard) female on wire leads		
F - Weather Pack (Packard) female on wire leads		
Coil Voltage		
Code	Coil Voltage	
00	No Coil, nut included, (p/n 02-175698)	
12D	12 VDC	
24D	24 VDC	
115A	115 VAC**	
230A	230 VAC**	
12B	2VDC/w diode*	
24B	24 VDC/w diode*	
*Optional arc suppression diode		
**Internally rectified		
***Other voltage options available		

Solenoid Valves

SV15-24-03


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 50 l/min [13.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are open. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to isolate a function until required. The open center will allow all pressure in all ports to decay when de-energized. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	50 l/min [13.2 US gpm]
Coil Option	M19
Weight	0.95 kg [2.09 lb]
Cavity	NCS 12/4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 24 - 03 - 12D - DE - B - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800968)

**DIN only - external rectifier needed

Connector Type

Code	Connector Type
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885

Solenoid Valves

SV08-24-04


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 8 l/min [2 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to port 1 and ports 2 and 4 are blocked. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to control a unidirectional function when required. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	8 l/min [2 US gpm]
Coil Options	M13, R13
Weight	0.31 kg [0.68 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 24 - 04 - 12D - DE - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-4-4S
6S	#6 SAE, AL	CP08-4-6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003419

Solenoid Valves

SV15-24-04


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 50 l/min [13.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to port 1 and ports 2 and 4 are blocked. When energized, port 3 is open to 4 and port 2 to 1. These valves can be used to control a unidirectional function when required. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	50 l/min [13.2 US gpm]
Coil Options	M19
Weight	0.95 kg [2.09 lb]
Cavity	NCS 12/4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 24 - 04 - 12D - DE - BV - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800968)

**DIN only - external rectifier needed

Connector Type

Code	Connector Type
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

** Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885

Solenoid Valves

SV10-24-05


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 30 l/min [8 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. When de-energized, port 3 is open to 4 and port 2 to 1. In the energized condition, all ports are blocked. These valves can be used to isolate a function when required. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	30 l/min [8 US gpm]
Coil Options	M16, R16
Weight	0.45 kg [0.99 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 24 - 05 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	CP10-4-6S
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Solenoid Valves

SV10-24-06


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 30 l/min [8 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are blocked. When energized, port 3 and 4 are open to 1 and port 3 is blocked. These valves can be used to switch a motor into a free-wheeling mode or a cylinder into a float condition. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	30 l/min [8 US gpm]
Coil Options	M16, R16
Weight	0.45 kg [1.0 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles.

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 24 - 06 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Solenoid Valves

SV10-24-07


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 30 l/min [8 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are blocked. When energized, port 3 is open to 2 and port 4 to 1. These valves can be used to isolate a function until required. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]



■ PERFORMANCE DATA

Rated Pressure* 230 bar [3300 psi]**

Flow Capability 30 l/min [8 US gpm]

Coil Options M16, R16

Weight 0.45 kg [0.99 lb]


Cavity SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)


**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles.

■ PERFORMANCE CURVES

Pressure Drop



Operating envelope



— Rated per NFPA T 2.6.1 at 1 million cycles
- - - - Rated per NFPA T 2.6.1 at reduced operational life

■ MODEL CODE

SV10 - 24 - 07 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Solenoid Valves

SV08-24-08


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 18 l/min [4.7 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, ports 2 and 4 are open to port 1 with port 3 closed. When energized, port 1 is open to 2 and port 3 to 4. In the de-energized condition, these valves can allow a motor into a free-wheel mode or a cylinder to float condition. Energizing the valve will provide unidirectional flow. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	18 l/min [4.7 US gpm]
Coil Options	M13, R13
Weight	0.45 kg [0.99 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 24 - 08 - 12D - DE - B - 4S

Coil Voltage

Standard Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800588)

*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-4-4S
6S	#6 SAE, AL	CP08-4-6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003919

Solenoid Valves

SV10-24-12


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 25 l/min [6.6 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, port 3 is open to 1 while ports 2 and 4 are blocked. When energized, port 1 is open to 4 and port 2 open to 3. This valve allows the inlet oil to pass through the valve to tank or a separate system while holding the actuator in position. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	25 l/min [6.6 US gpm]
Coil Options	M16, R16
Weight	0.31 kg [0.68 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 24 - 12 - 12D - DE - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)

*Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Solenoid Valves

SV10-24-13


Solenoid Valve, 4-way, 2-position, Spool Type

230 bar [3300 psi] • 33 l/min [8.7 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. In the de-energized condition, all ports are open. When energized, port 1 is open to 4 and port 2 open to 3. This valve allows pressure to decay in all ports in its de-energized condition and provides unidirectional flow when energized. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	33 l/min [8.7 US gpm]
Coil Options	M16, R16
Weight	0.45 kg [0.99 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 24 - 13 - 12D - DE - B - 6S					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	
10D	R10D	10 VDC	6S	#6 SAE, AL	CP10-4-6S
12D	R12D	12 VDC	8S	#8 SAE, AL	CP10-4-8S
20D	R20D	20 VDC	S8S	#8 SAE, Steel	CP10-4-S8S
24D	R24D	24 VDC	L3B	3/8 BSP, AL	SDC10-4-L3B
110A		110 VAC**	L4B	1/2 BSP, AL	SDC10-4-L4B
220A		220 VAC**	S4B	1/2 BSP, Steel	CP10-4-S4B
*Standard Coil - Plastic coil nut and o-rings (p/n 17400021)					
*Robust Coil - Steel coil nut and no o-rings (p/n 173804910)					
**DIN only - external rectifier needed					
Connector Type			Seal Option		
Standard Coil Code	Robust Coil Code	Connector Type	Code	Seal kit	
00	00	No Coil	B-Buna - N	354001919	
AJ		Amp Junior	V-Viton	354002019	
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			

*Bi-directional diode

Solenoid Valves

SV7M-12-4P


Solenoid Valve, 4-way, 2-position, Spool Type

210 bar [3000 psi] • 45 l/min [12 USgpm]

■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. When de-energized, port 3 is open to 4 and port 2 to 1. In the energized condition, port 3 is open to 2 and port 4 to 1. These valves can be used to isolate a function when required. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ PERFORMANCE DATA


Rated Pressure	210 bar [3000 psi]
Flow Capability	45 l/min [12 USgpm]
Coil Options	R series
Weight	0.86 kg [1.9 lb]
Cavity	C-12-4

■ DIMENSIONS

mm [in]


Coil nut torque

2.5-3 Nm [1.8-2.2 ft. lbs]



Installation torque
34-41 Nm [25-30 ft. lbs]

■ PERFORMANCE CURVES



A - Port 2 to 1, port 3 to 4 • B - Port 3 to 2, port 4 to 1

■ MODEL CODE

SV7M - 12 - V - 4P - A - 6G - 12D - N - R			
Seal Option			
Code	Seal kit		
Omit - Buna - N	02-160980		
V-Viton	02-160979		
Housing Material			
Omit - No housing			
A - Aluminum			
S - Steel			
Housing			
Code	Ports	Aluminum	Steel
0	No Housing		
6G	3/4" BSP	5986432-001	5991073-001
10T	#10 SAE	5986434-001	
12T	#12 SAE	5986436-001	
10H	#10 SAE		5991074-001
12H	#12 SAE		5991075-001
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].			
* Additional housings available			
Connector Type			
Omit	No coil		
N	Deutsch male, DT04-2P, integrated		
Coil Voltage			
Code	Coil Voltage		
00	No Coil, nut included, (p/n 6036194-001)		
12D	12 VDC		
24D	24 VDC		
12B	2VDC/w diode*		
24B	24 VDC/w diode*		
*Optional arc suppression diode			
**Internally rectified			

Solenoid Valves

SV17M-12-4P


Solenoid Valve, 4-way, 2-position, Spool Type

350 bar [5000 psi] • 45 l/min [12 US gpm]

■ OPERATION AND DESCRIPTION

This is a 4-way, 2-position, spool type, direct acting solenoid valve. When de-energized, port 3 is open to 4 and port 2 to 1. In the energized condition, port 3 is open to 2 and port 4 to 1. These valves can be used to isolate a function when required. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ PERFORMANCE DATA

Rated Pressure	350 bar [5000 psi]*
Flow Capability	45 l/min [12 US gpm]
Coil Options	R series
Weight	0.86 kg [1.9 lb]
Cavity	C-12-4


*Max pressure at port 1 is 210 bar [3000 psi]

■ DIMENSIONS

mm [in]

Coil Nut Torque


2.5-3 Nm [1.8-2.2 ft. lbs]



Installation torque
81-95 Nm [60-70 ft. lbs]

■ PERFORMANCE CURVES

Pressure Drop



A - Port 2 to 1, port 3 to 4 • B - Port 3 to 2, port 4 to 1

■ MODEL CODE

SV17M - 12 - V - 4P - A - 6G - 12D - N - R			
Seal Option			
Code	Seal kit		
Omit - Buna - N	02-160980		
M-Viton	02-160979		
Housing Material			
Omit - No housing			
A - Aluminum			
S - Steel			
Housing			
Code	Ports	Aluminum	Steel
0	No Housing		
6G	3/4" BSP	5986432-001	5991073-001
10T	#10 SAE	5986434-001	
12T	#12 SAE	5986436-001	
10H	#10 SAE		5991074-001
12H	#12 SAE		5991075-001
* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].			
* Additional housings available			
Coil Series			
Omit	No coil		
R	R - R series, 30W		
Connector Type			
Omit	No coil		
N	Deutsch male, DT04-2P, integrated		
Coil Voltage			
Code	Coil Voltage		
00	No Coil, nut included, (p/n 6036194-001)		
12D	12 VDC		
24D	24 VDC		
12B	2VDC/w diode*		
24B	24 VDC/w diode*		
*Optional arc suppression diode			
**Internally rectified			

Solenoid Valves

SV08-34-02


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 16 l/min [4.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state (all ports blocked). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	16 l/min [4.2 US gpm]
Coil Options	M13, R13
Weight	0.55 kg [1.21 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 34 - 02 - 12D - DE - PB - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400011)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-4-4S
6S	#6 SAE, AL	CP08-4-6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

** Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003919

Manual Override Option

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type
- PAP-Push and Pull

Solenoid Valves

HSV08-34-02


Solenoid Valve, 4-way, 3-position, Spool Type

350 bar [5000 psi] • 17 l/min [4.5 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way 3-position direct acting solenoid operated spool valve. In the center condition, all ports are blocked. By energizing one solenoid, port 3 opens to 2 and port 4 to 1. When energizing the other solenoid port opens port 3 to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state (all ports blocked). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	350 bar [5000 psi]
Flow Capability	17 l/min [4.5 US gpm]
Coil Options	M13, R13
Weight	0.55kg [1.21 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 34 - 02 - 12D - DE - PN - P - S3B					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports	Housing Model Code
00	R00	No Coil, nut included*	00	1	No Housing
10D	R10D	10 VDC	S3B	2/8 BSP, Steel	CP08-4-S3B
12D	R12D	12 VDC	S6S	#6 SAE, Steel	CP08-4-S6S
20D	R20D	20 VDC			
24D	R24D	24 VDC			
110A		110 VAC**			
220A		220 VAC**			
*Standard Coil - Plastic coil nut and o-rings (p/n 17400011)			**Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)			* Additional housings available		
**DIN only - external rectifier needed					
Connector Type			Seal Option		
Standard Coil Code	Robust Coil Code	Connector Type	Code	Seal kit	
00	00	No Coil	P-Polyurethane Single Seal	11167316	
AJ		Amp Junior			
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			

*Bi-directional diode

Solenoid Valves

SV10-34-02


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 25 l/min [6.6 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state (all ports blocked). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	25 l/min [6.6 US gpm]
Coil Options	M16, R16
Weight	0.81 kg [1.79 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 34 - 02 - 12D - DE - PB - B - 6S					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	CP10-4-6S
10D	R10D	10 VDC	6S	#6 SAE, AL	CP10-4-6S
12D	R12D	12 VDC	8S	#8 SAE, AL	CP10-4-8S
20D	R20D	20 VDC	S8S	#8 SAE, Steel	CP10-4-S8S
24D	R24D	24 VDC	L3B	3/8 BSP, AL	SDC10-4-L3B
110A		110 VAC**	L4B	1/2 BSP, AL	SDC10-4-L4B
220A		220 VAC**	S4B	1/2 BSP, Steel	CP10-4-S4B
*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)			* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].		
**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)			* Additional housings available		
**DIN only - external rectifier needed					
Connector Type			Seal Option		
Standard Coil Code	Robust Coil Code	Connector Type	Code	Seal kit	
00	00	No Coil	B	B-Buna - N	354001919
AJ		Amp Junior	V	V-Viton	354002019
AJD		Amp Junior with Diode			
AS	AS	AMP SuperSeal 1.5			
ASD	ASDB*	AMP SuperSeal with Diode			
DE	DE	Deutsch			
DED	DEDDB*	Deutsch with Diode			
FL	FL	Flying Leads			
FLD	FLDB*	Flying Leads with Diode			
DN		DIN 43650			
*Bi-directional diode			Manual Override Option		
Omit-Push Pin			0		
PB-Push Button			P		
SPS-Screw Type			S		
OPS-Protected Push Pin			OP		
PAT-Push and Twist			PT		
PAP-Push and Pull			PA		

Solenoid Valves

SV15-34-02


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 60 l/min [16 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state (all ports blocked). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	60 l/min [16 US gpm]
Coil Options	M19
Weight	1400 kg [3.09 lb]
Cavity	NCS 12/4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 34 - 02 - 12D - DE - B - F - 8S							
Coil Voltage				Housing			
Standard Coil Code	Robust Coil Code	Coil Voltage		Code	Ports & Material	Housing Model Code	
00	R00	No Coil, nut included*		00	No Housing		
10D	R10D	10 VDC		8S	#8 SAE, AL	NCS12/4-L-8S	
12D	R12D	12 VDC		12S	#12 SAE, AL	NCS12/4-L-12S	
20D	R20D	20 VDC		4B	1/2 BSP, AL	NCS12/4-L-1/2	
24D	R24D	24 VDC		6B	3/4 BSP, AL	NCS12/4-L-3/4	
110A		110 VAC**					
220A		220 VAC**					
*Standard Coil - Plastic coil nut and o-rings (p/n 173800978)							
**DIN only - external rectifier needed							
Connector Type				Filter Option			
Code	No Coil			0mit	- No filter		
00				F	F - Filter 300 µm		
AJ	Amp Junior						
AJD	Amp Junior with Diode						
DE	Deutsch						
DED	Deutsch with Diode						
FL	Flying Leads						
DN	DIN 43650						
Seal Option							
Code	Seal kit						
B-Buna - N	11115884						
V-Viton	11115885						

Solenoid Valves

SV08-34-03


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 8 l/min [2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are open. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state (all ports open). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. valve. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	8 l/min [2 US gpm]
Coil Options	M13, R13
Weight	0.55 kg [1.21 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 34 - 03 - 12D - DE - PB - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400011)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
4S	#4 SAE, AL	CP08-4-4S
6S	#6 SAE, AL	CP08-4-6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003919

Manual Override Option

Omit-Push Pin

PB-Push Button

SPS-Screw Type

Solenoid Valves

SV15-34-03


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 50 l/min [13.2 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are open. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens port 3 to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state (all ports open). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only)

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	50 l/min [13.2 US gpm]
Coil Options	M19
Weight	1.40 kg [3.09 lb]
Cavity	NCS 12/4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 34 - 03 - 12D - DE - B - 4B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800978)

**DIN only - external rectifier needed

Connector Type

Code
00
AJ
AJD
DE
DED
FL
DN

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885

Solenoid Valves

SV10-34-03


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 24 l/min [6.3 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are open. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state (all ports open). It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	24 l/min [6.3 US gpm]
Coil Options	M16, R16
Weight	0.81 kg [1.79 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 34 - 03 - 12D - DE - PB - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar (3000 psi).

** Additional housings available

Seal Option

Code	Seal kit
B	B-Buna - N
V	V-Viton

Manual Override Option

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type
- OPS-Protected Push Pin

Solenoid Valves

SV08-34-04


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 8 l/min [2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2 and 4 are closed while port 3 is connected to port 1. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state allowing the inlet flow to pass to tank or to another function while the work ports are blocked. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	8 l/min [2 US gpm]
Coil Options	M13, R13
Weight	0.55 kg [1.21 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 34 - 04 - 12D - DE - PB - B - 4S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400011)

**Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	CP08-4-4S
4S	#4 SAE, AL	CP08-4-6S
6S	#6 SAE, AL	CP08-4-S6S
S6S	#6 SAE, Steel	CP08-4-S6S
L2B	1/4 BSP, AL	SDC08-4-L2B
S3B	3/8 BSP, Steel	CP08-4-S3B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354003319
V-Viton	354003919

Manual Override Option

Omit-Push Pin

PB-Push Button

SPS-Screw Type

Solenoid Valves

SV15-34-04


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 50 l/min [13.2 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2 and 4 are closed while port 3 is connected to port 1. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state allowing the inlet flow to pass to tank or to another function while the work ports are blocked. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	50 l/min [13.2 US gpm]
Coil Options	M19
Weight	1.4 kg [3.09 lb]
Cavity	NCS 12/4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV15 - 34 - 04 - 12D - DE - B - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800978)

**DIN only - external rectifier needed

Connector Type

Code	Connector Type
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885

Solenoid Valves

SV10-34-04


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 24 l/min [6.3 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2 and 4 are closed while port 3 is connected to port 1. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state allowing the inlet flow to pass to tank or to another function while the work ports are blocked. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only)

■ SCHEMATIC



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	24 l/min [6.3 US gpm]
Coil Options	M16, R16
Weight	0.81 kg [1.79 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 34 - 04 - 12D - DE - PB - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Manual Override Options

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type
- OPS-Protected Push Pin

Solenoid Valves

SV08-34-05


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 12 l/min [3.2 US gpm]


■ OPERATION AND DESCRIPTION

This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2, 4 and 1 are open while port 3 is blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state allowing the work ports to be referenced to tank, removing locked in pressure with the inlet port 3 closed. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	12 l/min [3.2 US gpm]
Coil Options	M13, R13
Weight	0.55 kg [1.21 lb]
Cavity	SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 500,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV08 - 34 - 05 - 12D - DE - PB - B - 4S																																							
Coil Voltage																																							
<table border="1"> <thead> <tr> <th>Standard Coil Code</th> <th>Robust Coil Code</th> <th>Coil Voltage</th> </tr> </thead> <tbody> <tr> <td>00</td> <td>R00</td> <td>No Coil, nut included*</td> </tr> <tr> <td>10D</td> <td>R10D</td> <td>10 VDC</td> </tr> <tr> <td>12D</td> <td>R12D</td> <td>12 VDC</td> </tr> <tr> <td>20D</td> <td>R20D</td> <td>20 VDC</td> </tr> <tr> <td>24D</td> <td>R24D</td> <td>24 VDC</td> </tr> <tr> <td>110A</td> <td></td> <td>110 VAC**</td> </tr> <tr> <td>220A</td> <td></td> <td>220 VAC**</td> </tr> </tbody> </table>							Standard Coil Code	Robust Coil Code	Coil Voltage	00	R00	No Coil, nut included*	10D	R10D	10 VDC	12D	R12D	12 VDC	20D	R20D	20 VDC	24D	R24D	24 VDC	110A		110 VAC**	220A		220 VAC**									
Standard Coil Code	Robust Coil Code	Coil Voltage																																					
00	R00	No Coil, nut included*																																					
10D	R10D	10 VDC																																					
12D	R12D	12 VDC																																					
20D	R20D	20 VDC																																					
24D	R24D	24 VDC																																					
110A		110 VAC**																																					
220A		220 VAC**																																					
<small>*Standard Coil - Plastic coil nut and o-rings (p/n 17400011) **Robust Coil - Steel coil nut and no o-rings (p/n 173800539) **DIN only - external rectifier needed</small>																																							
Connector Type																																							
<table border="1"> <thead> <tr> <th>Standard Coil Code</th> <th>Robust Coil Code</th> <th>Connector Type</th> </tr> </thead> <tbody> <tr> <td>00</td> <td>00</td> <td>No Coil</td> </tr> <tr> <td>AJ</td> <td></td> <td>Amp Junior</td> </tr> <tr> <td>AJD</td> <td></td> <td>Amp Junior with Diode</td> </tr> <tr> <td>AS</td> <td>AS</td> <td>AMP SuperSeal 1.5</td> </tr> <tr> <td>ASD</td> <td>ASDB*</td> <td>AMP SuperSeal with Diode</td> </tr> <tr> <td>DE</td> <td>DE</td> <td>Deutsch</td> </tr> <tr> <td>DED</td> <td>DED*</td> <td>Deutsch with Diode</td> </tr> <tr> <td>FL</td> <td>FL</td> <td>Flying Leads</td> </tr> <tr> <td>FLD</td> <td>FLDB*</td> <td>Flying Leads with Diode</td> </tr> <tr> <td>DN</td> <td></td> <td>DIN 43650</td> </tr> </tbody> </table>						Standard Coil Code	Robust Coil Code	Connector Type	00	00	No Coil	AJ		Amp Junior	AJD		Amp Junior with Diode	AS	AS	AMP SuperSeal 1.5	ASD	ASDB*	AMP SuperSeal with Diode	DE	DE	Deutsch	DED	DED*	Deutsch with Diode	FL	FL	Flying Leads	FLD	FLDB*	Flying Leads with Diode	DN		DIN 43650	
Standard Coil Code	Robust Coil Code	Connector Type																																					
00	00	No Coil																																					
AJ		Amp Junior																																					
AJD		Amp Junior with Diode																																					
AS	AS	AMP SuperSeal 1.5																																					
ASD	ASDB*	AMP SuperSeal with Diode																																					
DE	DE	Deutsch																																					
DED	DED*	Deutsch with Diode																																					
FL	FL	Flying Leads																																					
FLD	FLDB*	Flying Leads with Diode																																					
DN		DIN 43650																																					
<small>*Bi-directional diode</small>																																							
Housing																																							
<table border="1"> <thead> <tr> <th>Code</th> <th>Ports & Material</th> <th>Housing Model Code</th> </tr> </thead> <tbody> <tr> <td>00</td> <td>No Housing</td> <td></td> </tr> <tr> <td>4S</td> <td>#4 SAE, AL</td> <td>CP08-4-4S</td> </tr> <tr> <td>6S</td> <td>#6 SAE, AL</td> <td>CP08-4-6S</td> </tr> <tr> <td>S6S</td> <td>#6 SAE, Steel</td> <td>CP08-4-S6S</td> </tr> <tr> <td>L2B</td> <td>1/4 BSP, AL</td> <td>SDC08-4-L2B</td> </tr> <tr> <td>S3B</td> <td>3/8 BSP, Steel</td> <td>CP08-4-S3B</td> </tr> </tbody> </table>						Code	Ports & Material	Housing Model Code	00	No Housing		4S	#4 SAE, AL	CP08-4-4S	6S	#6 SAE, AL	CP08-4-6S	S6S	#6 SAE, Steel	CP08-4-S6S	L2B	1/4 BSP, AL	SDC08-4-L2B	S3B	3/8 BSP, Steel	CP08-4-S3B													
Code	Ports & Material	Housing Model Code																																					
00	No Housing																																						
4S	#4 SAE, AL	CP08-4-4S																																					
6S	#6 SAE, AL	CP08-4-6S																																					
S6S	#6 SAE, Steel	CP08-4-S6S																																					
L2B	1/4 BSP, AL	SDC08-4-L2B																																					
S3B	3/8 BSP, Steel	CP08-4-S3B																																					
<small>* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi]. * Additional housings available</small>																																							
Seal Option																																							
<table border="1"> <thead> <tr> <th>Code</th> <th>Seal kit</th> </tr> </thead> <tbody> <tr> <td>B-Buna - N</td> <td>354003319</td> </tr> <tr> <td>V-Viton</td> <td>354003919</td> </tr> </tbody> </table>						Code	Seal kit	B-Buna - N	354003319	V-Viton	354003919																												
Code	Seal kit																																						
B-Buna - N	354003319																																						
V-Viton	354003919																																						
Manual Override Option																																							
<table border="1"> <thead> <tr> <th>Omit-Push Pin</th> </tr> </thead> <tbody> <tr> <td>PB-Push Button</td> </tr> <tr> <td>SPS-Screw Type</td> </tr> <tr> <td>PAP-Push and Pull</td> </tr> </tbody> </table>						Omit-Push Pin	PB-Push Button	SPS-Screw Type	PAP-Push and Pull																														
Omit-Push Pin																																							
PB-Push Button																																							
SPS-Screw Type																																							
PAP-Push and Pull																																							

Solenoid Valves

HSV08-34-05


Solenoid Valve, 4-way, 3-position, Spool Type

350 bar [5000 psi] • 17 l/min [4.5 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2, 4 and 1 are open while port 3 is blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state allowing the work ports to be referenced to tank, removing locked in pressure with the inlet port 3 closed. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]



■ PERFORMANCE DATA

Rated Pressure* 350 bar [5000 psi]

Flow Capability 17 l/min [4.5 US gpm]


Coil Options M13, R13

Weight 0.55 kg [1.21 lb]

Cavity SDC08-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

■ PERFORMANCE CURVES



■ MODEL CODE

HSV08 - 34 - 05 - 12D - DE - PN - P - S3B

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400011)

*Robust Coil - Steel coil nut and no o-rings (p/n 173800539)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports	Housing Model Code
00	No Housing	
S3B	3/8 BSP, Steel	CP08-4-S3B
S6S	#6 SAE, Steel	CP08-4-S6S

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
P-Polyurethane Single Seal	11167316

Solenoid Valves

SV10-34-05


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 24 l/min [6.3 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2, 4 and 1 are open while port 3 is blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens port 3 to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state allowing the work ports to be referenced to tank, removing locked in pressure with the inlet port 3 closed. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	24 l/min [6.3 US gpm]
Coil Options	M16, R16
Weight	0.81 kg [1.79 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ MODEL CODE

SV10 - 34 - 05 - 12D - DE - PB - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	CP10-4-6S
8S	#8 SAE, AL	CP10-4-8S
S8S	#8 SAE, Steel	CP10-4-S8S
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Manual Override Option

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type
- OPS-Protected Push Pin
- PAT-Push and Twist
- PAP-Push and Pull

Solenoid Valves


SV15-34-05

Solenoid Valve, 4-way, 3-position, Spool Type
230 bar [3300 psi] • 60 l/min [16 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2, 4 and 1 are open while port 3 is blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state allowing the work ports to be referenced to tank, removing locked in pressure with the inlet port 3 closed. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	60 l/min [16 US gpm]
Coil Options	M19
Weight	1.4 kg [3.09 lb]
Cavity	NCS 12/4


*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles

■ PERFORMANCE CURVES



■ OPERATING ENVELOPE



■ MODEL CODE

SV15 - 34 - 05 - 12D - DE - V - F - 8S

Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 173800978)

**DIN only - external rectifier needed

Connector Type

Code	
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

** Additional housings available

Filter Option

0omit	- No filter
F	- Filter 300 µm

Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885

Solenoid Valves

SV10-34-11


Solenoid Valve, 4-way, 3-position, Spool Type

230 bar [3300 psi] • 28 l/min [7.4 US gpm]

■ OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2 and 3 blocked while port 4 is open to 1. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port 3 opens to 4 and port 2 to 1. This valve provides a directional control function with a neutral de energized state allowing the service line from port 4 to be referenced to tank removing locked in pressure with ports 3 and 2 closed. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

■ SCHEMATIC



■ DIMENSIONS

mm [in]





■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	28 l/min [7.4 US gpm]
Coil Options	M16, R16
Weight	0.81 kg [1.79 lb]
Cavity	SDC10-4

*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



1) 3 to 4 S2 Energized, 3 to 2 S1 Energized
2) 2 to 1 S2 Energized, 4 to 1 S1 Energized

■ MODEL CODE

SV10 - 34 - 11 - 12D - DE - PB - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A	110 VAC**	
220A	220 VAC**	

*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DED*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
65	#6 SAE, AL	CP10-4-65
85	#8 SAE, AL	CP10-4-85
585	#8 SAE, Steel	CP10-4-585
L3B	3/8 BSP, AL	SDC10-4-L3B
L4B	1/2 BSP, AL	SDC10-4-L4B
S4B	1/2 BSP, Steel	CP10-4-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	354001919
V-Viton	354002019

Manual Override Option

- Omit-Push Pin
- PB-Push Button
- SPS-Screw Type
- OPS-Protected Push Pin
- PAT-Push and Twist
- PAP-Push and Pull

Solenoid Valves

SV10-35-02


Solenoid Valve, 5-way, 3-position, Spool Type

230 bar [3300 psi] • 30 l/min [8 US gpm]

■ OPERATION AND DESCRIPTION


This is a 5-way, 3-position, spool type, direct acting solenoid valve. In the center condition, all ports are blocked. By energizing one coil, port 5 opens to 2 and 1 and port 4 to 3. When energizing the other coil, port 5 will be open to 4 and 1, and port 2 connects to 3. This valve provides a directional control function with a neutral de-energized state with all ports closed including port 1, which is normally used as a load sense port. The valve can be used in any hydraulic application where an actuator needs to be controlled in both directions needing a load sense line to activate a pump controller. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS

mm [in]




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	30 l/min [8 US gpm]
Coil Options	M16, R16
Weight	0.9 kg [1.98 lb]
Cavity	SDC10-5


*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



Operating envelope



■ MODEL CODE

SV10 - 35 - 02 - 12D - DE - PB - B - 6S

Coil Voltage

Standard Coil Code	Robust Coil Code	Coil Voltage
00	R00	No Coil, nut included*
10D	R10D	10 VDC
12D	R12D	12 VDC
20D	R20D	20 VDC
24D	R24D	24 VDC
110A		110 VAC**
220A		220 VAC**

*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)

**Robust Coil - Steel coil nut and no o-rings (p/n 173804910)

**DIN only - external rectifier needed

Connector Type

Standard Coil Code	Robust Coil Code	Connector Type
00	00	No Coil
AJ		Amp Junior
AJD		Amp Junior with Diode
AS	AS	AMP SuperSeal 1.5
ASD	ASDB*	AMP SuperSeal with Diode
DE	DE	Deutsch
DED	DEDB*	Deutsch with Diode
FL	FL	Flying Leads
FLD	FLDB*	Flying Leads with Diode
DN		DIN 43650

*Bi-directional diode

Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
6S	#6 SAE, AL	SDC10-5-6S
8S	#8 SAE, AL	SDC10-5-8S
S8S	#8 SAE, Steel	SDC10-5-S8S
L3B	3/8 BSP, AL	SDC10-5-L3B
L4B	1/2 BSP, AL	SDC10-5-L4B
S4B	1/2 BSP, Steel	SDC10-5-S4B

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

* Additional housings available

Seal Option

Code	Seal kit
B-Buna - N	11192395
V-Viton	11192396

Manual Override Option

Omit-Push Pin

PB-Push Button

SPS-Screw Type

OPS-Protected Push Pin

PAP-Push and Pull*

*For PAP override, load sense pressure must be less than 150 bar

Solenoid Valves

SV10-35-05


Solenoid Valve, 5-way, 3-position, Spool Type

230 bar [3300 psi] • 30 l/min [8 US gpm]


■ OPERATION AND DESCRIPTION

This is a 5-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2 and 4 are connected to port 3, and port 5 and 1 are blocked. By energizing one coil, port 5 opens to 2 and 1 and port 4 to 3. When energizing the other coil, port 5 will be open to 4 and 1, port 2 connects to 3. This valve provides a directional control function with a neutral de-energized state with the service lines open to tank allowing pressure to decay. Port 5 and port 1, which is normally used as a load sense port, are closed. The valve can be used in any hydraulic application where an actuator needs to be controlled in both directions needing a load sense line to activate a pump controller. Always check the operating envelope to make sure the valve will work under the required application conditions.

■ SCHEMATIC



■ DIMENSIONS




■ PERFORMANCE DATA

Rated Pressure*	230 bar [3300 psi]**
Flow Capability	30 l/min [8 US gpm]
Coil Options	M16, R16
Weight	0.9 kg [1.98 lb]
Cavity	SDC10-5


*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

**Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 400,000 cycles

■ PERFORMANCE CURVES



■ OPERATING ENVELOPE



■ MODEL CODE

SV10 - 35 - 05 - 12D - DE - PB - B - 6S					
Coil Voltage			Housing		
Standard Coil Code	Robust Coil Code	Coil Voltage	Code	Ports & Material	Housing Model Code
00	R00	No Coil, nut included*	00	No Housing	
10D	R10D	10 VDC	6S	#6 SAE, AL	SDC10-5-6S
12D	R12D	12 VDC	8S	#8 SAE, AL	SDC10-5-8S
20D	R20D	20 VDC	S8S	#8 SAE, Steel	SDC10-5-S8S
24D	R24D	24 VDC	L3B	3/8 BSP, AL	SDC10-5-L3B
110A		110 VAC**	L4B	1/2 BSP, AL	SDC10-5-L4B
220A		220 VAC**	S4B	1/2 BSP, Steel	SDC10-5-S4B
*Standard Coil - Plastic coil nut and o-rings (p/n 17400031)					
*Robust Coil - Steel coil nut and no o-rings (p/n 173804910)					
**DIN only - external rectifier needed					
Connector Type			Seal Option		
Standard Coil Code	Robust Coil Code	Connector Type	Code	Seal kit	
00	00	No Coil	B-Buna - N	11192395	
AJ		Amp Junior	V-Viton	11192396	
AJD		Amp Junior with Diode	Manual Override Option		
AS	AS	AMP SuperSeal 1.5	0mit-Push Pin		
ASD	ASDB*	AMP SuperSeal with Diode	PB-Push Button		
DE	DE	Deutsch	SPS-Screw Type		
DED	DED*	Deutsch with Diode	OPS-Protected Push Pin		
FL	FL	Flying Leads	PAP-Push and Pull*		
FLD	FLDB*	Flying Leads with Diode	*For PAP override, load sense pressure must be less than 150 bar		
DN		DIN 43650			
*Bi-directional diode					

Danfoss