




Danfoss

Concrete, Plaster and Grout

Engineered to pump with confidence



Marauder® EHK006 hose

Boston® Marauder EHK006 is designed for concrete, plaster and grout pumping. Marauder is built to withstand the toughest environments and meets a constant pressure of 1,233 psi. across our full size range, bringing you the pressure you need in any application.

Features:

- High pressure use up to 1233 psi.
- Meets the requirements of ASME B30.27-2014
- For high pressure concrete pumping and spraying plaster, grout, sand, gypsum, and ready mixed concrete
- Light weight for hand held applications

Benefits:

- **Meets ASME B30.27-2014:** Ensures high safety and reliability.
- **High-Pressure (1233 psi):** Provides powerful and efficient material flow.
- **Versatile:** Suitable for plaster, grout, sand, gypsum, and concrete.
- **Easy to handle,** reducing operator fatigue and increasing precision.



Markets & Applications:

- Construction
- Cement
- Swimming pool
- Tunnel faces
- Dams
- Ready-mix concrete
- Gypsum spraying
- Transfer of sand



Marauder® EHK006

High pressure solution for spraying plaster and grout, sand and ready-mix concrete pumping



Number	Hose I.D.		Hose O.D.		Operating Pressure		Min. Burst Pressure		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kg/m	lbs/ft
EHK006-20-100	32.0	1.25	48.8	1.92	85.0	1233	178	2581	1.22	.820	30.5	100
EHK006-24-100	38.0	1.50	58.7	2.31	85.0	1233	178	2581	1.81	1.21	30.5	100
EHK006-32-100	50.8	2.00	72.0	2.83	85.0	1233	178	2581	2.40	1.61	30.5	100
EHK006-40-100	63.5	2.50	86.3	3.40	85.0	1233	178	2581	3.01	2.02	30.5	100
EHK006-48-100	76.2	3.00	96.6	3.92	85.0	1233	178	2581	3.65	2.45	30.5	100
EHK006-64-100	101.6	4.00	126.0	4.92	85.0	1233	178	2581	4.74	3.18	30.5	100
EHK006-80-100	127.0	5.00	153.5	6.04	85.0	1233	178	2581	6.38	4.29	30.5	100

Construction

Tube Abrasion resistant anti-static natural rubber

Reinforcement

High tensile synthetic textile and anti-static copper wire

Cover Abrasion, ozone and weather resistant pin-pricked synthetic rubber

Colors Black

Operating Temperature

-40°C to +70°C
(-40°F to +158°F)

Certification

Meets the requirements of ASME B30.27-2014

Type of couplings

Danfoss offers customized solutions

Contact coupling manufacturer for attachment procedure and other coupling recommendations

Visit PowerSource crimp specs at danfoss.com/crimp for crimp specifications.

Boston is a registered trademark of Danfoss. All other trademarks are property of their respective owners.

Danfoss can accept no responsibility for possible errors in catalogs, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without sub sequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.

