



Danfoss Ally™
Compatible

Danfoss Ally™

Danfoss Ally™ Gateway

Description

The Danfoss Ally™ Gateway is a programmable, wireless control system that connects all the Danfoss Ally™ devices to the internet and intelligently controls your heating via a free app downloadable from Google Play and App Store. The power supply and LAN cable for the internet connection are included.

Features & Benefits

- Controls the daily heating schedule for every room allowing quick and easy adjustments to be made.
- The Pre-Heat function is used to ensure you have the right temperature when you want it.
 - When Pre-Heat function is "On" it means that, it is ramping upto the next scheduled At Home mode.
- The Danfoss Ally™ Gateway software is automatically updated from the internet.

Ordering

Product code numbers

Description	Code number
Danfoss Ally™ Gateway	014G2400

Languages
EN, DE, DA, FR, IT, ES, PL, CS, UA, RU, SE, FI, IS, ET, LV, LT, SK, SL, RO, HR, TR

Accessories code numbers

 <p>014G2479 Danfoss Ally™ Boiler Relay, Zigbee Boiler relay device for the Danfoss Ally™ system</p> <p>Related products 014G2400</p>	 <p>014G2420 Radiator thermostat, Danfoss Ally™, Adapter type: RA; M30, 2.4 GHz Electronic thermostatic radiator valve for the Danfoss Ally™ system, Zigbee, RA; M30, Zigbee</p> <p>Related products 014G2400</p>
 <p>014G2460 Radiator thermostat, Danfoss Ally™, Adapter type: RAV; RA; RAVL; M30, 2.4 GHz Electronic thermostatic radiator valve for the Danfoss Ally™ system, Zigbee, RAV; RA; RAVL; M30, Zigbee</p> <p>Related products 014G2400</p>	 <p>014G2480 Danfoss Ally™ Room Sensor, Zigbee Wireless remote room sensor for the Danfoss Ally™ Radiator Thermostats, Zigbee</p> <p>Related products 014G2400</p>



Product details

General data



Danfoss Ally™ Gateway	
Device Function	Smart Home Gateway
Recommended Use	Residential indoor (pollution degree 2)
Application	Radiators, water-based floor heating
LED Indicators (green)	Power/Status, Network Connection
Button	Press Reset Button for 5 sec. to perform factory reset
Power Supply	5 VDC
Adapter	Input: AC 100-240V 50/60Hz; Output: DC 5V 1A
Power Consumption / Standby	< 5 W / < 2 W
Wired Communication	10/100M Ethernet Port (RJ45, LAN)
Wireless Communication	Zigbee / IEEE 802.15.4
Transmission Frequency / Power	2,4 GHz / < 10 dBm (10 mW)
Transmission range inside buildings	up to 30 m
Firmware Update	Support for over the air updates
Operation Temperature	-10 °C to 55 °C
Storage Temperature	-20 °C to 60 °C
Color	RAL 9016
Size	95 mm x 95 mm x 23 mm
IP class	20
Integrations	Amazon Alexa, Google Assistant, Partner API
Approval, markings etc.	 

System requirements


The total number of units for the one Danfoss Ally™ Gateway must not exceed 199 mains and battery powered devices:

Danfoss Ally™ Radiator Thermostat	32 units
Danfoss Ally™ Room Sensor	
Danfoss Ally™ Zigbee Repeater	
Danfoss Ally™ Boiler Relay	
Danfoss Icon™ Zigbee Module / Danfoss Icon™ Master Controller (floor heating)	199 units
Danfoss Icon2™ Main Controller (floor heating)	
Danfoss Icon™ Room Thermostat	
Danfoss Icon2™ Room Thermostat	
Number of devices per room	50 units
Number of rooms per Home/Family	20 pcs.
Number of Homes/Families per one account	20 pcs.
Number of devices per account (20 homes/families and 200 units per each)	4000 units
Number of Home/Family members per one account	20 pcs.
Number of devices per one Home/Family	200 units

Dimensions & weights



Installation



Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
EU Declaration	Danfoss EU BF352458865198EN-000101.05	Danfoss	EU RoHS
Wireless Certificate	CAB UA.RTR.052.379-20	CAB - Conformity Assessment Body Ukrchastotnagliad	
Wireless Certificate	ACMA CF15614 AU-Rev.00	ACMA - Australian Communication and Media Authority	RCM
Statement of Compliance	Danfoss SoC 40312EN0379101.01	Danfoss	UK PSTI
Manufacturer's Declaration	Danfoss MD BF18122023-en01.01	Danfoss	Compliance misc. Standards
Wireless Certificate	RSM CF15614 NZ-Rev.00	RSM - Radio Spectrum Management	RCM

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenterdanfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partnerdanfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues, descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.