



Pressure transmitter

MBS 1700 / MBS 1750

For general purpose

Description

The compact pressure transmitters MBS 1700 and MBS 1750 are designed for use as a general purpose transmitter, and offers a reliable pressure measurement, even under harsh environmental conditions.

The version MBS 1750 with integrated pulsesnubber is designed for use in applications with severe medium influences like cavitation, liquid hammer or pressure peaks and offers a reliable pressure measurement, even under harsh environmental conditions.


Excellent vibration stability, robust construction, and a high degree of EMC / EMI protection equip the pressure transmitter to meet the most stringent industrial requirements.

Features & benefits

- Enclosure and wetted parts of acid-resistant stainless steel (AISI 316L)
- Pressure ranges in relative (gauge) from 0 – 25 bar
- Output signal: 4 – 20 mA
- Pressure connections: G ¼ A & G ½ A EN837 (MBS 1700); G ¼ DIN 3852-E, Gasket DIN 3869-15 (MBS 1750)
- Fully digitally compensated

Applications

Application and media conditions (MBS 1750)



1 Pulse-snubber

Application

Cavitation, liquid hammer and pressure peaks may occur in liquid filled systems with changes in flow velocity, e.g. fast closing of a valve or pump starts and stops. The problem may occur on the inlet and outlet side, even at rather low operating pressures.

Media condition

Clogging of the nozzle may occur in liquids containing particles. Mounting the transmitter in an upright position minimizes the risk of clogging, because the flow in the nozzle is limited to the start-up period until the dead volume behind the nozzle orifice is filled. The media viscosity has only little effect on the response time. Even at a viscosities up to 100 cSt, the response time will not exceed 4 ms.

Ordering

Product code numbers

Plug; Pg 9 (EN 175301-803-A)

Measuring range P _e ⁽¹⁾ [bar]	Output signal	Pressure connection	Code No.
0 – 6	4 – 20 mA	G ¼ A EN 837	060G6100
0 – 10			060G6101
0 – 16			060G6102
0 – 25			060G6103
0 – 6		G ½ A EN 837	060G6104
0 – 10			060G6105
0 – 16			060G6106
0 – 25			060G6107

⁽¹⁾ Relative / gauge

Plug; Pg 9 (EN 175301-803-A)

Measuring range P _e ⁽¹⁾ [bar]	Output signal	Pressure connection	Code No.
0 – 60	4 – 20 mA	DIN 3852-E G ¼ Gasket DIN 3869-14	060G6108
0 – 100			060G6112
0 – 160			060G6109
0 – 250			060G6110
0 – 400			060G6111

⁽¹⁾ Sealed gauge

Product details

General data

Performance (EN 60770)

Features		Description
Accuracy (incl. non-linearity, hysteresis and repeatability)		≤ ± 0.5% FS (typ.)
		≤ ± 1.0% FS (max.)
Non-linearity BFSL (conformity)		≤ ± 0.2% FS
Hysteresis and repeatability		≤ ± 0.1% FS
Thermal zero point shift		≤ ± 0.1% FS/10K (typ.)
		≤ ± 0.2% FS/10K (max.)
Thermal sensitivity (span) shift		≤ ± 0.1% FS/10K (typ.)
		≤ ± 0.2% FS/10K (max.)
Response time	Air and gases (MBS 1700)	< 4 ms
	Air and gases (MBS 1750)	< 35 ms
Overload pressure (static)		6 × FS (max. 1500 bar)
Burst pressure		6 × FS (max. 2000 bar)
Power-up time		< 50 ms
Durability, P: 10 – 90% FS		> 10 × 10 ⁶ cycles

Electrical specifications

Features	Description
Nom. output signal (short-circuit protected)	4 – 20 mA
Supply voltage [U _B], polarity protected	9 – 32 V d.c.
Supply – current consumption	–
Supply voltage dependency	≤ ± 0.1% FS/10 V
Current limitation	22.4 mA (typ.)
Output impedance	–
Load [R _L] (load connected to 0 V)	$R_L \leq (U_B - 9 \text{ V})/0.02 \text{ A } [\Omega]$

Environmental conditions


Features			Description
Sensor temperature range		Normal	-40 – 85 °C
media temperature range			-40 – 85 °C
Ambient temperature range			-40 – 85 °C
Compensated temperature range			0 – 80 °C
Transport / storage temperature range			-50 – 85 °C
EMC – Emission			EN 61000-6-3
EMC – Immunity			EN 61000-6-2
Insulation resistance			> 100 MΩ at 100 V
Mains frequency test			Based on SEN 361503
Vibration stability	Sinusoidal	15.9 mm-pp, 5 Hz-25 Hz	IEC 60068-2-6
		20 g, 25 Hz – 2 kHz	
	Random	7.5 grms, 5 Hz – 1 kHz	IEC 60068-2-64
Shock resistance	Shock	500 g / 1 ms	IEC 60068-2-27
	Free fall	1 m	IEC 60068-2-32
Enclosure			IP65

Mechanical characteristics

Materials	Wetted parts	EN 10088-1; 1.4404 (AISI 316 L)
	Enclosure	EN 10088-1; 1.4404 (AISI 316 L)
	Electrical connections	Glass filled polyamid PA 6.6
Net weight		0.25 kg




Guideline for installations at high media temperature
Installations at high media temperature



Electrical connections

Medium temperature (t_m) 120 °C	
Heat isolator (L)	Transmitter temperature (t_t)
2 cm	85 °C
5 cm	75 °C
10 cm	70 °C

Dimensions



A	G ¼ A (EN 837)(MBS 1700)
B	G ½ A (EN 837)(MBS 1700)
C	G ¼ (DIN 3852-E) Gasket DIN 3869-14-NBR(MBS 1750)

Torque Specification

Type code	MBS 170	MBS 1750
Recommended torque ⁽¹⁾	30 – 35 Nm	30 – 35 Nm


⁽¹⁾ Depends on different parameters as packing material, mating material, thread lubrication and pressure level



Connections

Electrical connection

EN 175301-803-A



Type code	A1
Ambient temperature	-40 – 85 °C
Enclosure (IP protection fulfilled together with mating connector)	IP65
Material	Glass filled polyamid, PA 6.6
Electrical connection, 4 – 20 mA output (2 wire)	Pin 1: + supply Pin 2: ÷ supply Pin 3: Not used  Earth: Connected to MBS enclosure

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
EU-UK Declaration	Danfoss EU-UK 060R9400.04	Danfoss	EMC, EU RoHS, UK RoHS
Manufacturer's Declaration	Danfoss MD 060R3160.00	Danfoss	China RoHS
Pressure Safety Certificate	LLC CDC EURO-TYSK UA.TR.089.1015.05-22	LLC CDC EURO TYSK - Ukraine	Pressure
UA Declaration	Danfoss UA 2024-07-25 cooling sensors	Danfoss	LVD, EMC
Export Control Declaration	Pressure & Temperature Sensors	Danfoss	
Electrical Safety Certificate	UL E510763	UL - Underwriters Laboratories inc.	
Electrical Safety Certificate	UL E494625	UL - Underwriters Laboratories inc.	
UA Declaration	Danfoss UA 2023-01-10 Regulators PL01 PL04	Danfoss	Pressure, PED
EAC Declaration	EAC KZ 7100841.13.12.00005	EAC - Eurasian Customs Union	EMC

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
