



Temperature sensor

MBT 3270

Compact industrial temperature sensor

Description

The flexible temperature sensor MBT 3270 can be used in many industrial applications such as: Air Compressors, Mobile Hydraulics and Exhaust gas return systems. In other words applications where robustness, size and performance are essentials.

The sensor can be equipped with different sensing elements (RTD, NTC and PTC) and is available with different electrical connections (Cable, Delphi Metri Pack, AMP junior power Timer, Deutch DT04).

Features & benefits

- OEM Temperature Sensor program
- Various sensor elements available (RTD, NTC, PTC)
- Robust, high protection against moisture
- Fixed measuring insert
- Brass or stainless steel
- Very low response times
- Temperature range up to 300 °C
- Available with cable or integrated plug(Delphi Metri Pack, AMP junior power Timer,Deutch DT04)



Ordering

Product code numbers

Cable version
Ordering for MBT 3270

Type MBT 3270									

Integrated plug version

Ordering for MBT 3270

Type MBT 3270			
Measuring range		Connection	
-50 – 150 °C	0	0	2-wire
-50 – 200 °C	1	9	Other
-50 – 300 °C	2		
Other	9		
Resistance value		Plug	
1 × Pt 100	0	0	None
1 × Pt 1000	2	3	AMP Junior Power Timer
NTC 2000, B25/85 2880 - 4570	6	4	Delphi Metri-pack Integrated – 102
NTC 2700, B25/85 2880 - 4570	K	C	Deutsch Integrated DT04 – 2 pin
NTC 3000, B25/50 3499	A	9	Other
NTC 5000, B25/100 3988	L		
Other (e.g. NTC)	9		
Tolerance		Insert	
EN 60751 Class B	0	0	Fixed
± 1%	1		
± 2%	2		
± 3%	3		
Other	9		
NTC characteristic		Process connection	
No NTC	0	0	G ¼ A
Other	9	1	G 3/8 A
		2	G ½ A
		3	M10 × 1
		B	M14 × 1.5
		9	Other
Protection tube			
Brass	0		
Acid-Proof Steel, AISI 316	1		
Other	9		
Insertion length (80 mm max)			
24 mm	0 2 4		
28 mm	0 2 8		
40 mm	0 4 0		
Other (21 – 80)	x x x		

Note: Non-standard build-up combinations may be selected. However, minimum order quantities may apply. Please contact your local Danfoss office for further information or request on other versions.

Note: For a detailed overview of our existing code numbers, please visit the Danfoss Product Store at store.danfoss.com. You can use the filtering options to find the right sensor for your specific needs.




Product details

General data

Technical data

a) Cable version



General data

Features		Description	
Ambient temperature	Cable	PVC	-40 – 100 °C
		Silicon	-40 – 200 °C
		Teflon	-40 – 200 °C
		Polyolefin (oil resistant)	-40 – 150 °C
	Plug	AMP spade	-40 – 200 °C
		AMP Junior Power Timer	-40 – 125 °C
		Delphi Metri Pack 102	-40 – 125 °C
		Deutsch DT04-3P	-40 – 125 °C
Media temperature		Pt 100	-50 – 300 °C
		NTC	-50 – 150 °C, Special versions up to 300 °C
		PTC	-50 – 150 °C
Max. external pressure		Operating pressure	500 bar
		Burst pressure	> 900 bar
Max. tightening torque		M10	17 Nm
		M14	24 Nm

Performance

Features		Description
Sensor Element		Pt 100, Pt 1000, NTC, PTC
Process Connection		Refer to ordering standard, see Ordering chapter, Cable version
Sensor insertion length	Brass	80 mm @ d ≥ 8 mm
		60 mm @ 8 > d > 5 mm
		40 mm @ d ≤ 5 mm
	Stainless steel	70 mm @ d ≥ 8 mm
		50 mm @ 8 > d > 5 mm
		35 mm @ d ≤ 5 mm
Electrical Connection		Stripped wire ends Cable with AMP spade (6.35) Cable with AMP Junior Power Timer Cable with Delphi Metri Pack 102 Cable with Deutsch DT04-3P-2P Other on request
Connection		2, 3 or 4 wire (depending on electrical connection)

Indicative response times

Material protection tube	Protection tube	Indicative response times	
		Water 0.2 m/s	
		$t_{0.5}$	$t_{0.9}$
Stainless steel	ø6 mm	6 s	18 s
	ø4 mm	2 s	6 s
	ø3 mm	1.5 s	3 s

Note: Response times can vary very much depending on the design of the sensor and the temperature element chosen.

Mechanical and environmental specifications


Features	Description	
Sensor tolerances	Pt 1000 / Pt 100	EN 60751 Class B: $\pm (0.3 + 0.005 \times t)$
	NTC	On request
	PTC 2000 (KTY 81 – 210)	$\pm 1\%$ at 25 °C
Vibration stability	Shock	50 g / 6 ms
	Vibrations, x-y-z directions	15.3 g sine, 20 – 2000 Hz, 8 hours
Enclosure	Sensor only	IP65 according to IEC 60529
	Cable with AMP spade	
	Cable with AMP Junior Timer	
	Cable with Delphi Metri Pack 102	
	Cable with Deutsch DT04	

Materials

Features	Description
Protection tube in contact with media	AISI 316 Brass
Process connection	AISI 316 Brass
Cable	PVC, Silicon, Teflon (other on request)
Gasket	Viton, NBR (other on request)
Plug	PPS (Ryton 4)



b) Integrated plug version



General data

Features		Description
Ambient temperature	Plug	-40 – 125 °C
Media temperature	Pt 1000, Pt 100	-50 – 300 °C
	NTC	-50 – 150 °C, Special versions up to 300 °C
	PTC	-50 – 150 °C
Max. external pressure	Operating pressure	500 bar
	Burst pressure	> 900 bar
Max. tightening torque	M10	17 Nm
	M14	24 Nm

Performance

Features		Description
Sensor Element		Pt 100, Pt 1000, NTC, PTC
Process Connection		Refer to ordering standard, see Ordering chapter, Integrated plug version
Sensor insertion length	Brass	80 mm @ d ≥ 8 mm
		60 mm @ 8 > d > 5 mm
		40 mm @ d ≤ 5 mm
	Stainless steel	70 mm @ d ≥ 8 mm
		50 mm @ 8 > d > 5 mm
		35 mm @ d ≤ 5 mm
Electrical Connection		AMP Junior Power Timer Delphi Metri Pack Deutsch DT04 Other on request
Connection		2 wire

Indicative response times

Material protection tube	Protection tube	Indicative response times	
		Water 0.2 m/s	
		t _{0.5}	t _{0.9}
Stainless Steel	ø6 mm	6 s	18 s
	ø4 mm	2 s	6 s
	ø3 mm	0.5 s	1.5 s

Note: Response times can vary very much depending on the design of the sensor and the temperature element chosen.



Mechanical and environmental specifications



Features	Description	
Sensor tolerances	Pt 1000 / Pt 100	EN 60751 Class B
	NTC	On request
Vibration stability	PTC 2000 (KTY 81 – 210)	± 1% at 25 °C
	Shock	50 g / 6 ms
Enclosure	Vibrations, x-y-z directions	15.3 g sine, 20 – 2000 Hz, 8 hours
	AMP Junior Power Timer Delphi Metri Pack Deutsch DT04	IP65 according to IEC 60529

Materials

Features	Description
Protection tube in contact with media	AISI 316 Brass
Process connection	AISI 316 Brass
Gasket	Viton, NBR (other on request)
Plug	PPS (Ryton 4)

Dimensions

Cable version dimensions

-50 – 150 °C	-50 – 150 °C / 300 °C
	

Examples:

Insertion length: Li = 21 to xx (max. 80 mm)

Cable length: Lc = 0.5 m to x.xx m

Tube diameter depends on the chosen sensor element and the wanted response time.






Note: Dimensions are in mm, unless stated otherwise.






Connections

Electrical connection

Electrical connection of cable version

AMP spade (6.35)	AMP Junior Power Timer	Deutsch DT04 3 pin	Deutsch DT04 2 pin	Delphi Metri Pack 102
				

Electrical connection of integrated plug version

Deutsch DT04	AMP Junior Power Timer	Delphi Metri Pack 102
		

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
Manufacturer's Declaration	Danfoss MD 084R1022.01	Danfoss	China RoHS
Export Control Declaration	Pressure & Temperature Sensors	Danfoss	
EU-UK Declaration	Danfoss EU-UK 084R1019.04	Danfoss	EMC, EU RoHS, UK RoHS
Manufacturer's Declaration	Simple Apparatus	Danfoss	Simples apparatus

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
