




Micro channel heat exchanger

MCHE D1500-C Bare Version

Condenser – standard series

Description

D1500-C is ideal for use in many different applications, such as chillers and commercial split/roof tops.

MCHes have an ingeniously simple all-aluminum design that is not only lightweight but also prevents galvanic corrosion.

The refrigerant-carrying tubes are formed to optimize heat transfer, enabling the production of more compact, but equally effective, cooling solutions. The smart louvered fin design maximizes surface contact, reducing the airside pressure loss, improving efficiency and reducing noise levels.

Features & benefits

- Reduce refrigerant system charge
- Improve efficiency - More compact, better COP, increased capacity
- Cost: Less sensitive to fluctuations in raw material prices
- Better strength and better anticorrosion characteristic

Product details

General data

Table: Technical data

Model	Coil length	Coil height	Core depth	Fin pitch	Inlet ID diameter	Outlet ID diameter	Continuous operating temperature	Max. working pressure
D1500-C	1074 mm	517 mm	25.4 mm	1.1 mm	12.9 mm	12.9 mm	-40 – 121 °C	45 bar
	42.3 in	20.3 in	1.0 in	23 FPI	0.51 in	0.51 in	-40 – 250 °F	650 psi

Weight / internal volume

Coil weight: 6.57 kg / 14.49 lb

Internal volume: 1.15 l / 70.18 in³

Materials

MPE Tube: 9153

Fins: 3003

Manifold: 3003

End plate: 3003

Inlet/Outlet tubes: Copper

Performance and environmental conditions

Performance data of R410A and R134a

Air Velocity	Performance [KW/Btu/h×1000]							
[m/s]	R410A				R134a			
[ft/min]	Δ=10 K / 18 °F	Δ=15 K / 27 °F	Δ=20 K / 36 °F	Δ=25 K / 45 °F	Δ=10 K / 18 °F	Δ=15 K / 27 °F	Δ=20 K / 36 °F	Δ=25 K / 45 °F
1.0/197	5.54/18.9	8.24/28.11	11.33/38.66	14.41/49.17	5.31/18.12	8.1/27.64	10.85/37.02	13.62/46.47
1.5/295	7.9/26.95	12.05/41.11	16.47/56.2	20.79/70.94	7.48/25.52	11.46/39.1	15.41/52.58	19.36/66.06
2.0/394	10.03/34.22	15.33/52.31	21.12/72.06	26.68/91.03	9.4/32.07	14.45/49.3	19.49/66.5	24.86/84.82
2.5/492	11.97/40.84	18.78/64.08	25.42/86.73	32.13/109.63	11.11/37.91	17.14/58.48	23.12/78.89	29.46/100.52
3.0/591	13.75/46.92	21.73/74.14	29.41/100.35	37.22/126.99	12.67/43.23	19.58/66.81	26.92/91.85	33.71/115.02

Performance data of R404A and R407C

Air Velocity	Performance [KW/Btu/h×1000]							
[m/s]	R404A				R407C			
[ft/min]	Δ=10 K / 18 °F	Δ=15 K / 27 °F	Δ=20 K / 36 °F	Δ=25 K / 45 °F	Δ=10 K / 18 °F	Δ=15 K / 27 °F	Δ=20 K / 36 °F	Δ=25 K / 45 °F
1.0/197	5.52/18.83	8.41/28.69	11.29/38.52	14.45/49.3	3.7/12.62	2.98/10.17	9.81/33.47	12.74/43.47
1.5/295	7.8/26.61	11.92/40.67	16.47/56.2	20.78/70.9	5.19/17.71	4.1/13.99	13.99/47.73	18.19/62.06
2.0/394	9.82/33.51	15.57/53.12	21.01/71.69	26.53/90.52	6.51/22.21	5.08/17.33	17.74/60.53	23.5/80.18
2.5/492	11.64/39.72	18.6/63.46	25.17/85.88	31.79/108.47	7.69/26.24	5.93/20.23	21.2/72.33	28.18/96.15
3.0/591	13.28/45.31	21.41/73.05	28.97/98.85	36.63/124.98	8.75/29.86	16.84/57.46	24.93/85.06	32.48/110.82

Performance data of R454B and R452B

Air Velocity	Performance [KW/Btu/h×1000]							
[m/s]	R454B				R452B			
[ft/min]	Δ=10 K / 18 °F	Δ=15 K / 27 °F	Δ=20 K / 36 °F	Δ=25 K / 45 °F	Δ=10 K / 18 °F	Δ=15 K / 27 °F	Δ=20 K / 36 °F	Δ=25 K / 45 °F
1.0/197	5.09/17.37	7.99/27.26	10.87/37.09	13.77/46.98	5.15/17.57	8.04/27.43	10.94/37.33	13.83/47.19
1.5/295	7.27/24.81	11.44/39.03	15.58/53.16	20.01/68.27	7.36/25.11	11.52/39.31	15.66/53.43	20.11/68.62
2.0/394	9.24/31.53	14.57/49.71	20.2/68.92	25.67/87.59	9.35/31.9	14.68/50.09	20.3/69.26	25.79/88.00
2.5/492	11.05/37.7	17.46/59.57	24.28/82.84	30.91/105.46	11.18/38.15	17.59/60.02	24.44/83.39	31.08/106.04
3.0/591	12.72/43.4	20.4/69.6	28.1/95.88	35.81/122.18	12.87/43.91	20.7/70.63	28.29/96.53	35.98/122.76

Dimensions

Figure: Dimensions





Figure: Mounting



Aluminum MCHEs expand and contract when exposed to big temperature changes. Installation supports/brackets must allow the MCHE to move in two dimensions.

Connections

Standard connections

The product is equipped with standard copper pipe connections for easy mounting. Never bend or stress the inlet/outlet connections during mounting, and design installations to avoid vibration in operation.

Bending

Micro Channel Heat Exchangers can easily be bent to fit in any application. Ask your local Danfoss Sales representative for advice.

Availability

Our local stocking and distribution network allows standard MCHEs to be delivered globally with short delivery times. Contact your local Danfoss sales representative for the standard lead times in your region.

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
Manufacturer's Declaration	Danfoss MD CN-ROHS-DoC-202306-01.01	Danfoss	China RoHS
Export Control Declaration	Micro Channel Heat Exchanger	Danfoss	
Manufacturer's Declaration	Danfoss MD EU-ROHS-DoC-202306-01	Danfoss	EU RoHS
Manufacturer's Declaration	Danfoss MD UK-ROHS-MOD-202306-01.01	Danfoss	UK RoHS, EU RoHS
Pressure Safety Certificate	BV CE-0062-PED-H-DMC 001-23-CHN-Rev.B	BV - Bureau Veritas	PED, Pressure

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
