



Hermetic burn-out filter drier

DAS

Used in the suction line to clean up refrigeration and air conditioning systems

Description

Hermetic burn-out filter driers type DAS are used in the suction line to clean up refrigeration and air conditioning systems after a compressor motor burn-out.

The solid core, which is composed of 70% activated alumina and 30% Molecular Sieve, adsorbs harmful acids as well as moisture.

Available with flare and solder (pure copper) connections.


Features & benefits

- The Core type DAS is recommended for use with HFO, HC, HFC and HCFC refrigerants
 - Solid core with 70% activated alumina and 30% Molecular Sieve for adsorption of acid and moisture
- The Shell is available in sizes 8 – 60 cubic inches
 - PED approved for PS 35 bar
 - Available with flare and solder (pure copper) connections
 - Corrosion resistant powder-painted finish
 - Allows installation with any orientation provided the flow is in the arrow direction
 - 2 Schrader access valves to measure pressure drop across the drier
- The Filter has 120 mesh wire mesh provides solid particle retention with minimal pressure drop

Ordering


Product code numbers

Figure: Flare connection



Type	Connection	Multi-pack	
	[in]	Qty.	Code no.
DAS 083VV	$\frac{3}{8}$	24	023Z1001
DAS 084VV	$\frac{1}{2}$	24	023Z1002
DAS 164VV	$\frac{1}{2}$	12	023Z1007
DAS 165VV	$\frac{5}{8}$	12	023Z1008

Figure: Solder connection




Type	Connection	Multi-pack	
	[in]	Qty.	Code no.
DAS 083sVV	$\frac{3}{8}$	24	023Z1003
DAS 084sVV	$\frac{1}{2}$	24	023Z1004
DAS 085sVV	$\frac{5}{8}$	24	023Z1005
DAS 086sVV	$\frac{3}{4}$	24	023Z1006
DAS 164sVV	$\frac{1}{2}$	12	023Z1009
DAS 165sVV	$\frac{5}{8}$	12	023Z1010
DAS 166sVV	$\frac{3}{4}$	12	023Z1011
DAS 167sVV	$\frac{7}{8}$	12	023Z1012
DAS 305sVV	$\frac{5}{8}$	8	023Z1013
DAS 306sVV	$\frac{3}{4}$	8	023Z1014
DAS 307sVV	$\frac{7}{8}$	8	023Z1015
DAS 309sVV	$1\frac{1}{8}$	8	023Z1016
DAS 417sVV	$\frac{7}{8}$	8	023Z1017
DAS 419sVV	$1\frac{1}{8}$	8	023Z1018
DAS 607sVV	$\frac{7}{8}$	12	023Z1019
DAS 609sVV	$1\frac{1}{8}$	12	023Z1020



Functions

Hermetic filter driers protect refrigeration and air-conditioning systems from moisture, acids, and solid particles. By adsorbing harmful acids after a compressor motor damage, the DAS hermetic burn-out filter drier protects the new compressor against premature failure.

Figure: Functional diagram



Product details

General data
Identification

Table: Type codes

Type	Codes	Description
Filter drier	D	Drier
Solid core	A	Burn-out, 70% activated alumina / 30% Molecular Sieves
Application	S	Suction line
Size (volume)	8	8 in ³
	16	16 in ³
	30	30 in ³
	41	41 in ³
	60	60 in ³
Connection (filter connection in ⅓ of an inch increments)	3	⅜ in / 10 mm
	4	½ in / 12 mm
	5	⅝ in / 16 mm
	6	¾ in / 18 (19) mm
	7	⅞ in / 22 mm
	9	1 ⅛ in / 28 mm
Connection type	–	Flare connection
	s	Solder connection (pure copper)

Type	Codes	Description	
Access valves	–	Inlet:	Outlet:
	–	No access valves	No access valves
	V	Schrader valve	No access valves
	VV	Schrader valve	Schrader valve


Example for type codes

D	Filter drier
A	Solid core
S	Application
08	Size (volume)
3	Connection (filter connection in 1/8 of an inch increments)

s	Connection type
vv	Access valves

Design

Figure: Type DAS



1	Inlet
2	Spring
3	Solid core
4	Polyester ma
5	Metal mesh
6	Perforated plate
7	Schrader valve

The large diameter of the hermetic burn-out filter drier means that flow velocity is suitably low and the pressure drop minimal. Powder formation is eliminated because the solid core grains are bonded and cannot move against each other.

Capacity

Figure: Flare connection




Figure: Solder connection (pure copper)




Table: Type DAS

Type	Rated capacity, Q_n ⁽¹⁾			Acid capacity ⁽²⁾	Max.Working Pressure PS
	R22/R407C/R410A	R134a	R404A/R507		
	[kW]	[kW]	[kW]	[g]	[bar]
DAS 083	6	3.5	4.5	3.8	35
DAS 084	10	5.5	8	3.8	35
DAS 085	14.5	9	12.5	3.8	35
DAS 086	19	11.5	16.5	3.8	35
DAS 164	10.5	6	8.5	8.6	35
DAS 165	15	9.5	13	8.6	35
DAS 166	20	12	17	8.6	35
DAS 167	22	13.5	19	8.6	35
DAS 305	18	11	15	18.2	35
DAS 306	22	14	19	18.2	35
DAS 307	26	16	22	18.2	35
DAS 309	31	20	27	18.2	35
DAS 417	30	18	25	24.3	35
DAS 419	35	22	30	24.3	35
DAS 607	20	12	17	36.5	35

⁽¹⁾ Rated capacity is stated at: evaporating temperature $t_e = 4^\circ\text{C}$ pressure drop $\Delta p = 0.21$ bar

⁽²⁾ Adsorption capacity of oleic acid at 0.05 TAN (Total Acid Number)

Temperature range: -40 – 70 °C

Selection

Capacities for other temperatures than 4 °C are calculated by use of correction factors. Divide your actual evaporator capacity with the correction factor given for your actual evaporating temperature.

Look up the capacity table for the necessary rated capacity:

Q_e/F_e	Q_n
Q_e	Actual evaporator capacity
Q_n	Nominal capacity
F_e	Correction factor

Table: Correction factors F_e for evaporating temperatures [°C]

[°C]	4	0	-5	-10	-15	-20	-25	-30	-35	-40
F_e	1	0.9	0.75	0.6	0.5	0.4	0.35	0.25	0.2	0.15


Example:

To select a hermetic burn-out filter drier for a R22 plant with an evaporator capacity at 8.5 kW at -20 °C you may use a burn-out filter drier with a rated capacity of $8.5 / 0.4 = 21.25$ kW or bigger.

For example, DAS 306.

Dimensions


Figure: Solder connections



Type	A	B	L	D1	D2	F	Net weight
	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[kg]
DAS 083sVV	101	120	139	58	54	40	0.47
DAS 084sVV	101	122	143	58	54	40	0.5
DAS 085sVV	101	125	149	58	54	40	0.5
DAS 086sVV	101	131	161	58	54	40	0.5
DAS 164sVV	110	131	152	80	76	50	0.83
DAS 165sVV	110	134	158	80	76	50	0.84
DAS 166sVV	110	140	170	80	76	50	0.84
DAS 167sVV	110	141	172	80	76	50	0.84
DAS 169sVV	110	142	173	80	76	50	1.9
DAS 305sVV	186	210	234	80	76	50	1.31
DAS 306sVV	186	216	246	80	76	50	1.31
DAS 307sVV	186	217	248	80	76	50	1.33
DAS 309sVV	186	218	249	80	76	50	1.35
DAS 417sVV	187	218	249	93	89	55	2.08
DAS 419sVV	187	219	250	93	89	55	2.08
DAS 607sVV	337	363	399	80	76	50	2.39
DAS 609sVV	337	358	400	80	76	50	2.4



Figure: Flare connections



Type	A	L	D1	D2	F	Net weight
	[mm]	[mm]	[mm]	[mm]	[mm]	[kg]
DAS 083VV	101	158	58	54	40	0.51
DAS 084VV	101	166	58	54	40	0.62
DAS 164VV	110	175	80	76	40	0.91
DAS 165VV	110	184	80	76	40	0.95

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
UA Declaration	Danfoss UA 2023-01-10 Filters PL01	Danfoss	PED, Pressure
Manufacturer's Declaration	Danfoss MD 023U9601.AI	Danfoss	Explosive, EU RoHS, PED, Pressure, ATEX
Mechanical Safety Certificate	UL SA6398 19980330 US-CA	UL - Underwriters Laboratories inc.	
Manufacturer's Declaration	Danfoss MD 023Z9610.AA	Danfoss	China RoHS
Pressure Safety Certificate	LLC CDC EURO-TYSK UA.TR.089.1015.07-22	LLC CDC EURO TYSK - Ukraine	Pressure
Export Control Declaration	Filter Driers 023U and 023Z	Danfoss	

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
