



Inclination position sensor

DST X730

Description

The Danfoss DST X730 high level Inclination sensors are developed to ensure a robust and high-performance solution for applications such as agricultural- and construction machines, as well as material handling equipments. These sensors are typically used in safety applications in order to keep the inclination of a machine, or just a part of it, a safety zone for working people, under control.

Danfoss DST X730 series uses MEMS technology for single and dual axis with measurement ranges up to 360° in both single and redundant versions, with extended resolution and linearity.

All sensors are designed for off-highway applications and resistant to shock and vibrations and with high electromagnetic compatibility and comes with either analogue or CANopen output.

Single and redundant sensor types are available, making the complete portfolio suitable for safety-critical applications.

Features & benefits

- MEMS technology for almost infinite sensor life time
- Single or Redundant ranges up to 360° ($\pm 180^\circ$)
- Output: Analogue or CANopen
- Electrical connector: M12, 5-pin or cable
- IP protection IP67, IPX9K
- Accuracy: $< \pm 0.15\%$ FS $\leq \pm 60^\circ$ dual axis and 180° single axis; 0.3 FS $\pm 85^\circ$ dual axis
- Resolution 0.01°

Ordering

Product code numbers

Type	Output signal	Configurations	Code no.
DST X730	36 V CANopen	1 x M12 5p; Single axis; $\pm 180^\circ$; 36 V	098G3500
	36 V CANopen	2 x M12 5p; Single axis; Redundant; $\pm 180^\circ$; 36 V	098G3501
	36 V CANopen	1 x M12 5p; Dual axis; $\pm 85^\circ$; 36 V	098G3502
	36 V CANopen	2 x M12 5p; Dual axis; Redundant; $\pm 85^\circ$; 36 V	098G3503

Others on request

Ordering code -on request

Electrical connections	
M12 connector output	M
Cable output (specify cable length)	F

Axis type	
Dual axis (XY axis)	O
Single axis (Z axis)	V

Circuit type	
Single	S
Redundant	R

Output 1 Measuring range (Output for single circuit)	
Measuring range (indicate) single axis always 360° dual axis $\pm 10^\circ \pm 15^\circ \pm 20^\circ \pm 30^\circ \pm 45^\circ \pm 60^\circ \pm 85^\circ$	xxx

Output 2 Measuring range (Only for redundant version)	
Measuring range (indicate) single axis always 360° dual axis $\pm 10^\circ \pm 15^\circ \pm 20^\circ \pm 30^\circ \pm 45^\circ \pm 60^\circ \pm 85^\circ$	xxx

Supply voltage	
5 V DC (only for A1 output)	L
10 - 36 V DC (see output signal for right supply voltage)	H

Output type	
0.5 - 4.5 V DC output (available with supply L = ratiometric output and with supply H = 0.5 - 4.5 V output)	A1
0 - 10 V DC output (powered at 11 - 36 V DC)	A2
4 - 20 mA output (powered at 10 - 36 V DC)	A3
CANopen output (powered at 10 - 36 V DC)	C1

Reserved	
Always "0"	0

Certificate	
No certificate attached	0
Linearity curve to be attached	L

Version	
Standard	033

Accessories	
No accessories	X
Magnetic pen (PKIT 312)	Y

Cable length	
100 mm	01
200 mm	02
500 mm	05

Cable length	
1 m	10
2 m	20
Other length on request	-

Example of ordering: DST X730-MVR360360HC10 0033X00

M	M12 connector
V	Single (Z axis)
R	Redundant
360	$\pm 185^\circ$
360	$\pm 185^\circ$
H	+5 V DC
A1	10 – 36 V DC

C1	CANopen
0	Reserved
0	No certificate
033	Standard
X	No accessories
00	Not defined (only cable version)


Note: For a detailed overview of our existing code numbers, please visit the Danfoss Product Store at store.danfoss.com. You can use the filtering options to find the right sensor for your specific needs.

Functions


Zero function

Available for analog single circuit versions in DST X730
XY configuration (dual axis)

M12 version



Cable version



To activate the Autozero function make sure that:

- sensor is powered
- fixing surface is free of dust or grease
- sensor is fixed on the horizontal plane with suitable screws



ATTENTION:

The Autozero function can be defined within a maximum range of $\pm 4.5^\circ$ from the original zero position (factory set).
Hold the **magnetic pen** (accessory to order PKIT312) to the **ZERO POINT** indicated on the product label.
Hold the position for **at least 3-5 seconds** so that the operation is successful.

Magnetic pen



Product details

General data

Performance

Measuring range	$\pm 10^\circ \pm 15^\circ \pm 20^\circ \pm 30^\circ \pm 45^\circ \pm 60^\circ \pm 85^\circ$ (single axis Z / XY dual axis) $360^\circ (\pm 180^\circ)$ (single Z axis)
Accuracy (Factory verification @25°C)	Single axis: $< \pm 0.15\%$ FS Dual axis: $< \pm 0.15\%$ FS in the range $\leq \pm 60^\circ$, $\pm 0.3\%$ FS otherwise
Temperature coefficient @ 0°	Typical $< \pm 0.006^\circ/\text{K}$
Long term repeatability	Single axis: Typical $< \pm 0.5^\circ$ in the range $\pm 180^\circ$ Dual axis: Typical $< \pm 0.5^\circ$ in the range $\leq \pm 60^\circ$, $\pm 2^\circ$ otherwise
Resolution	CANopen output; 0.01° ; 12 bit analog output

Electrical specifications

Electrical connections	M12 connector or cable
Output signal	CANopen, Ratiometric 10-90% of Vs, 0.5 - 4.5 V DC, 0 - 10 V DC or 4 - 20 mA
Supply voltage	CANopen, 0.5 - 4.5 V DC, 4 - 20 mA: 10 - 36 V DC, 0 - 10 V DC : 11 - 36 V DC Ratiometric: 10 - 90% of Vs: 5 V DC
Current consumption	Analogue: < 20 mA / pr. channel (no load) CANopen/J1939: < 15 mA / per channel (no load)
MTTFd [Years]	CANopen: 631 (Single channel) Analogue: 731 (Single channel)


Environmental conditions

Operating temperature range			-40 - 85 °C
EMC	Emission		EN 55011
	Immunity		EN 61236-3-2
Vibration stability	Sinusoidal	20 g, 10 Hz - 2,000 kHz	IEC 60068-2-6
Shock resistance	Impulsive on 3 axes	50 g, 11 ms	IEC 60068-2-27
Enclosure			IP67, IPX9K

Mechanical characteristics

Materials	Enclosure	PBT (Polybutylene terephthalate)
Net weight		0.26 kg (without cable)

Output signals graphs




Load conditions


0.5 - 4.5 V DC output with power 10 - 36 V DC and 0 - 10 V DC output with power 11 - 36 V DC: apply a load resistance > 100 K Ω

Dimensions

M12 version



Cable version




Note: Dimensions are in mm, unless stated otherwise.

Connections

Electrical connections


M12 version



Connections

1	n.c.
2	+ Supply
3	Ground
4	CAN H
5	CAN L

Cable version



Connections

White	+ Supply
Yellow	Ground
Grey	Output X
Blue	Output Y
Pink	n.c.
Green	n.c.
Brown	n.c.

White	+ Supply
Yellow	Ground
Grey	Can H
Blue	Can L
Pink	n.c.
Green	n.c.
Brown	n.c.

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
EU-UK Declaration	Danfoss EU-UK 098R0009.04	Danfoss	UK RoHS
UA Declaration	Danfoss UA 2023-01-10 Regulators PL01 PL04	Danfoss	PED
Pressure Safety Certificate	LLC CDC EURO-TYSK UA.TR.089.1015.05-22	LLC CDC EURO TYSK - Ukraine	Pressure
UA Declaration	Danfoss UA 2024-07-25 cooling sensors	Danfoss	EMC
Export Control Declaration	Pressure & Temperature Sensors	Danfoss	
Export Control Declaration	Refrigerant Leakage Sensor	Danfoss	

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
