



# DST P110 pressure sensor, improved **performance,** **reliability** and **self-diagnostics**

Introducing the DST P110 pressure sensor

A photograph of a large industrial HVAC system, likely a chiller or heat pump, with several large, silver, insulated pipes. A small pressure sensor is mounted on one of the pipes. The system is supported by a metal frame. The background shows a clear sky and some other industrial equipment.

### Application fit:

- Chillers
- Heat pumps
- Data centers
- Commercial refrigeration
- Transport refrigeration
- Variable speed HVAC
- Variable refrigerant flow (VRF)

# Premium MEMS technology at a competitive price

Take advantage of the strong, reliable characteristics of an oil-filled sensing element to best support your application.

The physical properties of silicon provide a superior dynamic range leading to scalable accuracy over temperature and outstanding overpressure capabilities. The DST P110 sensor is built with a robust, stainless steel welded design — eliminating the need for an internal O-ring and reducing the number of potential leak points. The hermetically-sealed design provides excellent media compatibility and making it ready for **today's and future refrigerants and coolants**.



## Product highlights

The DST P110 sensor is:


- Tailored performance. The sensor provides improved accuracy in a lower temperatures range, allowing a more efficient super heat control.
- Rugged and reliable. The DST P110 is protected by a corrosion-resistant stainless-steel housing and is designed to resist extreme vibration, temperature change, and electrical interference.
- Thoroughly tested. Danfoss uses a rigorous “test-to-failure” product development methodology that pushes every aspect of the design past the breaking point. This insight has hardened the DST P110 design and established a knowledge base for faster qualification in OEM applications.
- Forward-looking. The DST P110's onboard diagnostics identify and communicate internal failure modes to the controller. Together with harness fault detection capabilities, P110 saves troubleshooting costs by helping technicians rapidly identify the root cause of a problem.
- Scalable and customizable. The new electronics platform allows many performance specifications to be fine-tuned for application requirements.

# Self-diagnostic features

Increase machine uptime and reduce troubleshooting costs with the self-diagnostic features available with the DST P110 sensor — onboard diagnostics identify and communicate internal failure modes to the controller. Together with harness fault detection features, DST P110 saves troubleshooting costs by helping technicians rapidly identify the root cause of a problem.

## Flexible output and diagnostics

Ratiometric example



The DST P110's output and fault signals can be programmed to fit application requirements:

### Pressure output range

Defines the measuring range of the sensor.

### Output clamp levels

Limit the pressure output signal if the pressure exceeds the normal range.

### Sensor fault signal

Placed in fault signal range above or below the pressure output range. Output at this level signals a sensor fault.

### Harness fault detection

Low leakage current of the sensor allows the controller to recognize harness fault conditions. (requires a pull-down or pull-up resistor at the controller interface).



## Performance specifications

<b>Pressure ranges (absolute and gauge)</b>	0 – 1 bar through 0 – 50 bar (0 – 15 psi through 0 – 725 psi)
<b>Total error band</b>	Optimized for application fit +/- 1% F.S. max
<b>Operating temperature range</b>	-40° to 125°C (-40° to 257°F)
<b>Media temperature range</b>	-40° to 135°C (-40° to 275°F)
<b>Overload pressure</b>	4x fullscale pressure
<b>Burst pressure</b>	300 bar/4351 psi (absolute and sealed gauge)
<b>Endurance</b>	>10 million cycles, 10%-110% F.S.
<b>Response Ttime</b>	<2 ms Programmable filtering available
<b>Wetted materials</b>	304L Stainless Steel 316L Stainless Steel

## Electrical specifications

<b>Output modes</b>	Ratiometric (programmable, ex. 10%-90% Vss) Absolute voltage (programmable, ex. 1-5Vdc) Current (programmable, ex. 4-20mA)
<b>Output limiting (clamping)</b>	Programmable
<b>Over and reverse voltage</b>	Protected
<b>Short circuit</b>	Protected
<b>Miswiring</b>	Protected
<b>Diagnostic fault signal</b>	Programmable
<b>EMC</b>	EN 61000-6-3 EN 61000-6-2
<b>ESD</b>	IEC 6100-4-2 8kV contact, 15kV air

Please contact Danfoss for full specifications and available configurations.

## Environmental specifications


<b>Enclosure</b>	IP67
<b>Mech. vibration, random</b>	IEC 600068-2-64, 16.5 gRms 3 x 2h, 10Hz-2 kHz, at 25°C
<b>Mech. shock</b>	IEC 60068-2-27, Level : 500g/1msec
<b>Free fall</b>	IEC60068-2-32, 3x1m (xyz) on concrete
<b>Media interface materials</b>	Stainless steel, AISI304L / AISI316L



## Application examples


- Chillers
- Heat pumps
- Data centers
- Commercial refrigeration
- Transport refrigeration
- Variable speed HVAC
- Variable refrigerant flow (VRF)

## Dimensions



Shown with Packard Metri-Pack and SAE female flare with depression pin.

Please contact Danfoss for other available configurations.



Pin configurations

A = -Supply    B = +Supply    C = Output

For more information, visit [sensors.danfoss.com](https://sensors.danfoss.com)



# A dedicated partner you can rely on

Danfoss develops new product solutions with both its customers and its extensive application expertise in mind. Years of producing reliable, effective solutions for the refrigeration and cooling market have provided valuable insight that can then be leveraged to work for you.

Danfoss is committed to working with you to find the right solution for your unique application needs.



## System solutions

Danfoss products are designed to provide value on their own and as part of an optimized system.



## Application expertise

Your challenges are also our challenges. We understand your unique needs because we partner with you every step of the way for a wide variety of cooling applications.

Danfoss A/S  
Nordborgvej 81  
6430 Nordborg  
Denmark  
danfoss@danfoss.com  
CVR reg. no. 20165715

© Danfoss 2026

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.