

Data Sheet

EM-PMI375-T200-690V

Electric machine, permanent magnet internal

FEATURES

- Synchronous Reluctance assisted Permanent Magnet (SRPM) technology
- Extremely compact and robust aluminum frame structure
- Highest efficiency throughout the operation range on the market (~96 %)
- Liquid cooled with water-glycol mixture
- Low coolant flow required
- Allowed coolant temperature up to +65°C
- IP65 enclosure class to maximize reliability, IP67 available as option
- Multiple mounting possibilities



GENERATOR SPECIFIC FEATURES

- Standard SAE flange mounting to match the diesel engine connection
- Wide selection of speed ratings allowing the generator to be selected to customer specific applications with various voltage requirements
- Can also be used as starter motor for the ICE

MOTOR SPECIFIC FEATURES

- Extended speed and torque capabilities compared to standard PM motors from Danfoss reluctance assisted permanent magnet motor technology
- Motor structure is designed to be able to produce high starting torque: EM-PMI motor can produce instantly full torque to a non-rotating shaft
- Optimized speed range to meet the most common gear ratios used in heavy mobile machinery

GENERAL

The machine is developed especially for demanding applications. It is smaller, lighter and more efficient than conventional products on the market.

TYPICAL APPLICATIONS

- Generator for diesel-electric/serial hybrid applications
- Traction/propulsion motor
- Generator/Motor for parallel hybrid applications

SPECIFICATIONS

| General electrical properties | |
|-----------------------------------------------------------|---------------------|
| Nominal voltage (line-to-line) | 690 V _{AC} |
| Nominal efficiency | 96 % |
| Pole pair number | 6 |
| Power supply | Inverter fed |
| Minimum inverter switching frequency | 4 kHz |
| Maximum phase-to-phase peak-to-peak voltage without du/dt | 2 kV |
| Maximum voltage rise time without du/dt | 8 kV/μs |

| Basic information | |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Machine type | Synchronous reluctance assisted permanent magnet |
| Frame material | Aluminum |
| Mounting direction | Can be used in all directions, see user guide for details. Greased for life bearings required. |
| Mounting (IEC 60034-7) | IM 3009-B5 (flange horizontal), IM 3019-V1 (flange and D-end down) |
| Standard flange D-end (SAE J617) | SAE 3 transmission housing |
| Standard axle spline D-end | DIN5480 W50x2x24x8f |
| Standard flange N-end (SAE J617) | SAE 4 flywheel housing |
| Standard rotation direction | Clockwise (both directions possible) |
| Bearing type | Standard: 6211-2RS1/C3WT +BHS option: 6211/C3 (with LGHP2 grease) +BIN option: D-end: 6211-2RS1/C3WT N-end: 6211-2RS1/HC5C3WT +BIA option: 6211-2RS1/HC5C3WT +BHS+BIN options: D-end: 6211/C3 (with LGHP2 grease) N-end: 6211/HC5C3WT (with LGHP2 grease) +BHS+BIA options: 6211/HC5C3 (with LGHP2 grease) |
| Protection class | IP65 IP67 available as option +IP67 |
| Duty type (IEC 60034-1) | S1/S9 |
| Machine coating | Dark grey RAL7024 |
| Altitude | Up to 3000 m, see Picture 3 |

| Mechanical | |
|---------------------------------------------------------------------|------------------------------------------------------------------------------|
| Total weight | 98 kg (no options) |
| Moment of inertia | 0.21 kgm ² |
| Torsional stiffness of shaft drive end | 4*10 ^{^5} Nm/rad (from middle of the D-end spline to rotor air gap) |
| Rotating mass | 26.5 kg |
| Maximum static torque range on the shaft, max. 25000 cycles, R=0 (* | 3400 Nm |

| | |
|--------------------------------------------------------------------|---------------------------------|
| Maximum dynamic torque range on the shaft, max. 1e6 cycles, R=0 (* | 2500 Nm |
| Maximum allowed vibratory torque range, 1e9...1e10 cycles (* | 0.3 x nominal torque of machine |
| Maximum deceleration (fault stop) | 6000 rad/s ² |

Dimensions

| | |
|------------------|--------|
| Length (frame) | 278 mm |
| Diameter (frame) | 450 mm |

Cooling

| | |
|-----------------------------------------|----------------------------------------------------------------------------------|
| Cooling liquid | Plain water with appropriate corrosive inhibitor (max. 50 % corrosive inhibitor) |
| Cooling liquid corrosive inhibitor type | Ethylene glycol (Glysantin G48 recommended) |
| Cooling method (IEC 60034-6) | IC 71 W |
| Minimum cooling liquid flow | 20 l/min |
| Coolant circuit capacity | 0.8 l |
| Maximum operating pressure | 3 bar |
| Pressure loss | 0.4 bar with 20 l/min (+25°C coolant) |
| Nominal cooling liquid temperature | +65°C, +40°C with +CL option |
| Minimum cooling liquid temperature | -20°C |
| Maximum cooling liquid temperature | +65°C |

Temperature rating

| | |
|--------------------------------|-------------------------------|
| Insulation class (IEC 60034-1) | H (+180°C) |
| Temperature rise (IEC 60034-1) | +85°C (F) |
| Maximum winding temperature | +150°C |
| Nominal ambient temperature | +65°C / +45°C with +CL option |
| Min. ambient temperature | -40°C |

Vibration & Shock tolerance

| | |
|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Mechanical vibration | <p>5.9 G_{RMS} ISO 16750-3:2003 Test VII – Commercial vehicle, sprung masses – Table 12 Notes: Test duration 8h axis (two axes tested; radial and axial) Total spectral acceleration 5.91 G_{RMS} Test done with EM-PMI375-T800 (with flange mounting)</p> |
| Mechanical shock | <p>50 G ISO 16750-3:2003 4.2.2 Test for devices on rigid points on the body and on the frame Notes: –acceleration: 500 m/s²; –duration: 6 ms; –number of shocks: 10 per test direction Test done with EM-PMI375-T800 (with flange mounting)</p> |

| Connections | |
|-------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Coolant connection | 2 x G3/4 bore (see dimension drawing for details) |
| Cable direction | Standard cable direction towards D-end |
| HV cables | 3 x 70 mm ² max. |
| HV cable glands | Pflitsch blueglobe TRI bg 225ms tri |
| HV cable recommended type | HUBER+SUHNER Radox Elastomer S, screened, single core, automotive cable (FHLR4GC13X) www.hubersuhner.com |
| HV cable lug size | 35-8, 50-8, 70-8 |
| Recommended cable lug | 35 mm ² : Druseidt with narrow flange 03901 50 mm ² : Druseidt with narrow flange 03903 70 mm ² : Druseidt with narrow flange 03906 www.druseidt.de |
| HV connection boxes | 1 x 3 phase box |
| LV connector | 47 pin DEUTSCH HD34-24-47PE for resolver and temperature measurement https://www.te.com |
| LV connector type | DEUTSCH HD34-24-47PE |
| LV connector pin type | Gold plated |
| LV mating connector type | DEUTSCH HD36-24-47SE or DEUTSCH HD36-24-47SE-059 (**) |
| LV mating connector pin type | DEUTSCH 0462-201-1631 DEUTSCH 0462-005-2031 Plug: DEUTSCH 0413-204-2005 (size 20) Plug: DEUTSCH 0413-003-1605 (size 16) |
| LV connector pin configuration | See Table 1 |
| LV connections (+LVB1 option) | Connection box with 3 x M25, 1 x M20 cable glands (reserve/plugged 1 x M16) and terminal block for LV connections. See Table 4 |
| Angle/Speed sensor | Type: Externally excited SIN/COS resolver Pole pair number 6 Input 7 V Frequency 10 kHz Output 2 V +/- 0.2 V Input impedance 110 Ohm +/- 10 % Output impedance 330 Ohm +/- 15 % |
| Anti-condensation heater (+HEAT1 option) | 65 W 230 V _{AC} single phase heater resistor |
| Heater connector (+HEAT1 option) | Hummel art no. 7651 0 51 01 D (combination of housing 7651 0 00 00 0, insert 7084 9 51 10 1 / 7084 9 51 12 1, crimp pins 7010 9 42 01 1) https://www.hummel.com |
| Heater mating connector | Hummel art no. 7550 6 51 02 D (combination of housing 7550 6 00 00 0, insert 7084 9 51 10 2 / 7084 9 51 12 2 and crimp socket 7010 9 42 00 2) |
| Heater connector pin type | Hummel 7010 9 42 01 1 |
| Heater connector pin configuration | See Table 2 |
| Bearing temp. measurement connector type | 4-pin M12 A coded male |
| Bearing temp. measurement mating type | 4-pin M12 A coded female |
| Bearing temp. measurement connector pin configuration | See Table 3 |

(* The values are based on structural analysis, and they are not applicable to any marine class rules or requirements.

(** Connector IP-rating of IP67 is reached only when connector mating part is installed and all unused pin holes are plugged in the connector mating part with the following plugs, depending on the hole size: DEUTSCH 0413-003-1605 (size 16) or DEUTSCH 0413-204-2005 (size 20). For further information, contact the connector manufacturer TE connectivity directly.

| PIN | Description | Option |
|-----|-------------------------------------------------|--------|
| 47 | Temperature 1, PT100 (P), windings | |
| 46 | Temperature 1, PT100 (N), windings | |
| 33 | Temperature 2, PT100 (P), windings | |
| 32 | Temperature 2, PT100 (N), windings | |
| 45 | Temperature 3, PT100 (P), windings | |
| 31 | Temperature 3, PT100 (N), windings | |
| 30 | Temperature 4, PT100 (P), windings | +TEMP4 |
| 29 | Temperature 4, PT100 (N), windings) | +TEMP4 |
| 44 | Temperature 5, PT100 (P), windings | +TEMP4 |
| 43 | Temperature 5, PT100 (N), windings | +TEMP4 |
| 28 | Temperature 6, PT100 (P), windings | +TEMP4 |
| 16 | Temperature 6, PT100 (N), windings | +TEMP4 |
| 35 | Resolver, RES_COS_N, inbuilt non-contacting | |
| 20 | Resolver, RES_COS_P, inbuilt non-contacting | |
| 36 | Resolver, RES_SIN_N, inbuilt non-contacting | |
| 21 | Resolver, RES_SIN_P, inbuilt non-contacting | |
| 22 | Resolver, EXCN, inbuilt non-contacting | |
| 10 | Resolver, EXCP, inbuilt non-contacting | |
| 34 | Resolver, SHIELD/GROUND, inbuilt non-contacting | |


Table 1 Pin configuration of LV-connector

| PIN | Description |
|-----|----------------------------|
| 1 | Phase, 230 V _{AC} |
| 2 | Neutral |
| ⊥ | Ground / protective earth |
| 4 | Reserve |
| 5 | Reserve |

Table 2 Pin configuration of heater with connector

| PIN | Description |
|-----|-------------|
| 1 | PT100 |
| 2 | |
| 3 | PT100_GND |
| 4 | |

Table 3 Pin configuration of bearing temperature sensor connector (one sensor)




Picture 1 LVB1 terminal box

| Rails | PIN | Description | | Option |
|----------|-----|----------------------------------------------|-----------------------------------|--------|
| Rail 1 | 1 | Heater, phase, 230 V _{AC} | | +HEAT1 |
| | 2 | Heater, neutral | | +HEAT1 |
| M4 screw | ⊥ | General shielding, ground / protective earth | | |
| Rail 2 | 3 | Resolver | RES_COS_N, Inbuilt non-contacting | +RES1 |
| | 4 | Resolver | RES_COS_P, Inbuilt non-contacting | +RES1 |
| | 5 | Resolver | RES_SIN_N, Inbuilt non-contacting | +RES1 |
| | 6 | Resolver | RES_SIN_P, Inbuilt non-contacting | +RES1 |
| | 7 | Resolver | EXCN, Inbuilt non-contacting | +RES1 |
| | 8 | Resolver | EXCP, Inbuilt non-contacting | +RES1 |
| | 9 | Not in use | | |
| | 10 | Temperature | PT100 (P), bearing, N-end | +BTMP1 |
| | 11 | Temperature | PT100 (N), bearing, N-end | +BTMP1 |
| Rail 3 | 12 | Temperature 1 | PT100 (P), windings | |
| | 13 | Temperature 1 | PT100 (N), windings | |
| | 14 | Temperature 2 | PT100 (P), windings | |
| | 15 | Temperature 2 | PT100 (N), windings | |
| | 16 | Temperature 3 | PT100 (P), windings | |
| | 17 | Temperature 3 | PT100 (N), windings | |
| | 18 | Temperature 4 | PT100 (P), windings | +TEMP4 |
| | 19 | Temperature 4 | PT100 (N), windings | +TEMP4 |
| | 20 | Temperature 5 | PT100 (P), windings | +TEMP4 |
| | 21 | Temperature 5 | PT100 (N), windings | +TEMP4 |
| | 22 | Temperature 6 | PT100 (P), windings | +TEMP4 |

| | | | | |
|--|----|---------------|---------------------|--------|
| | 23 | Temperature 6 | PT100 (N), windings | +TEMP4 |
| | 24 | Reserve | | |
| | 25 | Reserve | | |
| | 26 | Reserve | | |
| | 27 | Reserve | | |
| | 28 | Reserve | | |
| | 29 | Reserve | | |
| | 30 | Reserve | | |
| | 31 | Reserve | | |
| | 32 | Reserve | | |
| | 33 | Reserve | | |
| | 34 | Reserve | | |
| | 35 | Reserve | | |
| | 36 | Reserve | | |
| | 37 | Reserve | | |


Table 4 Pin configuration of LV connections

PRESSURE LOSS VS COOLANT FLOW



Picture 2 Pressure loss vs coolant flow

ALTITUDE DERATING



Picture 3 Altitude derating

MOTORS (temperature class F, maximum winding temperature +150°C)

| Type | Coolant temperature +65°C | | | Coolant temperature +40°C | | | Coolant temperature +40 / +65°C | | | |
|--------------------------|---------------------------|------------------|------------------|---------------------------|------------------|------------------|---------------------------------|------------------|------------------------|----------------------------------------------|
| | Cont. Torque [Nm] | Cont. Power [kW] | Nom. Current [A] | Cont. Torque [Nm] | Cont. Power [kW] | Nom. Current [A] | Nom. speed [rpm] | Max. speed [rpm] | Peak torque SINGLE (a) | Volt/ speed ratio [V _{AC} /rpm] (b) |
| EM-PMI375-T200-690V-2700 | 150 | 42 | 42 | 157 | 44 | 44 | 2700 | 3800 | 497 | 0.282 |

(a Peak torque achieved with one 210A inverter
(b Back EMF for cold (+20°C))

The maximum allowed peak torque duration at stator winding starting temperature +90°C is 1 minute. The given values indicate typical duration and are not verified. In case more accurate values are required, cyclic dimensions are needed.

PRODUCT CODE AND OPTIONS

Use product code including all needed options for ordering. Standard options are not given with the code as they are selected by default if a non-standard option is not selected. Standard options are indicated by a star (*).

| Product code | Description |
|-----------------------------------|------------------------------------------------------------|
| EM-PMI375-T200-690V-2700 | 2700 rpm unit with standard options |
| EM-PMI375-T200-690V-2700+BIN+RES1 | 2700 rpm unit with insulated bearing in N-end and resolver |

Table 5 Product code examples

| Variant | Code | Description | Additional information |
|--------------------------------------------|-------|---------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Low voltage connections | * | Low voltage connections done with connector | DEUTSCH HD34-24-47PE connector for LV connections |
| | +LVB1 | Low voltage connections done with connection box and terminal strip | Connection box with 3 x M25, 1 x M20 cable glands (reserve/plugged 1 x M16) and terminal block for LV connections. |
| N-end attachment | * | Flange | SAE 4 flywheel housing |
| | +NE2 | Male shaft + Flange | DIN5480 W50x2x24x8f + SAE 4 flywheel housing |
| Bearing lubrication and mounting direction | * | Greased for life | Deep groove ball bearing, contact seal on both sides, any mounting direction (see user guide for details) |
| | +BHS | Grease lubricated | Deep groove ball bearing, open design, horizontal mounting direction (see user guide for details) |
| Bearing insulation | * | Non-insulated bearings | Non-insulated bearings |
| | +BIN | Insulated bearing in N-end | Insulated bearing in N-end |
| | +BIA | Insulated bearing in both ends | Insulated bearing in both ends |
| Shaft grounding | * | None | |
| | +SG1 | D-end shaft grounding | Inbuilt grounding ring |
| Protection class | * | Standard protection class | IP65 protection class |
| | +IP67 | IP67 protection class | IP67 protection class, not available with +BHS option |
| Cable direction | * | Cable direction fixed | Cable direction towards D-end |
| | +CNE | Cable direction towards N-end | Cable direction towards N-end |
| Rotation sensor | * | None | No resolver |
| | +RES1 | Resolver | Inbuilt non-contacting resolver, 6-pole pair |
| Side mounting | * | None | No side mounting holes available. In case side mounting holes are present, they are plugged by default. |
| | +SM1 | Side mounting | 12 x side mounting threaded holes M10x1.5. Plugged by default with M10x10, DIN 913, (ISO 4026), set screw |

| | | | |
|----------------------------------|--------|------------------------------------|------------------------------------------------------------------|
| Winding temperature sensors (**) | * | Temperature surveillance | 3 x PT100 (two wire) in windings |
| | +TEMP4 | Redundant temperature surveillance | 6 x PT100 (two wire) in windings |
| Bearing temperature sensors | * | None | |
| | +BTMP1 | PT100 in bearings | Plug-in connector |
| Anti-condensation heaters | * | None | |
| | +HEAT1 | One anti-condensation heater | 230 V _{AC} / 65 W (see user guide for more information) |
| Marine classification | * | No marine classification | |
| | +CL1 | | ABS American Bureau of Shipping |
| | +CL2 | | BV Bureau Veritas |
| | +CL3 | | DNV |
| | +CL4 | | LR Lloyd's Register |
| | +CL5 | | RINA |
| | +CL6 | | CCS China Classification Society |

(* Standard option)

(** Winding temperature sensors are for stator winding. The selection of high voltage connections does not have an influence on the quantity of PT100 elements.

Table 6 Option list

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.
