



Instructions

Service kits




M1	CuSn5ZnPb (Rg5)
M2	EN-GJS-400-18-LT (GGG 40.3)




2	PN 25	AVPBT	M1
3	PN 25	AVPBT	M2
5	PN 25	AVPQT	M1
6	PN 25	AVPQT	M2


1




2




3




5




4




1




2





3




4




5




7




6




1




2




3




5




4




1




2




3




4



5



7



6

