

Data sheet

Anti-Drip Spray Nozzles Type 4023

Application

Many nozzles are satisfactory for spraying liquids, but for a positive cut-off ask for the Hago type 4023 nozzle. Our exclusive design produces a precisely controlled flow rate and spray angle and includes a liquid cut-off near the orifice. Fluid cut-off near the orifice can be very important in situations where excessive after drip can damage or destroy things located beneath the nozzle.

Chemicals, insecticides, and even plain water, if allowed to drip, can foul the environment or injure livestock, seedlings and industrial materials.

With the type 4023 anti-drip nozzles, operators can achieve fluid cut-off near the orifice while maintaining pressure within the nozzle supply system.

The type 4023 nozzle emits a finely atomized spray mist suitable for nearly all humidifying, light wetting and evaporative cooling application. This nozzle has become a nozzle of choice for the insect spray system industry.

Application and Features

- Insect control
- Odor control chemicals
- Green houses
- Agriculture, farms, livestock, barns
- Environmentally hazardous chemicals
- Reduces undesirable nozzle after-drip
- Field proven performance for over 40 years
- Accurate, flow rate and spray angle
- Produces a finely atomized mist

Availability

- Insect control
- Standard flow rate: 0.75 GPH at 160 psi (11bar), water.
- Spray angle: 70 Degrees at 160 psi, water.
- Spray pattern: Semi solid cone.

Accessories

Standard adapters:

- Brass 1/8" or 1/4"

Identification

The nozzles are marked with the following information:

**Stamped on the flats**

4023	Anti-Drip spray nozzle
HP	High Pressure
NSB	Nickel Silver tip and Brass disc
12345	Batch code

Data sheet**Anti-Drip Spray Nozzles Type 4023****Technical Data****Material and construction**

Our nozzle tip in nickel silver tip and brass disc is our most popular and corrosion resistant offering for water applications. Nickel Silver is a trade name for a non-magnetic copper nickel alloy. This also includes a stainless steel spring.

Performance

Minimum recommended operation pressure is 160 psi (11 bar).

The nozzle is rated 0,75 gph (water) at 160 psi (11bar) where it delivers a semi solid spray pattern.

Cut off valve

The cut off valve has a closing pressure between 40-70 psi (~3 to 5 bar)

Filtration

30-40 µm sintered bronze filter

Recommended tightening torque




130 to 180 in-lbs (15 to 20 Nm).

Maximum tightening torque

180 in-lbs (20 Nm).

Design

A: Tip
B: Disc
C: Cut-off valve
D: Sintered filter

**Spray angle and pattern****Dimensions****Program**

Standard flow rate	Semi Solid	Remarks
Usgal/h	70°	-
0.75	030L4501	-
0.75	030L4502	With O-ring

Danfoss A/S

Heating Segment • heating.danfoss.com • +45 7488 2222 • E-Mail: heating@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and all Danfoss logotypes are trademarks of Danfoss A/S. All rights reserved.