

# Need flexible VFDs to create more competitive systems?

## Highlights

- > Modular and configurable variable frequency drive (VFD)
- > STO and SIL3 as standard
- > Functional safety by fieldbus: PROFIsafe
- > Scalable control platform
- > Powerful hardware-based security including end-to-end encrypted data transfer
- > Connectivity with multiple fieldbuses without changing the hardware
- > Industrial IoT-ready with secure OPC UA
- > High-torque machine performance
- > Superior motor control
- > Ultra compact

The iC7 series of intelligent drives delivers high torque performance in a compact footprint. Frequency converters in the iC7 series are optimized for wall-mounted, cabinet-mounted, or free-standing installation.

### Supply voltage and power range

3 x 380-500 V AC  
0.37-710 kW



Feature	Benefit
Compact side-by-side mounting	Save space and reduce installation costs
Isolated cooling channel minimizes required installation space	Reduce space requirement and air-conditioning load
Integrated options such as functional extensions, common-mode filters, fuses and disconnects mean no extra external devices are required	Save cost and time in installation
Installer-friendly design includes pluggable control terminals, pluggable power terminals, and replaceable fans	Save cost and time in installation and service
Robust by design, high uptime and quality	Reliable in heavy-duty service
Modular concept	Maximum design flexibility
Synchronization and positioning integrated into the Motion application	Easy to enable using license key
OPC UA	Secure communication and easy integration and asset management across your installed base
Easy to use and powerful logic blocks and states	Unprecedented flexibility beyond parametrization
Compliance with IEC 61800-5-1 Edition 3	Future-ready safety compliance supporting upcoming CE requirements
Integrated ATEX option for Ex d and Ex de motors	The drive provides thermal protection to motors installed in an explosive environment, without external devices
Certified industrial cybersecurity (IEC 62443-4-2 SL2)	Best-in-class security and easier system certification
PROFINET S2 controller redundancy built into the drive	Increased uptime with seamless controller failover and no additional hardware

## Key specifications: Frequency converters

Input	
Voltage rating	380-500 V AC, -15%/+10%
Supply frequency	50/60 Hz
Switching on input	1-2 times pr. minute
Grid type	TN, TT, IT, Delta
Output	
Output frequency	0-590 Hz <sup>1)</sup>
Overload capacity	110% and 150/160%
Protection ratings	
Frames Fx: IP20 – UL Open Type, FKxx: IP21 – UL Type 1, FBxx: IP54 – UL Type 12	
Environmental conditions	
Rated temperature	-30 to 50 °C (-22 to 122 °F) <sup>2)</sup>
Nominal temperature 24 hours	-30 to 45 °C (-22 to 113 °F) <sup>2)</sup>
Maximum temperature with derating	60 °C (140 °F)
Rated altitude	1000 m (3280 feet)
Maximum altitude	4400 m (14400 feet) with derating
Relative humidity	3K22, maximum 95% non-condensing
Particles (IEC 60721-3-3:2019)	Solid particles (nonconductive particles/dust) 3S6
Chemically active substances (IEC 60721-3-3:2019, ISO 9223:2012)	– C3 (P1) – Medium corrosivity – Non coated (3C2) <sup>3)</sup> – C4 (P2) – High corrosivity (3C3) <sup>3)</sup> – Coated in IP54/IP55/UL Type 12 enclosure or for IP20/UL Open Type and IP21/UL Type 1 following installation guidance.
Shock & vibration (IEC 60721-3-3:2019)	3M12

Functional Safety I/O	
STO and SS1-t	Dual-channel, with galvanic isolation
STO and SS1-t feedback	Single channel, with galvanic isolation
External supply	
Rating	24 V/2 A
Basic I/O	
Digital inputs	4+2 <sup>4)</sup>
– Logic	NPN/PNP selectable – 0/24 V
– Pulse/Encoder input	0-110 kHz
Digital outputs	2 <sup>3)</sup>
– Logic	NPN/PNP selectable – 0/24 V
– Pulse output	0-100 kHz
Analog inputs	2
– Voltage mode	0-10 V or ±10 V, scalable
– Current mode	0/4-20 mA
Analog output	0/4-20 mA
Relay output	2
– Function	NO/NC
– Rating	250 V AC 2 A, 24 V DC 2 A
Analog output	0/4-20 mA

<sup>1)</sup> Higher output frequencies are possible. Contact Danfoss for advice.

<sup>2)</sup> Frames Fx09-Fx12: For low overload conditions, the maximum permissible ambient air temperatures without derating are 40 °C (104 °F) average over 24 hours duration; and 45 °C (113 °F) for 1 hour duration, respectively.


<sup>3)</sup> The environments used as reference for the design criteria are described in standard IEC 60721-3-3:2019, unless otherwise specified.

For references based on IEC/EN 61800-2, see the example below.

Example  
“C3 (P1) – Medium corrosivity – Non coated” refers to IEC 60721-3-3:2019  
“3C2” refers to the older IEC 60721-3-3:2019

<sup>4)</sup> 2 of the inputs can be reconfigured to outputs

EMC category (model code)	Frame	EN/IEC 61800-3 compliance class					
		Conducted emission			Radiated emission		
		C1	C2	C3	C1	C2	C3
		<b>Cable length [m]</b>					
F1 – Combined C1 and C2 filter	<b>Fx02–Fx08</b>	50	150	150	No	Yes	Yes
F2 – C2 filter	<b>Fx02–Fx08</b>	–	150	150	No	Yes	Yes
	<b>Fx09–Fx12</b>	–	150	150	No	Yes	Yes
F3 – C3 filter	<b>Fx02–Fx05</b>	–	–	250	No	No	Yes
	<b>Fx06–Fx08</b>	–	–	300	No	No	Yes
	<b>Fx09–Fx12</b>	–	–	150	No	No	Yes



## Dimensions and weight

Protection rating		IP20		IP20		IP20	IP21	IP55	IP20	IP21	IP55	IP20	IP21	IP55
Frame		FA02a	FA03a	FA04a	FA05a	FA06	FK06	FB06	FA07	FK07	FB07	FA08	FK08	FB08
[mm]	Width	90	114	130	165	200	209	216	230	239	246	255	267	274
	Height	270	270	399	399	555	671	672	600	770	771	743	980	982
	Depth	221	221	262	269	294	303	303	308	327	327	368	367	367
[kg]	Weight	4.7	5.7	11.6	14.1	26	28	29	35	38	38	55	62	62
[in]	Width	3.5	4.5	5.1	6.5	7.9	8.2	8.5	9.1	9.4	9.6	10.0	10.5	10.8
	Height	10.6	10.6	15.7	15.7	21.9	26.4	26.5	23.6	30.3	30.4	29.3	38.6	38.7
	Depth	8.7	8.7	10.3	10.6	11.6	11.9	11.9	12.1	12.9	12.9	14.0	14.4	14.4
[lb]	Weight	10.4	12.6	25.6	31.1	57	61	64	77	84	84	121	137	137

Frames FA02b to FA05b: Add 26 mm (1 in) to depth.

Outer dimensions include mounting flange, without EMC shield plates.

Weight is maximum weight.

Protection rating		IP20	IP21/IP54	IP21/IP54	IP20	IP21/IP54	IP21/IP54	IP20	IP21/IP54	IP20	IP21/IP54
Frame		FA09	FK09a/ FB09a	FK09c/ FB09c	FA10	FK10a/ FB10a	FK10c/ FB10c	FA11	FK11/FB11	FA12	FK12/FB12
[mm]	Width	250	327	327	350	422	436	508	602	604	698
	Height	889	999	1423	1096	1230	1779	1578	2043	1578	2043
	Depth	370	378	378	370	378	378	482	510	482	510
[kg]	Weight	81	89	107	127	139	174	225	244	298	327
[in]	Width	9.8	12.9	12.9	13.8	16.6	17.2	20	23.7	23.9	27.5
	Height	35	39.3	56	43.1	48.4	77.8	62.1	80.4	62.1	80.4
	Depth	14.6	14.9	14.9	14.6	14.9	14.9	19	20.1	19	20.1
[lb]	Weight	179	196	236	280	306	384	496	538	654	721

Weight is maximum weight.



## Your ambition. Our drive. Meet iC7 series iC7-Automation | iC7-Marine | iC7-Hybrid | iC7-HVACR | iC7-Aqua

Imagine versatile and highly secure motor control and power conversion. The iC7 series puts this capability securely in your hands. Intensely powerful and compact variable frequency drives and converters built to optimize a vast range of systems, while giving you the flexibility to distribute intelligence the way you want. Paving the way for new ambitions, where intelligent, efficient, and connected systems are the new reality.

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

**Danfoss Drives A/S**  
Ulsnaes 1  
6300 Graasten  
Denmark  
CVR reg. no. 19883876

© Danfoss 2026.05