


Operating Guide


VRB2, VRB 3, VRG 2, VRG 3 DN 15-50




MAINTENANCE
FREE




VRB 2, VRG 2 (DN 15-50)



VRB 3, VRG 3 (DN 15-50)





AMV(E) 435




AMV(E) 25 (SU/SD), 35 +
adapter **065Z0311**



AMV(E) 438 SU



IP 54
AMV(E) 438 SU
AMV(E) 25 (SU/SD), 35



IP 54
AMV(E) 435



MADE IN SLOVENIA	
Code:	Name:
DN:	Kvs: PT 24
PN:	T: 2...130°C
Date:	


VRB 2, VRB 3, VRG 2, VRG 3



MADE IN SLOVENIA		
Code: _____	Name: _____	
DN: _____	Kvs: _____	PT 24
PN: _____	T: 2...130°C	
Date: _____		







VRB 2, VRB 3
CuSn5ZnPb (Rg5)

P_{max} (bar)



VRG 2, VRG 3
EN-GJL-250 (GG-25)




P_{max} (bar)



Stem heater 065Z0315




DN	Actuators
15-50	AMV(E) 435
	AMV(E) 438 SU
	AMV(E) 25 (SU/SD) + adapter
	AMV(E) 35 + adapter

VRB 2, VRB 3, VRG 2, VRG 3



Type	DN	Rp ¹⁾	G ²⁾	L	L ₁	H	H ₁	H ₂
VRB 2 VRG 2	15	1/2	1	80	128	25	191	216
	20	3/4	1 1/4	80	128	29	194	218
	25	1	1 1/2	95	151	29	197	222
	32	1 1/4	2	112	178	35	202	226
	40	1 1/2	2 1/4	132	201	43	213	237
	50	2	2 3/4	160	234	47	217	242

¹⁾ Rp EN 10226-1
²⁾ G DIN ISO 228/01



Type	DN	Rp ¹⁾	G ²⁾	L	L ₁	H	H ₁	H ₂	H ₃
VRB 3 VRG 3	15	1/2	1	80	128	40	191	216	64
	20	3/4	1 1/4	80	128	45	194	218	69
	25	1	1 1/2	95	151	50	197	222	78
	32	1 1/4	2	112	178	58	202	226	91
	40	1 1/2	2 1/4	132	201	75	230	255	110
	50	2	2 3/4	160	234	83	243	268	120

¹⁾ Rp EN 10226-1
²⁾ G DIN ISO 228/01



VRB 2, VRB 3, VRG 2, VRG 3

Danfoss A/S

Climate Solutions • climatesolutions.danfoss.com • +45 7488 2222 • E-Mail: climatesolutions@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.