



New mobility experience with BD-Micro Perfect performance/dimension ratio

Fridge and cooling box using BD1.4F-Micro free up space for maximum storage and compact unit in car, bus, van, boat... Cool beverages on demand make moving so much more of an experience...

μ -micro

less is more

BD 1.4F: Reduced weight and size compared to previous solutions.

45%

less weight

for the compressor that fits in 10 to 15l fridge or portable cooling box





BD1.4F Micro - small but powerful

Lose excess weight and use the extra space on what really matters. The new BD Micro from Danfoss is 60% smaller than previous models and weighs in at only 2.5 kilos. Perfect for 10-15 litre in-car/van/boat cabinets or portable boxes that need to fit into tight spaces without compromising storage space. Specially designed for maximum efficiency and reliability this tiny powerhouse of a compressor makes it easier than ever to provide class-leading mobile fridges. Variable speed function enables to increase the system COP. Low energy consumption

is good for car/boat/van batteries – and for the environment. The optimized, low-noise motor ensures outstanding performance when you want to provide that extra degree of luxury on the move.

Electronic thermostat provides an accurate temperature while failure detection allows a fast fault diagnosis. Computer interface makes it easier for customization.

Cool beverages on demand make moving so much more of an experience.

Features

- Low weight. Only 2.5 kg
- Small dimensions. Increased net volume
- Transport stable
- Fan failure detection
- Low acoustic noise level < 36dB(A)
- Meets EMI requirements for harsh environments

Functions

- Variable speed. Possible to adapt speed to the application and thereby get increased system COP.
- Electronic thermostat. Easy to set and 100% repeatability
- ECO mode thermostat. Energy saving and optimized operation.
- Fan speed control. Energy saving and noise reduction
- Computer/customers interface (1-wire Modbus). Customize and optimize operation
- Alarm log read out. Fast fault diagnosis

Technical data


General	BD1.4F
Code number (without electronic unit)	109Z0200
Electronic unit	101N2100

Application	
Application	LBP/MBP
Evaporating temperature °C	-25 to +5
Voltage/max. voltage V DC	9 - 34
Speed range	2000 - 4000 rpm

Performance data (EN12900/CECOMAF • 3,000 rpm)					
Evaporating temperature °C		-25	-10	-5	0
Cooling capacity W		14.3	50.0	66.4	85.5
Power consumption W		26.1	40.0	45.2	50.4
Current consumption A		1.98	3.03	3.42	3.82
COP W/W		0.55	1.25	1.47	1.70

Performance data (ASHRAE • 3,000 rpm)					
Evaporating temperature °C		-23.3	-10	-6.7	0
Cooling capacity W		22.1	62.3	75.3	106
Power consumption W		27.5	39.9	43.3	50.3
Current consumption A		2.08	3.03	3.28	3.81
COP W/W		0.80	1.56	1.74	3.12

Dimensions		
Height mm		96
Width mm		110
Length mm		175



Danfoss A/S • Nordborgvej 81 • 6430 Nordborg • Denmark • Phone: +45 7488 2222 • compressors.danfoss.com
 Products presented in current brochure are manufactured by Secop GMBH, formerly Danfoss Household Compressors. They are available through Danfoss sales network.

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed.

All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved