



H62L-C Heat pump Condenser For increased heat pump business

Innovative | Optimised | Low hold-up volume | High heat transfer | Compact | Rapid delivery

Save \$70

Per heat exchanger


On refrigerant because the H62L-C's low hold-up volume.

40%

Reduction refrigerant

Charge compared to traditional BPHE. This new evaporator is the ideal solution to help you meet the world's climate and energy aspirations.

H62L-C



INTRODUCTION The H62L-C is a condenser optimised for R410A for use in high-efficiency heat pumps with capacities of 4-40 kW (13-136 kBTU/hr). The heat exchanger features innovative Micro Plate technology that improves heat transfer and reduces the amount of material used. To meet demands for higher COPs in heat pumps, the H62L-C is designed to work efficiently with close temperature approaches. The H62L-C is approved to 48 bar (696 psi) to cope with high water temperature applications such as the renovation market. The design has been verified with regards to the defrost operation cycle. The low hold-up volume reduces the refrigerant charge and offers valuable savings.

- KEY FEATURES**
- Minimal hold up volume: Less refrigerant charge
 - High heat transfer: For a more efficient heat pump
 - Smaller footprint: Enabling more compact heat pumps
 - Reduced CO₂ footprint: Environmentally friendly with high heat transfer and minimal refrigerant charge.

TECHNICAL DATA
n = NUMBER OF PLATES

Min. working temperature: -196 °C (-320 °F)
 Max. working temperature: 200 °C (390 °F)
 Max. working pressure: 48bar (696psi) for PED, 45bar (650psi) for UL
 Hold up volume (l): Q1-Q2/ Q3-Q4 (l): $0.066 \times n / 2$ / $0.066 \times (n-2) / 2$
 (ft³): Q1-Q2/ Q3-Q4 $0.002 \times n / 2$ / $0.002 \times (n-2) / 2$
 Weight: 3.35 kg + $0.145 \times n$ (7.40lb + $0.32 \times n$)

STANDARD MATERIALS

Cover plates: AISI 304L
 Connections: AISI 304L
 Plates: AISI 316L
 Brazing filler: Pure copper
 Other material combinations are available on request. Please contact your Danfoss sales representative for more information.

STANDARD CONNECTIONS

The standard connections below are optimised for this product in condenser duties in heat pump systems. For other connections, please contact your Danfoss representative.

Q3 (Refrigerant outlet): soldering 1/4" or 3/8" or 5/8"
 Q4 (Refrigerant inlet): soldering 1/2" or 7/8"
 Q1-Q2 (Water side): External threaded 1 1/4"



THIRD-PARTY APPROVALS

Europe: Pressure Equipment Directive (PED). America: Underwriters Laboratory Inc (UL). The third party approvals stated are standard for all our products. For details of other existing approvals or to discuss how we can meet your local needs, please contact your Danfoss representative.

ACCESSORIES – STUD BOLTS

Stud bolts on front and/or back plates for mounting support are available upon request. Please contact your Danfoss sales representative for further information.

ACCESSIBILITY

We will help you set up a logistics solution that will meet your needs.

CORRESPONDING CONDENSERS

A corresponding MPHE for evaporator duties (H62L-E) is also available, fully tested and ready for heat pump applications

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequent changes being necessary in specifications already agreed. All trademarks in this material are the property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.