





Installation Guide

AHQM, DN 15-32





max. t: 120 °C
min. t: 2 °C

max. PN: 16 bar



max. P_{test} : 24 bar

$P_{\text{test}} = 1.5 \times \text{PN}$













1



2










3












Installation Guide AHQM, DN 15-32


DN	L (mm)
15	69
20	74
25	79
32	104



AMV(E) 10, 13




Installation Guide AHQM, DN 15-32




DN		15	20	25	32
SW		32 (G ¾A)	41 (G 1A)	50 (G 1¼A)	63 (G 1¾A)
d		21	26	33	42
R ¹⁾		½	¾	1	1 ¼
L		65	82	104	130
L1 ²⁾		130	150	160	-
L2		131	144	160	177
L3	mm	139	154	159	184
H		24	31	39	49
H1		57	59	72	84
D (ISO 228/1)		G ¾ A	G 1 A	G 1¼ A	G 1¾ A
k		65	75	85	-
d ₂		14	14	14	-
n		4	4	4	-
Valve weight	kg	0.51	0.67	1.47	2.23

¹⁾ EN 10226-1

²⁾ EN 1092-2




AMV(E) 10 + AHQM



AMV(E) 13 + AHQM

DN		15	20	25	32
L*	AMV(E) 10	137	137	153	172
L*	AMV(E) 13	147	147	164	183
L**	AMV(E) 10	178	186	204	224
L**	AMV(E) 13	188	196	214	234
H*	AMV(E) 10	195	201	223	245
H*	AMV(E) 13	210	216	238	260
H**	AMV(E) 10	174	184	202	222
H**	AMV(E) 13	180	190	208	228



AMV(E) 130(H)/140(H) + AHQM

DN		15	20	25	32
L*		118	125	141	160
L**		148	156	174	194
H*		168	178	196	216
H**		152	162	180	200