

Data Sheet

PLUS+1® Mobile Machine Displays

DP211 Series



Danfoss DP211 Series Displays are elements of the PLUS+1® family of mobile machine management products.

The DP211 Series provide high quality, cost effective performance solutions to fit the needs of today's mobile machines.

The DP211 Series features a USB mini-B connection at the front of the display. This port allows full access to all devices on the machine CAN network via the PLUS+1® GUIDE Service Tool.

Large function-programmable buttons provide tactile feedback. The high resolution display is viewable in a wide range of lighting conditions. Backlight and contrast settings are adjustable.

The DP211 Series feature robust mechanical, electrical and ingress protection specifications that meet the demands of mobile machine operation.



Features

Model dependent


- 3.8" high resolution grayscale LCD display
- 4 programmable soft keys
- 2 red, 2 green, 2 amber software controlled LEDs
- 2 CAN 2.0B ports
- 1 fixed-range analog input
- 2 digital/analog/frequency/current/rheostat inputs
- 1 (0.5A) digital output
- Real time clock
- USB 2.0 port with mini-B connector
- PLUS+1® GUIDE programmable
- J1939 engine monitor software package (requires application key)
- Data logging capability
- Rugged IP 54 rated housing
- Integrated DEUTSCH connector

- Extended temperature performance range
- CE and E marked
- Mounting hardware and panel seal gasket included

Comprehensive technical literature is online at www.danfoss.com

Dimensions

mm [in]



P200120


Specifications

Processor	ARM 7 core, 16/32 bit, 72 MHz
RAM	64 KB on-chip, 8 MB on board
FRAM	8 KB
Supply voltage	9 to 63 V dc/6.5 Watts
Connector	DEUTSCH DTM-12
Type	LCD with 32 grayscale levels
Resolution	240 × 160 pixels
Viewable area	80 mm × 55 mm [3.15 × 2.16]
IP Rating	IP 54*
Operation temperature	−40° C to +70° C [−40° F to +158° F]
Storage temperature	−40° C to +85° C [−40° F to +176° F]
Weight	250 g [0.5 lb]
Vibration/shock	5 g / 50 g
EMC/ESD	100 V/m / 15 kV
Digital output (0.5A)	1

* USB in front display carries a full IP54 rating only if the USB mating connector or seal plug cover is in place.

This display series is recommended for in-cab installation only.


Pin assignments



P200 129

USB mini-B pin connector

1	VBUS
2	D-
3	D+
4	NC
5	GND



kwa1449086169773

Use care when wiring mating connector.
Diagram shows device pins.

DEUTSCH 12-pin connector

1	Power ground-
2	Power supply+
3	CAN 0 High
4	CAN 0 Low
5	AIN/CAN Shield
6	N/A
7	N/A
8	CAN 1 High
9	CAN 1 Low
10	DIN/AIN/FREQ IN/CURRENT IN, RHEOSTAT
11	DIN/AIN/FREQ IN/CURRENT IN, RHEOSTAT
12	DOUT (0.5A)

Model features

A	B	C	D	E	F	Part number
DP211	04	01	02	04	01	11134226
	04	01	03	04	01	11134227

A: Model name

DP211	PLUS+1 [®] Mobile Machine Displays
--------------	---

B: Input/output options

04	2 CAN, 2 DIN/AIN/Freqin/Rheo/4-20mA In, 1 AIN/CAN Shield
-----------	--

C: Real time clock

01	RTC
-----------	-----

D: Flash memory/application key

02	2 MB without Application Key
03	2 MB with Application Key

E: Application log (vault memory)

04	2 MB
-----------	------

F: USB port type

01	USB device
-----------	------------

Related product	Part number
DEUTSCH Mating Connector Bag Assembly (16-20 AWG)	10102025
DEUTSCH Mating Connector Bag Assembly (20-34 AWG)	10100944
DP211 Mounting Hardware Kit	10107264
PLUS+1 [®] GUIDE Single User License	10101000
DP211 Panel Seal Replacement Gasket	11053020

