

Data sheet

Electronic Ignition Units EBI4 C Series


Application



The EBI4 C unit series is specially designed for applications where constant ignition is required.


EBI4 CM is a 2-pole version with secondary mid-point grounded. EBI4 C1P is a 1-pole version for ignition between 1 electrode and frame.

Applications and Features

- 1- or 2-pole ignition
- Low power consumption due to high efficiency (new technology)
- Earth connection through the primary cable
- Same dimensions and flexible mounting as the well-known EBI series
-  marking in accordance with the directives: EMC, LVD, RoHS


EBI4 CM

- Oil/gas burners requiring constant ignition
- 2-pole ignition
- Secondary mid-point connected to earth/frame
- 100% ED at 35°C/70% ED at 60°C
- Top or front connection for secondary cables
- 230 V



EBI4 C1P

- Gas burners a.o. application requiring constant ignition
- 1-pole ignition between 1 electrode and frame
- 100% ED at 35°C/70% ED at 60°C
- Top or front connection for secondary cables
- 230 V



Data sheet

Electronic Ignition Units EBI4 C Series


Technical data

Type	EBI4 CM	EBI4 C1P
Mains connection	230 V - 0.25 A - 50/60 Hz - 60 VA	
Working range	187-255 V	
Main fuse	10 A	
ED % in 3 min.	100% at 35°C/70% at 60°C	
Secondary connection* Short circuit current (rms) Frequency	2 x 7.5 kV 30 mA (rms) 25 kHz	12 kV 30 mA (rms) 25 kHz
Ambient temperature	-10 to +60°C	
Storage temperature	-25 to +85°C	
Enclosure	IP 40	
Primary connection	3 x 0.5 mm ² cable with special plug 3 x 0.75 mm ² cable with standard AMP connection	
Secondary connections	2 x Ø4 mm plugs	1 x Ø4 mm plugs
Earthing	Through the primary cable	
Distance between electrodes	Recommended 2.5 mm to 5 mm	
Weight	300 g	

* Avoid use of divergent electrodes due to risk of electrical cable break down and too high ignition voltage.

Dimensions and connections

EBI4 CM EBI4 C1P	EBI4 CM EBI4 C1P	a: Left terminal b: Right terminal c: Earth connection
a+b+c	b+c	



Additional documentation on burner components is available on <http://heating.danfoss.com/>

Danfoss A/S

Heating Segment • heating.danfoss.com • +45 7488 2222 • E-Mail: heating@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and all Danfoss logotypes are trademarks of Danfoss A/S. All rights reserved.