

Data sheet

# Micro plate heat exchanger (MPHE): XB05

Description



Micro Plate Heat Exchangers - a revolutionary technology from Danfoss. Characterized by their unique plate pattern, MPHEs enable heat to be transferred more effectively than any previous model of heat exchangers.

**Benefits:**

- Energy and cost savings
- Better heat transfer
- Lower pressure loss
- More flexible design
- Longer life time

more on:  
[MPHE.danfoss.com](http://MPHE.danfoss.com)

XB05 is heat exchanger, designed and configured for District Heating, District Cooling and other Heating applications.

**Approval:**  
Pressure Equipment Directive (PED).

Ordering

1-pass heat exchanger **XB05M Cu**

Picture	No. of plates, n	Connection	Code No.
	10	Thread G 3/4	004B3556
	16		004B3557
	20		004B3558
	26		004B3559
	30		004B3560
	36		004B3561
	40		004B3562
	50		004B3563
	60		004B3564
	70		004B3565

Accessories-**Tailpieces**

Picture	Description	Connection	Code No. <sup>1)</sup>
	Solder tailpieces	G 3/4 /15 mm	004B2945
		G 3/4 /18 mm	004B2946
	Weld-on tailpieces	G 3/4 /DN 20	004B2944
	Threaded tailpieces	G 3/4 /G 3/4	004B2947
		G 3/4 /G 1	004B2953

<sup>1)</sup> One set contains 2 tailpieces with union nuts and gaskets

1-pass heat exchanger **XB05X Cu**

Picture	No. of plates, n	Connection	Code No.
	10	Thread G 3/4	079G1231
	16		079G1232
	20		079G1233
	26		079G1234
	30		079G1235
	36		079G1236
	40		079G1237
	50		079G1238
	60		079G1239
	70		079G1240

1-pass heat exchanger **XB05X StS**

Picture	No. of plates, n	Connection	Code No.
	10	Thread G 3/4	079G1242
	16		079G1243
	20		079G1244
	26		079G1245
	30		079G1246
	36		079G1247
	40		079G1248
	50		079G1249
	60		079G1250
	70		079G1251

Data sheet

**XB05**

Technical data

		XB05M Cu	XB05X Cu	XB05X StS
Max. working pressure	bar	25		10
Min. / Max. temperature	°C	-10/180	-10/150	
Flow medium		DH: Circulation water / glycolic water up to 50% DC: ethylene-, propylene-glycolic water, ethanol-water solutions and other suitable heat transfer media. (Please contact your Danfoss representative).		
Volume/channel	Ltr	0.021	L <sup>1)</sup> : 0.037 H <sup>2)</sup> : 0.026	
Connection type		Cylindrical external thread acc. to DIN ISO 228/1		
Connection size		G ¾		
Weight	kg	0.58 + 0.045 × n	0.51 + 0.048 × n	0.51 + 0.046 × n
<b>Materials</b>				
Plate		Stainless steel, EN 1.4404 (AISI 316L)		
Brazing		Copper (Cu); Stainless steel (StS)		

<sup>1)</sup> Low pressure drop side - can be either primary or secondary side, depends on selection in Hexact.  
<sup>2)</sup> High pressure drop side - can be either primary or secondary side, depends on selection in Hexact.  
 n = number of plates

Dimensions

Type	Connection	E (mm)	Weight empty (kg)
XB05M -...	G ¾ <sup>1)</sup>	8 + 1.19 × n	0.58 + 0.045 × n
XB05X -...	G ¾ <sup>1)</sup>	7.1 + 1.6 × n	0.51 + 0.048 × n

<sup>1)</sup> Cylindrical external thread acc. to DIN ISO 228/1  
 n = number of plates

**Tailpieces**

Picture	Description	Connection	mm			Code No.
			a	b	SW <sup>2)</sup>	
	Solder tailpieces	G ¾ / 15 mm	15	35	32	<b>004B2945</b>
		G ¾ / 18 mm	18	35	32	<b>004B2946</b>
	Weld-on tailpieces	G ¾ / DN 20	21.2	35	32	<b>004B2944</b>
	Threaded tailpieces	G ¾ / G ¾	¾"	40	32	<b>004B2947</b>
		G ¾ / G 1	1"	22	32	<b>004B2953</b>

<sup>2)</sup> Union nut, with across flats

**Danfoss A/S**

Heating Segment • heating.danfoss.com • +45 7488 2222 • E-Mail: heating@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and all Danfoss logotypes are trademarks of Danfoss A/S. All rights reserved.