

Data Sheet

Danfoss *Icon*™ Display

- Room Thermostat, 230 V

Description

Danfoss *Icon*™ Display 088U1010Danfoss *Icon*™ Display 088U1015

Danfoss *Icon*™ is a range of flush and surface mounted room thermostats for hydronic floor heating applications.

Danfoss *Icon*™ Display is mains powered and can be used as a stand-alone thermostat or in combination with wiring center 088H001601.

The thermostat uses a triac output and can control up to 5 thermal actuators.

The user can set the desired room temperature via the touch user interface and read the measured room temperature.

The thermostat uses a "touch on glass" interface with a shine through display. The display is "OFF" in normal operation.

Features

- Accurate PWM-control
- Inwall version compatible with 3'rd party wall frames
- Shine through display
- Range limitation via user menu
- Neutral design and simple user interface
- Frost protection setting
- Can be used with 230 V NC or NO actuators
- The thermostat can be optimized for different heat sources via service menu
- Valve exercise feature
- Very high UV-resistance

Ordering

Product	Version	Size	For junction box	Code no.
Danfoss <i>Icon</i> ™ Display	In-wall	80 x 80 mm	Euro, Ø68 mm	088U1010
Danfoss <i>Icon</i> ™ Display	In-wall	86 x 86 mm	Square, 70x70 mm	088U1011
Danfoss <i>Icon</i> ™ Display	In-wall	88 x 88 mm	Swiss type	088U1012
Danfoss <i>Icon</i> ™ Display	On-wall	86 x 86 mm	N.A.	088U1015

Accessories



Product	Description	Code no.
Danfoss FH-WC, 230V	Wiring center, 8 channels, up to 16 outputs	088H001601

Technical specifications


Type	Electronic thermostat with touch user interface
User interface	Capacitive touch and shine through display
User interface features	Heating icon, arrow up/down, confirm key, back key
Display type	Hybrid: red single LED's and custom segment
Display features	Switches OFF after 10 sec. with no interaction
Temperature setting range	5 - 35° C (frost protection setting = 5° C)
Ambient temperature, storage	-20 to 60° C
Ambient temperature, used in application	0 to + 40° C
Controller, type	Adjustable Pulse Width Modulation
Max. continuous load (output)	< 50 mA /10 W (= 5 pcs. Danfoss TWA actuators)
Max. inrush current (actuator)	3 A ≤ 100 ms
Power consumption	0.2 W
Power supply (excl. actuators)	220-240 V, 50/60 Hz
Sensor, room	47 kΩ NTC
Shell material	White parts: PC ASA Grey parts: PC, 10% glass
IP and Protection class	IP: 21 Protection class: II
ErP class	 (2%)
Approval	CE, RohS, WEEE
Colour	White RAL9010 / Dark Grey RAL7024
Dimensions, in-wall versions	80 x 80 x 11 mm (088U1010) 86 x 86 x 11 mm (088U1011) 88 x 88 x 13 mm (088U1012)
Dimensions, on-wall version	86 x 86 x 25 mm (088U1015)

Application examples

Wiring without wiring center, neutral wire from main installation




Wiring with wiring center




¹⁾ **Note!** Wiring center FH-WC 088H001601 only supports NC actuators.


Dimensions




Danfoss Icon™ Display 088U1010



Danfoss Icon™ Display 088U1011



Danfoss Icon™ Display 088U1012
(incl. Feller EDIZIOnue frame and adapter)



Danfoss Icon™ Display 088U1015

Danfoss Ltd.

Ampthill Road
Bedford MK42 9ER
Tel: 01234 364621
Fax: 01234 219705
Email: ukheating@danfoss.com
Website: www.heating.danfoss.co.uk