

## Data sheet

# Direct-operated 3/2-way compact solenoid valves

## Type EV310A



EV310A covers a wide range of small competitive, direct-operated 3/2-way solenoid valves for use within industrial applications, for example as pilot valve.

**Features**

- For water, oil, compressed air and similar neutral media
- Differential pressure: Up to 20 bar
- Ambient temperature: Up to 50 °C
- Media temperature from -10 – 100 °C
- Coil enclosure: Up to IP65
- Viscosity: Up to 20 cSt
- $K_v$  values up to 0.08 m<sup>3</sup>/h
- Thread connection:
  - NC G 1/8 – G 1/4
  - NO G 1/8
  - NC MAN G 1/8 – G 1/4
- Flange connection:
  - NC FL 32 x 32 mm

**Brass valve body, NC**



Connection ISO 228/1	Seal material	Orifice size	K <sub>v</sub> - value [m³/h]	Differential pressure, min. to max. [bar]			Media temperature min. to max. [°C]	Code number
				AC / AM				
				Water	Oil	Air		
G 1/8	FKM	1.2	0.04	0 – 18	0 – 9	0 – 20	-10 – 100	<b>032H8085</b>
	FKM	1.5	0.07	0 – 10	0 – 5	0 – 12	-10 – 100	<b>032H8087</b>
G 1/4	FKM	1.2	0.04	0 – 18	0 – 9	0 – 20	-10 – 100	<b>032H8095</b>
	FKM	1.5	0.07	0 – 10	0 – 5	0 – 12	-10 – 100	<b>032H8097</b>
	FKM	2	0.08	0 – 6.5	0 – 4	0 – 8	-10 – 100	<b>032H8099</b>

**Brass valve body, NO**



Connection ISO 228/1	Seal material	Orifice size	K <sub>v</sub> - value [m³/h]	Differential pressure, min. to max. [bar]							Media temperature min. to max. [°C]	Code number
				Coil type								
				AB AC	AB DC	AC AC	AC DC	AM AC	AM DC	AK DC		
G 1/8	FKM	1.2	0.04	0 – 6	0 – 4	0 – 9	0 – 7	0 – 13	0 – 9	0 – 4	-10 – 100	032H8125
	FKM	1.5	0.07	0 – 3	0 – 2	0 – 5	0 – 3.5	0 – 7	0 – 5	0 – 2	-10 – 100	032H8127

**Technical data**

Main type	EV310A NC/NO
Time to open [ms] <sup>1)</sup>	7 – 10
Time to close [ms] <sup>1)</sup>	7 – 10

<sup>1)</sup> The times are indicative.

Type	EV310A NC/NO		
Installation	Vertical solenoid system is recommended		
Max. test pressure	50 bar		
Ambient temperature	Up to 50 °C		
Medium temperature	-10 – 100 °C		
Viscosity	Max. 20 cSt		
Materials	Valve body:	Brass	W.no. 2.0401
	Valve orifice:	Stainless steel	W.no. 1.4305 / AISI 303
	Armature:	Stainless steel	W.no. 1.4016 / AISI 430
	Armature tube:	Stainless steel	W.no. 1.4303 / AISI 305
	Armature stop:	Stainless steel	W.no. 1.4016 / AISI 430
	Spring:	Stainless steel	W.no. 1.4310 / AISI 301
	O-rings/valve plate:	FKM	–

### Brass valve body, NC MAN



Connection ISO 228/1	Seal material	Orifice size	K <sub>v</sub> - value [m³/h]	Differential pressure, min. to max. [bar]			Media temperature min. to max. [°C]	Code number
				AC / AM				
				Water	Oil	Air		
G 1⁄8	FKM	1.5	0.07	0 – 10	0 – 5	0 – 12	-10 – 100	<b>032H8143</b>
G 1⁄4	FKM	1.5	0.07	0 – 10	0 – 5	0 – 12	-10 – 100	<b>032H8153</b>

### Technical data

Main type	EV310A NC Man
Time to open [ms] <sup>1)</sup>	7 – 10
Time to close [ms] <sup>1)</sup>	7 – 10

<sup>1)</sup> The times are indicative.

Type	EV310A NC Man		
Installation	Vertical solenoid system is recommended.		
Max. test pressure	50 bar		
Ambient temperature	Up to 50 °C		
Medium temperature	-10 – 100 °C		
Viscosity	Max. 20 cSt		
Materials	Valve body:	Brass	W.no. 2.0401
	Valve orifice:	Stainless steel	W.no. 1.4305 / AISI 303
	Armature:	Stainless steel	W.no. 1.4016 / AISI 430
	Armature tube:	Stainless steel	W.no. 1.4303 / AISI 305
	Armature stop:	Stainless steel	W.no. 1.4016 / AISI 430
	Spring:	Stainless steel	W.no. 1.4305 / AISI 303
	Other parts:	Stainless steel	W.no. 1.4016 / AISI 430F
	O-rings/valve plate:	FKM	–
	Manual override	Polymer	Polysulfon black

# Brass valve body, NC FL



Connection ISO 228/1	Seal material	Orifice size	K <sub>v</sub> - value [m³/h]	Differential pressure, min. to max. [bar]			Media temperature min. to max. [°C]	Code number
				AC / AM				
				Water	Oil	Air		
32 x 32	FKM	1.5	0.08	0 – 10	0 – 5	0 – 12	-10 – 100	<b>032H8183</b>

## Technical data

Main type	EV310A NC FL
Time to open [ms] <sup>1)</sup>	7 – 10
Time to close [ms] <sup>1)</sup>	7 – 10


<sup>1)</sup> The times are indicative.

Type	EV310A NC FL		
Installation	Vertical solenoid system is recommended.		
Max. test pressure	50 bar		
Ambient temperature	Up to 50 °C		
Medium temperature	-10 – 100 °C		
Viscosity	Max. 20 cSt		
Materials	Valve body:	Brass	W.no. 2.0401
	Valve orifice:	Stainless steel	W.no. 1.4305 / AISI 303
	Armature:	Stainless steel	W.no. 1.4016 / AISI 430
	Armature tube:	Stainless steel	W.no. 1.4303 / AISI 305
	Armature stop:	Stainless steel	W.no. 1.4016 / AISI 430
	Springs:	Stainless steel	W.no. 1.4310 / AISI 301
	O-rings/valve plate:	FKM	–

### Dimensions and weight, NC, NO and NC MAN

Thread ISO 228/1	L [mm]	B [mm] Coil type		H [mm]	A [mm]	Weight without coil [kg]
		AB / AC	AM / AK			
G 1/8	26	22	33	54	13	0.085
G 1/4	35	22	33	59	17.5	0.110


### Dimensions




### Dimensions and weight, NC FL

Flange [mm]	B [mm] Coil type		H [mm]	Weight without coil [kg]
	AC	AM		
32 x 32	22	33	50.5	0.085





### Dimensions



### Mounting angle




### Below coils can be used with EV310A

Coil	Type	Power consumption	Enclosure	Features
	AM	7.5 W AC 9.5 W DC	IP00 with spade connector, IP65 with cable plug	Cable plug
	AC	7 W AC 10 W DC	IP00 with spade connector, IP65 with cable plug	Industrial plug
	AB	4.5 W AC 5 W DC	IP00 with spade connector, IP65 with cable plug	Industrial plug
	AK	3 W DC	IP00 with spade connector, IP65 with cable plug	Cable plug

### Accessories:


#### Cable plug

Application	Code number
GDM 2011 (grey) cable plug according to DIN 43650-A PG11	<b>042N0156</b>




#### Industrial plug

Application	Code number
GM 209 (Black) cable plug according to DIN 43650-B PG9	<b>042N0139</b>



# Function, NC / NC MAN

- 1. Opening spring
- 2. Armature
- 3. Valve plate
- 4. Coil
- P: Pressure gate
- A: Working gate
- R: Relief gate



## Coil voltage disconnected (closed):


When the voltage to the coil (4) is disconnected, the armature (2) with the valve plates (3) is pressed down by the closing spring (1) and closes the connection between P and A. At the same time, the connection between gates A and R is opened. The connection between P and A will be closed for as long as the voltage to the coil is disconnected.

## Coil voltage connected (open):

When voltage is applied, the armature (2) with the valve plates (3) is lifted and closes the connection between A and R. At the same time, the connection between P and A is opened. The connection between P and A will be open for as long as there is voltage to the coil.

# Function, NO

- 1. Opening spring
- 2. Armature
- 3. Valve plate
- 4. Coil
- P: Pressure gate
- A: Working gate
- R: Relief gate



## Coil voltage disconnected (open):


When the voltage is disconnected, the armature (2) with the valve plates (3) is pressed down by the opening spring (1) and closes the connection between A and R. At the same time, the connection between P and A is open. The connection between P and A will be open for as long as the voltage to the coil is disconnected.

## Coil voltage connected (closed):

When voltage is applied to the coil (4), the armature (2) with the valve plates (3) is lifted and closes the connection between P and A. At the same time, the connection between gates A and R is opened. The connection between P and A will be closed for as long as there is voltage to the coil.

## Function, NC FL

- 1.Closing spring
- 2.Armature
- 3.Valve plate
- 4.Coil
- P:Pressure gate
- A:Working gate
- R:Relief gate



### Coil voltage disconnected (open):

When the voltage to the coil (4) is disconnected, the armature (2) with the valve plates (3) is pressed down by the closing spring (1) and closes the connection between P and A. At the same time, the connection between gates A and R is opened. The connection between P and A will be closed for as long as the voltage to the coil is disconnected.

### Coil voltage connected (closed):

When voltage is applied, the armature (2) with the valve plates (3) is lifted and closes the connection between A and R. At the same time, the connection between P and A is opened. The connection between P and A will be open for as long as there is voltage to the coil.