

Data sheet

Micro Plate Heat Exchanger (MPHE): XB25

Description



Micro Plate Heat Exchangers - a revolutionary technology from Danfoss.

Characterized by their unique plate pattern, MPHEs enable heat to be transferred more efficient than any previous model of heat exchangers.

Benefits:

- Energy and cost savings
- Better heat transfer
- Lower pressure loss
- More flexible design
- Longer life time

more on:

MPHE.danfoss.com


XB25 is copper brazed heat exchanger, designed and configured for District Heating, District Cooling and other Heating applications.

Approval:




Pressure Equipment Directive (PED).

Ordering

1-pass heat exchanger XB25

Picture	No. of plates, n	Connection	Code No.
	8	Thread G 3/4	004H4324
	10		004H4325
	16		004H4326
	20		004H4327
	26		004H4328
	30		004H4329
	36		004H4330
	40		004H4331
	50		004H4332
	60		004H4333
	66		004H4334

Accessories-Tailpieces

Picture	Description	Connection	Code No. ¹⁾
	Solder tailpieces	G 3/4/15 mm	004B2945
		G 3/4/18 mm	004B2946
	Weld-on tailpieces	G 3/4/DN 20	004B2944
	Threaded tailpieces	G 3/4/G 3/4	004B2947
		G 3/4/G 1	004B2953

¹⁾ One set contains 2 tailpieces with union nuts and gaskets

Data sheet

Micro Plate Heat Exchanger (MPHE) XB25

Technical data

Type		Heat exchanger XB25H
Max. working pressure	bar	25
Max. operating temp.	°C	DH 180, DC 100
Min. operating temp.		-10
Flow medium		"DH: Circulation water / glycolic water up to 50% transfer media. DC: ethylene-, propylene-glycolic water, ethanol-water solutions and other suitable heat transfer media. (Please contact your Danfoss representative)."
Volume / Channel	Ltr	0.059
Connection type		Cylindrical external thread acc. to DIN ISO 228/1
Connection size		G¾"
Weight	kg	0.09 x NoP + 0.99
Materials		
Plate		Stainless steel, EN 1.4404 (AISI 316L)
Brazing		Copper (Cu); Copper-Nickel (CuNi)*

* Available on enquiry




Dimension

Type	Connection	E (mm)
XB25	G $\frac{3}{4}$ ¹⁾	H: 6.5 + 1.55 × n

n = number of plates

¹⁾ Cylindrical external thread acc. to DIN ISO 228/1

Tailpieces

Picture	Description	Connection	a	b	SW ¹⁾	Code No.
			mm			
	Solder tailpieces	G $\frac{3}{4}$ / 15 mm	15	35	32	004B2945
		G $\frac{3}{4}$ / 18 mm	18	35	32	004B2946
	Weld-on tailpieces	G $\frac{3}{4}$ / DN 20	21.2	35	32	004B2944
	Threaded tailpieces	G $\frac{3}{4}$ / G $\frac{3}{4}$	$\frac{3}{4}$ "	40	32	004B2947
		G $\frac{3}{4}$ / G 1	1"	22	32	004B2953

¹⁾ Union nut, width across flats

Danfoss A/S

Heating Segment • heating.danfoss.com • +45 7488 2222 • E-Mail: heating@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed.

All trademarks in this material are property of the respective companies. Danfoss and all Danfoss logotypes are trademarks of Danfoss A/S. All rights reserved.