

Data Sheet

Danfoss Link™ Hydronic Controller

Application



Danfoss Link™ HC is a part of the Danfoss Link™, a programmable, wireless control system for heating systems in residential buildings.

The Danfoss Link™ HC allows control of hydronic floor heating systems. The system offers a wide range of extended functionalities for optimal comfort and energy saving, with individual room temperature control.

The Danfoss Link™ HC includes features like: 2-way wireless transmission, up to 5 or 10 short-circuit protected outputs for 24 V NC or NO actuators, relays for both pump and boiler control, selfdiagnosing program, contact for Away Function, heating/cooling function, regulation by ON/OFF or Pulse Width Modulation principles (PWM) etc.

The system can consist of up to three Danfoss Link™ HC, offering a possibility of up to 30 outputs for even larger systems. The Danfoss Link™ HC has easy connection directly to 230 V power supply without the need for further transforming, supplying all actuator outputs with 24 V.

Systems of up to three Danfoss Link™ HC can be accessed wirelessly by the Danfoss Link™ CC. The Danfoss Link™ CC offers a wide range of functionalities and features, like individual settings for each Danfoss Link™ HC output, override and locking of local room temperature settings, setback and period programming, system status etc.

Features:

- 2-way wireless transmission at 868.2 MHz, for higher transmission certainty and direct link test option on each system component like room sensors, etc.
- 5 or 10 short-circuit protected outputs with LED indication.
- Outputs for 24 V NC or NO actuators.
- Valve motion for all outputs approx. 12 minutes every second week with no heat demand.
- Regulation by PWM (Pulse Width Modulation) principle.
- Input (ON/OFF) for heating/cooling.
- Input (ON/OFF) for Away Function. When the switch is closed (ON), the system overrides all room thermostat set points and change it to 15° C.
- Relay for pump control with automatic pump motion every third day for 1 min. to avoid damage during standby periods.
- Relay for boiler control, activated only at heat demand.
- Easy cable fixing at each actuator output for several cable types (squared or circular).
- Automatic self-diagnosis providing indication of several error possibilities like missing wireless connection or missing/non-functional actuator on output, etc.


Ordering

Product	Type	Supply voltage	Output voltage	Code no.
Danfoss Link™ HC, 5 outputs	HC-5	230 V AC	24 V DC	014G0103
Danfoss Link™ HC, 10 outputs	HC-10			014G0100


Accessories

Product	Type	Code no.
External antenna, with 2 m cable	CF-EA	088U0250

Technical specifications

Transmission frequency	868.42 MHz
Transmission range in normal constructions	(up to) 30 m
Transmission power	< 1 mW
Supply voltage	230 V AC
Actuator outputs	5 or 10 / 24 V DC
Max. continued output load (total)	35 VA
Relays	230 V AC/ 8 (2) A
Ambient temperature	0 - 50° C
IP class	30
ErP class	 (2%)
Mains cable	1.5 m
Weight	700 g
Dimensions (l x h x d) in mm	325 x 78 x 47

Wiring



1. Input 2, Away Function.
2. Input 3, Heating/Cooling.
3. Relays.
4. Actuator outputs.
5. External antenna.

Danfoss A/S

Floor Heating Hydronics • Ulvehavevej 61 • DK-7100 Vejle • Denmark • Phone: +45 7488 8500 • Fax: +45 7488 8501
 heating@danfoss.com • www.floorheating.danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed.
 All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.