

ASV automatic balancing valves

Drive **energy efficiency** and increase **customer satisfaction**

Currently, 80-90% of buildings are equipped with inefficient two-pipe heating systems. They waste precious energy and cause residents to complain about uneven heat distribution, system noise, high energy bills and unfair heat cost allocation.

Danfoss automatic balancing valves (ASV) provide a simple, reliable and cost-effective way to create hydronic balancing in two-pipe heating systems. Only automatic balancing valves solve the technical issue of pressure fluctuations, which are the root cause of system imbalance and all related problems.



Up to

20%

energy savings
through correct
system balancing.

4 good reasons to choose a Danfoss ASV automatic balancing solution

We recommend using ASV automatic balancing valves for balancing your 2-pipe heating system. The ASV automatically creates optimal hydronic balance within the installation, whether under full or partial load.

Benefits:

1. Fewer complaints
2. Lower maintenance costs
3. Increased indoor comfort
4. Lower energy bills

ASV valves are comprised of an ASV-PV differential pressure controller and an ASV-BD partner valve, connected with an impulse tube. Used together with Danfoss presetting radiator thermostatic valves, they form part of the integrated Danfoss two-pipe solution.

Choose the ASV-PV to experience its many unique features:

- Visible setting without any tools
- Low build-in height
- Easy and practical flushing function

Next time you are involved in a new-build or retrofit project for a multi-family building, school, office or other public building, we will be pleased to help you design the ideal balanced heating system to meet your customer's goals. Just get in touch!

ASV technical data

Nominal diameter

DN 15 - 50

Connections

Internal thread Rp 1/2" - Rp 2"
External thread G 3/4" A - G 2" A

Setting range

5 - 25 kPa
20 - 60 kPa

Differential pressure over the valve

10 - 250 kPa

Max. pressure

PN 16

Valve body + cone

Brass + DZR brass

Membrane + o-rings

EPDM



Danfoss A/S · Heating Segment · Ulvehavevej 61 · 7100 Vejle · Denmark
Tel.: +45 7488 8500 · Email: heating@danfoss.com · www.heating.danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.