

## Adaptive Energy Optimization (AEO) with High Speed Electronit Unit

### Introduction

Herewith a description of a function in the high speed electronic unit. The unit contains a feature called **Adaptive Energy Optimization (AEO)**. It is very suitable for systems with huge load variations and applications where energy is an important issue.

### Function

#### *Initial start up conditions*

Every start up of the compressor takes place at low speed (soft start). The start up speed is equal to: the speed at thermostat cut out minus 300 rpm. After start up the speed of the compressor will be ramped up and adapted to the load. The ramp up speed is 9.4 rpm/min.

#### *Adaptation of the capacity.*

The software algorithm adapts the capacity of the compressor to the actual load of the system.

The unit regulates the capacity so that the compressor runtime is approximately 24 minutes. If the compressor does not reach cut out temperature within 48 minutes the speed is set to 4400 rpm.

#### *Example how to determine the speed*

Start up speed: 3250 rpm  
 Runtime: 15 minutes  
 Speed at cut out:  $3250+(9.4 \times 15)$   
 ~3390 rpm

Start up speed:  $3390-300 = 3090$  rpm  
 Runtime: 20 minutes  
 Speed at cut out:  $3090+(9.4 \times 20)$   
 ~3280 rpm

Start up speed:  $3280-300 = 2980$  rpm  
 Runtime: 30 minutes  
 Speed at cut out:  $2980+(9.4 \times 30)$   
 ~3260 rpm

### Curves

The graphs on page 2 show the relation between cabinet temperature and speed. After a power cut out the start speed will always be set to 3250 rpm.

After a thermostat cut out the start up speed is calculated as speed at stop minus 300.


The speed will be adapted automatically so that the thermostat runtime will be approximately 24 minutes.

### Benefits

- Independent of load variations
- Energy savings
- Reduced number of compressor starts
- Prevents short cycling of the compressor
- Battery protection
- Soft start in tropical conditions

### Code nos.

Single pack 101N0280  
 Industrial pack 101N0281 (28 pcs)



Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.

**Danfoss Compressors GmbH**  
 Mads-Clausen-Str. 7  
 D-24939 Flensburg / Germany  
 compressors.danfoss.com