



1. CONTRACTOR WILL USE DANFOSS AB-QM PRESSURE INDEPENDENT CONTROL VALVE
2. UNLESS INDICATED OTHERWISE, ALL RHC CONNECTION HHWS/R PIPE SIZES SHALL BE 3/4" MINIMUM, RHC WITH SCHEDULES HHW FLOW RATES GREATER THAN 3 GPM SHALL USE 1-INCH DIAMETER PIPING MINIMUM. PROVIDE PIPE REDUCERS TO CONNECT TO EXISTING LARGER SIZE PIPES.

3. CONTRACTOR OPTION TO PROVIDE PACKAGE ASSEMBLY OR FIELD FABRICATE FROM INDIVIDUAL COMPONENTS OR COMBINATION OF PACKAGED AND COMPONENTS SO LONG AS THE FIT, FORM AND FUNCTION OF THIS ASSEMBLY IS PROVIDED AND THE MINIMUM MATERIAL QUALITIES ARE MAINTAINED SUBMITTED AND APPROVED BY UCI.

Danfoss

REHEAT COIL PIPING DETAIL
NOT TO SCALE