

EVR series of solenoid valves


Enhanced **reliability** and **savings** in HVACR applications

The Danfoss range of EVR solenoid valves has undergone a wide series of improvements throughout 2017. Reinforcements and rationalization make them capable of accommodating the higher pressures of refrigerants and a broader range of applications while reducing the references, inventory, and servicing time.

New streamlined
platform approved
with more than

20

refrigerants
reduces inventory



Improved performance and reliability in standard and niche applications

The new EVR range covers four product envelopes, including valves to replace previous Danfoss models.

Typical applications include refrigeration systems in the air conditioning and food service industry, such as walk-in cold rooms, display freezers, and refrigerators. EVR valves are also suitable for icemakers

and ice cream machines where they undergo additional stress due to the rapid defrosting cycles and/or short hot gas injection cycles, depending on the application. EVR works smoothly and reliably even in such challenging systems.

The more robust EVR valves improve the reliability and service life of the products in which they are used.

The streamlining of the range makes life easier for you since you can catalog and stock fewer articles that meet a broader range of needs.

As a manufacturer, the reduction in the number of models means the valves you need are more likely to be available. It will help you manage inventory and avoid logistics issues.



Upgrades and new features compatible with modern refrigerants

EVR valves are optimized for the business success of our customers, manufacturers, and end users. All innovations were tested to ensure they improved the product and optimized it to meet the needs of today's customers.

More robust design and system reliability

Several design features enable operation with a higher maximum working pressure (MWP). The new EVR range is compatible with higher pressure refrigerants such as R410A, and suitable for applications such as heat pumps and chillers running in extreme ambient temperatures during periods of maximum load.

- Increased diameter of cover screws enhance the reinforced covers for greater reliability under higher pressures.
- Robust housing design and stronger covers make EVR valves more reliable, extending their MWP up to 45 bar.
- Thicker copper connections reduce the risk of valve failure raising MWP.
- Improved gasket design increases the valve's robustness and reliability.

Enhanced functionality

Other design features within the new EVR range enhance its functionality making it suitable for applications, which operate at part load for long periods, such as chillers. It can also now be used in applications such as icemakers and ice cream machines where a suction line solenoid valve is required for defrosting.

- Single-layer diaphragm instead of the usual two optimizes the opening of the valve and increases versatility and reliability. In high-capacity applications and tough operating conditions (e.g. hot gas defrost), the Danfoss single-layer solid 'monophragm' eliminates the risk of delamination.
- New pilot orifice design allows a higher maximum opening pressure differential (MOPD) with standard coils. This means you can use the new EVR with high-pressure refrigerants under demanding operating conditions.
- The new pilot orifice design also optimizes the opening of the valve. It reduces pressure drop within the valve and makes it compatible with suction line applications.


Easier service

EVR valves are ideal for applications such as food retail display cases since they enable service and maintenance to be carried out quickly, with no disruption to store trading hours. There is no need to de-solder the complete valve and put a new one into the system. Just leave the valve body in place, replace the internal parts as required and you can get the system up and running again quickly. Service kits are also available.

- New EVR features the same easy and fast serviceability as the current solenoid valves from Danfoss.

Switch to lower wattage coils

In addition to all the features mentioned above, the overall improvements in our EVR valves open up the possibility of changing to standard coils in applications where the operating conditions allow it. This would further streamline logistics and reduce your costs.



Fewer models. Broader scope.

Our revitalized EVR range saves on applied, development, and storage costs. Fewer more versatile products are applicable to more applications and refrigerants while being backward compatible.

30%

Range streamlining
for optimized
logistics

Air Conditioning:

Superior performance in high temperature applications (105 °C) and optimized for variable refrigerant flow conditions due to superior max. OPD and min. OPD. Available connection sizes from 6 mm to 42 mm - 1/4" to 2 1/8". Reliable and versatile design.

Refrigeration:

Reliable and versatile valve platform covers a wide range of functions, applications, and refrigerants. Improves life of refrigeration systems contributing to food safety while reducing energy consumption. Best in class product features.

Food Retail:

One platform approved for lower-GWP (Global Warming Potential) refrigerants, including R290 propane. Tight solenoid closure safeguards the system and with enhanced flow characteristics for high efficiency.

EVR V2 type	Kv value [m ³ /h]	Opening differential pressure with standard coil Δp [bar]		
		Min.	Max. (= MOPD) liquid	
			AC coil [10 W]	DC coil [20 W]
EVR 2 NC	0.15	0.00	38	33
EVR 3 NC	0.26	0.00	38	18
EVR 4 NC	0.7	0.03	38	28
EVR 6 NC	1.0	0.03	38	28
EVR 6 NO	1.0	0.03	21	21
EVR 8 NC	1.15	0.03	38	28
EVR 10 NC	1.47/2.2	0.03	38	20
EVR 10 NO	2.2	0.03	21	21
EVR 15 NC	3.3	0.03	38	20
EVR 15 NO	3.3	0.03	21	21
EVR 18 NC	3.9	0.03	38	20
EVR 20 NC	6.0	0.03	38	20
EVR 20 NO	6.0	0.03	19	19
EVR 22 NC	6.0	0.03	38	20
EVR 22 NO	6.0	0.03	19	19
EVR 25 NC	9.8	0.20	38	17
EVR 32 NC	16.7	0.20	38	17
EVR 40 NC	24.2	0.20	38	17

For Manual operation EVR please refer to Datasheet.

More than 20 refrigerants can be used:

R22/R407C, R134a, R404A/R507, R410A, R407A, R32, R290, R600, R600a, R1234yf, R1234ze, R404A, R407F, R125, R152A, R448A, R449A, R452A, and R450A.

For a complete list of approved refrigerants, visit www.products.danfoss.com and search for individual code numbers, where refrigerants are listed as part of technical data or check in **Coolselector®**.



Danfoss A/S Nordborgvej 81, 6430 Nordborg, Denmark.
Telephone: +45 74 88 22 22. Fax: +45 7449 0949.

For more information with other refrigerants, scan here and access our Danfoss Coolselector® software.
coolselector.danfoss.com



Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed materials. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without consequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.