

Data Sheet

EM-PMI540-T4000

Electric machine, permanent magnet internal

FEATURES

- Synchronous Reluctance assisted Permanent Magnet (SRPM) technology
- Extremely compact and robust structure
- Highest efficiency throughout the operation range on the market (~96 %)
- Liquid cooled with plain water or water/glycol mixture
- Low coolant flow required
- Allowed coolant temperature up to +40°C
- IP65 enclosure class to maximize reliability
- Multiple mounting possibilities

GENERATOR SPECIFIC FEATURES

- Standard SAE flange mounting to match the diesel engine connection
- Wide selection of speed ratings allowing the generator to be selected to customer specific applications with various voltage requirements
- Can be also used as starter motor for the ICE

MOTOR SPECIFIC FEATURES

- Extended speed and torque capabilities compared to standard PM motors from Danfoss reluctance assisted permanent magnet motor technology
- Motor structure is designed to be able to produce high starting torque: EM-PMI motor can produce instantly full torque to a non-rotating shaft
- Optimized speed range to meet the most common gear ratios used in heavy mobile machinery



GENERAL

The machine is developed especially for demanding applications. The design of these machines makes them smaller, lighter and more efficient than conventional products on the market.

TYPICAL APPLICATIONS

- Generator for diesel-electric/serial hybrid applications
- Traction/propulsion motor
- Generator/Motor for parallel hybrid applications

SPECIFICATIONS

General electrical properties

Nominal voltage (line to line)	500 V _{AC}
Voltage stress	IEC 60034-25, Curve A: Without filters for motors up to 500 V _{AC}
Nominal efficiency	96 %
Pole pair number	8
Power supply	Inverter fed.
Nominal inverter switching frequency	8 kHz

Basic information

Machine type	Synchronous reluctance assisted permanent magnet
Mounting direction	Only horizontal assembly, see user guide for details
Mounting (IEC 60034-7)	IM1001-B3 (Horizontal foot mounting) IM2001-B35 (Horizontal foot + flange mounting)
Standard Flange D-end (SAE J617)	SAE ½, transmission housing
D-end shaft	Male cylindrical shaft, diameter 70 mm h7
N-end attachment	SAE ½ flywheel housing partly available for supporting structures (see main dimension drawings)
Bearing type	Standard: 6216/C3 (with LGHP2 grease) +BIN option: D-end: 6216/C3 (with LGHP2 grease) N-end: 6216/C3VL0241 (with LGHP2 grease) +BIA option: 6216/C3VL0241 (with LGHP2 grease)
Standard rotation direction	Clockwise (both directions possible)
Protection class	IP65 Following best design principles
Duty type (IEC 60034-1)	S9
Standard color	Dark grey RAL7024 wet painting
Mechanical	
Total weight	950 kg (no options)
Moment of inertia	10.3 kgm ²
Rotating mass	380 kg
Maximum static torque on the shaft	6800 Nm

Maximum dynamic torque on the shaft	4600 Nm
Maximum deceleration (shaft braking)	1000 rad/s ²
Dimensions	
Length (frame)	1040 mm
Height (frame)	665 mm
Cooling	
Cooling liquid	Plain water with appropriate corrosive inhibitor (max. 50 % corrosive inhibitor)
Cooling liquid corrosive inhibitor type	Ethylene glycol Glysantin G48 recommended
Cooling method (IEC 60034-6)	IC 71 W
Minimum cooling liquid flow	40 l/min
Coolant circuit capacity	4.4 l
Maximum operating pressure	2 bar
Pressure loss	0.9 bar with 40l/min (+25°C coolant)
Cooling liquid temperature max	+65°C / +40°C with +CL option (derating required if exceeded)
Temperature rating	
Insulation class (IEC 60034-1)	H (180°C)
Temperature rise (IEC 60034-1)	85°C / 110°C with +CL option
Maximum winding temperature	150°C
Nominal ambient temperature	65°C
Min. ambient temperature	-40°C
Nominal altitude (IEC 60034-1)	1000 m
Connections	
Coolant connection	2 x G3/4 bore
HV cables	2 x 3 x 95 mm ² max. 4 x 3 x 95 mm ² max.
HV cable glands	Pflitsch blueglobe TRI bg 232ms tri
HV cable	Recommended H+S Radox screened cable
HV cable lug size	70-8, 95-8
HV connection boxes	2 x 3 phase box 4 x 3 phase box

LV connector	47-pin DEUTSCH HD34-24-47PE for resolver and temperature measurement.	Heater connector (+HEAT2 option)	Hummel art. no. 7651 0 51 01 D
LV connector type	DEUTSCH HD34-24-47PE	Heater mating connector	Hummel art. no. 7550 6 51 02 D
LV connector pin type	Gold plated	Heater connector pin type	Hummel art. no. 7010 9 42 01 1
LV mating connector type	DEUTSCH HD36-24-47SE or DEUTSCH HD36-24-47SE-059	Heater connector pin configuration	See Table below
LV mating connector pin type	DEUTSCH 0462-201-1631 DEUTSCH 0462-005-2031 Plug: DEUTSCH 0413-204-2005 (size 20) Plug: DEUTSCH 0413-003-1605 (size 16)	Bearing temp. measurement connector type	4-pin M12 A coded male
LV connector pin configuration	See Table below	Bearing temp. measurement mating type	4-pin M12 A coded female
Anti-condensation heater (+HEAT2 option)	2 x 130 W 230 V _{AC} single phase heater resistors	Bearing temp. measurement connector pin configuration	See Table below

PIN	Description
47	Temperature 1, PT100 (P), windings
46	Temperature 1, PT100 (N), windings
33	Temperature 2, PT100 (P), windings
32	Temperature 2, PT100 (N), windings
45	Temperature 3, PT100 (P), windings
31	Temperature 3, PT100 (N), windings
30	Temperature 4, PT100 (P), windings
29	Temperature 4, PT100 (N), windings
44	Temperature 5, PT100 (P), windings
43	Temperature 5, PT100 (N), windings
28	Temperature 6, PT100 (P), windings
16	Temperature 6, PT100 (N), windings
42	Temperature 7, PT100 (P), windings (+TEMP4 option)
27	Temperature 7, PT100 (N), windings (+TEMP4 option)
15	Temperature 8, PT100, (P) windings (+TEMP4 option)
14	Temperature 8, PT100 (N), windings (+TEMP4 option)
40	Temperature 9, PT100 (P), windings (+TEMP4 option)
26	Temperature 9, PT100 (N), windings (+TEMP4 option)
41	Temperature 10, PT100 (P), windings (+TEMP4 option)
13	Temperature 10, PT100 (N), windings (+TEMP4 option)
39	Temperature 11, PT100 (P), windings (+TEMP4 option)
38	Temperature 11, PT100 (N), windings (+TEMP4 option)
25	Temperature 12, PT100 (P), windings (+TEMP4 option)
12	Temperature 12, PT100 (N), windings (+TEMP4 option)
35	Resolver, RES_COS_N, in-built non-contacting
20	Resolver, RES_COS_P, in-built non-contacting
36	Resolver, RES_SIN_N, in-built non-contacting
21	Resolver, RES_SIN_P, in-built non-contacting
22	Resolver, EXCN, in-built non-contacting
10	Resolver, EXCP, in-built non-contacting
34	Resolver, SHIELD/GROUND, in-built non-contacting

Table 1 Pin configuration of LV-connector


PIN	Description
1	Phase, 230 V _{AC}
2	Neutral
⏚	Ground/protective earth
4	Reserve
5	Reserve

Table 2 Pin configuration of heater

PIN	Description
1	PT-100
2	
3	PT-100_GND
4	

Table 3 Pin configuration of bearing temperature sensor connector (one sensor)

PRESSURE LOSS VS COOLANT FLOW



Picture 1 Pressure loss vs coolant flow

MOTORS

Type	Coolant temperature +65°C			Coolant temperature +40°C			Coolant temperature +40 / +65°C			
	Cont. Torque [Nm]	Cont. Power [kW]	Nom. Current [A]	Cont. Torque [Nm]	Cont. Power [kW]	Nom. Current [A]	Nom. speed [rpm]	Max. speed [rpm]	Peak torque DUAL (*)	Peak torque QUAD (**)
EM-PMI540-T4000-600	4522	284	387	5454	342	463	600	1200	5930	5930
EM-PMI540-T4000-1200	4229	531	716	4692	590	790	1200	2400	4158	5930
EM-PMI540-T4000-1600	4183	701	954	4639	777	1058	1600	3200	3062	5930
EM-PMI540-T4000-2400	3565	896	1232	4067	1022	1422	2400	4000	NA	4000

(* Peak torque achieved with two 350A inverters

(** Peak torque achieved with four 350A inverters

GENERATORS

Type	Coolant temperature +65°C				Coolant temperature +40°C				Coolant temperature +40 / +65°C		
	Apparent power [kVA]	Cont. power [kW]	Nom. Current [A]	Power factor	Apparent power [kVA]	Cont. Power [kW]	Nom. Current [A]	Power factor	Nom. speed [rpm]	Nom. Freq. [Hz]	Volt/ speed ratio [V/rpm] (***)
EM-PMI540-T4000-600	340	336	388	0,99	408	397	464	0,97	800	107	0,816
EM-PMI540-T4000-1200	609	589	705	0.97	674	648	779	0.96	1400	187	0.416
EM-PMI540-T4000-1600	809	759	942	0.94	825	808	965	0.98	1800	240	0.29
EM-PMI540-T4000-2400	984	911	1185	0.92	1074	1024	1308	0.95	2500	333	0.193

(*** Back EMF for cold (20°C) generator

PRODUCT CODE AND OPTIONS

Use product code including all needed options for ordering. Standard options are not given with the code as they are selected by default if a non-standard option is not selected. Standard options are indicated by a star (*).

Product code	Description
EM-PMI540-T4000-1600-DUAL	Standard 1600 rpm unit with standard options
EM-PMI540-T4000-1600-DUAL+BIA+RES1	Standard unit otherwise but with isolated bearings and resolver

Table 4 Product code examples

Variant	Code	Description	Additional information
High voltage connections	-DUAL	Two galvanically isolated 3 phase systems	Two connection boxes each containing one 3 phase system with one M32 cable gland per phase
	-QUAD	Four galvanically isolated 3 phase systems	Four connection boxes each containing one 3 phase system with one M32 cable gland per phase
Bearing insulation	*	Non-insulated bearings	Non-insulated bearings
	+BIN	Insulated bearing in N-end	Insulated bearing in N-end
	+BIA	Insulated bearing in both ends	Insulated bearing in both ends
Shaft grounding	*	None	
	+SG1	D-end shaft grounding	In-built grounding ring
Rotation sensor	*	None	No resolver
	+RES1	Resolver	In-built non contacting resolver, 8-pole pair
Winding temperature sensors	*	Temperature surveillance	6 x PT100 in windings
	+TEMP4	Redundant temperature surveillance	12 x PT100 in windings
Bearing temperature sensors	*	None	
	+BTMP1	PT100 in bearings	Plug-in connector
Anti-condensation heaters	*	None	
	+HEAT2	Two anti-condensation heaters	2 x 230 V _{AC} / 130 W
Marine classification	*	No marine classification	
	+CL1		ABS American Bureau of Shipping
	+CL2		BV Bureau Veritas
	+CL3		DNV GL DNV GL AS
	+CL4		LR Lloyd's Register
	+CL5		RINA

*Standard option

Table 5 Option list

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.